

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203750

Luminaire Tested: **LE_6B20D010 EC6B10208027 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208027 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1642.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203750

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203750

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94
3	104	98	93	90	102	97	92	89	94	91	88		92	89	86		89
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203750

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.9	16.6
10°-20°	524.4	31.9
20°-30°	476.7	29.0
30°-40°	288.9	17.6
40°-50°	65.8	4.0
50°-60°	8.4	0.5
60°-70°	3.8	0.2
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1274.0	77.6
0°-40°	1562.9	95.2
0°-60°	1637.1	99.7
0°-90°	1642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3224	
5°	3039	273
15°	1888	524
25°	1034	477
35°	458	289
45°	73	66
55°	8	8
65°	3	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203750

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3223.8
2.5°	3184.6
5°	3039.4
7.5°	2804.8
10°	2505.9
12.5°	2195.8
15°	1888.5
17.5°	1609.1
20°	1374.4
22.5°	1184.5
25°	1033.6
27.5°	899.5
30°	768.2
32.5°	614.6
35°	458.1
37.5°	321.2
40°	212.2
42.5°	131.2
45°	72.6
47.5°	33.5
50°	14.0
52.5°	11.1
55°	8.4
57.5°	8.4
60°	5.6
62.5°	5.6
65°	2.8
67.5°	2.8
70°	2.8
72.5°	2.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)