

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212654

Luminaire Tested: **LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6062.4 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48916	48916	48916
5°	134276	45074	18394
10°	294243	36886	7013
15°	449449	28077	8224
20°	520736	20889	12774
25°	568047	17174	20613
30°	634331	15581	21055
35°	645400	10686	14433
40°	656735	5070	7307
45°	657800	2107	3191
50°	556111	911	985
55°	179076	631	158
60°	35564	723	0
65°	3627	856	0
70°	403	1183	0
75°	0	1564	0
80°	0	2579	273
85°	0	5138	543

TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.2	2.5
10°-20°	797.7	13.2
20°-30°	1527.3	25.2
30°-40°	1799.4	29.7
40°-50°	1413.4	23.3
50°-60°	344.4	5.7
60°-70°	14.8	0.2
70°-80°	5.6	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2479.2	40.9
0°-40°	4278.7	70.6
0°-60°	6036.5	99.6
0°-90°	6062.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6062.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1136	1136	1136	1136	1136	
5°	3107	2248	1043	546	426	411
15°	10083	5179	630	180	184	2815
25°	11957	6297	362	378	434	5573
35°	12279	3981	203	262	275	7699
45°	10803	1230	35	48	52	8117
55°	2386	45	8	5	2	2839
65°	36	5	8	5	0	94
75°	0	5	9	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	1947.4	1943.3	1914.9	1941.2	1861.5	1858.3	1822.7	1806.9	1760.9	1716.8	1654.0
5°	3106.8	3038.5	2983.1	2985.0	2832.1	2803.8	2724.1	2643.4	2519.7	2404.4	2248.2
7.5°	4735.5	4654.8	4537.4	4488.1	4195.8	4109.8	3945.2	3730.3	3460.9	3192.7	2903.3
10°	6730.2	6742.7	6590.8	6450.3	6008.0	5834.0	5567.8	5144.3	4633.9	4129.6	3617.2
12.5°	8737.3	8728.9	8547.7	8334.9	7789.8	7544.6	7190.3	6662.0	5985.9	5204.0	4402.2
15°	10083.1	10142.9	10066.3	9896.6	9431.1	9150.2	8750.9	8034.0	7210.2	6260.5	5178.9
17.5°	10927.9	10984.5	10957.3	10824.1	10413.3	10113.6	9780.3	9193.3	8240.5	7046.7	5791.0
20°	11365.1	11454.2	11441.5	11296.8	10986.6	10738.2	10370.3	9826.3	9001.5	7592.8	6187.2
22.5°	11656.4	11724.5	11743.4	11579.8	11259.2	11023.3	10753.9	10202.7	9427.0	7926.1	6344.4
25°	11957.2	12077.7	11959.3	11758.0	11463.5	11237.2	10949.9	10421.7	9630.3	8062.3	6297.2
27.5°	12326.2	12383.8	12115.5	11932.0	11605.0	11359.8	11054.7	10548.5	9666.0	7953.3	6027.9
30°	12759.0	12520.1	12332.5	11968.7	11597.7	11358.7	11048.5	10468.8	9478.4	7591.7	5505.9
32.5°	12687.7	12468.7	12255.9	11871.3	11504.5	11267.5	10921.7	10203.7	9035.0	6986.9	4785.8
35°	12279.0	12326.2	12096.6	11778.0	11363.0	11118.8	10741.4	9826.3	8282.5	6152.7	3980.9
37.5°	11934.1	12037.9	11888.1	11593.6	11172.2	10842.0	10332.6	9220.5	7300.3	5094.0	3217.8
40°	11684.6	11718.3	11637.5	11307.4	10801.2	10324.2	9735.1	8132.5	6107.5	3998.7	2539.7
42.5°	11297.9	11387.0	11244.4	10883.9	10116.6	9576.9	8723.7	6875.9	4743.9	3054.3	1911.8
45°	10803.1	10888.2	10712.1	10112.5	9045.4	8254.1	7213.3	5361.3	3509.2	2251.4	1230.5
47.5°	9996.1	10048.5	9707.9	8878.8	7327.6	6582.3	5515.4	3737.7	2260.9	1258.9	598.5
50°	8302.3	8277.2	7575.0	6555.1	4901.2	4119.2	3282.8	2026.1	1015.6	596.4	374.2
52.5°	5350.8	5293.1	4598.2	3670.7	2482.0	1893.9	1423.4	874.1	529.3	333.3	147.8
55°	2385.6	2363.6	1934.9	1503.1	1015.6	874.1	667.7	428.7	282.0	116.3	45.0
57.5°	884.7	864.7	762.0	639.4	490.5	407.7	323.9	205.4	72.3	38.8	24.2
60°	413.0	412.0	362.6	298.7	207.5	157.2	91.2	48.2	30.4	21.0	13.6
62.5°	132.0	129.0	90.2	66.0	47.1	40.9	32.5	24.2	15.7	11.5	8.4
65°	35.6	35.6	32.5	27.2	22.0	18.9	15.7	11.5	7.4	6.3	5.3
67.5°	13.6	13.6	12.5	11.5	8.4	7.4	6.3	5.3	4.2	5.3	5.3
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.2	4.2	5.3
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.3	5.3
75°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.3	5.3
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.3	5.3
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.3	5.3
82.5°	0.0	0.0	1.1	2.1	2.1	2.1	3.2	4.2	4.2	5.3	6.3
85°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.2	4.2	5.3	6.3
87.5°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.2	4.2	5.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	1607.9	1538.7	1443.3	1387.7	1374.1	1344.8	1293.5	1216.9	1153.9	1093.2	1057.6
5°	2116.2	1952.7	1769.3	1640.4	1588.0	1517.7	1393.0	1264.0	1145.6	1042.9	962.1
7.5°	2654.9	2385.6	2088.9	1850.0	1764.0	1652.9	1449.6	1257.8	1095.3	952.8	844.8
10°	3190.6	2756.6	2354.1	2008.2	1867.8	1716.8	1448.6	1200.1	1009.4	843.7	724.3
12.5°	3726.1	3102.5	2549.1	2103.7	1921.3	1730.5	1405.5	1112.1	900.4	731.5	617.4
15°	4220.8	3378.1	2681.2	2136.2	1916.0	1690.7	1318.5	1005.2	786.1	629.9	524.0
17.5°	4589.8	3522.8	2711.5	2086.8	1833.2	1583.7	1185.5	879.4	677.2	539.7	431.8
20°	4771.1	3545.9	2639.2	1946.3	1690.7	1431.8	1039.8	758.9	583.8	455.9	364.7
22.5°	4771.1	3436.9	2482.0	1770.3	1512.5	1256.8	899.3	659.3	510.4	397.2	320.8
25°	4589.8	3219.9	2271.3	1567.0	1316.4	1083.7	777.7	584.9	453.8	361.5	297.7
27.5°	4237.6	2920.1	2000.9	1340.6	1123.6	929.7	681.3	516.8	410.9	325.9	327.0
30°	3753.4	2552.2	1690.7	1101.5	925.5	764.1	573.3	432.8	329.1	313.4	322.9
32.5°	3193.7	2112.0	1339.5	854.2	716.9	601.7	436.0	306.1	262.0	264.1	274.6
35°	2619.3	1662.4	1008.3	633.1	533.5	436.0	286.2	201.3	199.2	203.3	210.7
37.5°	2068.0	1244.1	729.6	463.3	358.5	268.4	154.0	138.3	138.3	142.6	146.8
40°	1549.2	882.6	502.0	274.6	174.0	122.6	97.4	90.2	89.1	90.2	95.4
42.5°	1063.9	558.6	298.7	110.1	83.8	71.3	61.8	56.6	55.6	56.6	59.8
45°	597.4	343.7	116.3	58.7	50.3	45.0	38.8	35.6	34.6	34.6	36.7
47.5°	374.2	136.2	52.4	36.7	31.4	29.3	25.2	23.1	22.0	22.0	23.1
50°	143.6	53.5	32.5	24.2	21.0	18.9	16.8	14.7	13.6	13.6	14.7
52.5°	49.2	31.4	21.0	15.7	13.6	12.5	10.4	9.4	9.4	9.4	9.4
55°	27.2	18.9	12.5	9.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
57.5°	16.8	11.5	8.4	7.4	7.4	7.4	7.4	7.4	7.4	8.4	8.4
60°	9.4	7.4	6.3	6.3	6.3	6.3	7.4	7.4	7.4	8.4	8.4
62.5°	6.3	6.3	6.3	6.3	6.3	6.3	7.4	7.4	8.4	8.4	8.4
65°	5.3	5.3	5.3	6.3	6.3	6.3	7.4	7.4	8.4	8.4	8.4
67.5°	5.3	5.3	6.3	6.3	6.3	7.4	7.4	8.4	8.4	8.4	8.4
70°	5.3	6.3	6.3	7.4	7.4	7.4	8.4	8.4	8.4	9.4	9.4
72.5°	5.3	6.3	6.3	7.4	7.4	7.4	8.4	8.4	9.4	9.4	9.4
75°	6.3	6.3	6.3	7.4	7.4	7.4	8.4	9.4	9.4	9.4	9.4
77.5°	6.3	6.3	7.4	7.4	7.4	8.4	8.4	9.4	9.4	9.4	9.4
80°	6.3	6.3	7.4	7.4	8.4	8.4	9.4	9.4	9.4	10.4	10.4
82.5°	6.3	6.3	7.4	8.4	8.4	8.4	9.4	9.4	10.4	10.4	10.4
85°	6.3	7.4	7.4	8.4	8.4	8.4	9.4	9.4	10.4	10.4	10.4
87.5°	6.3	7.4	7.4	8.4	8.4	8.4	9.4	9.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	1010.5	966.4	922.4	889.8	874.1	858.4	823.8	778.8	759.9	732.6	716.9
5°	880.4	806.0	747.4	708.6	685.5	655.1	615.3	571.3	546.1	517.8	499.0
7.5°	746.3	659.3	602.7	567.1	544.0	506.2	455.9	403.5	373.2	341.7	319.7
10°	628.8	546.1	482.2	441.3	412.0	367.9	317.6	280.9	254.8	227.4	205.4
12.5°	525.1	436.0	367.9	333.3	313.4	271.5	229.5	188.6	172.9	167.6	167.6
15°	425.6	344.8	287.2	257.8	236.9	191.8	183.5	181.4	180.3	179.3	181.4
17.5°	346.9	278.8	218.1	203.3	201.3	200.2	201.3	201.3	202.4	205.4	210.7
20°	291.3	228.5	224.3	225.3	225.3	229.5	234.8	238.9	243.1	248.4	257.8
22.5°	258.9	257.8	265.2	266.2	271.5	277.7	287.2	293.4	304.0	309.1	322.9
25°	298.7	306.1	319.7	323.9	332.2	342.8	357.5	365.8	378.4	384.6	400.4
27.5°	338.6	350.1	366.8	372.1	379.4	396.1	406.7	414.0	420.3	424.5	433.9
30°	335.4	345.8	362.6	363.7	374.2	385.7	392.0	398.2	402.5	401.4	406.7
32.5°	284.1	293.4	309.1	309.1	320.8	330.1	333.3	338.6	338.6	338.6	340.7
35°	218.1	224.3	234.8	237.9	247.4	253.7	255.7	262.0	262.0	259.9	259.9
37.5°	150.9	159.3	166.7	168.7	175.0	179.3	184.5	185.5	183.5	184.5	184.5
40°	98.5	103.8	109.0	110.1	115.2	118.4	123.7	123.7	124.7	123.7	125.8
42.5°	60.9	64.9	68.1	70.2	72.3	74.4	77.6	78.7	79.6	78.7	80.7
45°	37.8	39.9	42.0	43.0	44.0	45.0	48.2	48.2	48.2	48.2	49.2
47.5°	23.1	24.2	25.2	25.2	26.3	27.2	28.2	28.2	28.2	28.2	29.3
50°	13.6	14.7	14.7	14.7	15.7	15.7	16.8	16.8	16.8	15.7	16.8
52.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	8.4	9.4
55°	8.4	8.4	7.4	7.4	7.4	7.4	7.4	6.3	5.3	5.3	4.2
57.5°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.3	5.3	4.2	3.2
60°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.3	4.2	4.2	3.2
62.5°	8.4	7.4	7.4	7.4	7.4	6.3	6.3	5.3	4.2	4.2	3.2
65°	8.4	8.4	7.4	7.4	7.4	6.3	6.3	5.3	5.3	4.2	3.2
67.5°	8.4	8.4	8.4	7.4	8.4	7.4	6.3	6.3	5.3	4.2	4.2
70°	9.4	8.4	8.4	8.4	8.4	7.4	7.4	6.3	5.3	4.2	4.2
72.5°	9.4	9.4	8.4	8.4	8.4	7.4	7.4	6.3	5.3	5.3	4.2
75°	9.4	9.4	8.4	8.4	8.4	7.4	7.4	6.3	6.3	5.3	4.2
77.5°	9.4	9.4	9.4	8.4	8.4	8.4	7.4	7.4	6.3	5.3	4.2
80°	9.4	9.4	9.4	9.4	9.4	8.4	8.4	7.4	6.3	5.3	4.2
82.5°	10.4	9.4	9.4	9.4	9.4	8.4	8.4	7.4	6.3	5.3	5.3
85°	10.4	10.4	9.4	9.4	9.4	8.4	8.4	7.4	6.3	6.3	5.3
87.5°	10.4	9.4	9.4	9.4	9.4	8.4	8.4	7.4	6.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212654

CATALOG NUMBER: LDSQA6A60935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	701.2	692.9	692.9	678.1	676.1	664.5	674.0	667.7
5°	478.0	464.4	460.2	445.5	440.2	426.6	430.8	425.6
7.5°	300.8	287.2	283.0	272.6	266.2	255.7	256.7	253.7
10°	183.5	170.8	167.6	164.6	161.4	160.4	161.4	160.4
12.5°	166.7	165.7	163.5	164.6	162.5	163.5	164.6	163.5
15°	181.4	183.5	181.4	182.4	181.4	183.5	184.5	184.5
17.5°	212.8	217.0	214.9	218.1	217.0	222.2	222.2	222.2
20°	261.0	268.4	266.2	270.5	270.5	276.7	276.7	278.8
22.5°	328.0	337.5	336.5	345.8	343.7	351.1	351.1	353.2
25°	408.8	418.2	419.2	425.6	424.5	431.8	431.8	433.9
27.5°	442.3	447.6	446.6	449.6	450.6	454.9	458.0	455.9
30°	415.0	419.2	418.2	420.3	420.3	423.5	426.6	423.5
32.5°	349.0	352.2	352.2	356.4	353.2	354.3	359.6	356.4
35°	267.3	269.4	267.3	269.4	270.5	270.5	275.6	274.6
37.5°	190.7	191.8	191.8	195.0	191.8	191.8	197.1	198.1
40°	127.9	129.0	127.9	132.0	130.0	130.0	133.1	130.0
42.5°	81.7	82.8	81.7	84.9	82.8	84.9	85.9	87.0
45°	50.3	50.3	49.2	51.3	50.3	51.3	52.4	52.4
47.5°	29.3	29.3	28.2	30.4	29.3	29.3	29.3	30.4
50°	15.7	15.7	15.7	16.8	15.7	15.7	15.7	14.7
52.5°	8.4	8.4	7.4	8.4	7.4	7.4	7.4	7.4
55°	4.2	3.2	3.2	3.2	2.1	2.1	2.1	2.1
57.5°	3.2	2.1	2.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	3.2	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	4.2	3.2	2.1	2.1	1.1	1.1	0.0	0.0
80°	4.2	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
85°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)