

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212660

Luminaire Tested: **LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6199.9 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	66	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	57	49	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	36	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	50031	50031	50031
5°	137319	46099	18809
10°	300919	37726	7166
15°	459652	28719	8407
20°	532548	21361	13063
25°	580940	17573	21083
30°	648729	15934	21532
35°	660048	10927	14764
40°	671641	5176	7470
45°	672736	2156	3264
50°	568737	938	1005
55°	183144	646	158
60°	36373	741	0
65°	3708	876	0
70°	403	1209	0
75°	0	1597	0
80°	0	2653	273
85°	0	5286	543

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.5
10°-20°	815.8	13.2
20°-30°	1562.0	25.2
30°-40°	1840.3	29.7
40°-50°	1445.5	23.3
50°-60°	352.2	5.7
60°-70°	15.1	0.2
70°-80°	5.7	0.1
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2535.5	40.9
0°-40°	4375.7	70.6
0°-60°	6173.5	99.6
0°-90°	6199.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6199.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1162	1162	1162	1162	1162	
5°	3177	2299	1067	558	435	420
15°	10312	5296	644	184	189	2879
25°	12229	6440	370	387	444	5700
35°	12558	4071	208	268	281	7874
45°	11048	1258	35	49	54	8301
55°	2440	46	9	5	2	2904
65°	36	5	9	5	0	97
75°	0	5	10	6	0	0
85°	0	6	11	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0
2.5°	1991.6	1987.4	1958.4	1985.1	1903.7	1900.5	1864.1	1848.0	1800.9	1755.9	1691.4
5°	3177.2	3107.5	3050.7	3052.9	2896.3	2867.4	2786.0	2703.4	2576.9	2459.0	2299.3
7.5°	4842.9	4760.4	4640.3	4590.0	4290.9	4203.0	4034.7	3814.9	3539.4	3265.2	2969.2
10°	6882.9	6895.7	6740.3	6596.7	6144.3	5966.4	5694.1	5261.0	4738.9	4223.3	3699.2
12.5°	8935.6	8927.0	8741.6	8524.0	7966.6	7715.8	7353.5	6813.2	6121.8	5322.1	4502.1
15°	10312.0	10373.1	10294.8	10121.1	9645.2	9357.9	8949.5	8216.3	7373.8	6402.7	5296.4
17.5°	11175.9	11233.9	11206.0	11069.8	10649.6	10343.0	10002.2	9401.8	8427.5	7206.5	5922.4
20°	11622.9	11714.1	11701.1	11553.3	11236.0	10981.9	10605.7	10049.3	9205.7	7765.0	6327.6
22.5°	11920.9	11990.6	12009.9	11842.6	11514.6	11273.5	10998.0	10434.2	9640.9	8106.0	6488.3
25°	12228.6	12351.9	12230.7	12024.9	11723.7	11492.2	11198.5	10658.2	9848.9	8245.2	6440.1
27.5°	12605.9	12664.9	12390.4	12202.9	11868.4	11617.6	11305.7	10787.8	9885.3	8133.8	6164.7
30°	13048.6	12804.1	12612.3	12240.4	11860.9	11616.5	11299.2	10706.4	9693.4	7764.0	5630.9
32.5°	12975.7	12751.7	12534.1	12140.7	11765.4	11523.2	11169.4	10435.3	9240.0	7145.4	4894.4
35°	12557.7	12605.9	12371.2	12045.3	11620.8	11371.0	10985.2	10049.3	8470.4	6292.2	4071.1
37.5°	12205.0	12311.1	12157.9	11856.6	11425.7	11088.0	10567.1	9429.8	7465.9	5209.5	3290.8
40°	11949.8	11984.1	11901.6	11564.0	11046.3	10558.5	9956.1	8317.1	6246.1	4089.4	2597.2
42.5°	11554.4	11645.4	11499.7	11130.9	10346.3	9794.3	8921.6	7031.9	4851.5	3123.6	1955.2
45°	11048.4	11135.3	10955.1	10341.9	9250.7	8441.4	7377.0	5482.9	3588.8	2302.5	1258.5
47.5°	10223.0	10276.6	9928.2	9080.3	7493.9	6731.7	5640.5	3822.5	2312.1	1287.4	612.1
50°	8490.8	8465.0	7746.8	6703.9	5012.3	4212.6	3357.3	2072.0	1038.7	610.0	382.7
52.5°	5472.2	5413.2	4702.5	3753.9	2538.4	1937.0	1455.7	894.0	541.3	340.8	151.1
55°	2439.8	2417.2	1978.8	1537.1	1038.7	894.0	682.8	438.4	288.3	118.9	46.1
57.5°	904.7	884.4	779.3	653.9	501.6	417.0	331.2	210.1	73.9	39.6	24.7
60°	422.4	421.2	370.9	305.4	212.3	160.8	93.2	49.4	31.0	21.4	14.0
62.5°	135.0	131.9	92.1	67.6	48.2	41.8	33.3	24.7	16.1	11.7	8.6
65°	36.4	36.4	33.3	27.9	22.6	19.3	16.1	11.7	7.5	6.5	5.4
67.5°	14.0	14.0	12.8	11.7	8.6	7.5	6.5	5.4	4.2	5.4	5.4
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.2	4.2	5.4
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	5.4
75°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	5.4
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	5.4
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	5.4
82.5°	0.0	0.0	1.1	2.1	2.1	2.1	3.2	4.2	4.2	5.4	6.5
85°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.2	4.2	5.4	6.5
87.5°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.2	4.2	5.4	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0
2.5°	1644.3	1573.6	1476.0	1419.3	1405.3	1375.3	1322.8	1244.5	1180.2	1118.0	1081.6
5°	2164.3	1997.0	1809.5	1677.6	1624.0	1552.2	1424.5	1292.8	1171.6	1066.6	984.1
7.5°	2715.2	2439.8	2136.3	1892.0	1804.0	1690.4	1482.5	1286.3	1120.2	974.4	863.9
10°	3262.9	2819.1	2407.5	2053.8	1910.2	1755.9	1481.4	1227.3	1032.2	862.9	740.7
12.5°	3810.7	3172.9	2606.9	2151.3	1964.8	1769.7	1437.5	1137.3	920.8	748.2	631.4
15°	4316.7	3454.8	2742.0	2184.6	1959.5	1729.1	1348.5	1028.0	804.0	644.3	535.9
17.5°	4693.9	3602.8	2773.1	2134.2	1874.8	1619.6	1212.3	899.3	692.5	552.0	441.7
20°	4879.4	3626.3	2699.1	1990.6	1729.1	1464.3	1063.4	776.0	597.0	466.2	373.0
22.5°	4879.4	3514.9	2538.4	1810.5	1546.8	1285.3	919.8	674.3	522.1	406.3	328.0
25°	4693.9	3293.0	2322.8	1602.5	1346.4	1108.4	795.4	598.1	464.1	369.9	304.4
27.5°	4333.8	2986.4	2046.3	1371.0	1149.1	950.8	696.7	528.4	420.2	333.4	334.5
30°	3838.6	2610.2	1729.1	1126.6	946.6	781.4	586.3	442.7	336.6	320.5	330.1
32.5°	3266.2	2159.9	1369.9	873.6	733.3	615.3	445.9	313.0	268.0	270.1	280.9
35°	2678.8	1700.0	1031.2	647.5	545.6	445.9	292.6	205.8	203.7	207.9	215.4
37.5°	2114.9	1272.3	746.1	473.7	366.6	274.4	157.6	141.5	141.5	145.7	150.1
40°	1584.3	902.6	513.5	280.9	177.9	125.4	99.7	92.1	91.1	92.1	97.5
42.5°	1087.9	571.3	305.4	112.6	85.8	72.9	63.2	57.9	56.8	57.9	61.1
45°	611.0	351.6	118.9	60.1	51.5	46.1	39.6	36.4	35.4	35.4	37.5
47.5°	382.7	139.4	53.6	37.5	32.2	30.0	25.7	23.6	22.6	22.6	23.6
50°	146.9	54.6	33.3	24.7	21.4	19.3	17.2	15.0	14.0	14.0	15.0
52.5°	50.4	32.2	21.4	16.1	14.0	12.8	10.7	9.6	9.6	9.6	9.6
55°	27.9	19.3	12.8	9.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
57.5°	17.2	11.7	8.6	7.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6
60°	9.6	7.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	8.6	8.6
62.5°	6.5	6.5	6.5	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6
65°	5.4	5.4	5.4	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6
67.5°	5.4	5.4	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6	8.6
70°	5.4	6.5	6.5	7.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6
72.5°	5.4	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6
75°	6.5	6.5	6.5	7.5	7.5	7.5	8.6	9.6	9.6	9.6	9.6
77.5°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6	9.6
80°	6.5	6.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6	10.7	10.7
82.5°	6.5	6.5	7.5	8.6	8.6	8.6	9.6	9.6	10.7	10.7	10.7
85°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	10.7	10.7	10.7
87.5°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0
2.5°	1033.3	988.3	943.3	910.0	894.0	877.9	842.6	796.5	777.1	749.2	733.3
5°	900.4	824.3	764.3	724.7	701.1	669.9	629.2	584.2	558.5	529.6	510.2
7.5°	763.2	674.3	616.3	579.9	556.4	517.7	466.2	412.6	381.6	349.4	327.0
10°	643.1	558.5	493.2	451.3	421.2	376.2	324.9	287.2	260.4	232.6	210.1
12.5°	537.0	445.9	376.2	340.8	320.5	277.6	234.7	193.0	176.9	171.5	171.5
15°	435.2	352.7	293.7	263.7	242.2	196.2	187.6	185.5	184.4	183.3	185.5
17.5°	354.8	285.1	222.9	207.9	205.8	204.7	205.8	205.8	206.8	210.1	215.4
20°	298.1	233.6	229.4	230.5	230.5	234.7	240.1	244.5	248.7	254.1	263.7
22.5°	264.8	263.7	271.3	272.3	277.6	284.1	293.7	300.2	310.9	316.3	330.1
25°	305.4	313.0	327.0	331.2	339.8	350.5	365.5	374.1	387.0	393.4	409.5
27.5°	346.2	358.0	375.1	380.6	388.1	405.2	415.9	423.5	429.8	434.1	443.8
30°	343.1	353.8	370.9	372.0	382.7	394.4	400.9	407.4	411.6	410.5	415.9
32.5°	290.5	300.2	316.3	316.3	328.0	337.7	340.8	346.2	346.2	346.2	348.3
35°	222.9	229.4	240.1	243.3	252.9	259.4	261.5	268.0	268.0	265.8	265.8
37.5°	154.3	162.9	170.4	172.5	179.0	183.3	188.6	189.7	187.6	188.6	188.6
40°	100.7	106.1	111.5	112.6	117.9	121.2	126.5	126.5	127.5	126.5	128.6
42.5°	62.2	66.4	69.7	71.8	73.9	76.2	79.3	80.4	81.4	80.4	82.5
45°	38.5	40.8	42.9	44.0	45.0	46.1	49.4	49.4	49.4	49.4	50.4
47.5°	23.6	24.7	25.7	25.7	26.8	27.9	28.9	28.9	28.9	28.9	30.0
50°	14.0	15.0	15.0	15.0	16.1	16.1	17.2	17.2	17.2	16.1	17.2
52.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	8.6	9.6
55°	8.6	8.6	7.5	7.5	7.5	7.5	7.5	6.5	5.4	5.4	4.2
57.5°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.4	5.4	4.2	3.2
60°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.4	4.2	4.2	3.2
62.5°	8.6	7.5	7.5	7.5	7.5	6.5	6.5	5.4	4.2	4.2	3.2
65°	8.6	8.6	7.5	7.5	7.5	6.5	6.5	5.4	5.4	4.2	3.2
67.5°	8.6	8.6	8.6	7.5	8.6	7.5	6.5	6.5	5.4	4.2	4.2
70°	9.6	8.6	8.6	8.6	8.6	7.5	7.5	6.5	5.4	4.2	4.2
72.5°	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	5.4	5.4	4.2
75°	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	6.5	5.4	4.2
77.5°	9.6	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	5.4	4.2
80°	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.4	4.2
82.5°	10.7	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.4	5.4
85°	10.7	10.7	9.6	9.6	9.6	8.6	8.6	7.5	6.5	6.5	5.4
87.5°	10.7	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212660

CATALOG NUMBER: LDSQA6A60940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0	1162.0
2.5°	717.2	708.6	708.6	693.5	691.4	679.7	689.3	682.8
5°	488.8	474.8	470.6	455.5	450.3	436.3	440.6	435.2
7.5°	307.7	293.7	289.5	278.7	272.3	261.5	262.7	259.4
10°	187.6	174.8	171.5	168.3	165.1	163.9	165.1	163.9
12.5°	170.4	169.4	167.2	168.3	166.2	167.2	168.3	167.2
15°	185.5	187.6	185.5	186.5	185.5	187.6	188.6	188.6
17.5°	217.5	221.9	219.8	222.9	221.9	227.3	227.3	227.3
20°	266.9	274.4	272.3	276.5	276.5	283.0	283.0	285.1
22.5°	335.5	345.2	344.1	353.8	351.6	359.0	359.0	361.3
25°	418.0	427.7	428.7	435.2	434.1	441.7	441.7	443.8
27.5°	452.4	457.8	456.6	459.9	460.9	465.2	468.5	466.2
30°	424.5	428.7	427.7	429.8	429.8	433.1	436.3	433.1
32.5°	356.9	360.2	360.2	364.5	361.3	362.3	367.6	364.5
35°	273.4	275.5	273.4	275.5	276.5	276.5	282.0	280.9
37.5°	195.1	196.2	196.2	199.3	196.2	196.2	201.6	202.6
40°	130.8	131.9	130.8	135.0	132.9	132.9	136.1	132.9
42.5°	83.6	84.7	83.6	86.9	84.7	86.9	87.9	89.0
45°	51.5	51.5	50.4	52.5	51.5	52.5	53.6	53.6
47.5°	30.0	30.0	28.9	31.0	30.0	30.0	30.0	31.0
50°	16.1	16.1	16.1	17.2	16.1	16.1	16.1	15.0
52.5°	8.6	8.6	7.5	8.6	7.5	7.5	7.5	7.5
55°	4.2	3.2	3.2	3.2	2.1	2.1	2.1	2.1
57.5°	3.2	2.1	2.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	3.2	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	4.2	3.2	2.1	2.1	1.1	1.1	0.0	0.0
80°	4.2	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
85°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)