

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219643

Luminaire Tested: **LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5611.9 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68209	68209	68209
5°	132176	65003	21921
10°	224563	56884	9850
15°	346036	45377	15655
20°	500924	29526	27230
25°	734938	28494	35008
30°	854540	26996	26832
35°	864943	14302	14181
40°	716104	5384	5958
45°	540848	1833	2174
50°	370033	670	670
55°	51472	586	83
60°	1343	586	0
65°	336	795	0
70°	138	982	0
75°	0	1298	0
80°	0	2207	273
85°	0	4397	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.2	3.0
10°-20°	702.6	12.5
20°-30°	1602.7	28.6
30°-40°	1854.7	33.0
40°-50°	1118.5	19.9
50°-60°	152.0	2.7
60°-70°	4.9	0.1
70°-80°	5.3	0.1
80°-90°	5.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2471.5	44.0
0°-40°	4326.2	77.1
0°-60°	5596.7	99.7
0°-90°	5611.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5611.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1584	1584	1584	1584	1584	
5°	3058	2504	1504	823	507	356
15°	7763	4364	1018	313	351	2298
25°	15470	5171	600	721	737	7001
35°	16456	3942	272	278	270	9917
45°	8882	1074	30	37	36	6945
55°	686	8	8	6	1	1344
65°	3	4	8	4	0	5
75°	0	6	8	6	0	0
85°	0	6	9	6	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2
2.5°	2291.0	2269.9	2278.8	2255.3	2196.4	2184.1	2183.1	2167.4	2117.1	2078.1	2031.3
5°	3058.2	3057.1	3062.6	3012.5	2908.8	2876.4	2860.7	2822.9	2701.4	2607.8	2504.0
7.5°	4015.9	4009.1	4002.5	3911.1	3748.3	3685.9	3645.7	3508.6	3341.4	3175.3	2990.1
10°	5136.4	5133.0	5107.3	4946.8	4685.9	4571.0	4493.0	4275.5	4006.9	3770.5	3456.1
12.5°	6437.5	6407.2	6361.6	6126.4	5768.5	5643.6	5471.9	5127.4	4714.8	4352.6	3913.3
15°	7763.1	7719.5	7638.1	7336.0	6892.3	6679.4	6466.4	6012.6	5452.9	4926.7	4363.7
17.5°	9059.6	9011.7	8821.1	8308.1	7874.6	7614.8	7378.4	6755.1	6097.4	5420.7	4707.0
20°	10932.7	10758.8	10426.5	9618.2	8812.1	8343.9	8067.4	7408.4	6594.6	5806.4	4951.2
22.5°	13434.5	13048.8	12340.7	11027.4	9875.7	9200.0	8747.4	7871.2	6952.5	6058.3	5101.7
25°	15470.2	15295.2	14490.3	12621.6	10824.5	10028.4	9398.6	8239.1	7213.3	6226.8	5170.9
27.5°	16782.5	16739.1	15819.2	13941.7	11599.3	10554.8	9851.2	8482.1	7339.4	6262.3	5137.4
30°	17188.3	17256.4	16373.3	14390.0	11823.6	10660.6	9891.3	8485.5	7242.4	6100.7	4923.4
32.5°	17158.2	17161.7	16079.0	14003.1	11458.9	10353.0	9556.9	8203.4	6884.5	5696.0	4516.4
35°	16455.9	16283.1	15058.9	12814.6	10610.5	9634.9	8894.6	7657.1	6294.7	5087.4	3942.2
37.5°	14913.9	14687.6	13260.5	11292.8	9605.9	8704.0	8106.4	6940.2	5592.4	4437.3	3349.1
40°	12740.9	12420.0	11242.5	9878.0	8506.7	7828.8	7327.0	6138.6	4840.9	3799.5	2792.8
42.5°	10565.9	10408.7	9630.5	8521.1	7582.4	6944.7	6420.8	5299.1	4118.4	3170.8	2089.3
45°	8882.4	8747.4	8224.6	7493.2	6572.3	5990.4	5485.3	4423.8	3199.8	2127.1	1073.7
47.5°	7656.0	7546.7	7046.2	6278.0	5267.8	4631.3	4110.6	2901.0	1812.8	918.6	268.6
50°	5524.3	5412.8	4922.3	4032.6	3120.6	2587.7	2213.1	1295.5	514.0	186.2	27.9
52.5°	2708.2	2616.7	2283.2	1709.1	1147.2	825.0	603.2	242.9	59.1	20.1	13.3
55°	685.7	629.9	525.1	330.0	161.7	97.0	62.5	22.3	14.6	11.1	7.8
57.5°	39.0	37.9	34.6	25.7	18.9	16.7	14.6	11.1	7.8	6.8	5.6
60°	15.6	14.6	13.3	11.1	8.9	7.8	7.8	5.6	4.4	4.4	4.4
62.5°	6.8	6.8	6.8	5.6	4.4	4.4	4.4	3.3	4.4	4.4	4.4
65°	3.3	3.3	3.3	2.2	2.2	2.2	3.3	3.3	3.3	4.4	4.4
67.5°	2.2	1.1	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.4	4.4
70°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.4	5.6
72.5°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.4	5.6
75°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.4	4.4	5.6
77.5°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.4	4.4	5.6
80°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.4	4.4	5.6
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.4	4.4	5.6
85°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.4	4.4	5.6
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.4	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2
2.5°	1971.1	1931.0	1872.0	1832.8	1794.9	1759.3	1700.2	1666.7	1606.6	1550.8	1502.9
5°	2379.2	2278.8	2157.4	2053.6	1986.7	1921.0	1801.7	1713.5	1603.2	1504.0	1412.6
7.5°	2791.8	2614.5	2414.9	2244.2	2140.6	2039.1	1860.7	1718.1	1562.0	1420.4	1285.4
10°	3166.4	2899.9	2617.8	2373.6	2233.1	2101.6	1866.3	1676.7	1476.2	1301.1	1131.6
12.5°	3514.1	3149.6	2781.7	2462.8	2288.8	2130.5	1843.0	1611.0	1372.4	1165.1	967.7
15°	3824.1	3355.8	2901.0	2514.1	2310.0	2122.7	1788.4	1518.5	1249.8	1018.0	768.2
17.5°	4059.3	3484.0	2953.3	2506.3	2272.1	2063.8	1694.6	1402.5	1119.4	838.3	556.4
20°	4202.0	3538.7	2942.2	2446.1	2190.8	1970.0	1583.1	1276.6	962.2	644.4	490.5
22.5°	4262.2	3534.2	2889.7	2355.7	2090.4	1867.4	1476.2	1154.0	797.2	583.0	511.8
25°	4272.3	3488.6	2816.1	2256.6	1991.3	1769.4	1368.0	1014.5	692.3	599.8	573.0
27.5°	4195.5	3381.5	2677.9	2113.8	1851.9	1622.2	1206.3	806.1	650.0	597.6	615.5
30°	3967.9	3137.3	2433.8	1863.1	1609.9	1380.2	861.8	632.2	539.7	543.0	547.5
32.5°	3567.6	2731.5	2041.3	1496.2	1219.7	909.8	536.2	422.6	410.3	410.3	408.0
35°	3033.6	2235.4	1602.0	946.5	606.5	437.1	277.6	278.7	273.2	272.1	270.8
37.5°	2481.8	1763.7	1014.5	391.4	263.1	182.8	163.9	166.1	163.9	167.2	165.0
40°	1956.7	1089.3	370.1	124.9	92.6	89.2	91.4	93.6	93.6	95.8	95.8
42.5°	1137.2	361.2	97.0	50.1	50.1	47.9	49.0	51.4	52.4	53.6	52.4
45°	337.9	74.7	31.2	27.9	27.9	26.7	26.7	27.9	29.0	30.1	30.1
47.5°	53.6	21.1	17.9	15.6	15.6	15.6	15.6	15.6	16.7	16.7	17.9
50°	16.7	13.3	11.1	10.0	10.0	8.9	8.9	10.0	10.0	10.0	11.1
52.5°	10.0	7.8	7.8	6.8	7.8	7.8	6.8	7.8	7.8	7.8	8.9
55°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8
57.5°	5.6	5.6	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
60°	5.6	5.6	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	7.8
62.5°	5.6	5.6	6.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8
65°	5.6	5.6	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
67.5°	5.6	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8	7.8	7.8
70°	5.6	6.8	6.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
72.5°	5.6	6.8	6.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
75°	6.8	6.8	6.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	8.9
77.5°	6.8	6.8	7.8	7.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9
80°	6.8	6.8	7.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	8.9
82.5°	6.8	6.8	7.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	8.9
85°	6.8	6.8	7.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	8.9
87.5°	6.8	6.8	7.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2
2.5°	1461.6	1410.2	1385.8	1351.3	1326.6	1272.0	1249.8	1211.9	1180.6	1129.4	1132.7
5°	1334.5	1237.6	1171.9	1120.5	1084.8	997.9	939.8	878.6	822.8	753.7	728.0
7.5°	1158.4	1039.1	938.7	877.3	831.8	715.7	587.6	487.2	411.4	356.8	335.6
10°	982.3	827.2	667.9	573.0	507.2	395.8	338.9	312.2	287.6	257.5	237.5
12.5°	777.2	556.4	411.4	373.6	346.7	310.0	273.2	244.2	249.7	250.8	258.6
15°	530.7	400.3	354.6	329.0	299.9	278.7	291.0	298.9	313.2	314.4	324.4
17.5°	431.5	375.8	338.9	337.9	340.1	352.2	371.2	381.3	400.3	404.7	419.2
20°	431.5	399.0	430.4	430.4	435.9	452.6	477.2	491.7	512.9	520.7	538.5
22.5°	491.7	514.0	553.0	557.5	559.7	577.5	608.7	623.3	647.7	652.2	671.1
25°	599.8	619.8	655.5	658.9	660.1	673.4	696.8	704.7	721.2	712.5	723.6
27.5°	634.4	643.3	665.5	667.9	662.3	667.9	676.8	676.8	682.2	664.5	667.9
30°	557.5	559.7	570.9	571.9	559.7	561.9	563.0	561.9	560.8	541.8	541.8
32.5°	413.6	413.6	428.2	424.7	411.4	414.8	414.8	414.8	413.6	398.0	395.8
35°	274.2	275.4	287.6	285.4	275.4	277.6	277.6	281.0	277.6	268.6	266.4
37.5°	167.2	168.3	173.9	175.0	171.7	172.8	173.9	172.8	175.0	170.7	168.3
40°	97.0	99.2	103.7	104.7	103.7	103.7	104.7	106.0	110.3	104.7	102.5
42.5°	56.8	57.9	60.2	60.2	60.2	60.2	61.4	62.5	63.5	62.5	61.4
45°	32.4	33.5	34.6	34.6	35.7	34.6	35.7	35.7	36.8	35.7	35.7
47.5°	18.9	18.9	20.1	20.1	21.1	20.1	21.1	21.1	21.1	20.1	20.1
50°	11.1	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	11.1	11.1
52.5°	8.9	8.9	8.9	8.9	8.9	7.8	7.8	7.8	7.8	6.8	6.8
55°	7.8	7.8	7.8	7.8	7.8	7.8	6.8	5.6	5.6	4.4	4.4
57.5°	6.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	3.3	3.3
60°	7.8	7.8	7.8	7.8	6.8	6.8	6.8	5.6	4.4	3.3	3.3
62.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	3.3	3.3
65°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	3.3	3.3
67.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	4.4	3.3
70°	7.8	8.9	8.9	7.8	7.8	7.8	6.8	5.6	5.6	4.4	3.3
72.5°	7.8	8.9	8.9	7.8	7.8	7.8	6.8	5.6	5.6	4.4	3.3
75°	8.9	8.9	8.9	8.9	7.8	7.8	6.8	6.8	5.6	4.4	3.3
77.5°	8.9	8.9	8.9	8.9	7.8	7.8	6.8	6.8	5.6	4.4	3.3
80°	8.9	8.9	8.9	8.9	8.9	7.8	7.8	6.8	5.6	4.4	4.4
82.5°	8.9	8.9	8.9	8.9	8.9	7.8	7.8	6.8	5.6	4.4	4.4
85°	8.9	8.9	8.9	8.9	8.9	7.8	7.8	6.8	5.6	4.4	3.3
87.5°	8.9	8.9	8.9	8.9	7.8	7.8	6.8	6.8	5.6	4.4	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219643

CATALOG NUMBER: LDSQA6A60950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2	1584.2
2.5°	1091.5	1065.8	1054.8	1072.6	1063.6	1036.9	1042.4	1025.8
5°	651.1	612.1	587.6	598.7	563.0	530.7	530.7	507.2
7.5°	314.4	302.1	295.5	297.6	290.0	279.8	274.2	274.2
10°	220.8	216.3	217.5	217.5	224.0	223.0	226.4	225.3
12.5°	262.1	264.3	265.4	269.8	275.4	275.4	278.7	276.4
15°	335.6	333.3	340.1	341.1	350.1	351.2	355.7	351.2
17.5°	426.9	431.5	438.2	437.1	454.8	456.0	456.0	454.8
20°	549.6	553.0	559.7	561.9	583.0	585.3	593.2	594.3
22.5°	683.4	683.4	686.8	691.2	711.3	712.5	715.7	715.7
25°	729.1	722.5	723.6	729.1	740.4	735.8	739.1	736.9
27.5°	670.1	660.1	657.8	665.5	673.4	661.1	665.5	665.5
30°	544.0	535.1	532.9	540.7	546.2	532.9	537.3	539.7
32.5°	398.0	392.5	391.4	396.9	401.4	390.1	394.7	398.0
35°	268.6	266.4	264.3	265.4	272.1	263.1	267.6	269.8
37.5°	170.7	166.1	167.2	169.4	173.9	168.3	172.8	172.8
40°	104.7	102.5	102.5	104.7	107.1	102.5	104.7	106.0
42.5°	61.4	61.4	61.4	62.5	63.5	61.4	61.4	62.5
45°	35.7	34.6	34.6	35.7	36.8	34.6	35.7	35.7
47.5°	20.1	18.9	18.9	20.1	20.1	18.9	20.1	20.1
50°	11.1	10.0	10.0	11.1	11.1	10.0	10.0	10.0
52.5°	5.6	5.6	5.6	5.6	5.6	5.6	4.4	4.4
55°	3.3	3.3	2.2	2.2	2.2	2.2	2.2	1.1
57.5°	2.2	2.2	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.3	2.2	2.2	1.1	1.1	1.1	0.0	0.0
72.5°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	0.0
80°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	1.1
82.5°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	1.1
85°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	0.0
87.5°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)