

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219645

Luminaire Tested: **LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6131.3 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47615	47615	47615
5°	122149	43315	13493
10°	238107	33293	6484
15°	427429	22608	8696
20°	634601	17164	14350
25°	721322	14138	22513
30°	781920	15467	21174
35°	823619	10018	13125
40°	841431	4451	6391
45°	759967	1699	2375
50°	500267	670	670
55°	136994	586	0
60°	27366	672	0
65°	1926	907	0
70°	277	1120	0
75°	0	1664	0
80°	0	2479	273
85°	0	4940	543

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.5	2.2
10°-20°	719.7	11.7
20°-30°	1631.3	26.6
30°-40°	1958.1	31.9
40°-50°	1380.0	22.5
50°-60°	284.7	4.6
60°-70°	10.1	0.2
70°-80°	6.0	0.1
80°-90°	5.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2486.5	40.6
0°-40°	4444.6	72.5
0°-60°	6109.4	99.6
0°-90°	6131.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6131.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1106	1106	1106	1106	1106	
5°	2826	2059	1002	417	312	348
15°	9589	4219	507	181	195	2846
25°	15184	5103	298	417	474	7007
35°	15670	3573	191	250	250	9741
45°	12481	1225	28	38	39	9180
55°	1825	24	8	6	0	2405
65°	19	6	9	6	0	56
75°	0	6	10	7	0	0
85°	0	7	10	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9
2.5°	1885.3	1828.4	1850.7	1785.0	1770.4	1758.1	1770.4	1699.2	1658.9	1607.7	1566.3
5°	2826.2	2758.2	2773.9	2659.0	2606.6	2571.0	2564.2	2417.1	2306.7	2185.2	2059.2
7.5°	3934.4	3869.7	3860.9	3682.4	3574.4	3513.0	3487.3	3276.6	3086.1	2869.7	2633.3
10°	5446.2	5299.0	5253.2	4994.7	4788.5	4658.0	4497.5	4160.7	3826.3	3499.5	3198.6
12.5°	7205.4	7125.2	7011.5	6555.5	6194.2	6009.1	5769.5	5243.3	4737.1	4197.4	3693.7
15°	9589.1	9303.7	9109.7	8450.8	7868.8	7583.4	7233.3	6428.4	5663.6	4980.1	4218.8
17.5°	11918.1	11768.7	11465.5	10610.4	9713.9	9263.5	8741.7	7648.2	6567.7	5595.5	4665.8
20°	13850.2	13709.7	13364.1	12558.0	11563.6	10899.1	10242.4	8741.7	7330.3	6086.2	4964.5
22.5°	14775.5	14686.4	14404.2	13714.2	12866.9	12234.7	11528.9	9672.7	7894.4	6407.2	5100.7
25°	15183.6	15142.3	14960.6	14416.5	13618.3	13082.0	12415.3	10331.6	8245.5	6556.7	5102.9
27.5°	15597.2	15605.0	15203.7	14773.2	14016.3	13501.2	12859.0	10623.7	8309.2	6473.1	4935.6
30°	15727.6	15645.1	15467.9	14850.3	14131.1	13583.8	12894.8	10488.7	8048.4	6129.6	4602.2
32.5°	15674.0	15641.8	15446.6	14793.3	13936.0	13332.9	12550.1	9953.6	7533.2	5639.1	4129.5
35°	15669.7	15609.5	15162.3	14601.6	13545.8	12801.0	11769.9	9088.5	6804.1	4992.4	3573.1
37.5°	15386.5	15237.1	14901.4	14145.6	12754.2	11809.9	10653.8	8031.6	5912.2	4266.7	3021.3
40°	14970.7	14770.0	14328.5	13184.5	11383.0	10294.8	9166.6	6830.9	4967.9	3550.9	2435.0
42.5°	14102.1	13798.8	13174.5	11601.4	9555.6	8574.5	7635.8	5614.4	4051.4	2893.2	1858.5
45°	12481.0	12066.4	11222.3	9495.4	7719.4	6918.9	6164.2	4517.4	3243.2	2146.1	1225.2
47.5°	10031.7	9647.0	8878.9	7558.9	6053.7	5377.1	4775.1	3360.2	2198.6	1243.1	585.3
50°	7468.6	7138.6	6538.8	5253.2	4063.8	3531.9	3016.8	1908.7	1030.1	590.8	242.9
52.5°	4456.1	4292.3	3760.5	2913.2	2006.8	1729.2	1388.1	808.3	519.5	214.0	65.7
55°	1825.0	1684.6	1484.9	1191.8	873.0	740.2	633.3	399.0	161.7	44.6	24.5
57.5°	825.0	793.7	703.5	553.0	401.4	336.8	227.4	75.8	35.7	22.3	14.6
60°	317.8	286.5	245.3	132.6	56.8	47.9	39.0	25.7	17.9	12.2	8.9
62.5°	45.8	43.5	39.0	31.2	24.5	22.3	18.9	13.3	10.0	7.8	6.8
65°	18.9	18.9	16.7	13.3	11.1	10.0	8.9	6.8	5.6	5.6	5.6
67.5°	7.8	7.8	6.8	5.6	4.4	4.4	4.4	3.3	4.4	4.4	5.6
70°	2.2	2.2	2.2	2.2	2.2	2.2	3.3	3.3	4.4	4.4	5.6
72.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.4	5.6	5.6
75°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.4	5.6	5.6
77.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	5.6
80°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	6.8
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	6.8
85°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	6.8
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9
2.5°	1530.7	1459.4	1439.3	1377.0	1324.4	1298.9	1266.5	1194.0	1139.4	1066.9	1023.5
5°	1971.1	1836.2	1729.2	1598.8	1512.8	1457.0	1370.2	1237.6	1130.5	1002.2	910.8
7.5°	2447.1	2200.7	2007.8	1792.8	1668.9	1572.0	1423.8	1233.0	1075.9	905.2	763.7
10°	2906.5	2538.5	2235.4	1926.5	1763.7	1628.8	1424.8	1185.2	976.6	761.5	612.1
12.5°	3311.2	2836.2	2409.3	2012.4	1810.5	1642.3	1386.9	1099.4	847.3	626.5	495.0
15°	3649.0	3067.0	2531.9	2044.6	1813.9	1613.1	1307.7	976.6	703.5	507.2	414.8
17.5°	3905.5	3188.6	2569.7	2005.6	1749.2	1530.7	1186.2	821.6	570.9	430.4	348.9
20°	4038.1	3211.9	2515.1	1899.8	1629.9	1405.9	1026.9	666.6	483.9	374.6	292.1
22.5°	4054.9	3146.2	2384.7	1748.1	1479.5	1254.2	850.6	556.3	431.5	331.1	257.5
25°	3955.5	3003.5	2198.6	1576.4	1314.5	1080.2	692.3	498.4	392.5	297.6	296.5
27.5°	3743.8	2758.2	1975.6	1377.0	1114.9	878.6	587.6	450.4	350.1	315.4	335.5
30°	3445.0	2443.9	1701.3	1124.9	870.8	675.6	495.0	371.2	307.6	311.1	327.8
32.5°	3040.3	2053.6	1379.1	824.0	623.3	508.4	371.2	253.1	255.3	256.5	270.8
35°	2531.9	1646.6	1030.1	554.1	438.2	357.9	209.7	186.2	189.6	190.6	200.7
37.5°	2029.1	1265.5	684.5	369.0	275.4	188.3	130.4	124.9	127.1	126.0	137.2
40°	1554.2	881.9	410.3	182.8	106.0	88.1	80.3	76.9	78.0	79.2	85.8
42.5°	1100.4	478.3	202.9	69.2	55.7	51.4	47.9	45.8	46.8	46.8	51.4
45°	558.6	226.4	69.2	37.9	34.6	31.2	29.0	27.9	27.9	27.9	30.1
47.5°	241.9	74.7	32.4	23.5	21.1	20.1	17.9	16.7	16.7	16.7	17.9
50°	75.8	30.1	20.1	15.6	13.3	12.2	11.1	11.1	11.1	10.0	11.1
52.5°	27.9	18.9	13.3	10.0	8.9	8.9	8.9	7.8	8.9	7.8	8.9
55°	16.7	12.2	8.9	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
57.5°	11.1	8.9	7.8	7.8	6.8	6.8	7.8	7.8	7.8	7.8	7.8
60°	7.8	7.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8	7.8
62.5°	6.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8	8.9
65°	5.6	6.8	6.8	6.8	6.8	6.8	7.8	7.8	8.9	8.9	8.9
67.5°	5.6	6.8	6.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	8.9
70°	6.8	6.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	8.9	10.0
72.5°	6.8	6.8	7.8	7.8	7.8	7.8	8.9	8.9	10.0	10.0	10.0
75°	6.8	7.8	7.8	7.8	7.8	8.9	8.9	8.9	10.0	10.0	10.0
77.5°	6.8	7.8	7.8	8.9	8.9	8.9	8.9	10.0	10.0	10.0	10.0
80°	6.8	7.8	7.8	8.9	8.9	8.9	10.0	10.0	10.0	10.0	11.1
82.5°	6.8	7.8	7.8	8.9	8.9	8.9	10.0	10.0	10.0	10.0	11.1
85°	7.8	7.8	8.9	8.9	8.9	8.9	10.0	10.0	10.0	10.0	11.1
87.5°	7.8	7.8	8.9	8.9	8.9	8.9	10.0	10.0	11.1	10.0	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9
2.5°	965.5	900.8	856.2	839.5	807.2	755.9	725.8	697.9	645.5	634.4	605.4
5°	806.1	702.3	628.8	600.9	564.1	520.7	478.3	450.4	416.9	403.6	383.6
7.5°	635.4	531.9	468.3	445.8	420.4	384.7	346.7	318.9	284.3	266.4	249.7
10°	499.4	422.6	369.0	346.7	320.0	282.2	242.9	206.2	176.2	157.1	153.9
12.5°	405.8	342.3	285.4	262.0	230.8	192.9	165.0	163.9	161.7	160.5	162.9
15°	332.2	270.8	210.7	185.0	176.2	175.0	178.4	181.8	180.6	184.0	186.2
17.5°	273.2	207.5	194.0	195.1	196.1	199.6	205.1	214.0	215.1	220.8	225.2
20°	223.0	219.6	225.2	229.6	233.0	239.7	251.9	263.1	266.4	274.2	283.2
22.5°	253.1	263.1	275.4	281.0	285.4	297.6	311.1	329.0	335.5	345.7	357.9
25°	305.4	322.2	341.1	347.9	354.6	374.6	390.1	411.4	416.9	429.3	441.5
27.5°	348.9	366.8	386.9	395.8	401.4	421.4	434.7	448.2	448.2	454.8	463.7
30°	342.3	356.8	373.6	380.1	382.5	396.9	410.3	414.8	412.6	415.8	422.6
32.5°	284.3	295.5	308.9	314.4	316.6	326.8	337.9	337.9	336.8	336.8	341.1
35°	210.7	218.5	225.2	230.8	234.1	240.8	250.8	249.7	249.7	247.5	250.8
37.5°	141.5	146.0	153.9	156.1	157.1	161.7	169.4	169.4	167.2	168.3	170.7
40°	85.8	91.4	95.8	97.0	99.2	102.5	108.2	108.2	108.2	108.2	109.3
42.5°	51.4	54.6	57.9	57.9	59.1	63.5	65.7	65.7	65.7	65.7	66.9
45°	30.1	31.2	33.5	34.6	34.6	36.8	37.9	37.9	37.9	37.9	39.0
47.5°	17.9	18.9	18.9	20.1	20.1	21.1	22.3	22.3	21.1	21.1	21.1
50°	11.1	11.1	11.1	11.1	12.2	12.2	12.2	12.2	12.2	12.2	11.1
52.5°	8.9	8.9	8.9	8.9	7.8	7.8	7.8	7.8	6.8	6.8	5.6
55°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	6.8	5.6	4.4	3.3
57.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	4.4	3.3
60°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	4.4	3.3
62.5°	8.9	8.9	7.8	7.8	7.8	6.8	6.8	5.6	5.6	4.4	3.3
65°	8.9	8.9	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	3.3
67.5°	8.9	8.9	8.9	8.9	7.8	7.8	7.8	6.8	5.6	4.4	3.3
70°	10.0	10.0	8.9	8.9	8.9	7.8	7.8	6.8	5.6	5.6	4.4
72.5°	10.0	10.0	8.9	8.9	8.9	8.9	7.8	6.8	6.8	5.6	4.4
75°	10.0	10.0	10.0	10.0	8.9	8.9	7.8	7.8	6.8	5.6	4.4
77.5°	10.0	10.0	10.0	10.0	8.9	8.9	8.9	7.8	6.8	5.6	4.4
80°	10.0	10.0	10.0	10.0	10.0	8.9	8.9	7.8	6.8	5.6	4.4
82.5°	11.1	11.1	10.0	10.0	10.0	8.9	8.9	7.8	6.8	5.6	5.6
85°	11.1	11.1	10.0	10.0	10.0	8.9	8.9	7.8	6.8	6.8	5.6
87.5°	11.1	11.1	10.0	10.0	10.0	8.9	8.9	7.8	6.8	6.8	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219645

CATALOG NUMBER: LDSQA6A60950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9	1105.9
2.5°	587.6	554.1	543.0	550.8	541.8	535.1	526.2	521.8
5°	368.0	343.3	335.5	337.9	330.0	323.3	314.4	312.2
7.5°	226.4	202.9	194.0	194.0	185.0	177.2	171.7	168.3
10°	151.5	147.2	148.3	149.3	148.3	149.3	146.0	148.3
12.5°	162.9	160.5	162.9	163.9	163.9	166.1	161.7	165.0
15°	189.6	187.2	190.6	192.9	192.9	196.1	191.8	195.1
17.5°	231.8	230.8	236.4	238.6	239.7	245.3	239.7	244.2
20°	293.3	292.1	299.9	303.3	302.1	313.2	305.4	313.2
22.5°	372.3	370.1	381.3	384.7	385.7	400.3	393.5	399.0
25°	451.5	453.8	459.4	465.0	466.0	478.3	468.3	473.9
27.5°	468.3	465.0	468.3	475.0	476.1	481.6	472.7	477.2
30°	423.7	418.0	419.2	426.9	429.3	431.5	423.7	425.9
32.5°	344.4	335.5	335.5	343.3	345.7	348.9	335.5	341.1
35°	254.3	246.4	246.4	251.9	253.1	255.3	245.3	249.7
37.5°	173.9	167.2	169.4	171.7	172.8	175.0	173.9	172.8
40°	111.5	107.1	110.3	110.3	111.5	112.5	112.5	113.7
42.5°	67.9	64.7	66.9	66.9	67.9	67.9	67.9	69.2
45°	39.0	37.9	37.9	39.0	39.0	39.0	37.9	39.0
47.5°	21.1	20.1	21.1	21.1	21.1	21.1	21.1	21.1
50°	11.1	10.0	10.0	10.0	10.0	10.0	10.0	10.0
52.5°	5.6	4.4	4.4	4.4	3.3	4.4	3.3	3.3
55°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
57.5°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.3	2.2	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.3	2.2	2.2	1.1	1.1	0.0	0.0	0.0
72.5°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	3.3	3.3	2.2	2.2	1.1	1.1	1.1	0.0
80°	4.4	3.3	2.2	2.2	2.2	1.1	1.1	1.1
82.5°	4.4	3.3	2.2	2.2	2.2	1.1	1.1	1.1
85°	4.4	3.3	3.3	2.2	2.2	1.1	1.1	1.1
87.5°	4.4	3.3	3.3	2.2	2.2	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)