

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212694

Luminaire Tested: **LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5318.6 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41308	41308	41308
5°	105954	37576	11704
10°	206541	28877	5622
15°	370766	19613	7546
20°	550473	14891	12449
25°	625696	12266	19530
30°	678266	13418	18370
35°	714434	8694	11385
40°	729880	3856	5547
45°	659224	1474	2058
50°	433954	583	583
55°	118836	510	0
60°	23732	586	0
65°	1671	795	0
70°	252	982	0
75°	0	1447	0
80°	0	2157	223
85°	0	4298	445

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	2.2
10°-20°	624.3	11.7
20°-30°	1415.0	26.6
30°-40°	1698.5	31.9
40°-50°	1197.1	22.5
50°-60°	247.0	4.6
60°-70°	8.8	0.2
70°-80°	5.2	0.1
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2156.9	40.6
0°-40°	3855.4	72.5
0°-60°	5299.5	99.6
0°-90°	5318.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5318.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	959	959	959	959	959	
5°	2452	1786	869	362	271	302
15°	8318	3660	440	157	169	2468
25°	13171	4426	258	362	411	6078
35°	13592	3100	165	217	217	8450
45°	10826	1063	24	33	34	7963
55°	1583	21	7	5	0	2086
65°	16	5	8	5	0	49
75°	0	5	9	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4
2.5°	1635.4	1586.0	1605.4	1548.3	1535.7	1525.0	1535.7	1473.8	1439.0	1394.5	1358.8
5°	2451.5	2392.5	2406.2	2306.5	2261.1	2230.2	2224.3	2096.6	2001.0	1895.5	1786.2
7.5°	3412.9	3356.7	3349.1	3194.2	3100.5	3047.3	3025.1	2842.3	2676.8	2489.2	2284.2
10°	4724.2	4596.5	4556.9	4332.5	4153.6	4040.5	3901.2	3609.2	3319.0	3035.6	2774.6
12.5°	6250.3	6180.6	6082.0	5686.5	5373.2	5212.6	5004.6	4548.2	4109.2	3641.0	3204.0
15°	8317.9	8070.3	7902.0	7330.4	6825.6	6578.1	6274.4	5576.2	4912.8	4320.0	3659.5
17.5°	10338.1	10208.5	9945.5	9203.7	8426.2	8035.6	7582.9	6634.2	5697.1	4853.8	4047.3
20°	12014.1	11892.3	11592.5	10893.2	10030.5	9454.2	8884.6	7582.9	6358.6	5279.3	4306.4
22.5°	12816.8	12739.4	12494.7	11896.2	11161.2	10612.8	10000.6	8390.5	6847.9	5557.9	4424.4
25°	13170.7	13134.9	12977.2	12505.4	11813.0	11347.8	10769.5	8961.9	7152.6	5687.4	4426.4
27.5°	13529.5	13536.2	13188.1	12814.9	12158.2	11711.4	11154.4	9215.3	7207.7	5614.8	4281.3
30°	13642.7	13571.1	13417.3	12881.6	12257.8	11782.9	11185.3	9098.3	6981.4	5317.0	3992.2
32.5°	13596.2	13568.2	13399.0	12832.3	12088.6	11565.3	10886.5	8634.1	6534.6	4891.5	3582.0
35°	13592.4	13540.2	13152.4	12665.9	11750.1	11104.1	10209.6	7883.7	5902.1	4330.6	3099.5
37.5°	13346.7	13217.1	12926.0	12270.3	11063.4	10244.4	9241.4	6966.8	5128.5	3701.0	2620.8
40°	12986.0	12811.9	12428.9	11436.8	9873.9	8930.1	7951.3	5925.3	4309.4	3080.2	2112.1
42.5°	12232.6	11969.6	11428.0	10063.4	8288.9	7437.8	6623.5	4870.2	3514.4	2509.5	1612.1
45°	10826.5	10466.8	9734.7	8236.7	6696.0	6001.7	5347.0	3918.6	2813.2	1861.6	1062.9
47.5°	8701.8	8368.2	7701.8	6556.8	5251.2	4664.3	4142.1	2914.7	1907.1	1078.4	507.8
50°	6478.6	6192.3	5671.9	4556.9	3525.1	3063.7	2616.9	1655.7	893.6	512.6	210.9
52.5°	3865.4	3723.3	3262.0	2526.9	1740.7	1499.9	1204.1	701.1	450.7	185.6	57.1
55°	1583.1	1461.2	1288.2	1033.8	757.2	642.2	549.2	346.2	140.3	38.7	21.3
57.5°	715.6	688.6	610.2	479.7	348.1	292.1	197.3	65.8	30.9	19.4	12.6
60°	275.6	248.6	212.8	115.0	49.3	41.6	33.8	22.2	15.5	10.7	7.8
62.5°	39.6	37.7	33.8	27.0	21.3	19.4	16.4	11.6	8.7	6.8	5.9
65°	16.4	16.4	14.6	11.6	9.6	8.7	7.8	5.9	4.8	4.8	4.8
67.5°	6.8	6.8	5.9	4.8	3.9	3.9	3.9	2.9	3.9	3.9	4.8
70°	2.0	2.0	2.0	2.0	2.0	2.0	2.9	2.9	3.9	3.9	4.8
72.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	3.9	4.8	4.8
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	3.9	4.8	4.8
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	3.9	4.8	4.8
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	3.9	4.8	5.9
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	3.9	4.8	5.9
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	3.9	4.8	5.9
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	3.9	4.8	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4
2.5°	1327.8	1265.9	1248.5	1194.3	1148.9	1126.7	1098.6	1035.7	988.4	925.5	887.8
5°	1709.8	1592.8	1499.9	1386.8	1312.4	1264.0	1188.6	1073.4	980.6	869.4	790.1
7.5°	2122.8	1909.0	1741.7	1555.1	1447.7	1363.6	1235.0	1069.6	933.3	785.3	662.5
10°	2521.2	2202.1	1939.0	1671.2	1530.0	1413.0	1235.9	1028.0	847.2	660.5	530.9
12.5°	2872.2	2460.2	2089.9	1745.6	1570.5	1424.5	1203.0	953.6	735.0	543.5	429.4
15°	3165.2	2660.5	2196.2	1773.6	1573.4	1399.3	1134.4	847.2	610.2	440.0	359.7
17.5°	3387.7	2765.9	2229.1	1739.8	1517.4	1327.8	1029.0	712.8	495.2	373.2	302.6
20°	3502.7	2786.2	2181.8	1647.9	1413.9	1219.5	890.6	578.4	419.8	325.0	253.4
22.5°	3517.3	2729.1	2068.6	1516.4	1283.4	1088.0	737.9	482.6	374.3	287.2	223.3
25°	3431.2	2605.3	1907.1	1367.5	1140.2	937.0	600.6	432.2	340.5	258.2	257.3
27.5°	3247.5	2392.5	1713.7	1194.3	967.1	762.1	509.6	390.7	303.7	273.7	291.1
30°	2988.3	2119.9	1475.8	975.8	755.3	586.0	429.4	322.0	266.9	269.9	284.3
32.5°	2637.2	1781.4	1196.3	714.7	540.5	441.0	322.0	219.6	221.5	222.4	235.0
35°	2196.2	1428.4	893.6	480.6	380.1	310.4	181.9	161.5	164.5	165.4	174.1
37.5°	1760.1	1097.6	593.8	320.1	238.8	163.4	113.1	108.3	110.2	109.3	119.0
40°	1348.1	764.9	355.9	158.6	91.9	76.4	69.7	66.7	67.7	68.6	74.5
42.5°	954.5	414.8	176.0	59.9	48.4	44.5	41.6	39.6	40.6	40.6	44.5
45°	484.5	196.3	59.9	32.9	30.0	27.0	25.1	24.2	24.2	24.2	26.1
47.5°	209.8	64.7	28.1	20.3	18.3	17.4	15.5	14.6	14.6	14.6	15.5
50°	65.8	26.1	17.4	13.5	11.6	10.7	9.6	9.6	9.6	8.7	9.6
52.5°	24.2	16.4	11.6	8.7	7.8	7.8	7.8	6.8	7.8	6.8	7.8
55°	14.6	10.7	7.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
57.5°	9.6	7.8	6.8	6.8	5.9	5.9	6.8	6.8	6.8	6.8	6.8
60°	6.8	6.8	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8	6.8
62.5°	5.9	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8	7.8
65°	4.8	5.9	5.9	5.9	5.9	5.9	6.8	6.8	7.8	7.8	7.8
67.5°	4.8	5.9	5.9	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
70°	5.9	5.9	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8	8.7
72.5°	5.9	5.9	6.8	6.8	6.8	6.8	7.8	7.8	8.7	8.7	8.7
75°	5.9	6.8	6.8	6.8	6.8	7.8	7.8	7.8	8.7	8.7	8.7
77.5°	5.9	6.8	6.8	7.8	7.8	7.8	7.8	8.7	8.7	8.7	8.7
80°	5.9	6.8	6.8	7.8	7.8	7.8	8.7	8.7	8.7	8.7	9.6
82.5°	5.9	6.8	6.8	7.8	7.8	7.8	8.7	8.7	8.7	8.7	9.6
85°	6.8	6.8	7.8	7.8	7.8	7.8	8.7	8.7	8.7	8.7	9.6
87.5°	6.8	6.8	7.8	7.8	7.8	7.8	8.7	8.7	9.6	8.7	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4
2.5°	837.5	781.4	742.7	728.3	700.2	655.7	629.6	605.4	559.9	550.3	525.1
5°	699.1	609.3	545.5	521.3	489.3	451.6	414.8	390.7	361.7	350.1	332.7
7.5°	551.2	461.2	406.1	386.9	364.7	333.6	300.8	276.6	246.6	231.1	216.6
10°	433.3	366.5	320.1	300.8	277.6	244.7	210.9	178.9	152.8	136.4	133.5
12.5°	352.0	296.9	247.5	227.2	200.2	167.3	143.1	142.2	140.3	139.2	141.2
15°	288.2	235.0	182.8	160.6	152.8	151.8	154.7	157.7	156.6	159.5	161.5
17.5°	237.0	179.9	168.2	169.3	170.2	173.2	178.0	185.6	186.7	191.5	195.4
20°	193.4	190.6	195.4	199.2	202.2	207.9	218.5	228.3	231.1	237.9	245.7
22.5°	219.6	228.3	238.8	243.8	247.5	258.2	269.9	285.4	291.1	299.8	310.4
25°	264.9	279.5	295.9	301.7	307.6	325.0	338.5	356.8	361.7	372.3	383.0
27.5°	302.6	318.1	335.5	343.3	348.1	365.6	377.1	388.8	388.8	394.6	402.4
30°	296.9	309.5	324.0	329.8	331.8	344.2	355.9	359.7	357.8	360.8	366.5
32.5°	246.6	256.2	267.9	272.7	274.7	283.4	293.0	293.0	292.1	292.1	295.9
35°	182.8	189.5	195.4	200.2	203.1	208.9	217.6	216.6	216.6	214.6	217.6
37.5°	122.8	126.8	133.5	135.3	136.4	140.3	147.0	147.0	145.1	146.0	147.9
40°	74.5	79.3	83.2	84.1	86.1	88.9	93.9	93.9	93.9	93.9	94.8
42.5°	44.5	47.4	50.3	50.3	51.2	55.1	57.1	57.1	57.1	57.1	58.0
45°	26.1	27.0	29.0	30.0	30.0	31.8	32.9	32.9	32.9	32.9	33.8
47.5°	15.5	16.4	16.4	17.4	17.4	18.3	19.4	19.4	18.3	18.3	18.3
50°	9.6	9.6	9.6	9.6	10.7	10.7	10.7	10.7	10.7	10.7	9.6
52.5°	7.8	7.8	7.8	7.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8
55°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	5.9	4.8	3.9	2.9
57.5°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	3.9	2.9
60°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	3.9	2.9
62.5°	7.8	7.8	6.8	6.8	6.8	5.9	5.9	4.8	4.8	3.9	2.9
65°	7.8	7.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9
67.5°	7.8	7.8	7.8	7.8	6.8	6.8	6.8	5.9	4.8	3.9	2.9
70°	8.7	8.7	7.8	7.8	7.8	6.8	6.8	5.9	4.8	4.8	3.9
72.5°	8.7	8.7	7.8	7.8	7.8	7.8	6.8	5.9	5.9	4.8	3.9
75°	8.7	8.7	8.7	8.7	7.8	7.8	6.8	6.8	5.9	4.8	3.9
77.5°	8.7	8.7	8.7	8.7	7.8	7.8	7.8	6.8	5.9	4.8	3.9
80°	8.7	8.7	8.7	8.7	8.7	7.8	7.8	6.8	5.9	4.8	3.9
82.5°	9.6	9.6	8.7	8.7	8.7	7.8	7.8	6.8	5.9	4.8	4.8
85°	9.6	9.6	8.7	8.7	8.7	7.8	7.8	6.8	5.9	5.9	4.8
87.5°	9.6	9.6	8.7	8.7	8.7	7.8	7.8	6.8	5.9	5.9	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212694

CATALOG NUMBER: LDSQA6A70930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	959.4	959.4	959.4	959.4	959.4	959.4	959.4	959.4
2.5°	509.6	480.6	471.0	477.8	470.0	464.2	456.4	452.7
5°	319.2	297.8	291.1	293.0	286.3	280.4	272.7	270.8
7.5°	196.3	176.0	168.2	168.2	160.6	153.8	149.0	146.0
10°	131.6	127.7	128.6	129.6	128.6	129.6	126.8	128.6
12.5°	141.2	139.2	141.2	142.2	142.2	144.0	140.3	143.1
15°	164.5	162.5	165.4	167.3	167.3	170.2	166.4	169.3
17.5°	201.1	200.2	205.0	207.0	207.9	212.8	207.9	211.8
20°	254.3	253.4	260.1	263.0	262.1	271.7	264.9	271.7
22.5°	323.0	321.1	330.7	333.6	334.6	347.2	341.4	346.2
25°	391.7	393.6	398.4	403.3	404.3	414.8	406.1	411.1
27.5°	406.1	403.3	406.1	412.0	413.0	417.8	410.0	413.9
30°	367.5	362.7	363.6	370.4	372.3	374.3	367.5	369.5
32.5°	298.9	291.1	291.1	297.8	299.8	302.6	291.1	295.9
35°	220.5	213.7	213.7	218.5	219.6	221.5	212.8	216.6
37.5°	150.9	145.1	147.0	149.0	149.9	151.8	150.9	149.9
40°	96.7	92.8	95.7	95.7	96.7	97.6	97.6	98.7
42.5°	59.0	56.0	58.0	58.0	59.0	59.0	59.0	59.9
45°	33.8	32.9	32.9	33.8	33.8	33.8	32.9	33.8
47.5°	18.3	17.4	18.3	18.3	18.3	18.3	18.3	18.3
50°	9.6	8.7	8.7	8.7	8.7	8.7	8.7	8.7
52.5°	4.8	3.9	3.9	3.9	2.9	3.9	2.9	2.9
55°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
57.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
60°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
65°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.9	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.9	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.9	2.9	2.0	2.0	0.9	0.9	0.9	0.0
80°	3.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	3.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
85°	3.9	2.9	2.9	2.0	2.0	0.9	0.9	0.9
87.5°	3.9	2.9	2.9	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)