

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212700

Luminaire Tested: **LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5677.4 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	44089	44089	44089
5°	113103	40113	12491
10°	220479	30827	6003
15°	395781	20937	8055
20°	587609	15890	13287
25°	667915	13093	20846
30°	724025	14323	19603
35°	762632	9277	12157
40°	779127	4120	5918
45°	703705	1577	2198
50°	463226	616	616
55°	126853	548	0
60°	25334	629	0
65°	1793	846	0
70°	264	1045	0
75°	0	1530	0
80°	0	2281	248
85°	0	4545	494

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.5	2.2
10°-20°	666.4	11.7
20°-30°	1510.5	26.6
30°-40°	1813.1	31.9
40°-50°	1277.8	22.5
50°-60°	263.7	4.6
60°-70°	9.4	0.2
70°-80°	5.6	0.1
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2302.4	40.6
0°-40°	4115.5	72.5
0°-60°	5657.0	99.6
0°-90°	5677.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5677.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1024	1024	1024	1024	1024	
5°	2617	1907	928	386	289	322
15°	8879	3906	470	167	181	2635
25°	14059	4725	276	386	439	6488
35°	14509	3309	176	231	231	9020
45°	11557	1134	26	35	36	8500
55°	1690	23	7	5	0	2227
65°	18	5	8	5	0	52
75°	0	5	9	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0
2.5°	1745.6	1693.0	1713.7	1652.8	1639.3	1628.0	1639.3	1573.3	1536.1	1488.6	1450.4
5°	2616.9	2554.0	2568.4	2462.1	2413.6	2380.6	2374.3	2238.1	2135.9	2023.3	1906.7
7.5°	3643.1	3583.2	3575.0	3409.8	3309.7	3252.9	3229.1	3034.1	2857.5	2657.2	2438.4
10°	5043.0	4906.7	4864.3	4624.9	4433.9	4313.1	4164.4	3852.7	3543.0	3240.5	2961.8
12.5°	6672.0	6597.6	6492.3	6070.1	5735.6	5564.3	5342.4	4855.1	4386.3	3886.7	3420.2
15°	8879.1	8614.8	8435.2	7825.1	7286.2	7022.0	6697.7	5952.4	5244.2	4611.4	3906.4
17.5°	11035.6	10897.2	10616.4	9824.8	8994.7	8577.7	8094.4	7081.8	6081.4	5181.3	4320.3
20°	12824.6	12694.6	12374.6	11628.1	10707.3	10092.0	9484.0	8094.4	6787.6	5635.5	4596.9
22.5°	13681.5	13598.9	13337.7	12698.7	11914.1	11328.8	10675.3	8956.5	7309.9	5932.8	4722.9
25°	14059.4	14021.2	13852.8	13349.0	12609.9	12113.4	11496.0	9566.6	7635.2	6071.1	4725.0
27.5°	14442.4	14449.5	14077.8	13679.4	12978.4	12501.6	11907.0	9837.1	7693.9	5993.7	4570.2
30°	14563.1	14486.7	14322.5	13750.6	13084.8	12577.9	11940.0	9712.2	7452.4	5675.8	4261.4
32.5°	14513.6	14483.6	14303.0	13698.0	12904.2	12345.6	11621.0	9216.6	6975.4	5221.6	3823.7
35°	14509.4	14453.7	14039.7	13520.4	12542.8	11853.3	10898.3	8415.6	6300.3	4622.8	3308.6
37.5°	14247.2	14108.9	13798.1	13098.2	11809.8	10935.5	9864.9	7436.9	5474.4	3950.7	2797.6
40°	13862.2	13676.3	13267.5	12208.3	10540.1	9532.5	8487.8	6325.2	4600.0	3288.0	2254.6
42.5°	13058.0	12777.2	12199.1	10742.4	8848.1	7939.6	7070.4	5198.8	3751.5	2678.9	1720.9
45°	11557.0	11172.8	10391.4	8792.4	7147.9	6406.7	5707.8	4183.0	3003.0	1987.2	1134.5
47.5°	9288.9	8932.8	8221.5	6999.2	5605.6	4978.9	4421.4	3111.4	2035.8	1151.0	542.0
50°	6915.6	6610.0	6054.6	4864.3	3762.8	3270.4	2793.4	1767.4	953.8	547.2	225.0
52.5°	4126.2	3974.5	3482.0	2697.5	1858.2	1601.1	1285.3	748.4	481.1	198.2	61.0
55°	1689.9	1559.9	1375.0	1103.6	808.3	685.5	586.3	369.6	149.6	41.3	22.8
57.5°	763.9	735.0	651.4	512.1	371.7	311.7	210.6	70.2	33.0	20.7	13.4
60°	294.2	265.3	227.1	122.8	52.6	44.3	36.1	23.8	16.5	11.3	8.3
62.5°	42.4	40.3	36.1	28.9	22.8	20.7	17.6	12.4	9.2	7.3	6.2
65°	17.6	17.6	15.5	12.4	10.3	9.2	8.3	6.2	5.2	5.2	5.2
67.5°	7.3	7.3	6.2	5.2	4.2	4.2	4.2	3.1	4.2	4.2	5.2
70°	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1	4.2	4.2	5.2
72.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	5.2	5.2
75°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	5.2	5.2
77.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	5.2
80°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	6.2
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	6.2
85°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	6.2
87.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0
2.5°	1417.4	1351.4	1332.8	1274.9	1226.4	1202.6	1172.7	1105.6	1055.1	988.0	947.7
5°	1825.2	1700.3	1601.1	1480.3	1400.9	1349.3	1268.7	1146.0	1046.8	928.1	843.4
7.5°	2266.0	2037.9	1859.3	1660.0	1545.4	1455.6	1318.3	1141.8	996.2	838.2	707.2
10°	2691.3	2350.7	2069.9	1783.9	1633.2	1508.3	1319.4	1097.3	904.3	705.1	566.8
12.5°	3066.0	2626.3	2230.9	1863.4	1676.5	1520.6	1284.3	1017.9	784.6	580.2	458.4
15°	3378.8	2840.0	2344.4	1893.3	1679.6	1493.8	1211.0	904.3	651.4	469.7	384.0
17.5°	3616.2	2952.4	2379.5	1857.2	1619.7	1417.4	1098.4	760.9	528.6	398.4	323.2
20°	3739.1	2974.1	2329.0	1759.0	1509.3	1301.8	950.8	617.4	448.0	346.8	270.5
22.5°	3754.5	2913.3	2208.2	1618.6	1369.9	1161.4	787.7	515.2	399.5	306.5	238.4
25°	3662.8	2781.1	2035.8	1459.8	1217.1	1000.4	641.0	461.5	363.4	275.6	274.6
27.5°	3466.6	2554.0	1829.2	1274.9	1032.3	813.5	544.1	417.0	324.1	292.1	310.7
30°	3189.9	2262.9	1575.3	1041.6	806.3	625.6	458.4	343.7	285.0	288.1	303.6
32.5°	2815.2	1901.5	1277.0	762.8	577.1	470.7	343.7	234.4	236.3	237.4	250.9
35°	2344.4	1524.8	953.8	513.1	405.7	331.4	194.1	172.4	175.5	176.5	185.8
37.5°	1878.9	1171.7	633.9	341.6	254.9	174.5	120.8	115.6	117.6	116.6	127.0
40°	1439.1	816.5	379.9	169.3	98.0	81.5	74.4	71.2	72.3	73.3	79.4
42.5°	1018.9	442.9	187.8	64.0	51.6	47.4	44.3	42.4	43.4	43.4	47.4
45°	517.1	209.6	64.0	35.1	32.0	28.9	26.8	25.9	25.9	25.9	27.8
47.5°	224.0	69.2	29.9	21.7	19.6	18.6	16.5	15.5	15.5	15.5	16.5
50°	70.2	27.8	18.6	14.4	12.4	11.3	10.3	10.3	10.3	9.2	10.3
52.5°	25.9	17.6	12.4	9.2	8.3	8.3	8.3	7.3	8.3	7.3	8.3
55°	15.5	11.3	8.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
57.5°	10.3	8.3	7.3	7.3	6.2	6.2	7.3	7.3	7.3	7.3	7.3
60°	7.3	7.3	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3
62.5°	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3
65°	5.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3
67.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
70°	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3	9.2
72.5°	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	9.2	9.2	9.2
75°	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	9.2	9.2	9.2
77.5°	6.2	7.3	7.3	8.3	8.3	8.3	8.3	9.2	9.2	9.2	9.2
80°	6.2	7.3	7.3	8.3	8.3	8.3	9.2	9.2	9.2	9.2	10.3
82.5°	6.2	7.3	7.3	8.3	8.3	8.3	9.2	9.2	9.2	9.2	10.3
85°	7.3	7.3	8.3	8.3	8.3	8.3	9.2	9.2	9.2	9.2	10.3
87.5°	7.3	7.3	8.3	8.3	8.3	8.3	9.2	9.2	10.3	9.2	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0
2.5°	894.0	834.1	792.9	777.4	747.4	699.9	672.1	646.2	597.7	587.3	560.6
5°	746.3	650.4	582.3	556.4	522.3	482.0	442.9	417.0	386.1	373.8	355.2
7.5°	588.4	492.4	433.6	412.9	389.2	356.2	321.1	295.2	263.2	246.7	231.3
10°	462.5	391.3	341.6	321.1	296.3	261.2	225.0	191.0	163.2	145.6	142.5
12.5°	375.8	316.9	264.3	242.6	213.7	178.6	152.8	151.7	149.6	148.7	150.7
15°	307.6	250.9	195.1	171.3	163.2	162.1	165.2	168.2	167.2	170.3	172.4
17.5°	253.0	192.0	179.7	180.7	181.7	184.7	189.9	198.2	199.3	204.4	208.5
20°	206.4	203.3	208.5	212.7	215.8	221.9	233.4	243.6	246.7	253.9	262.2
22.5°	234.4	243.6	254.9	260.1	264.3	275.6	288.1	304.6	310.7	320.1	331.4
25°	282.9	298.4	315.9	322.1	328.2	346.8	361.3	380.9	386.1	397.4	408.8
27.5°	323.2	339.7	358.3	366.5	371.7	390.3	402.6	415.0	415.0	421.2	429.4
30°	316.9	330.3	345.8	352.0	354.1	367.5	379.9	384.0	381.9	385.1	391.3
32.5°	263.2	273.5	286.0	291.1	293.2	302.5	312.8	312.8	311.7	311.7	315.9
35°	195.1	202.3	208.5	213.7	216.8	223.0	232.3	231.3	231.3	229.2	232.3
37.5°	131.2	135.2	142.5	144.6	145.6	149.6	156.9	156.9	154.8	155.9	158.0
40°	79.4	84.6	88.8	89.8	91.9	95.0	100.1	100.1	100.1	100.1	101.1
42.5°	47.4	50.6	53.7	53.7	54.7	58.9	61.0	61.0	61.0	61.0	61.9
45°	27.8	28.9	30.9	32.0	32.0	34.1	35.1	35.1	35.1	35.1	36.1
47.5°	16.5	17.6	17.6	18.6	18.6	19.6	20.7	20.7	19.6	19.6	19.6
50°	10.3	10.3	10.3	10.3	11.3	11.3	11.3	11.3	11.3	11.3	10.3
52.5°	8.3	8.3	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2
55°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	6.2	5.2	4.2	3.1
57.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	4.2	3.1
60°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	4.2	3.1
62.5°	8.3	8.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.2	3.1
65°	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1
67.5°	8.3	8.3	8.3	8.3	7.3	7.3	7.3	6.2	5.2	4.2	3.1
70°	9.2	9.2	8.3	8.3	8.3	7.3	7.3	6.2	5.2	5.2	4.2
72.5°	9.2	9.2	8.3	8.3	8.3	8.3	7.3	6.2	6.2	5.2	4.2
75°	9.2	9.2	9.2	9.2	8.3	8.3	7.3	7.3	6.2	5.2	4.2
77.5°	9.2	9.2	9.2	9.2	8.3	8.3	8.3	7.3	6.2	5.2	4.2
80°	9.2	9.2	9.2	9.2	9.2	8.3	8.3	7.3	6.2	5.2	4.2
82.5°	10.3	10.3	9.2	9.2	9.2	8.3	8.3	7.3	6.2	5.2	5.2
85°	10.3	10.3	9.2	9.2	9.2	8.3	8.3	7.3	6.2	6.2	5.2
87.5°	10.3	10.3	9.2	9.2	9.2	8.3	8.3	7.3	6.2	6.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212700

CATALOG NUMBER: LDSQA6A70935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0	1024.0
2.5°	544.1	513.1	502.7	510.0	501.7	495.6	487.2	483.1
5°	340.7	318.0	310.7	312.8	305.6	299.4	291.1	289.0
7.5°	209.6	187.8	179.7	179.7	171.3	164.2	159.0	155.9
10°	140.4	136.2	137.3	138.3	137.3	138.3	135.2	137.3
12.5°	150.7	148.7	150.7	151.7	151.7	153.8	149.6	152.8
15°	175.5	173.4	176.5	178.6	178.6	181.7	177.6	180.7
17.5°	214.8	213.7	218.8	220.9	221.9	227.1	221.9	226.1
20°	271.4	270.5	277.7	280.8	279.8	290.0	282.9	290.0
22.5°	344.8	342.7	353.1	356.2	357.2	370.6	364.4	369.6
25°	418.1	420.2	425.4	430.4	431.5	442.9	433.6	438.8
27.5°	433.6	430.4	433.6	439.8	440.8	446.0	437.7	441.9
30°	392.3	387.1	388.2	395.3	397.4	399.5	392.3	394.3
32.5°	319.0	310.7	310.7	318.0	320.1	323.2	310.7	315.9
35°	235.4	228.2	228.2	233.4	234.4	236.3	227.1	231.3
37.5°	161.1	154.8	156.9	159.0	160.0	162.1	161.1	160.0
40°	103.2	99.1	102.2	102.2	103.2	104.3	104.3	105.3
42.5°	62.9	59.9	61.9	61.9	62.9	62.9	62.9	64.0
45°	36.1	35.1	35.1	36.1	36.1	36.1	35.1	36.1
47.5°	19.6	18.6	19.6	19.6	19.6	19.6	19.6	19.6
50°	10.3	9.2	9.2	9.2	9.2	9.2	9.2	9.2
52.5°	5.2	4.2	4.2	4.2	3.1	4.2	3.1	3.1
55°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
57.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
60°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.1	2.1	2.1	1.0	1.0	0.0	0.0	0.0
72.5°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
75°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	3.1	3.1	2.1	2.1	1.0	1.0	1.0	0.0
80°	4.2	3.1	2.1	2.1	2.1	1.0	1.0	1.0
82.5°	4.2	3.1	2.1	2.1	2.1	1.0	1.0	1.0
85°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
87.5°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)