

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203771

Luminaire Tested: **LE_6B30D010 EC6B30509035 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509035 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2155.6 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203771

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203771

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94
3	104	98	93	90	102	97	92	89	94	91	88		92	89	86		89
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203771

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.3	16.6
10°-20°	688.4	31.9
20°-30°	625.8	29.0
30°-40°	379.4	17.6
40°-50°	86.4	4.0
50°-60°	11.0	0.5
60°-70°	5.0	0.2
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1672.5	77.6
0°-40°	2051.8	95.2
0°-60°	2149.3	99.7
0°-90°	2155.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2155.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4232	
5°	3990	358
15°	2479	688
25°	1357	626
35°	602	379
45°	95	86
55°	11	11
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203771

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4232.1
2.5°	4180.8
5°	3990.0
7.5°	3682.0
10°	3289.6
12.5°	2882.5
15°	2479.1
17.5°	2112.4
20°	1804.4
22.5°	1555.0
25°	1356.9
27.5°	1180.9
30°	1008.5
32.5°	806.8
35°	601.5
37.5°	421.8
40°	278.8
42.5°	172.4
45°	95.4
47.5°	44.0
50°	18.4
52.5°	14.6
55°	11.0
57.5°	11.0
60°	7.4
62.5°	7.4
65°	3.6
67.5°	3.6
70°	3.6
72.5°	3.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)