

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212702

Luminaire Tested: **LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5970.6 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	66	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	47	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48175	48175	48175
5°	132241	44391	18114
10°	289784	36331	6908
15°	442638	27654	8099
20°	512846	20573	12582
25°	559443	16917	20300
30°	624721	15342	20732
35°	635623	10523	14213
40°	646787	4991	7194
45°	647838	2076	3142
50°	547684	898	965
55°	176366	623	158
60°	35030	715	0
65°	3576	846	0
70°	390	1158	0
75°	0	1530	0
80°	0	2554	248
85°	0	5088	494

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.9	2.5
10°-20°	785.6	13.2
20°-30°	1504.2	25.2
30°-40°	1772.2	29.7
40°-50°	1392.0	23.3
50°-60°	339.2	5.7
60°-70°	14.6	0.2
70°-80°	5.5	0.1
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2441.7	40.9
0°-40°	4213.8	70.6
0°-60°	5945.0	99.6
0°-90°	5970.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5970.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1119	1119	1119	1119	1119	
5°	3060	2214	1027	538	419	404
15°	9930	5100	620	178	182	2772
25°	11776	6202	356	373	427	5489
35°	12093	3920	200	258	270	7583
45°	10640	1212	34	47	52	7994
55°	2350	44	8	5	2	2796
65°	35	5	8	5	0	93
75°	0	5	9	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9
2.5°	1917.9	1913.9	1885.9	1911.8	1833.3	1830.1	1795.0	1779.6	1734.2	1690.8	1628.9
5°	3059.7	2992.5	2937.9	2939.8	2789.2	2761.3	2682.8	2603.4	2481.6	2368.0	2214.2
7.5°	4663.8	4584.3	4468.6	4420.1	4132.2	4047.6	3885.4	3673.8	3408.5	3144.3	2859.4
10°	6628.2	6640.5	6490.9	6352.6	5917.0	5745.6	5483.4	5066.4	4563.7	4067.0	3562.4
12.5°	8605.0	8596.6	8418.2	8208.6	7671.8	7430.3	7081.4	6561.1	5895.2	5125.1	4335.5
15°	9930.3	9989.2	9913.8	9746.6	9288.2	9011.6	8618.4	7912.3	7101.0	6165.6	5100.4
17.5°	10762.3	10818.1	10791.3	10660.1	10255.6	9960.3	9632.1	9054.0	8115.6	6939.9	5703.2
20°	11192.9	11280.6	11268.1	11125.7	10820.2	10575.5	10213.2	9677.5	8865.1	7477.7	6093.5
22.5°	11479.8	11546.9	11565.4	11404.4	11088.6	10856.3	10591.0	10048.1	9284.2	7806.0	6248.3
25°	11776.1	11894.7	11778.1	11579.9	11289.8	11066.9	10784.0	10263.8	9484.4	7940.1	6201.8
27.5°	12139.4	12196.2	11931.9	11751.2	11429.2	11187.7	10887.2	10388.7	9519.5	7832.8	5936.6
30°	12565.7	12330.4	12145.6	11787.4	11421.9	11186.6	10881.1	10310.2	9334.8	7476.7	5422.4
32.5°	12495.5	12279.8	12070.2	11691.4	11330.2	11096.8	10756.2	10049.1	8898.1	6881.0	4713.3
35°	12093.0	12139.4	11913.3	11599.5	11190.8	10950.3	10578.6	9677.5	8157.0	6059.4	3920.5
37.5°	11753.3	11855.5	11707.9	11417.9	11002.9	10677.7	10176.0	9080.8	7189.6	5016.8	3169.0
40°	11507.6	11540.8	11461.2	11136.1	10637.5	10167.8	9587.6	8009.3	6015.0	3938.1	2501.2
42.5°	11126.7	11214.4	11074.1	10719.0	9963.3	9431.8	8591.6	6771.7	4672.1	3008.1	1882.8
45°	10639.5	10723.2	10549.8	9959.3	8908.4	8129.0	7104.0	5280.1	3456.0	2217.3	1211.9
47.5°	9844.6	9896.2	9560.8	8744.3	7216.6	6482.6	5431.8	3681.1	2226.6	1239.8	589.4
50°	8176.5	8151.8	7460.2	6455.8	4826.9	4056.8	3233.1	1995.4	1000.2	587.3	368.6
52.5°	5269.7	5212.9	4528.6	3615.0	2444.4	1865.2	1401.8	860.9	521.3	328.2	145.6
55°	2349.5	2327.8	1905.5	1480.3	1000.2	860.9	657.5	422.2	277.7	114.5	44.3
57.5°	871.3	851.6	750.5	629.7	483.1	401.6	319.0	202.3	71.2	38.2	23.8
60°	406.8	405.7	357.1	294.2	204.4	154.8	89.8	47.4	29.9	20.7	13.4
62.5°	130.0	127.0	88.8	65.0	46.4	40.3	32.0	23.8	15.5	11.3	8.3
65°	35.1	35.1	32.0	26.8	21.7	18.6	15.5	11.3	7.3	6.2	5.2
67.5°	13.4	13.4	12.4	11.3	8.3	7.3	6.2	5.2	4.2	5.2	5.2
70°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2
72.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	5.2
75°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	5.2
77.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	5.2
80°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.2	5.2
82.5°	0.0	0.0	1.0	2.1	2.1	2.1	3.1	4.2	4.2	5.2	6.2
85°	0.0	0.0	1.0	2.1	2.1	3.1	3.1	4.2	4.2	5.2	6.2
87.5°	0.0	0.0	1.0	2.1	2.1	3.1	3.1	4.2	4.2	5.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9
2.5°	1583.5	1515.4	1421.4	1366.7	1353.3	1324.4	1273.9	1198.5	1136.5	1076.7	1041.6
5°	2084.2	1923.1	1742.5	1615.5	1563.9	1494.7	1371.9	1244.9	1128.3	1027.1	947.6
7.5°	2614.7	2349.5	2057.2	1822.0	1737.3	1627.9	1427.7	1238.8	1078.7	938.3	832.0
10°	3142.2	2714.8	2318.4	1977.8	1839.5	1690.8	1426.6	1182.0	994.1	831.0	713.3
12.5°	3669.6	3055.5	2510.4	2071.8	1892.2	1704.3	1384.2	1095.2	886.7	720.5	608.0
15°	4156.9	3327.0	2640.6	2103.8	1887.0	1665.0	1298.6	990.0	774.2	620.4	516.1
17.5°	4520.2	3469.4	2670.5	2055.2	1805.4	1559.7	1167.5	866.1	666.9	531.6	425.2
20°	4698.8	3492.2	2599.2	1916.8	1665.0	1410.1	1024.0	747.4	575.0	449.0	359.2
22.5°	4698.8	3384.8	2444.4	1743.4	1489.5	1237.7	885.7	649.4	502.7	391.2	315.9
25°	4520.2	3171.1	2236.9	1543.2	1296.5	1067.3	766.0	576.0	446.9	356.1	293.2
27.5°	4173.4	2875.9	1970.5	1320.3	1106.6	915.6	670.9	509.0	404.7	321.0	322.0
30°	3696.6	2513.6	1665.0	1084.9	911.4	752.6	564.6	426.3	324.1	308.6	318.0
32.5°	3145.4	2080.0	1319.2	841.2	706.0	592.5	429.4	301.5	258.0	260.1	270.4
35°	2579.6	1637.2	993.1	623.5	525.5	429.4	281.8	198.2	196.2	200.2	207.5
37.5°	2036.7	1225.2	718.5	456.3	353.1	264.3	151.7	136.2	136.2	140.4	144.6
40°	1525.7	869.2	494.4	270.4	171.3	120.8	95.9	88.8	87.8	88.8	94.0
42.5°	1047.8	550.2	294.2	108.4	82.6	70.2	60.8	55.8	54.7	55.8	58.9
45°	588.4	338.5	114.5	57.8	49.5	44.3	38.2	35.1	34.1	34.1	36.1
47.5°	368.6	134.2	51.6	36.1	30.9	28.9	24.8	22.8	21.7	21.7	22.8
50°	141.4	52.6	32.0	23.8	20.7	18.6	16.5	14.4	13.4	13.4	14.4
52.5°	48.5	30.9	20.7	15.5	13.4	12.4	10.3	9.2	9.2	9.2	9.2
55°	26.8	18.6	12.4	9.2	8.3	8.3	8.3	8.3	8.3	8.3	8.3
57.5°	16.5	11.3	8.3	7.3	7.3	7.3	7.3	7.3	7.3	8.3	8.3
60°	9.2	7.3	6.2	6.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3
62.5°	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3
65°	5.2	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3
67.5°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3	8.3
70°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3	8.3	9.2	9.2
72.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.2	9.2	9.2
75°	6.2	6.2	6.2	7.3	7.3	7.3	8.3	9.2	9.2	9.2	9.2
77.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.2	9.2	9.2	9.2
80°	6.2	6.2	7.3	7.3	8.3	8.3	9.2	9.2	9.2	10.3	10.3
82.5°	6.2	6.2	7.3	8.3	8.3	8.3	9.2	9.2	10.3	10.3	10.3
85°	6.2	7.3	7.3	8.3	8.3	8.3	9.2	9.2	10.3	10.3	10.3
87.5°	6.2	7.3	7.3	8.3	8.3	8.3	9.2	9.2	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9
2.5°	995.2	951.7	908.4	876.3	860.9	845.4	811.3	767.0	748.4	721.5	706.0
5°	867.1	793.8	736.1	697.8	675.1	645.2	605.9	562.6	537.8	510.0	491.4
7.5°	735.0	649.4	593.6	558.5	535.7	498.6	449.0	397.4	367.5	336.6	314.9
10°	619.3	537.8	474.9	434.6	405.7	362.3	312.8	276.6	250.9	224.0	202.3
12.5°	517.1	429.4	362.3	328.2	308.6	267.4	226.1	185.8	170.3	165.1	165.1
15°	419.1	339.6	282.9	253.9	233.4	188.9	180.7	178.6	177.6	176.5	178.6
17.5°	341.6	274.6	214.8	200.2	198.2	197.2	198.2	198.2	199.3	202.3	207.5
20°	286.9	225.0	220.9	221.9	221.9	226.1	231.3	235.3	239.5	244.7	253.9
22.5°	254.9	253.9	261.2	262.2	267.4	273.5	282.9	289.0	299.4	304.5	318.0
25°	294.2	301.5	314.9	319.0	327.2	337.6	352.0	360.2	372.7	378.8	394.3
27.5°	333.4	344.8	361.3	366.5	373.6	390.1	400.5	407.7	413.9	418.1	427.3
30°	330.3	340.6	357.1	358.2	368.6	379.9	386.1	392.2	396.4	395.3	400.5
32.5°	279.8	289.0	304.5	304.5	315.9	325.1	328.2	333.4	333.4	333.4	335.5
35°	214.8	220.9	231.3	234.3	243.6	249.9	251.8	258.0	258.0	256.0	256.0
37.5°	148.6	156.9	164.2	166.1	172.4	176.5	181.7	182.6	180.7	181.7	181.7
40°	97.0	102.2	107.4	108.4	113.5	116.6	121.8	121.8	122.8	121.8	123.9
42.5°	59.9	64.0	67.1	69.2	71.2	73.3	76.4	77.5	78.4	77.5	79.4
45°	37.2	39.3	41.3	42.4	43.3	44.3	47.4	47.4	47.4	47.4	48.5
47.5°	22.8	23.8	24.8	24.8	25.9	26.8	27.8	27.8	27.8	27.8	28.9
50°	13.4	14.4	14.4	14.4	15.5	15.5	16.5	16.5	16.5	15.5	16.5
52.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.3	9.2
55°	8.3	8.3	7.3	7.3	7.3	7.3	7.3	6.2	5.2	5.2	4.2
57.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.2	3.1
60°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	4.2	3.1
62.5°	8.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	4.2	3.1
65°	8.3	8.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.2	3.1
67.5°	8.3	8.3	8.3	7.3	8.3	7.3	6.2	6.2	5.2	4.2	4.2
70°	9.2	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.2	4.2
72.5°	9.2	9.2	8.3	8.3	8.3	7.3	7.3	6.2	5.2	5.2	4.2
75°	9.2	9.2	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.2
77.5°	9.2	9.2	9.2	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.2
80°	9.2	9.2	9.2	9.2	9.2	8.3	8.3	7.3	6.2	5.2	4.2
82.5°	10.3	9.2	9.2	9.2	9.2	8.3	8.3	7.3	6.2	5.2	5.2
85°	10.3	10.3	9.2	9.2	9.2	8.3	8.3	7.3	6.2	6.2	5.2
87.5°	10.3	9.2	9.2	9.2	9.2	8.3	8.3	7.3	6.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212702

CATALOG NUMBER: LDSQA6A70935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9	1118.9
2.5°	690.6	682.4	682.4	667.8	665.9	654.4	663.8	657.5
5°	470.7	457.3	453.2	438.8	433.6	420.2	424.3	419.1
7.5°	296.3	282.9	278.7	268.4	262.2	251.8	252.8	249.9
10°	180.7	168.2	165.1	162.1	159.0	158.0	159.0	158.0
12.5°	164.2	163.2	161.1	162.1	160.0	161.1	162.1	161.1
15°	178.6	180.7	178.6	179.7	178.6	180.7	181.7	181.7
17.5°	209.6	213.7	211.6	214.8	213.7	218.8	218.8	218.8
20°	257.0	264.3	262.2	266.4	266.4	272.5	272.5	274.6
22.5°	323.0	332.4	331.4	340.6	338.5	345.8	345.8	347.9
25°	402.6	411.8	412.9	419.1	418.1	425.2	425.2	427.3
27.5°	435.6	440.8	439.8	442.8	443.8	448.0	451.1	449.0
30°	408.7	412.9	411.8	413.9	413.9	417.0	420.2	417.0
32.5°	343.7	346.8	346.8	351.0	347.9	348.9	354.1	351.0
35°	263.2	265.3	263.2	265.3	266.4	266.4	271.4	270.4
37.5°	187.8	188.9	188.9	192.0	188.9	188.9	194.1	195.1
40°	126.0	127.0	126.0	130.0	128.0	128.0	131.0	128.0
42.5°	80.5	81.5	80.5	83.6	81.5	83.6	84.6	85.7
45°	49.5	49.5	48.5	50.6	49.5	50.6	51.6	51.6
47.5°	28.9	28.9	27.8	29.9	28.9	28.9	28.9	29.9
50°	15.5	15.5	15.5	16.5	15.5	15.5	15.5	14.4
52.5°	8.3	8.3	7.3	8.3	7.3	7.3	7.3	7.3
55°	4.2	3.1	3.1	3.1	2.1	2.1	2.1	2.1
57.5°	3.1	2.1	2.1	1.0	1.0	1.0	0.0	0.0
60°	2.1	2.1	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.1	2.1	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.1	2.1	2.1	1.0	1.0	0.0	0.0	0.0
70°	3.1	2.1	2.1	1.0	1.0	0.0	0.0	0.0
72.5°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
75°	3.1	3.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	4.2	3.1	2.1	2.1	1.0	1.0	0.0	0.0
80°	4.2	3.1	2.1	2.1	2.1	1.0	1.0	1.0
82.5°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
85°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
87.5°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)