

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219659

Luminaire Tested: **LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6350.3 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	51245	51245	51245
5°	140651	47214	19263
10°	308212	38640	7345
15°	470791	29415	8612
20°	545460	21883	13379
25°	595021	18000	21597
30°	664455	16317	22054
35°	676048	11196	15122
40°	687929	5300	7650
45°	689042	2204	3343
50°	582522	965	1032
55°	187581	661	165
60°	37252	758	0
65°	3800	897	0
70°	403	1246	0
75°	0	1647	0
80°	0	2703	248
85°	0	5385	494

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.5
10°-20°	835.6	13.2
20°-30°	1599.8	25.2
30°-40°	1884.9	29.7
40°-50°	1480.5	23.3
50°-60°	360.8	5.7
60°-70°	15.5	0.2
70°-80°	5.8	0.1
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2597.0	40.9
0°-40°	4481.8	70.6
0°-60°	6323.1	99.6
0°-90°	6350.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6350.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1190	1190	1190	1190	1190	
5°	3254	2355	1092	572	446	430
15°	10562	5425	660	189	193	2949
25°	12525	6596	379	396	455	5838
35°	12862	4170	213	274	288	8065
45°	11316	1289	36	50	55	8502
55°	2499	47	9	6	2	2974
65°	37	6	9	6	0	99
75°	0	6	10	7	0	0
85°	0	7	11	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2
2.5°	2039.9	2035.6	2005.8	2033.3	1949.9	1946.6	1909.3	1892.8	1844.5	1798.5	1732.4
5°	3254.3	3182.9	3124.6	3126.9	2966.6	2937.0	2853.6	2768.9	2639.4	2518.7	2355.1
7.5°	4960.4	4875.8	4752.8	4701.3	4394.9	4304.9	4132.5	3907.4	3625.2	3344.3	3041.2
10°	7049.7	7062.8	6903.7	6756.7	6293.2	6111.0	5832.1	5388.6	4853.8	4325.8	3788.8
12.5°	9152.2	9143.5	8953.5	8730.7	8159.7	7902.9	7531.7	6978.4	6270.2	5451.2	4611.3
15°	10561.9	10624.5	10544.4	10366.5	9879.1	9584.7	9166.5	8415.5	7552.6	6557.9	5424.7
17.5°	11446.9	11506.1	11477.6	11338.2	10907.8	10593.8	10244.6	9629.8	8631.8	7381.3	6066.0
20°	11904.7	11998.1	11984.8	11833.3	11508.3	11248.1	10862.8	10292.9	9428.8	7953.3	6481.0
22.5°	12209.9	12281.3	12301.0	12129.7	11793.8	11546.7	11264.6	10687.1	9874.6	8302.5	6645.6
25°	12525.0	12651.4	12527.2	12316.4	12007.9	11770.8	11470.0	10916.6	10087.7	8445.1	6596.3
27.5°	12911.5	12971.9	12690.8	12498.7	12156.1	11899.3	11579.8	11049.4	10125.0	8331.0	6314.2
30°	13364.9	13114.5	12918.0	12537.1	12148.4	11898.1	11573.1	10966.0	9928.5	7952.2	5767.3
32.5°	13290.3	13060.8	12838.0	12435.1	12050.7	11802.5	11440.2	10688.3	9464.0	7318.7	5013.1
35°	12862.1	12911.5	12671.0	12337.3	11902.5	11646.6	11251.4	10292.9	8675.8	6444.7	4169.9
37.5°	12500.9	12609.6	12452.5	12144.1	11702.6	11356.8	10823.3	9658.4	7646.9	5335.8	3370.5
40°	12239.6	12274.7	12190.2	11844.4	11314.1	10814.5	10197.4	8518.6	6397.6	4188.5	2660.2
42.5°	11834.5	11927.8	11778.5	11400.7	10597.1	10031.7	9137.9	7202.4	4969.1	3199.4	2002.6
45°	11316.2	11405.2	11220.7	10592.6	9474.9	8646.0	7555.8	5615.8	3675.8	2358.3	1289.0
47.5°	10470.8	10525.7	10168.9	9300.4	7675.6	6894.9	5777.2	3915.1	2368.2	1318.6	626.9
50°	8696.6	8670.3	7934.6	6866.4	5133.9	4314.8	3438.7	2122.2	1063.9	624.7	392.0
52.5°	5604.9	5544.4	4816.4	3845.0	2599.9	1983.9	1490.9	915.7	554.4	349.1	154.8
55°	2498.9	2475.8	2026.8	1574.5	1063.9	915.7	699.4	449.0	295.3	121.8	47.2
57.5°	926.6	905.8	798.2	669.8	513.8	427.1	339.2	215.3	75.7	40.6	25.3
60°	432.6	431.4	379.9	312.8	217.4	164.6	95.5	50.5	31.8	21.9	14.4
62.5°	138.3	135.1	94.3	69.3	49.3	42.8	34.1	25.3	16.5	12.1	8.8
65°	37.3	37.3	34.1	28.5	23.1	19.8	16.5	12.1	7.7	6.7	5.5
67.5°	14.4	14.4	13.1	12.1	8.8	7.7	6.7	5.5	4.4	5.5	5.5
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.4	4.4	5.5
72.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.4	5.5	5.5
75°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.4	5.5	5.5
77.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.4	5.5	5.5
80°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.4	5.5	5.5
82.5°	0.0	0.0	1.0	2.2	2.2	2.2	3.2	4.4	4.4	5.5	6.7
85°	0.0	0.0	1.0	2.2	2.2	3.2	3.2	4.4	4.4	5.5	6.7
87.5°	0.0	0.0	1.0	2.2	2.2	3.2	3.2	4.4	4.4	5.5	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2
2.5°	1684.2	1611.7	1511.8	1453.7	1439.4	1408.7	1354.8	1274.6	1208.8	1145.1	1107.8
5°	2216.8	2045.5	1853.3	1718.3	1663.4	1589.8	1459.1	1324.1	1200.1	1092.4	1008.0
7.5°	2781.1	2498.9	2188.1	1937.8	1847.8	1731.4	1518.4	1317.6	1147.3	998.1	884.8
10°	3342.0	2887.5	2465.9	2103.6	1956.4	1798.5	1517.4	1257.0	1057.3	883.8	758.6
12.5°	3903.1	3249.8	2670.1	2203.4	2012.4	1812.6	1472.3	1164.9	943.2	766.3	646.7
15°	4421.4	3538.6	2808.5	2237.6	2007.0	1771.0	1381.2	1052.9	823.5	659.9	548.9
17.5°	4807.7	3690.1	2840.2	2185.9	1920.3	1658.9	1241.7	921.1	709.3	565.4	452.4
20°	4997.6	3714.3	2764.5	2038.8	1771.0	1499.8	1089.2	794.9	611.5	477.6	382.1
22.5°	4997.6	3600.1	2599.9	1854.4	1584.2	1316.4	942.0	690.6	534.8	416.1	335.9
25°	4807.7	3372.8	2379.1	1641.3	1379.0	1135.3	814.7	612.6	475.4	378.9	311.8
27.5°	4438.9	3058.7	2095.9	1404.2	1176.9	973.9	713.5	541.2	430.4	341.5	342.6
30°	3931.6	2673.4	1771.0	1154.0	969.5	800.4	600.6	453.4	344.8	328.2	338.1
32.5°	3345.4	2212.3	1403.1	894.7	751.1	630.1	456.7	320.5	274.5	276.6	287.7
35°	2743.7	1741.3	1056.2	663.1	558.8	456.7	299.7	210.8	208.6	213.0	220.7
37.5°	2166.2	1303.2	764.2	485.3	375.4	281.1	161.4	145.0	145.0	149.2	153.7
40°	1622.7	924.5	525.9	287.7	182.2	128.4	102.1	94.3	93.3	94.3	99.9
42.5°	1114.4	585.1	312.8	115.3	87.9	74.7	64.8	59.4	58.1	59.4	62.6
45°	625.9	360.2	121.8	61.6	52.7	47.2	40.6	37.3	36.2	36.2	38.4
47.5°	392.0	142.8	54.9	38.4	33.0	30.7	26.4	24.2	23.1	23.1	24.2
50°	150.5	56.0	34.1	25.3	21.9	19.8	17.6	15.4	14.4	14.4	15.4
52.5°	51.7	33.0	21.9	16.5	14.4	13.1	10.9	9.9	9.9	9.9	9.9
55°	28.5	19.8	13.1	9.9	8.8	8.8	8.8	8.8	8.8	8.8	8.8
57.5°	17.6	12.1	8.8	7.7	7.7	7.7	7.7	7.7	7.7	8.8	8.8
60°	9.9	7.7	6.7	6.7	6.7	6.7	7.7	7.7	7.7	8.8	8.8
62.5°	6.7	6.7	6.7	6.7	6.7	6.7	7.7	7.7	8.8	8.8	8.8
65°	5.5	5.5	5.5	6.7	6.7	6.7	7.7	7.7	8.8	8.8	8.8
67.5°	5.5	5.5	6.7	6.7	6.7	7.7	7.7	8.8	8.8	8.8	8.8
70°	5.5	6.7	6.7	7.7	7.7	7.7	8.8	8.8	8.8	9.9	9.9
72.5°	5.5	6.7	6.7	7.7	7.7	7.7	8.8	8.8	9.9	9.9	9.9
75°	6.7	6.7	6.7	7.7	7.7	7.7	8.8	9.9	9.9	9.9	9.9
77.5°	6.7	6.7	7.7	7.7	7.7	8.8	8.8	9.9	9.9	9.9	9.9
80°	6.7	6.7	7.7	7.7	8.8	8.8	9.9	9.9	9.9	10.9	10.9
82.5°	6.7	6.7	7.7	8.8	8.8	8.8	9.9	9.9	10.9	10.9	10.9
85°	6.7	7.7	7.7	8.8	8.8	8.8	9.9	9.9	10.9	10.9	10.9
87.5°	6.7	7.7	7.7	8.8	8.8	8.8	9.9	9.9	10.9	10.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2
2.5°	1058.3	1012.2	966.2	932.0	915.7	899.2	863.0	815.8	795.9	767.4	751.1
5°	922.2	844.3	782.8	742.2	718.0	686.2	644.5	598.4	572.0	542.5	522.5
7.5°	781.8	690.6	631.3	593.9	569.9	530.3	477.6	422.7	390.8	357.9	334.9
10°	658.7	572.0	505.1	462.3	431.4	385.3	332.7	294.2	266.8	238.3	215.3
12.5°	550.0	456.7	385.3	349.1	328.2	284.3	240.3	197.7	181.2	175.7	175.7
15°	445.7	361.3	300.8	270.1	248.1	200.9	192.1	189.9	188.9	187.8	189.9
17.5°	363.4	292.0	228.4	213.0	210.8	209.7	210.8	210.8	211.8	215.3	220.7
20°	305.2	239.3	234.9	236.1	236.1	240.3	246.0	250.4	254.7	260.2	270.1
22.5°	271.2	270.1	277.9	278.9	284.3	291.0	300.8	307.4	318.4	324.0	338.1
25°	312.8	320.5	334.9	339.2	348.0	359.0	374.4	383.1	396.4	402.9	419.4
27.5°	354.6	366.7	384.3	389.8	397.5	415.1	426.0	433.7	440.2	444.7	454.6
30°	351.4	362.3	379.9	381.0	392.0	403.9	410.6	417.2	421.5	420.5	426.0
32.5°	297.5	307.4	324.0	324.0	335.9	345.8	349.1	354.6	354.6	354.6	356.8
35°	228.4	234.9	246.0	249.2	259.1	265.6	267.8	274.5	274.5	272.3	272.3
37.5°	158.1	166.8	174.5	176.7	183.4	187.8	193.2	194.3	192.1	193.2	193.2
40°	103.2	108.7	114.2	115.3	120.7	124.1	129.5	129.5	130.6	129.5	131.7
42.5°	63.6	68.0	71.3	73.5	75.7	78.0	81.2	82.4	83.4	82.4	84.4
45°	39.5	41.8	43.9	45.0	46.1	47.2	50.5	50.5	50.5	50.5	51.7
47.5°	24.2	25.3	26.4	26.4	27.5	28.5	29.6	29.6	29.6	29.6	30.7
50°	14.4	15.4	15.4	15.4	16.5	16.5	17.6	17.6	17.6	16.5	17.6
52.5°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	8.8	9.9
55°	8.8	8.8	7.7	7.7	7.7	7.7	7.7	6.7	5.5	5.5	4.4
57.5°	7.7	7.7	7.7	7.7	7.7	6.7	6.7	5.5	5.5	4.4	3.2
60°	7.7	7.7	7.7	7.7	7.7	6.7	6.7	5.5	4.4	4.4	3.2
62.5°	8.8	7.7	7.7	7.7	7.7	6.7	6.7	5.5	4.4	4.4	3.2
65°	8.8	8.8	7.7	7.7	7.7	6.7	6.7	5.5	5.5	4.4	3.2
67.5°	8.8	8.8	8.8	7.7	8.8	7.7	6.7	6.7	5.5	4.4	4.4
70°	9.9	8.8	8.8	8.8	8.8	7.7	7.7	6.7	5.5	4.4	4.4
72.5°	9.9	9.9	8.8	8.8	8.8	7.7	7.7	6.7	5.5	5.5	4.4
75°	9.9	9.9	8.8	8.8	8.8	7.7	7.7	6.7	6.7	5.5	4.4
77.5°	9.9	9.9	9.9	8.8	8.8	8.8	7.7	7.7	6.7	5.5	4.4
80°	9.9	9.9	9.9	9.9	9.9	8.8	8.8	7.7	6.7	5.5	4.4
82.5°	10.9	9.9	9.9	9.9	9.9	8.8	8.8	7.7	6.7	5.5	5.5
85°	10.9	10.9	9.9	9.9	9.9	8.8	8.8	7.7	6.7	6.7	5.5
87.5°	10.9	9.9	9.9	9.9	9.9	8.8	8.8	7.7	6.7	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219659

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2
2.5°	734.6	725.7	725.7	710.3	708.1	696.2	706.1	699.4
5°	500.7	486.3	481.9	466.5	461.1	446.8	451.3	445.7
7.5°	315.1	300.8	296.5	285.4	278.9	267.8	269.0	265.6
10°	192.1	179.0	175.7	172.4	169.1	168.0	169.1	168.0
12.5°	174.5	173.5	171.3	172.4	170.2	171.3	172.4	171.3
15°	189.9	192.1	189.9	191.0	189.9	192.1	193.2	193.2
17.5°	222.8	227.2	225.1	228.4	227.2	232.9	232.9	232.9
20°	273.4	281.1	278.9	283.3	283.3	289.8	289.8	292.0
22.5°	343.7	353.6	352.5	362.3	360.2	367.7	367.7	370.0
25°	428.2	438.0	439.1	445.7	444.7	452.4	452.4	454.6
27.5°	463.3	468.8	467.7	471.0	472.2	476.4	479.9	477.6
30°	434.8	439.1	438.0	440.2	440.2	443.6	446.8	443.6
32.5°	365.6	369.0	369.0	373.3	370.0	371.1	376.5	373.3
35°	280.0	282.2	280.0	282.2	283.3	283.3	288.8	287.7
37.5°	199.8	200.9	200.9	204.2	200.9	200.9	206.4	207.6
40°	134.0	135.1	134.0	138.3	136.1	136.1	139.4	136.1
42.5°	85.6	86.8	85.6	88.9	86.8	88.9	90.1	91.1
45°	52.7	52.7	51.7	53.8	52.7	53.8	54.9	54.9
47.5°	30.7	30.7	29.6	31.8	30.7	30.7	30.7	31.8
50°	16.5	16.5	16.5	17.6	16.5	16.5	16.5	15.4
52.5°	8.8	8.8	7.7	8.8	7.7	7.7	7.7	7.7
55°	4.4	3.2	3.2	3.2	2.2	2.2	2.2	2.2
57.5°	3.2	2.2	2.2	1.0	1.0	1.0	0.0	0.0
60°	2.2	2.2	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.2	2.2	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.2	2.2	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.2	2.2	2.2	1.0	1.0	0.0	0.0	0.0
70°	3.2	2.2	2.2	1.0	1.0	0.0	0.0	0.0
72.5°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
75°	3.2	3.2	2.2	2.2	1.0	1.0	0.0	0.0
77.5°	4.4	3.2	2.2	2.2	1.0	1.0	0.0	0.0
80°	4.4	3.2	2.2	2.2	2.2	1.0	1.0	1.0
82.5°	4.4	3.2	3.2	2.2	2.2	1.0	1.0	1.0
85°	4.4	3.2	3.2	2.2	2.2	1.0	1.0	1.0
87.5°	4.4	3.2	3.2	2.2	2.2	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)