

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204616

Luminaire Tested: **LE_6B50D010R EC6B30508035 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508035 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7442.5 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204616
CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204616

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																																				
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																																				
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																																				
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																																				
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																																				
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																																				
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																																				
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																																				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																																				
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204616

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.1	3.8
10°-20°	809.9	10.9
20°-30°	1219.7	16.4
30°-40°	1451.3	19.5
40°-50°	1448.7	19.5
50°-60°	1178.1	15.8
60°-70°	724.9	9.7
70°-80°	280.8	3.8
80°-90°	45.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2313.7	31.1
0°-40°	3765.1	50.6
0°-60°	6391.9	85.9
0°-90°	7442.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7442.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2999	
5°	2990	284
15°	2875	810
25°	2655	1220
35°	2324	1451
45°	1883	1449
55°	1318	1178
65°	728	725
75°	256	281
85°	35	45
90°	0	



TEST NUMBER: P204616

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2998.6
2.5°	3003.0
5°	2989.8
7.5°	2972.1
10°	2950.1
12.5°	2910.4
15°	2875.1
17.5°	2822.2
20°	2764.9
22.5°	2712.0
25°	2654.6
27.5°	2575.2
30°	2495.9
32.5°	2421.0
35°	2323.9
37.5°	2218.1
40°	2121.1
42.5°	2002.0
45°	1883.0
47.5°	1755.1
50°	1618.4
52.5°	1477.2
55°	1318.5
57.5°	1164.1
60°	1014.2
62.5°	868.8
65°	727.6
67.5°	595.4
70°	471.9
72.5°	357.2
75°	255.8
77.5°	167.6
80°	101.4
82.5°	61.8
85°	35.2
87.5°	17.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)