

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205230

Luminaire Tested: **LE_6B50D010R EC6B30508035 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508035 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6924.5 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205230

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P205230

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWL11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																																				
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																																				
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																																				
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																																				
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																																				
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																																				
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																																				
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																																				
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																																				
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205230

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWL11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.3	6.0
10°-20°	1254.3	18.1
20°-30°	1890.8	27.3
30°-40°	1935.3	27.9
40°-50°	1127.5	16.3
50°-60°	259.1	3.7
60°-70°	31.8	0.5
70°-80°	8.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3562.5	51.4
0°-40°	5497.8	79.4
0°-60°	6884.4	99.4
0°-90°	6924.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6924.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4326	
5°	4349	417
15°	4444	1254
25°	4145	1891
35°	3140	1935
45°	1452	1128
55°	251	259
65°	24	32
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P205230

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWL11

CANDELA DISTRIBUTION (FULL):

	0°
0°	4325.9
2.5°	4318.0
5°	4349.4
7.5°	4380.9
10°	4420.1
12.5°	4427.9
15°	4443.6
17.5°	4427.9
20°	4388.6
22.5°	4263.0
25°	4145.2
27.5°	3956.9
30°	3713.5
32.5°	3462.2
35°	3140.4
37.5°	2779.2
40°	2378.9
42.5°	1931.4
45°	1452.4
47.5°	1012.8
50°	667.4
52.5°	424.0
55°	251.2
57.5°	133.5
60°	70.6
62.5°	39.2
65°	23.5
67.5°	23.5
70°	15.8
72.5°	7.9
75°	7.9
77.5°	7.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)