

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P209000

Luminaire Tested: **LDSQA6A75927D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P209000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A75927D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5374.9 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P209000

CATALOG NUMBER: LDSQA6A75927D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P209000

CATALOG NUMBER: LDSQA6A75927D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	108	107	106	105	104		103	101	100		99
2	110	107	103	101	108	105	102	100	102	99	97		99	97	95		96
3	107	101	98	94	105	100	97	94	98	95	92		95	93	91		93
4	103	97	93	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	88	84	90	87	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	92	85	81	77	91	85	80	77	84	80	77		82	79	76		81
8	89	82	77	74	88	82	77	74	81	77	74		80	76	74		79
9	86	79	74	71	85	79	74	71	78	74	71		77	73	71		76
10	84	76	72	69	83	76	71	69	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	598956
5°	521451
10°	471147
15°	430501
20°	315238
25°	155556
30°	34538
35°	6996
40°	1169
45°	347
50°	60
55°	68
60°	78
65°	92
70°	113
75°	0
80°	0
85°	0



TEST NUMBER: P209000

CATALOG NUMBER: LDSQA6A75927D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1118.4	20.8
10°-20°	2595.0	48.3
20°-30°	1522.2	28.3
30°-40°	131.7	2.5
40°-50°	5.7	0.1
50°-60°	0.8	0.0
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5235.6	97.4
0°-40°	5367.3	99.9
0°-60°	5373.9	100.0
0°-90°	5374.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5374.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13911	
5°	12065	###
15°	9658	2595
25°	3274	1522
35°	133	132
45°	6	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P209000

CATALOG NUMBER: LDSQA6A75927D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	13911.2
2.5°	13072.1
5°	12065.0
7.5°	11394.8
10°	10776.5
12.5°	10262.1
15°	9658.0
17.5°	8614.1
20°	6880.1
22.5°	4975.3
25°	3274.4
27.5°	1845.3
30°	694.7
32.5°	358.7
35°	133.1
37.5°	40.6
40°	20.8
42.5°	11.3
45°	5.7
47.5°	2.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)