

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208933

Luminaire Tested: **LDSQA6A75830D010TE LARH20SP 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26676)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A75830D010TE LARH20SP 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5928.9 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.48
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208933

CATALOG NUMBER: LDSQA6A75830D010TE LARH20SP 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208933

CATALOG NUMBER: LDSQA6A75830D010TE LARH20SP 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	101	103	100	98		100	98	96		97
3	107	103	99	96	106	101	98	95	99	96	94		97	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		94	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	96	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	87	83	81	86	83	80		85	82	80		84
8	92	85	81	78	91	85	81	78	84	80	78		83	80	77		82
9	89	82	78	75	88	82	78	75	81	78	75		80	77	75		80
10	87	80	76	73	86	80	76	73	79	75	73		78	75	73		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1030585
5°	895966
10°	607085
15°	420837
20°	293273
25°	168758
30°	13235
35°	1088
40°	545
45°	371
50°	328
55°	270
60°	310
65°	367
70°	302
75°	200
80°	298
85°	0



TEST NUMBER: P208933

CATALOG NUMBER: LDSQA6A75830D010TE LARH20SP 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1764.2	29.8
10°-20°	2657.3	44.8
20°-30°	1463.9	24.7
30°-40°	30.3	0.5
40°-50°	4.9	0.1
50°-60°	3.7	0.1
60°-70°	3.1	0.1
70°-80°	1.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5885.4	99.3
0°-40°	5915.7	99.8
0°-60°	5924.2	99.9
0°-90°	5928.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5928.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23936	
5°	20730	###
15°	9441	2657
25°	3552	1464
35°	21	30
45°	6	5
55°	4	4
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P208933

CATALOG NUMBER: LDSQA6A75830D010TE LARH20SP 6LSQA1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	23936.1
2.5°	23220.0
5°	20730.3
7.5°	17620.5
10°	13885.8
12.5°	11435.0
15°	9441.2
17.5°	7959.2
20°	6400.7
22.5°	5006.3
25°	3552.3
27.5°	1516.0
30°	266.2
32.5°	34.0
35°	20.7
37.5°	13.4
40°	9.7
42.5°	7.3
45°	6.1
47.5°	4.9
50°	4.9
52.5°	4.9
55°	3.6
57.5°	3.6
60°	3.6
62.5°	3.6
65°	3.6
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)