

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204114

Luminaire Tested: **LE_6B60D010R EC6B60708040 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708040 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5581.2 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204114

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204114

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	103	109	106	103	101		102	100	98		98	97	95		95	93	92
2	105	99	94	90	102	97	92	89		94	90	87		91	87	85		88	85	83
3	98	90	84	79	96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	83	76	71	90	82	76	71		80	74	70		77	73	69		75	71	68
5	87	77	70	64	85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	59	80	70	63	59		68	63	58		67	62	58		66	61	57
7	77	66	59	54	75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50	71	61	54	50		60	54	49		59	53	49		58	53	49
9	69	58	51	46	67	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	47	43	64	54	47	43		53	47	43		52	46	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204114

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	425.0	7.6
10°-20°	1126.6	20.2
20°-30°	1504.1	26.9
30°-40°	1213.4	21.7
40°-50°	581.6	10.4
50°-60°	344.7	6.2
60°-70°	229.1	4.1
70°-80°	122.8	2.2
80°-90°	33.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3055.8	54.8
0°-40°	4269.2	76.5
0°-60°	5195.5	93.1
0°-90°	5581.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5581.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4577	
5°	4524	425
15°	4010	1127
25°	3291	1504
35°	1943	1213
45°	718	582
55°	381	345
65°	231	229
75°	115	123
85°	27	34
90°	0	



TEST NUMBER: P204114

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4577.2
2.5°	4577.2
5°	4524.0
7.5°	4435.2
10°	4311.1
12.5°	4178.0
15°	4009.5
17.5°	3849.9
20°	3672.4
22.5°	3486.1
25°	3291.0
27.5°	3087.0
30°	2794.2
32.5°	2386.1
35°	1942.6
37.5°	1534.6
40°	1188.6
42.5°	922.5
45°	718.5
47.5°	567.8
50°	479.0
52.5°	425.8
55°	381.4
57.5°	346.0
60°	301.6
62.5°	266.1
65°	230.6
67.5°	195.1
70°	168.5
72.5°	141.9
75°	115.4
77.5°	88.8
80°	71.0
82.5°	53.2
85°	26.6
87.5°	8.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)