

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219661

Luminaire Tested: **LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7444.4 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 82.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	57815	57815	57815
5°	148310	52595	16380
10°	289098	40423	7870
15°	518963	27453	10555
20°	770499	20838	17430
25°	875790	17169	27331
30°	949374	18773	25713
35°	999988	12163	15942
40°	1021619	5401	7762
45°	922719	2064	2880
50°	607406	817	817
55°	166337	713	0
60°	33222	818	0
65°	2353	1100	0
70°	340	1360	0
75°	0	2030	0
80°	0	3025	347
85°	0	6027	692



TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.5	2.2
10°-20°	873.9	11.7
20°-30°	1980.6	26.6
30°-40°	2377.5	31.9
40°-50°	1675.6	22.5
50°-60°	345.7	4.6
60°-70°	12.2	0.2
70°-80°	7.3	0.1
80°-90°	7.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3019.0	40.6
0°-40°	5396.4	72.5
0°-60°	7417.7	99.6
0°-90°	7444.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7444.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1343	1343	1343	1343	1343	
5°	3432	2500	1217	506	379	422
15°	11643	5122	616	219	237	3455
25°	18435	6196	361	506	575	8508
35°	19025	4338	231	303	303	11827
45°	15154	1488	34	46	47	11145
55°	2216	30	10	7	0	2920
65°	23	7	11	7	0	68
75°	0	7	12	8	0	0
85°	0	8	12	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8
2.5°	2288.9	2220.0	2247.0	2167.2	2149.6	2134.7	2149.6	2062.9	2014.2	1952.0	1902.0
5°	3431.5	3348.9	3367.8	3228.4	3164.8	3121.5	3113.4	2934.8	2800.7	2653.0	2500.2
7.5°	4777.0	4698.4	4687.7	4471.1	4339.7	4265.2	4234.3	3978.3	3746.9	3484.3	3197.4
10°	6612.5	6433.9	6378.3	6064.3	5813.8	5655.4	5460.5	5051.8	4645.7	4249.0	3883.6
12.5°	8748.6	8651.0	8512.9	7959.3	7520.8	7296.1	7005.1	6366.0	5751.6	5096.4	4484.6
15°	11642.6	11296.2	11060.5	10260.5	9554.0	9207.4	8782.4	7805.1	6876.5	6046.7	5122.2
17.5°	14470.5	14289.0	13920.7	12882.5	11794.2	11247.4	10613.8	9286.0	7974.2	6793.9	5665.0
20°	16816.2	16645.6	16226.1	15247.3	14039.9	13233.2	12435.8	10613.8	8900.1	7389.5	6027.7
22.5°	17939.7	17831.4	17489.0	16651.0	15622.3	14854.7	13998.0	11744.2	9585.1	7779.3	6192.8
25°	18435.1	18385.0	18164.4	17503.8	16534.6	15883.5	15074.1	12544.2	10011.5	7960.7	6195.6
27.5°	18937.5	18946.8	18459.6	17937.0	17017.9	16392.6	15612.8	12898.7	10088.7	7859.3	5992.6
30°	19095.8	18995.6	18780.3	18030.4	17157.4	16492.7	15656.2	12735.0	9771.9	7442.2	5587.8
32.5°	19030.8	18991.5	18754.5	17961.4	16920.4	16188.1	15237.9	12085.2	9146.6	6846.6	5013.8
35°	19025.2	18952.2	18409.5	17728.5	16446.7	15542.5	14290.3	11034.8	8261.2	6061.6	4338.4
37.5°	18681.5	18500.1	18092.8	17174.9	15485.5	14339.1	12935.3	9751.6	7178.4	5180.3	3668.4
40°	18176.6	17932.9	17396.9	16008.1	13820.6	12499.6	11129.6	8293.7	6031.8	4311.3	2956.3
42.5°	17122.1	16754.0	15995.9	14086.0	11601.9	10410.8	9271.0	6816.9	4919.1	3512.7	2256.5
45°	15153.9	14650.5	13625.8	11528.9	9372.6	8400.7	7484.2	5485.0	3937.8	2605.7	1487.6
47.5°	12180.0	11713.0	10780.3	9177.6	7350.2	6528.6	5797.7	4079.8	2669.4	1509.4	710.6
50°	9068.1	8667.4	7939.2	6378.3	4934.0	4288.3	3663.0	2317.4	1250.8	717.4	295.2
52.5°	5410.5	5211.5	4565.8	3537.0	2436.5	2099.4	1685.3	981.3	630.8	259.9	79.9
55°	2215.9	2045.4	1803.0	1447.0	1060.0	898.8	768.9	484.6	196.2	54.1	29.8
57.5°	1001.6	963.9	854.2	671.4	487.3	408.8	276.1	92.0	43.4	27.1	17.6
60°	385.8	347.9	297.9	161.1	69.1	58.1	47.3	31.2	21.6	14.9	10.8
62.5°	55.4	52.7	47.3	38.0	29.8	27.1	23.1	16.2	12.2	9.5	8.1
65°	23.1	23.1	20.3	16.2	13.5	12.2	10.8	8.1	6.8	6.8	6.8
67.5°	9.5	9.5	8.1	6.8	5.4	5.4	5.4	4.1	5.4	5.4	6.8
70°	2.7	2.7	2.7	2.7	2.7	2.7	4.1	4.1	5.4	5.4	6.8
72.5°	0.0	0.0	1.4	1.4	2.7	2.7	2.7	4.1	5.4	6.8	6.8
75°	0.0	0.0	1.4	1.4	2.7	2.7	2.7	4.1	5.4	6.8	6.8
77.5°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	6.8
80°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	8.1
82.5°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	8.1
85°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	8.1
87.5°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8
2.5°	1858.6	1772.0	1747.5	1671.7	1608.2	1577.0	1537.6	1449.7	1383.4	1295.4	1242.7
5°	2393.2	2229.4	2099.4	1941.1	1836.8	1769.2	1663.6	1502.6	1372.6	1216.9	1105.9
7.5°	2971.2	2672.1	2438.0	2176.7	2026.3	1908.7	1728.6	1497.1	1306.2	1099.2	927.3
10°	3528.9	3082.2	2714.1	2339.1	2141.5	1977.7	1729.9	1438.9	1185.8	924.6	743.2
12.5°	4020.3	3443.6	2925.1	2443.4	2198.2	1994.0	1684.0	1334.7	1028.8	760.8	600.9
15°	4430.4	3723.8	3074.1	2482.6	2202.3	1958.7	1587.9	1185.8	854.2	615.9	503.6
17.5°	4741.8	3871.4	3120.1	2435.2	2123.8	1858.6	1440.2	997.6	693.0	522.5	423.6
20°	4902.9	3899.8	3053.8	2306.6	1979.0	1707.0	1246.8	809.4	587.5	454.8	354.6
22.5°	4923.2	3819.9	2895.5	2122.4	1796.3	1522.9	1032.8	675.5	523.8	402.1	312.7
25°	4802.6	3646.8	2669.4	1914.0	1596.0	1311.6	840.6	605.2	476.5	361.4	360.0
27.5°	4545.5	3348.9	2398.7	1671.7	1353.6	1066.7	713.3	546.8	425.2	383.1	407.5
30°	4182.8	2967.1	2065.6	1365.8	1057.3	820.2	600.9	450.7	373.6	377.6	398.0
32.5°	3691.4	2493.4	1674.4	1000.3	756.7	617.2	450.7	307.3	310.0	311.4	328.8
35°	3074.1	1999.4	1250.8	672.8	532.0	434.5	254.5	226.1	230.0	231.4	243.6
37.5°	2463.6	1536.3	831.2	448.0	334.3	228.8	158.4	151.5	154.2	152.9	166.5
40°	1887.0	1070.8	498.2	222.0	128.6	106.9	97.4	93.4	94.7	96.1	104.2
42.5°	1336.1	580.7	246.4	83.9	67.7	62.2	58.1	55.4	56.8	56.8	62.2
45°	678.2	274.8	83.9	46.0	42.0	38.0	35.3	33.9	33.9	33.9	36.6
47.5°	293.8	90.7	39.3	28.5	25.8	24.4	21.6	20.3	20.3	20.3	21.6
50°	92.0	36.6	24.4	18.9	16.2	14.9	13.5	13.5	13.5	12.2	13.5
52.5°	33.9	23.1	16.2	12.2	10.8	10.8	10.8	9.5	10.8	9.5	10.8
55°	20.3	14.9	10.8	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
57.5°	13.5	10.8	9.5	9.5	8.1	8.1	9.5	9.5	9.5	9.5	9.5
60°	9.5	9.5	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5	9.5
62.5°	8.1	8.1	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5	10.8
65°	6.8	8.1	8.1	8.1	8.1	8.1	9.5	9.5	10.8	10.8	10.8
67.5°	6.8	8.1	8.1	9.5	9.5	9.5	9.5	10.8	10.8	10.8	10.8
70°	8.1	8.1	9.5	9.5	9.5	9.5	10.8	10.8	10.8	10.8	12.2
72.5°	8.1	8.1	9.5	9.5	9.5	9.5	10.8	10.8	12.2	12.2	12.2
75°	8.1	9.5	9.5	9.5	9.5	10.8	10.8	10.8	12.2	12.2	12.2
77.5°	8.1	9.5	9.5	10.8	10.8	10.8	10.8	12.2	12.2	12.2	12.2
80°	8.1	9.5	9.5	10.8	10.8	10.8	12.2	12.2	12.2	12.2	13.5
82.5°	8.1	9.5	9.5	10.8	10.8	10.8	12.2	12.2	12.2	12.2	13.5
85°	9.5	9.5	10.8	10.8	10.8	10.8	12.2	12.2	12.2	12.2	13.5
87.5°	9.5	9.5	10.8	10.8	10.8	10.8	12.2	12.2	13.5	12.2	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8
2.5°	1172.2	1093.7	1039.6	1019.3	980.0	917.8	881.3	847.4	783.8	770.2	735.0
5°	978.6	852.8	763.5	729.6	684.9	632.1	580.7	546.8	506.3	490.0	465.6
7.5°	771.6	645.6	568.6	541.4	510.2	467.0	420.9	387.2	345.2	323.4	303.3
10°	606.5	512.9	448.0	420.9	388.5	342.5	295.2	250.4	213.9	190.8	186.8
12.5°	492.8	415.5	346.5	318.1	280.2	234.1	200.3	199.0	196.2	194.9	197.6
15°	403.4	328.8	255.8	224.7	213.9	212.6	216.6	220.7	219.3	223.4	226.1
17.5°	331.6	251.8	235.5	236.8	238.2	242.2	249.1	259.9	261.2	268.0	273.4
20°	270.7	266.7	273.4	278.8	282.9	291.1	306.0	319.5	323.4	332.9	343.8
22.5°	307.3	319.5	334.3	341.1	346.5	361.4	377.6	399.4	407.5	419.5	434.5
25°	370.9	391.2	414.1	422.2	430.5	454.8	473.8	499.5	506.3	521.1	536.0
27.5°	423.6	445.3	469.8	480.6	487.3	511.6	527.9	544.1	544.1	552.2	563.2
30°	415.5	433.2	453.4	461.6	464.3	481.9	498.2	503.6	500.9	504.9	512.9
32.5°	345.2	358.7	374.9	381.8	384.5	396.7	410.2	410.2	408.8	408.8	414.1
35°	255.8	265.3	273.4	280.2	284.2	292.4	304.6	303.3	303.3	300.6	304.6
37.5°	171.9	177.3	186.8	189.5	190.8	196.2	205.8	205.8	203.1	204.5	207.2
40°	104.2	111.0	116.5	117.8	120.5	124.6	131.4	131.4	131.4	131.4	132.7
42.5°	62.2	66.2	70.4	70.4	71.8	77.2	79.9	79.9	79.9	79.9	81.2
45°	36.6	38.0	40.7	42.0	42.0	44.7	46.0	46.0	46.0	46.0	47.3
47.5°	21.6	23.1	23.1	24.4	24.4	25.8	27.1	27.1	25.8	25.8	25.8
50°	13.5	13.5	13.5	13.5	14.9	14.9	14.9	14.9	14.9	14.9	13.5
52.5°	10.8	10.8	10.8	10.8	9.5	9.5	9.5	9.5	8.1	8.1	6.8
55°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	8.1	6.8	5.4	4.1
57.5°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.1
60°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.1
62.5°	10.8	10.8	9.5	9.5	9.5	8.1	8.1	6.8	6.8	5.4	4.1
65°	10.8	10.8	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	4.1
67.5°	10.8	10.8	10.8	10.8	9.5	9.5	9.5	8.1	6.8	5.4	4.1
70°	12.2	12.2	10.8	10.8	10.8	9.5	9.5	8.1	6.8	6.8	5.4
72.5°	12.2	12.2	10.8	10.8	10.8	10.8	9.5	8.1	8.1	6.8	5.4
75°	12.2	12.2	12.2	12.2	10.8	10.8	9.5	9.5	8.1	6.8	5.4
77.5°	12.2	12.2	12.2	12.2	10.8	10.8	10.8	9.5	8.1	6.8	5.4
80°	12.2	12.2	12.2	12.2	12.2	10.8	10.8	9.5	8.1	6.8	5.4
82.5°	13.5	13.5	12.2	12.2	12.2	10.8	10.8	9.5	8.1	6.8	6.8
85°	13.5	13.5	12.2	12.2	12.2	10.8	10.8	9.5	8.1	8.1	6.8
87.5°	13.5	13.5	12.2	12.2	12.2	10.8	10.8	9.5	8.1	8.1	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219661

CATALOG NUMBER: LDSQA6A75950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8	1342.8
2.5°	713.3	672.8	659.3	668.7	657.9	649.8	638.9	633.5
5°	446.7	416.8	407.5	410.2	400.7	392.6	381.8	379.0
7.5°	274.8	246.4	235.5	235.5	224.7	215.3	208.5	204.5
10°	184.1	178.7	180.0	181.4	180.0	181.4	177.3	180.0
12.5°	197.6	194.9	197.6	199.0	199.0	201.8	196.2	200.3
15°	230.0	227.4	231.4	234.1	234.1	238.2	232.8	236.8
17.5°	281.5	280.2	286.9	289.6	291.1	297.9	291.1	296.5
20°	356.0	354.6	364.1	368.2	366.8	380.4	370.9	380.4
22.5°	452.1	449.4	462.9	467.0	468.3	486.0	477.9	484.6
25°	548.2	550.9	557.6	564.5	565.9	580.7	568.6	575.3
27.5°	568.6	564.5	568.6	576.7	578.0	584.8	574.0	579.4
30°	514.5	507.5	508.9	518.5	521.1	523.8	514.5	517.2
32.5°	418.2	407.5	407.5	416.8	419.5	423.6	407.5	414.1
35°	308.7	299.2	299.2	306.0	307.3	310.0	297.9	303.3
37.5°	211.2	203.1	205.8	208.5	209.9	212.6	211.2	209.9
40°	135.4	130.0	134.1	134.1	135.4	136.8	136.8	138.1
42.5°	82.6	78.5	81.2	81.2	82.6	82.6	82.6	83.9
45°	47.3	46.0	46.0	47.3	47.3	47.3	46.0	47.3
47.5°	25.8	24.4	25.8	25.8	25.8	25.8	25.8	25.8
50°	13.5	12.2	12.2	12.2	12.2	12.2	12.2	12.2
52.5°	6.8	5.4	5.4	5.4	4.1	5.4	4.1	4.1
55°	4.1	2.7	2.7	2.7	1.4	1.4	0.0	0.0
57.5°	2.7	1.4	1.4	1.4	0.0	0.0	0.0	0.0
60°	2.7	1.4	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.7	1.4	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.7	1.4	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	4.1	2.7	1.4	1.4	1.4	0.0	0.0	0.0
70°	4.1	2.7	2.7	1.4	1.4	0.0	0.0	0.0
72.5°	4.1	2.7	2.7	2.7	1.4	1.4	0.0	0.0
75°	4.1	2.7	2.7	2.7	1.4	1.4	0.0	0.0
77.5°	4.1	4.1	2.7	2.7	1.4	1.4	1.4	0.0
80°	5.4	4.1	2.7	2.7	2.7	1.4	1.4	1.4
82.5°	5.4	4.1	2.7	2.7	2.7	1.4	1.4	1.4
85°	5.4	4.1	4.1	2.7	2.7	1.4	1.4	1.4
87.5°	5.4	4.1	4.1	2.7	2.7	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)