

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843970

Luminaire Tested: **LD6C10DE010B35 EU6C10B35 6LBMLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B35 EU6C10B35 6LBMLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1072.4 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843970

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P843970

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73574
5°	72876
10°	69053
15°	62696
20°	55398
25°	47900
30°	37436
35°	22961
40°	11786
45°	4683
50°	1527
55°	526
60°	450
65°	350
70°	224
75°	297
80°	0
85°	0



TEST NUMBER: P843970

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.6	11.5
10°-20°	307.8	28.7
20°-30°	357.8	33.4
30°-40°	219.1	20.4
40°-50°	54.4	5.1
50°-60°	6.4	0.6
60°-70°	2.4	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.3	73.6
0°-40°	1008.4	94.0
0°-60°	1069.2	99.7
0°-90°	1072.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1072.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1342	
5°	1324	124
15°	1105	308
25°	792	358
35°	343	219
45°	60	54
55°	6	6
65°	3	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P843970

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1342.1
2.5°	1340.8
5°	1324.3
7.5°	1288.6
10°	1240.5
12.5°	1177.5
15°	1104.7
17.5°	1026.4
20°	949.6
22.5°	872.8
25°	791.9
27.5°	698.5
30°	591.4
32.5°	466.6
35°	343.1
37.5°	241.5
40°	164.7
42.5°	102.9
45°	60.4
47.5°	34.3
50°	17.9
52.5°	8.2
55°	5.5
57.5°	4.1
60°	4.1
62.5°	2.7
65°	2.7
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)