

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843973

Luminaire Tested: **LD6C10DE010B35 EU6C10B35 6LBNLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843973  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C10DE010B35 EU6C10B35 6LBNLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 953.9 lumens  
Efficiency: N/A  
Efficacy: 71.7 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 |  | 105 | 104 | 102 |  |  | 102 | 101 | 99  |  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  |  | 97  | 95  | 93  |  |  | 94  |
| 3   | 105 | 99  | 94  | 91  | 103 | 97  | 93  | 90  |  | 95  | 91  | 89  |  |  | 93  | 90  | 87  |  |  | 90  |
| 4   | 100 | 93  | 88  | 85  | 98  | 92  | 88  | 84  |  | 90  | 86  | 83  |  |  | 88  | 85  | 82  |  |  | 86  |
| 5   | 96  | 88  | 83  | 79  | 94  | 87  | 83  | 79  |  | 86  | 82  | 78  |  |  | 84  | 81  | 78  |  |  | 83  |
| 6   | 92  | 84  | 79  | 75  | 90  | 83  | 78  | 75  |  | 82  | 77  | 74  |  |  | 80  | 76  | 74  |  |  | 79  |
| 7   | 88  | 80  | 74  | 71  | 87  | 79  | 74  | 71  |  | 78  | 73  | 70  |  |  | 77  | 73  | 70  |  |  | 76  |
| 8   | 84  | 76  | 71  | 67  | 83  | 75  | 70  | 67  |  | 74  | 70  | 67  |  |  | 73  | 69  | 66  |  |  | 73  |
| 9   | 81  | 73  | 67  | 64  | 80  | 72  | 67  | 64  |  | 71  | 67  | 63  |  |  | 70  | 66  | 63  |  |  | 70  |
| 10  | 78  | 69  | 64  | 61  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  |  | 67  | 63  | 60  |  |  | 67  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 119069 |
| 5°  | 111352 |
| 10° | 90813  |
| 15° | 66828  |
| 20° | 46058  |
| 25° | 34194  |
| 30° | 25687  |
| 35° | 16015  |
| 40° | 7772   |
| 45° | 2667   |
| 50° | 350    |
| 55° | 258    |
| 60° | 153    |
| 65° | 182    |
| 70° | 224    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBNLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 180.6  | 18.9      |
| 10°-20°   | 324.1  | 34.0      |
| 20°-30°   | 262.1  | 27.5      |
| 30°-40°   | 151.0  | 15.8      |
| 40°-50°   | 31.9   | 3.3       |
| 50°-60°   | 2.7    | 0.3       |
| 60°-70°   | 1.4    | 0.1       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 766.8  | 80.4      |
| 0°-40°    | 917.7  | 96.2      |
| 0°-60°    | 952.4  | 99.8      |
| 0°-90°    | 953.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 953.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2172 |      |
| 5°  | 2024 | 181  |
| 15° | 1178 | 324  |
| 25° | 565  | 262  |
| 35° | 239  | 151  |
| 45° | 34   | 32   |
| 55° | 3    | 3    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B35 EU6C10B35 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2172.0 |
| 2.5°  | 2145.9 |
| 5°    | 2023.5 |
| 7.5°  | 1847.4 |
| 10°   | 1631.4 |
| 12.5° | 1409.9 |
| 15°   | 1177.5 |
| 17.5° | 953.2  |
| 20°   | 789.5  |
| 22.5° | 664.4  |
| 25°   | 565.3  |
| 27.5° | 481.4  |
| 30°   | 405.8  |
| 32.5° | 321.9  |
| 35°   | 239.3  |
| 37.5° | 166.5  |
| 40°   | 108.6  |
| 42.5° | 66.0   |
| 45°   | 34.4   |
| 47.5° | 13.7   |
| 50°   | 4.1    |
| 52.5° | 4.1    |
| 55°   | 2.7    |
| 57.5° | 2.7    |
| 60°   | 1.4    |
| 62.5° | 1.4    |
| 65°   | 1.4    |
| 67.5° | 1.4    |
| 70°   | 1.4    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)