

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250594

Luminaire Tested: **LD8B175D010 ER8B175935 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B175935 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9845.1 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250594

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBM0B

Luminous Intensity Polar Plot



TEST NUMBER: P250594

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71		
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	70	66	63	62		
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393909
5°	381865
10°	334437
15°	295260
20°	270559
25°	249125
30°	207349
35°	137725
40°	67027
45°	24277
50°	7306
55°	511
60°	0
65°	350
70°	0
75°	0
80°	852
85°	0



TEST NUMBER: P250594

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1122.0	11.4
10°-20°	2605.7	26.5
20°-30°	3305.7	33.6
30°-40°	2264.7	23.0
40°-50°	516.1	5.2
50°-60°	25.7	0.3
60°-70°	1.2	0.0
70°-80°	1.9	0.0
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7033.5	71.4
0°-40°	9298.2	94.4
0°-60°	9840.0	99.9
0°-90°	9845.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9845.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12774	
5°	12336	###
15°	9249	2606
25°	7322	3306
35°	3659	2265
45°	557	516
55°	10	26
65°	5	1
75°	0	2
85°	0	2
90°	0	



TEST NUMBER: P250594

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	12774.2
1°	12840.8
2°	12817.0
3°	12721.8
4°	12560.0
5°	12336.5
6°	12065.3
7°	11751.3
8°	11404.0
9°	11032.8
10°	10680.8
11°	10357.3
12°	10010.0
13°	9757.9
14°	9491.4
15°	9248.8
16°	9030.0
17°	8815.8
18°	8616.0
19°	8420.9
20°	8244.9
21°	8064.1
22°	7878.6
23°	7716.9
24°	7536.1
25°	7322.0
26°	7084.1
27°	6808.2
28°	6513.2
29°	6184.9
30°	5823.3
31°	5414.2
32°	4990.8
33°	4548.3
34°	4096.3
35°	3658.6
37.5°	2583.4
40°	1665.1
42.5°	980.1
45°	556.7
47.5°	299.8
50°	152.3
52.5°	28.5
55°	9.5
57.5°	4.8



TEST NUMBER: P250594

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	4.8
67.5°	0.0
70°	0.0
72.5°	4.8
75°	0.0
77.5°	0.0
80°	4.8
82.5°	0.0
85°	0.0
87.5°	4.8
90°	0.0

(END OF REPORT)