

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867258

Luminaire Tested: PRLX-2004-L-930-133L-G-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-74)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-930-133L-G-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2543.8 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.15
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867258

CATALOG NUMBER: PRLX-2004-L-930-133L-G-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867258

CATALOG NUMBER: PRLX-2004-L-930-133L-G-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	85	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	67	62	83	73	67	62	72	66	61		70	64	60		68	63	60	58
6	79	68	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	51	73	62	55	50	61	55	50		60	54	50		58	53	49	48
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	39		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7607
5°	7613
10°	7586
15°	7487
20°	7356
25°	7182
30°	6819
35°	6071
40°	5125
45°	4032
50°	2842
55°	1657
60°	1002
65°	862
70°	765
75°	681
80°	622
85°	589

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4032 cd/sqm

TEST NUMBER: P867258

CATALOG NUMBER: PRLX-2004-L-930-133L-G-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	5.7
10°-20°	413.0	16.2
20°-30°	605.0	23.8
30°-40°	625.8	24.6
40°-50°	444.4	17.5
50°-60°	185.0	7.3
60°-70°	74.6	2.9
70°-80°	38.4	1.5
80°-90°	11.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.0	45.8
0°-40°	1789.9	70.4
0°-60°	2419.3	95.1
0°-90°	2543.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2543.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1542	
5°	1537	146
15°	1466	413
25°	1319	605
35°	1008	626
45°	578	444
55°	193	185
65°	74	75
75°	36	38
85°	10	11
90°	0	

TEST NUMBER: P867258

CATALOG NUMBER: PRLX-2004-L-930-133L-G-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1541.8
2.5°	1540.7
5°	1537.2
7.5°	1529.1
10°	1514.1
12.5°	1492.2
15°	1465.7
17.5°	1435.7
20°	1401.1
22.5°	1363.1
25°	1319.3
27.5°	1269.7
30°	1197.0
32.5°	1109.4
35°	1007.9
37.5°	903.0
40°	795.7
42.5°	686.2
45°	577.8
47.5°	471.7
50°	370.2
52.5°	279.1
55°	192.6
57.5°	128.0
60°	101.5
62.5°	87.6
65°	73.8
67.5°	63.4
70°	53.0
72.5°	43.8
75°	35.7
77.5°	28.8
80°	21.9
82.5°	16.1
85°	10.4
87.5°	4.6
90°	0.0



TEST NUMBER: P867258
 CATALOG NUMBER: PRLX-2004-L-930-133L-G-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.98	10.27	9.35	10.58	10.90	8.98	10.27	9.35	10.58	10.90
	3H	10.05	11.19	10.43	11.52	11.88	10.05	11.19	10.43	11.52	11.88
	4H	10.45	11.50	10.85	11.85	12.24	10.45	11.50	10.85	11.85	12.24
	6H	10.75	11.72	11.16	12.09	12.48	10.75	11.72	11.16	12.09	12.48
	8H	10.85	11.77	11.28	12.16	12.57	10.85	11.77	11.28	12.16	12.57
	12H	10.92	11.80	11.35	12.18	12.61	10.92	11.80	11.35	12.18	12.61
4H	2H	9.29	10.35	9.69	10.70	11.08	9.29	10.35	9.69	10.70	11.08
	3H	10.58	11.44	10.99	11.84	12.24	10.58	11.44	10.99	11.84	12.24
	4H	11.09	11.85	11.52	12.27	12.72	11.09	11.85	11.52	12.27	12.72
	6H	11.51	12.17	11.97	12.62	13.09	11.51	12.17	11.97	12.62	13.09
	8H	11.66	12.27	12.13	12.72	13.19	11.66	12.27	12.13	12.72	13.19
	12H	11.77	12.31	12.25	12.80	13.27	11.77	12.31	12.25	12.80	13.27
8H	4H	11.24	11.86	11.71	12.31	12.78	11.24	11.86	11.71	12.31	12.78
	6H	11.77	12.28	12.28	12.78	13.26	11.77	12.28	12.28	12.78	13.26
	8H	11.99	12.44	12.51	12.96	13.45	11.99	12.44	12.51	12.96	13.45
	12H	12.18	12.58	12.69	13.07	13.65	12.18	12.58	12.69	13.07	13.65
12H	4H	11.24	11.78	11.72	12.26	12.74	11.24	11.78	11.72	12.26	12.74
	6H	11.79	12.25	12.31	12.76	13.26	11.79	12.25	12.31	12.76	13.26
	8H	12.06	12.46	12.58	12.96	13.53	12.06	12.46	12.58	12.96	13.53