

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600646

Luminaire Tested: PRLX-205-90-40K-LL7-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-205-90-40K-LL7-UNV-STD-X-X-WHHR-BR-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6121.9 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600646

CATALOG NUMBER: PRLX-205-90-40K-LL7-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600646

CATALOG NUMBER: PRLX-205-90-40K-LL7-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31070
5°	27591
10°	25490
15°	24865
20°	24597
25°	24542
30°	24374
35°	24163
40°	21417
45°	8719
50°	7672
55°	7423
60°	7267
65°	6963
70°	6681
75°	6416
80°	6153
85°	6032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8719 cd/sqm



TEST NUMBER: P600646

CATALOG NUMBER: PRLX-205-90-40K-LL7-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.0	5.4
10°-20°	880.7	14.4
20°-30°	1329.3	21.7
30°-40°	1585.2	25.9
40°-50°	819.7	13.4
50°-60°	494.4	8.1
60°-70°	378.9	6.2
70°-80°	227.3	3.7
80°-90°	74.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2542.0	41.5
0°-40°	4127.2	67.4
0°-60°	5441.2	88.9
0°-90°	6121.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6121.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4030	
5°	3565	332
15°	3116	881
25°	2885	1329
35°	2568	1585
45°	800	820
55°	552	494
65°	382	379
75°	215	227
85°	68	75
90°	0	



TEST NUMBER: P600646

CATALOG NUMBER: PRLX-205-90-40K-LL7-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	4030.3
2.5°	3902.4
5°	3565.4
7.5°	3360.7
10°	3256.2
12.5°	3181.6
15°	3115.5
17.5°	3055.8
20°	2998.2
22.5°	2944.9
25°	2885.2
27.5°	2819.1
30°	2738.1
32.5°	2642.1
35°	2567.5
37.5°	2488.6
40°	2128.2
42.5°	1418.1
45°	799.7
47.5°	712.2
50°	639.7
52.5°	588.6
55°	552.3
57.5°	513.9
60°	471.3
62.5°	426.5
65°	381.7
67.5°	339.1
70°	296.4
72.5°	253.8
75°	215.4
77.5°	174.9
80°	138.6
82.5°	102.4
85°	68.2
87.5°	34.1
90°	0.0

(END OF REPORT)