

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600677

Luminaire Tested: PRLX-215-90-30K-LL1-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600677  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PentaLux  
Catalog Number: PRLX-215-90-30K-LL1-UNV-STD-X-X-WHHR-FL-X  
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 932.2 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600677

CATALOG NUMBER: PRLX-215-90-30K-LL1-UNV-STD-X-X-WHHR-FL-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600677

CATALOG NUMBER: PRLX-215-90-30K-LL1-UNV-STD-X-X-WHHR-FL-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	87	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	56	49	45	66	56	49	45	55	49	45		54	48	44		53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	42		51	45	41		50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	12458
5°	10169
10°	9324
15°	9120
20°	9057
25°	8997
30°	7196
35°	3475
40°	3045
45°	2764
50°	2454
55°	2158
60°	1886
65°	1651
70°	1439
75°	1213
80°	844
85°	299

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2764 cd/sqm



TEST NUMBER: P600677

CATALOG NUMBER: PRLX-215-90-30K-LL1-UNV-STD-X-X-WHHR-FL-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.2	7.4
10°-20°	181.7	19.5
20°-30°	266.2	28.6
30°-40°	144.7	15.5
40°-50°	109.8	11.8
50°-60°	81.2	8.7
60°-70°	51.0	5.5
70°-80°	24.3	2.6
80°-90°	3.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.2	55.5
0°-40°	661.9	71.0
0°-60°	852.9	91.5
0°-90°	932.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	932.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	909	
5°	739	69
15°	643	182
25°	595	266
35°	208	145
45°	143	110
55°	90	81
65°	51	51
75°	23	24
85°	2	4
90°	0	



TEST NUMBER: P600677

CATALOG NUMBER: PRLX-215-90-30K-LL1-UNV-STD-X-X-WHHR-FL-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	909.0
2.5°	852.8
5°	739.2
7.5°	689.5
10°	670.0
12.5°	655.8
15°	642.8
17.5°	630.6
20°	621.0
22.5°	611.9
25°	595.0
27.5°	571.3
30°	454.7
32.5°	229.5
35°	207.7
37.5°	187.8
40°	170.2
42.5°	156.0
45°	142.6
47.5°	128.9
50°	115.1
52.5°	102.5
55°	90.3
57.5°	79.2
60°	68.8
62.5°	59.7
65°	50.9
67.5°	43.6
70°	35.9
72.5°	29.4
75°	22.9
77.5°	16.8
80°	10.7
82.5°	6.1
85°	1.9
87.5°	0.8
90°	0.0

(END OF REPORT)