

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600686

Luminaire Tested: PRLX-215-90-30K-LL4-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PentaLux  
Catalog Number: PRLX-215-90-30K-LL4-UNV-STD-X-X-WHHR-FL-X  
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2359.4 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85  
Luminous Opening: Circular (Dia: 1' x H: 0')  
CIE Type: Direct


Input Watts (W): 23.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600686

CATALOG NUMBER: PRLX-215-90-30K-LL4-UNV-STD-X-X-WHHR-FL-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600686

CATALOG NUMBER: PRLX-215-90-30K-LL4-UNV-STD-X-X-WHHR-FL-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	87	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	56	49	45	66	56	49	45	55	49	45		54	48	44		53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	42		51	45	41		50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	31533
5°	25740
10°	23600
15°	23086
20°	22926
25°	22775
30°	18213
35°	8794
40°	7706
45°	6997
50°	6211
55°	5457
60°	4775
65°	4174
70°	3646
75°	3077
80°	2139
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6997 cd/sqm



TEST NUMBER: P600686

CATALOG NUMBER: PRLX-215-90-30K-LL4-UNV-STD-X-X-WHHR-FL-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.2	7.4
10°-20°	460.0	19.5
20°-30°	673.8	28.6
30°-40°	366.2	15.5
40°-50°	277.9	11.8
50°-60°	205.6	8.7
60°-70°	129.2	5.5
70°-80°	61.7	2.6
80°-90°	9.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1309.0	55.5
0°-40°	1675.3	71.0
0°-60°	2158.8	91.5
0°-90°	2359.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2359.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2301	
5°	1871	175
15°	1627	460
25°	1506	674
35°	526	366
45°	361	278
55°	228	206
65°	129	129
75°	58	62
85°	5	10
90°	0	



TEST NUMBER: P600686

CATALOG NUMBER: PRLX-215-90-30K-LL4-UNV-STD-X-X-WHHR-FL-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2300.8
2.5°	2158.5
5°	1871.0
7.5°	1745.2
10°	1695.8
12.5°	1660.0
15°	1627.1
17.5°	1596.1
20°	1571.9
22.5°	1548.7
25°	1506.1
27.5°	1446.1
30°	1150.9
32.5°	580.8
35°	525.6
37.5°	475.3
40°	430.7
42.5°	394.9
45°	361.0
47.5°	326.2
50°	291.3
52.5°	259.4
55°	228.4
57.5°	200.4
60°	174.2
62.5°	151.0
65°	128.7
67.5°	110.3
70°	91.0
72.5°	74.5
75°	58.1
77.5°	42.6
80°	27.1
82.5°	15.5
85°	4.8
87.5°	1.9
90°	0.0

(END OF REPORT)