

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600700

Luminaire Tested: PRLX-215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 963.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85
Luminous Opening: Circular (Dia: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600700

CATALOG NUMBER: PRLX-215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600700

CATALOG NUMBER: PRLX-215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	87	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	56	49	45	66	56	49	45	55	49	45		54	48	44		53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	42		51	45	41		50	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12870
5°	10507
10°	9633
15°	9423
20°	9357
25°	9297
30°	7435
35°	3589
40°	3145
45°	2857
50°	2535
55°	2227
60°	1949
65°	1703
70°	1487
75°	1255
80°	876
85°	314

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2857 cd/sqm



TEST NUMBER: P600700

CATALOG NUMBER: PRLX-215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.5	7.4
10°-20°	187.8	19.5
20°-30°	275.1	28.6
30°-40°	149.5	15.5
40°-50°	113.4	11.8
50°-60°	83.9	8.7
60°-70°	52.7	5.5
70°-80°	25.2	2.6
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.3	55.5
0°-40°	683.8	71.0
0°-60°	881.2	91.5
0°-90°	963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	963.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	939	
5°	764	71
15°	664	188
25°	615	275
35°	214	149
45°	147	113
55°	93	84
65°	52	53
75°	24	25
85°	2	4
90°	0	



TEST NUMBER: P600700

CATALOG NUMBER: PRLX-215-90-35K-LL1-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	939.1
2.5°	881.0
5°	763.7
7.5°	712.3
10°	692.2
12.5°	677.6
15°	664.1
17.5°	651.5
20°	641.6
22.5°	632.1
25°	614.8
27.5°	590.3
30°	469.8
32.5°	237.1
35°	214.5
37.5°	194.0
40°	175.8
42.5°	161.2
45°	147.4
47.5°	133.1
50°	118.9
52.5°	105.9
55°	93.2
57.5°	81.8
60°	71.1
62.5°	61.6
65°	52.5
67.5°	45.0
70°	37.1
72.5°	30.4
75°	23.7
77.5°	17.4
80°	11.1
82.5°	6.3
85°	2.0
87.5°	0.8
90°	0.0

(END OF REPORT)