

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600556

Luminaire Tested: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-BR-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1035.6 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600556

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600556

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5256
5°	4667
10°	4312
15°	4206
20°	4161
25°	4152
30°	4123
35°	4087
40°	3623
45°	1475
50°	1298
55°	1255
60°	1229
65°	1178
70°	1129
75°	1084
80°	1039
85°	1017

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1475 cd/sqm



TEST NUMBER: P600556

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	5.4
10°-20°	149.0	14.4
20°-30°	224.9	21.7
30°-40°	268.1	25.9
40°-50°	138.7	13.4
50°-60°	83.6	8.1
60°-70°	64.1	6.2
70°-80°	38.4	3.7
80°-90°	12.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.0	41.5
0°-40°	698.2	67.4
0°-60°	920.4	88.9
0°-90°	1035.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	682	
5°	603	56
15°	527	149
25°	488	225
35°	434	268
45°	135	139
55°	93	84
65°	65	64
75°	36	38
85°	12	13
90°	0	



TEST NUMBER: P600556

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	681.8
2.5°	660.1
5°	603.1
7.5°	568.5
10°	550.8
12.5°	538.2
15°	527.0
17.5°	516.9
20°	507.2
22.5°	498.2
25°	488.1
27.5°	476.9
30°	463.2
32.5°	446.9
35°	434.3
37.5°	421.0
40°	360.0
42.5°	239.9
45°	135.3
47.5°	120.5
50°	108.2
52.5°	99.6
55°	93.4
57.5°	86.9
60°	79.7
62.5°	72.1
65°	64.6
67.5°	57.4
70°	50.1
72.5°	42.9
75°	36.4
77.5°	29.6
80°	23.4
82.5°	17.3
85°	11.5
87.5°	5.8
90°	0.0

(END OF REPORT)