

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600557

Luminaire Tested: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600557  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PentaLux  
Catalog Number: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-FL-X  
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1026.9 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600557

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-FL-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600557

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-FL-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5212
5°	4628
10°	4276
15°	4171
20°	4127
25°	4117
30°	4089
35°	4053
40°	3593
45°	1462
50°	1287
55°	1246
60°	1220
65°	1167
70°	1120
75°	1075
80°	1034
85°	1008

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1462 cd/sqm



TEST NUMBER: P600557

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-FL-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.7	5.4
10°-20°	147.7	14.4
20°-30°	223.0	21.7
30°-40°	265.9	25.9
40°-50°	137.5	13.4
50°-60°	82.9	8.1
60°-70°	63.5	6.2
70°-80°	38.1	3.7
80°-90°	12.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.4	41.5
0°-40°	692.3	67.4
0°-60°	912.8	88.9
0°-90°	1026.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	676	
5°	598	56
15°	523	148
25°	484	223
35°	431	266
45°	134	138
55°	93	83
65°	64	64
75°	36	38
85°	11	13
90°	0	



TEST NUMBER: P600557

CATALOG NUMBER: PRLX-225-90-27K-LL1-UNV-STD-X-X-WHHR-FL-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	676.1
2.5°	654.6
5°	598.1
7.5°	563.8
10°	546.2
12.5°	533.7
15°	522.6
17.5°	512.6
20°	503.0
22.5°	494.0
25°	484.0
27.5°	472.9
30°	459.3
32.5°	443.2
35°	430.7
37.5°	417.5
40°	357.0
42.5°	237.9
45°	134.1
47.5°	119.5
50°	107.3
52.5°	98.7
55°	92.7
57.5°	86.2
60°	79.1
62.5°	71.5
65°	64.0
67.5°	56.9
70°	49.7
72.5°	42.6
75°	36.1
77.5°	29.3
80°	23.3
82.5°	17.2
85°	11.4
87.5°	5.7
90°	0.0

(END OF REPORT)