

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600630

Luminaire Tested: PRLX-225-90-40K-LL1-UNV-STD-X-X-WHHR-SR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-225-90-40K-LL1-UNV-STD-X-X-WHHR-SR-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1170.8 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600630

CATALOG NUMBER: PRLX-225-90-40K-LL1-UNV-STD-X-X-WHHR-SR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600630

CATALOG NUMBER: PRLX-225-90-40K-LL1-UNV-STD-X-X-WHHR-SR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5942
5°	5277
10°	4875
15°	4755
20°	4704
25°	4694
30°	4662
35°	4621
40°	4096
45°	1667
50°	1467
55°	1419
60°	1389
65°	1332
70°	1278
75°	1227
80°	1176
85°	1159

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1667 cd/sqm



TEST NUMBER: P600630

CATALOG NUMBER: PRLX-225-90-40K-LL1-UNV-STD-X-X-WHHR-SR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	5.4
10°-20°	168.4	14.4
20°-30°	254.2	21.7
30°-40°	303.2	25.9
40°-50°	156.8	13.4
50°-60°	94.5	8.1
60°-70°	72.4	6.2
70°-80°	43.4	3.7
80°-90°	14.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.2	41.5
0°-40°	789.3	67.4
0°-60°	1040.6	88.9
0°-90°	1170.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	771	
5°	682	63
15°	596	168
25°	552	254
35°	491	303
45°	153	157
55°	106	95
65°	73	72
75°	41	43
85°	13	14
90°	0	



TEST NUMBER: P600630

CATALOG NUMBER: PRLX-225-90-40K-LL1-UNV-STD-X-X-WHHR-SR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	770.8
2.5°	746.3
5°	681.9
7.5°	642.7
10°	622.8
12.5°	608.5
15°	595.8
17.5°	584.4
20°	573.4
22.5°	563.2
25°	551.8
27.5°	539.2
30°	523.7
32.5°	505.3
35°	491.0
37.5°	475.9
40°	407.0
42.5°	271.2
45°	152.9
47.5°	136.2
50°	122.3
52.5°	112.6
55°	105.6
57.5°	98.3
60°	90.1
62.5°	81.6
65°	73.0
67.5°	64.8
70°	56.7
72.5°	48.5
75°	41.2
77.5°	33.4
80°	26.5
82.5°	19.6
85°	13.1
87.5°	6.5
90°	0.0

(END OF REPORT)