

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600645

Luminaire Tested: PRLX-225-90-40K-LL6-UNV-STD-X-X-WHHR-SR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600645  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PentaLux  
Catalog Number: PRLX-225-90-40K-LL6-UNV-STD-X-X-WHHR-SR-X  
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4716.4 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 39.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600645  
CATALOG NUMBER: PRLX-225-90-40K-LL6-UNV-STD-X-X-WHHR-SR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600645

CATALOG NUMBER: PRLX-225-90-40K-LL6-UNV-STD-X-X-WHHR-SR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	23937
5°	21257
10°	19638
15°	19156
20°	18950
25°	18907
30°	18777
35°	18615
40°	16500
45°	6717
50°	5911
55°	5719
60°	5598
65°	5365
70°	5148
75°	4941
80°	4741
85°	4653

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6717 cd/sqm



TEST NUMBER: P600645

CATALOG NUMBER: PRLX-225-90-40K-LL6-UNV-STD-X-X-WHHR-SR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	255.8	5.4
10°-20°	678.5	14.4
20°-30°	1024.1	21.7
30°-40°	1221.2	25.9
40°-50°	631.5	13.4
50°-60°	380.9	8.1
60°-70°	291.9	6.2
70°-80°	175.1	3.7
80°-90°	57.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1958.4	41.5
0°-40°	3179.6	67.4
0°-60°	4192.0	88.9
0°-90°	4716.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4716.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3105	
5°	2747	256
15°	2400	679
25°	2223	1024
35°	1978	1221
45°	616	632
55°	426	381
65°	294	292
75°	166	175
85°	53	57
90°	0	



TEST NUMBER: P600645

CATALOG NUMBER: PRLX-225-90-40K-LL6-UNV-STD-X-X-WHHR-SR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3105.0
2.5°	3006.5
5°	2746.9
7.5°	2589.2
10°	2508.7
12.5°	2451.2
15°	2400.2
17.5°	2354.2
20°	2309.9
22.5°	2268.8
25°	2222.8
27.5°	2171.9
30°	2109.4
32.5°	2035.5
35°	1978.0
37.5°	1917.2
40°	1639.6
42.5°	1092.5
45°	616.1
47.5°	548.7
50°	492.9
52.5°	453.4
55°	425.5
57.5°	395.9
60°	363.1
62.5°	328.6
65°	294.1
67.5°	261.2
70°	228.4
72.5°	195.5
75°	165.9
77.5°	134.7
80°	106.8
82.5°	78.9
85°	52.6
87.5°	26.3
90°	0.0

(END OF REPORT)