

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600628

Luminaire Tested: PRLX-235-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-235-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1176.4 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600628

CATALOG NUMBER: PRLX-235-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600628

CATALOG NUMBER: PRLX-235-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	67	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5971
5°	5302
10°	4898
15°	4778
20°	4726
25°	4716
30°	4683
35°	4643
40°	4116
45°	1676
50°	1474
55°	1426
60°	1397
65°	1337
70°	1285
75°	1233
80°	1181
85°	1159

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1676 cd/sqm



TEST NUMBER: P600628

CATALOG NUMBER: PRLX-235-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.8	5.4
10°-20°	169.2	14.4
20°-30°	255.4	21.7
30°-40°	304.6	25.9
40°-50°	157.5	13.4
50°-60°	95.0	8.1
60°-70°	72.8	6.2
70°-80°	43.7	3.7
80°-90°	14.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	488.5	41.5
0°-40°	793.1	67.4
0°-60°	1045.6	88.9
0°-90°	1176.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1176.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	685	64
15°	599	169
25°	554	255
35°	493	305
45°	154	158
55°	106	95
65°	73	73
75°	41	44
85°	13	14
90°	0	



TEST NUMBER: P600628

CATALOG NUMBER: PRLX-235-90-40K-LL1-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	774.5
2.5°	749.9
5°	685.1
7.5°	645.8
10°	625.7
12.5°	611.4
15°	598.7
17.5°	587.2
20°	576.1
22.5°	565.9
25°	554.4
27.5°	541.7
30°	526.1
32.5°	507.7
35°	493.4
37.5°	478.2
40°	409.0
42.5°	272.5
45°	153.7
47.5°	136.9
50°	122.9
52.5°	113.1
55°	106.1
57.5°	98.8
60°	90.6
62.5°	82.0
65°	73.3
67.5°	65.2
70°	57.0
72.5°	48.8
75°	41.4
77.5°	33.6
80°	26.6
82.5°	19.7
85°	13.1
87.5°	6.6
90°	0.0

(END OF REPORT)