

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979313

Luminaire Tested: PRLX-240-927-LL6-F-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-927-LL6-F-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 240 SHADE WITH FROSTED LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4247.1 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.37
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979313
CATALOG NUMBER: PRLX-240-927-LL6-F-U-S-WHTE-X

Luminous Intensity Polar Plot





TEST NUMBER: P979313

CATALOG NUMBER: PRLX-240-927-LL6-F-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	89	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58
5	81	69	61	55	79	68	61	55	66	59	54	64	58	54	62	57	53	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46
7	70	57	49	44	68	56	49	43	55	48	43	54	47	43	52	47	42	41
8	65	52	45	39	64	52	44	39	50	44	39	49	43	39	48	43	38	37
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19110
5°	19056
10°	18948
15°	18751
20°	18632
25°	18511
30°	18383
35°	18303
40°	18232
45°	17983
50°	16286
55°	10584
60°	4777
65°	3924
70°	4437
75°	4941
80°	5178
85°	5326

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17983 cd/sqm

TEST NUMBER: P979313

CATALOG NUMBER: PRLX-240-927-LL6-F-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.9	4.2
10°-20°	508.2	12.0
20°-30°	768.0	18.1
30°-40°	932.0	21.9
40°-50°	960.9	22.6
50°-60°	545.0	12.8
60°-70°	172.4	4.1
70°-80°	131.5	3.1
80°-90°	50.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1455.2	34.3
0°-40°	2387.2	56.2
0°-60°	3893.1	91.7
0°-90°	4247.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4247.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1898	
5°	1885	179
15°	1799	508
25°	1666	768
35°	1489	932
45°	1263	961
55°	603	545
65°	165	172
75°	127	132
85°	46	50
90°	0	

TEST NUMBER: P979313

CATALOG NUMBER: PRLX-240-927-LL6-F-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1897.9
2.5°	1895.1
5°	1885.3
7.5°	1870.0
10°	1853.2
12.5°	1829.5
15°	1798.8
17.5°	1770.9
20°	1738.8
22.5°	1705.3
25°	1666.2
27.5°	1624.4
30°	1581.1
32.5°	1536.5
35°	1489.0
37.5°	1440.2
40°	1387.1
42.5°	1331.3
45°	1262.9
47.5°	1173.6
50°	1039.7
52.5°	842.9
55°	602.9
57.5°	378.2
60°	237.2
62.5°	180.0
65°	164.7
67.5°	157.7
70°	150.7
72.5°	140.9
75°	127.0
77.5°	110.2
80°	89.3
82.5°	68.4
85°	46.1
87.5°	25.1
90°	0.0



TEST NUMBER: P979313
 CATALOG NUMBER: PRLX-240-927-LL6-F-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.89	18.36	17.25	18.67	18.99	16.89	18.36	17.25	18.67	18.99
	3H	17.78	19.09	18.16	19.41	19.78	17.78	19.09	18.16	19.41	19.78
	4H	18.39	19.61	18.79	19.96	20.34	18.39	19.61	18.79	19.96	20.34
	6H	18.99	20.11	19.40	20.48	20.87	18.99	20.11	19.40	20.48	20.87
	8H	19.22	20.29	19.65	20.68	21.08	19.22	20.29	19.65	20.68	21.08
	12H	19.41	20.43	19.84	20.81	21.24	19.41	20.43	19.84	20.81	21.24
4H	2H	17.01	18.23	17.41	18.58	18.96	17.01	18.23	17.41	18.58	18.96
	3H	18.25	19.25	18.67	19.65	20.06	18.25	19.25	18.67	19.65	20.06
	4H	19.08	19.97	19.51	20.39	20.83	19.08	19.97	19.51	20.39	20.83
	6H	19.88	20.66	20.34	21.10	21.57	19.88	20.66	20.34	21.10	21.57
	8H	20.20	20.93	20.67	21.38	21.84	20.20	20.93	20.67	21.38	21.84
	12H	20.46	21.11	20.95	21.59	22.07	20.46	21.11	20.95	21.59	22.07
8H	4H	19.39	20.12	19.86	20.56	21.03	19.39	20.12	19.86	20.56	21.03
	6H	20.36	20.97	20.86	21.46	21.94	20.36	20.97	20.86	21.46	21.94
	8H	20.78	21.33	21.30	21.84	22.33	20.78	21.33	21.30	21.84	22.33
	12H	21.15	21.64	21.66	22.14	22.70	21.15	21.64	21.66	22.14	22.70
12H	4H	19.43	20.08	19.92	20.56	21.04	19.43	20.08	19.92	20.56	21.04
	6H	20.44	20.99	20.96	21.50	21.99	20.44	20.99	20.96	21.50	21.99
	8H	20.93	21.43	21.44	21.92	22.49	20.93	21.43	21.44	21.92	22.49