

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979383

Luminaire Tested: PRLX-240-930-43L-F-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-43L-F-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 240 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4040.8 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.37
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979383

CATALOG NUMBER: PRLX-240-930-43L-F-U-S-WHTE-X

Luminous Intensity Polar Plot



TEST NUMBER: P979383

CATALOG NUMBER: PRLX-240-930-43L-F-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	104	101	98	100	98	95		96	94	92		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	84	77	72	81	75	71		78	73	69		76
4	87	77	69	63	85	75	68	62	73	67	62		71	65	61		69
5	81	69	61	55	79	68	61	55	66	59	54		64	58	54		62
6	75	63	55	49	73	62	54	49	60	53	48		59	52	48		57
7	70	57	49	44	68	56	49	43	55	48	43		54	47	43		52
8	65	52	45	39	64	52	44	39	50	44	39		49	43	39		48
9	61	48	41	35	59	48	40	35	47	40	35		46	39	35		45
10	57	45	37	32	56	44	37	32	43	37	32		42	36	32		41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18182
5°	18130
10°	18028
15°	17840
20°	17726
25°	17613
30°	17490
35°	17414
40°	17346
45°	17110
50°	15494
55°	10069
60°	4545
65°	3733
70°	4222
75°	4700
80°	4929
85°	5060

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 17110 cd/sqm

TEST NUMBER: P979383

CATALOG NUMBER: PRLX-240-930-43L-F-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.2	4.2
10°-20°	483.5	12.0
20°-30°	730.7	18.1
30°-40°	886.8	21.9
40°-50°	914.2	22.6
50°-60°	518.5	12.8
60°-70°	164.0	4.1
70°-80°	125.1	3.1
80°-90°	47.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1384.5	34.3
0°-40°	2271.2	56.2
0°-60°	3703.9	91.7
0°-90°	4040.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4040.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1806	
5°	1794	170
15°	1711	484
25°	1585	731
35°	1417	887
45°	1202	914
55°	574	518
65°	157	164
75°	121	125
85°	44	48
90°	0	

TEST NUMBER: P979383

CATALOG NUMBER: PRLX-240-930-43L-F-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1805.7
2.5°	1803.0
5°	1793.7
7.5°	1779.1
10°	1763.2
12.5°	1740.6
15°	1711.4
17.5°	1684.9
20°	1654.3
22.5°	1622.5
25°	1585.3
27.5°	1545.5
30°	1504.3
32.5°	1461.8
35°	1416.7
37.5°	1370.2
40°	1319.7
42.5°	1266.6
45°	1201.6
47.5°	1116.6
50°	989.1
52.5°	801.9
55°	573.6
57.5°	359.8
60°	225.7
62.5°	171.3
65°	156.7
67.5°	150.0
70°	143.4
72.5°	134.1
75°	120.8
77.5°	104.9
80°	85.0
82.5°	65.1
85°	43.8
87.5°	23.9
90°	0.0

TEST NUMBER: P979383

CATALOG NUMBER: PRLX-240-930-43L-F-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.71	18.18	17.08	18.50	18.81	16.71	18.18	17.08	18.50	18.81
	3H	17.61	18.91	17.98	19.24	19.60	17.61	18.91	17.98	19.24	19.60
	4H	18.21	19.43	18.61	19.78	20.16	18.21	19.43	18.61	19.78	20.16
	6H	18.81	19.94	19.23	20.30	20.70	18.81	19.94	19.23	20.30	20.70
	8H	19.05	20.12	19.48	20.51	20.91	19.05	20.12	19.48	20.51	20.91
	12H	19.24	20.26	19.67	20.64	21.07	19.24	20.26	19.67	20.64	21.07
4H	2H	16.84	18.06	17.24	18.41	18.79	16.84	18.06	17.24	18.41	18.79
	3H	18.08	19.08	18.49	19.48	19.88	18.08	19.08	18.49	19.48	19.88
	4H	18.90	19.80	19.34	20.22	20.66	18.90	19.80	19.34	20.22	20.66
	6H	19.71	20.49	20.17	20.93	21.39	19.71	20.49	20.17	20.93	21.39
	8H	20.03	20.76	20.49	21.20	21.67	20.03	20.76	20.49	21.20	21.67
	12H	20.29	20.94	20.77	21.42	21.89	20.29	20.94	20.77	21.42	21.89
8H	4H	19.22	19.95	19.68	20.39	20.86	19.22	19.95	19.68	20.39	20.86
	6H	20.19	20.79	20.69	21.29	21.77	20.19	20.79	20.69	21.29	21.77
	8H	20.61	21.16	21.12	21.67	22.16	20.61	21.16	21.12	21.67	22.16
	12H	20.98	21.47	21.49	21.96	22.53	20.98	21.47	21.49	21.96	22.53
12H	4H	19.26	19.91	19.74	20.39	20.86	19.26	19.91	19.74	20.39	20.86
	6H	20.27	20.82	20.78	21.33	21.82	20.27	20.82	20.78	21.33	21.82
	8H	20.76	21.26	21.27	21.75	22.31	20.76	21.26	21.27	21.75	22.31

END OF REPORT