

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979402

Luminaire Tested: PRLX-240-930-62L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-62L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4396.1 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979402

CATALOG NUMBER: PRLX-240-930-62L-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979402

CATALOG NUMBER: PRLX-240-930-62L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	106	104	101	102	100	98		99	97	95		95
2	105	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	90	81	74	68	88	80	73	68	77	72	67		75	70	66		73
5	84	73	66	61	82	72	65	60	70	64	60		69	63	59		67
6	78	67	59	54	77	66	59	54	64	58	53		63	57	53		61
7	73	61	54	48	71	61	53	48	59	53	48		58	52	48		57
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	51	44	40	50	44	39		49	43	39		48
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23126
5°	23059
10°	22892
15°	22536
20°	22258
25°	21942
30°	21551
35°	21269
40°	20945
45°	20359
50°	17355
55°	8862
60°	1436
65°	183
70°	171
75°	226
80°	226
85°	220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20359 cd/sqm

TEST NUMBER: P979402

CATALOG NUMBER: PRLX-240-930-62L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.4	4.9
10°-20°	610.1	13.9
20°-30°	909.1	20.7
30°-40°	1081.8	24.6
40°-50°	1080.0	24.6
50°-60°	473.7	10.8
60°-70°	16.4	0.4
70°-80°	5.9	0.1
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1735.6	39.5
0°-40°	2817.5	64.1
0°-60°	4371.1	99.4
0°-90°	4396.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4396.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2297	
5°	2281	216
15°	2162	610
25°	1975	909
35°	1730	1082
45°	1430	1080
55°	505	474
65°	8	16
75°	6	6
85°	2	3
90°	0	

TEST NUMBER: P979402

CATALOG NUMBER: PRLX-240-930-62L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2296.8
2.5°	2294.9
5°	2281.4
7.5°	2262.1
10°	2239.0
12.5°	2206.3
15°	2161.9
17.5°	2117.6
20°	2077.2
22.5°	2029.0
25°	1975.0
27.5°	1913.4
30°	1853.6
32.5°	1792.0
35°	1730.3
37.5°	1662.9
40°	1593.5
42.5°	1520.3
45°	1429.7
47.5°	1302.6
50°	1107.9
52.5°	832.4
55°	504.8
57.5°	227.4
60°	71.3
62.5°	15.4
65°	7.7
67.5°	5.8
70°	5.8
72.5°	5.8
75°	5.8
77.5°	5.8
80°	3.9
82.5°	3.9
85°	1.9
87.5°	1.9
90°	0.0

TEST NUMBER: P979402

CATALOG NUMBER: PRLX-240-930-62L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.22	14.56	13.58	14.88	15.19	13.22	14.56	13.58	14.88	15.19
	3H	13.09	14.27	13.47	14.60	14.97	13.09	14.27	13.47	14.60	14.97
	4H	13.03	14.12	13.43	14.47	14.86	13.03	14.12	13.43	14.47	14.86
	6H	12.96	13.96	13.37	14.33	14.72	12.96	13.96	13.37	14.33	14.72
	8H	12.92	13.87	13.35	14.26	14.66	12.92	13.87	13.35	14.26	14.66
	12H	12.88	13.79	13.31	14.17	14.60	12.88	13.79	13.31	14.17	14.60
4H	2H	13.02	14.11	13.42	14.46	14.85	13.02	14.11	13.42	14.46	14.85
	3H	12.90	13.78	13.31	14.18	14.58	12.90	13.78	13.31	14.18	14.58
	4H	12.82	13.60	13.26	14.02	14.46	12.82	13.60	13.26	14.02	14.46
	6H	12.75	13.42	13.22	13.87	14.33	12.75	13.42	13.22	13.87	14.33
	8H	12.70	13.33	13.17	13.77	14.24	12.70	13.33	13.17	13.77	14.24
	12H	12.66	13.21	13.14	13.69	14.17	12.66	13.21	13.14	13.69	14.17
8H	4H	12.69	13.31	13.16	13.76	14.23	12.69	13.31	13.16	13.76	14.23
	6H	12.59	13.11	13.10	13.61	14.09	12.59	13.11	13.10	13.61	14.09
	8H	12.54	13.01	13.06	13.52	14.01	12.54	13.01	13.06	13.52	14.01
	12H	12.49	12.91	13.01	13.41	13.98	12.49	12.91	13.01	13.41	13.98
12H	4H	12.64	13.19	13.12	13.67	14.15	12.64	13.19	13.12	13.67	14.15
	6H	12.53	13.00	13.05	13.51	14.00	12.53	13.00	13.05	13.51	14.00
	8H	12.49	12.91	13.00	13.40	13.98	12.49	12.91	13.00	13.40	13.98

END OF REPORT