

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979352

Luminaire Tested: PRLX-240-930-LL2-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-LL2-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1246.6 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979352

CATALOG NUMBER: PRLX-240-930-LL2-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979352

CATALOG NUMBER: PRLX-240-930-LL2-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	106	104	101	102	100	98		99	97	95		95
2	105	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	90	81	74	68	88	80	73	68	77	72	67		75	70	66		73
5	84	73	66	61	82	72	65	60	70	64	60		69	63	59		67
6	78	67	59	54	77	66	59	54	64	58	53		63	57	53		61
7	73	61	54	48	71	61	53	48	59	53	48		58	52	48		57
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	51	44	40	50	44	39		49	43	39		48
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6558
5°	6540
10°	6491
15°	6391
20°	6311
25°	6223
30°	6111
35°	6032
40°	5940
45°	5773
50°	4922
55°	2514
60°	407
65°	52
70°	47
75°	62
80°	64
85°	58

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5773 cd/sqm

TEST NUMBER: P979352

CATALOG NUMBER: PRLX-240-930-LL2-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	4.9
10°-20°	173.0	13.9
20°-30°	257.8	20.7
30°-40°	306.8	24.6
40°-50°	306.2	24.6
50°-60°	134.3	10.8
60°-70°	4.7	0.4
70°-80°	1.6	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.2	39.5
0°-40°	799.0	64.1
0°-60°	1239.6	99.4
0°-90°	1246.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1246.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	651	
5°	647	61
15°	613	173
25°	560	258
35°	491	307
45°	405	306
55°	143	134
65°	2	5
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P979352

CATALOG NUMBER: PRLX-240-930-LL2-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	651.3
2.5°	650.8
5°	647.0
7.5°	641.5
10°	634.9
12.5°	625.6
15°	613.1
17.5°	600.5
20°	589.0
22.5°	575.4
25°	560.1
27.5°	542.6
30°	525.6
32.5°	508.2
35°	490.7
37.5°	471.6
40°	451.9
42.5°	431.1
45°	405.4
47.5°	369.4
50°	314.2
52.5°	236.1
55°	143.2
57.5°	64.5
60°	20.2
62.5°	4.4
65°	2.2
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

TEST NUMBER: P979352

CATALOG NUMBER: PRLX-240-930-LL2-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.84	10.19	9.20	10.50	10.81	8.84	10.19	9.20	10.50	10.81
	3H	8.72	9.90	9.10	10.23	10.59	8.72	9.90	9.10	10.23	10.59
	4H	8.65	9.74	9.05	10.09	10.48	8.65	9.74	9.05	10.09	10.48
	6H	8.58	9.58	9.00	9.95	10.35	8.58	9.58	9.00	9.95	10.35
	8H	8.54	9.49	8.97	9.88	10.28	8.54	9.49	8.97	9.88	10.28
	12H	8.50	9.41	8.94	9.79	10.22	8.50	9.41	8.94	9.79	10.22
4H	2H	8.64	9.74	9.05	10.09	10.47	8.64	9.74	9.05	10.09	10.47
	3H	8.52	9.40	8.94	9.80	10.21	8.52	9.40	8.94	9.80	10.21
	4H	8.44	9.22	8.88	9.64	10.08	8.44	9.22	8.88	9.64	10.08
	6H	8.38	9.04	8.84	9.49	9.96	8.38	9.04	8.84	9.49	9.96
	8H	8.32	8.95	8.79	9.39	9.87	8.32	8.95	8.79	9.39	9.87
	12H	8.28	8.83	8.77	9.31	9.79	8.28	8.83	8.77	9.31	9.79
8H	4H	8.31	8.93	8.78	9.38	9.85	8.31	8.93	8.78	9.38	9.85
	6H	8.21	8.73	8.72	9.23	9.71	8.21	8.73	8.72	9.23	9.71
	8H	8.16	8.63	8.68	9.14	9.63	8.16	8.63	8.68	9.14	9.63
	12H	8.11	8.53	8.63	9.03	9.60	8.11	8.53	8.63	9.03	9.60
12H	4H	8.26	8.81	8.74	9.29	9.77	8.26	8.81	8.74	9.29	9.77
	6H	8.15	8.62	8.67	9.13	9.62	8.15	8.62	8.67	9.13	9.62
	8H	8.11	8.53	8.62	9.03	9.60	8.11	8.53	8.62	9.03	9.60

END OF REPORT