

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979372

Luminaire Tested: PRLX-240-930-LL4-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-LL4-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2208.3 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979372
CATALOG NUMBER: PRLX-240-930-LL4-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979372

CATALOG NUMBER: PRLX-240-930-LL4-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	106	104	101	102	100	98	99	97	95	95	94	92	90
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	57	51	47	46
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	51	44	40	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	11618
5°	11583
10°	11499
15°	11321
20°	11180
25°	11022
30°	10826
35°	10684
40°	10522
45°	10227
50°	8719
55°	4452
60°	721
65°	93
70°	85
75°	113
80°	110
85°	116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10227 cd/sqm

TEST NUMBER: P979372

CATALOG NUMBER: PRLX-240-930-LL4-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	4.9
10°-20°	306.5	13.9
20°-30°	456.7	20.7
30°-40°	543.4	24.6
40°-50°	542.5	24.6
50°-60°	237.9	10.8
60°-70°	8.2	0.4
70°-80°	2.9	0.1
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	871.9	39.5
0°-40°	1415.3	64.1
0°-60°	2195.8	99.4
0°-90°	2208.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2208.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1154	
5°	1146	109
15°	1086	306
25°	992	457
35°	869	543
45°	718	543
55°	254	238
65°	4	8
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P979372

CATALOG NUMBER: PRLX-240-930-LL4-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1153.8
2.5°	1152.8
5°	1146.0
7.5°	1136.3
10°	1124.7
12.5°	1108.3
15°	1086.0
17.5°	1063.8
20°	1043.4
22.5°	1019.2
25°	992.1
27.5°	961.2
30°	931.1
32.5°	900.2
35°	869.2
37.5°	835.3
40°	800.5
42.5°	763.7
45°	718.2
47.5°	654.3
50°	556.6
52.5°	418.1
55°	253.6
57.5°	114.2
60°	35.8
62.5°	7.7
65°	3.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	2.9
77.5°	2.9
80°	1.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0



TEST NUMBER: P979372
 CATALOG NUMBER: PRLX-240-930-LL4-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.82	12.17	11.19	12.48	12.80	10.82	12.17	11.19	12.48	12.80
	3H	10.70	11.88	11.08	12.21	12.57	10.70	11.88	11.08	12.21	12.57
	4H	10.64	11.73	11.04	12.08	12.46	10.64	11.73	11.04	12.08	12.46
	6H	10.57	11.57	10.98	11.94	12.33	10.57	11.57	10.98	11.94	12.33
	8H	10.53	11.47	10.96	11.86	12.27	10.53	11.47	10.96	11.86	12.27
	12H	10.49	11.39	10.92	11.77	12.20	10.49	11.39	10.92	11.77	12.20
4H	2H	10.63	11.72	11.03	12.07	12.45	10.63	11.72	11.03	12.07	12.45
	3H	10.51	11.38	10.92	11.79	12.19	10.51	11.38	10.92	11.79	12.19
	4H	10.43	11.20	10.86	11.62	12.07	10.43	11.20	10.86	11.62	12.07
	6H	10.36	11.03	10.82	11.47	11.94	10.36	11.03	10.82	11.47	11.94
	8H	10.31	10.93	10.78	11.38	11.85	10.31	10.93	10.78	11.38	11.85
	12H	10.26	10.82	10.75	11.30	11.77	10.26	10.82	10.75	11.30	11.77
8H	4H	10.29	10.92	10.76	11.36	11.83	10.29	10.92	10.76	11.36	11.83
	6H	10.20	10.71	10.70	11.21	11.69	10.20	10.71	10.70	11.21	11.69
	8H	10.14	10.61	10.66	11.13	11.62	10.14	10.61	10.66	11.13	11.62
	12H	10.10	10.52	10.61	11.01	11.58	10.10	10.52	10.61	11.01	11.58
12H	4H	10.24	10.79	10.73	11.28	11.75	10.24	10.79	10.73	11.28	11.75
	6H	10.13	10.60	10.65	11.12	11.61	10.13	10.60	10.65	11.12	11.61
	8H	10.09	10.51	10.61	11.01	11.58	10.09	10.51	10.61	11.01	11.58