

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212544

Luminaire Tested: **LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212544
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3382.4 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	26268	26268	26268
5°	67384	23896	7443
10°	131356	18367	3576
15°	235795	12476	4796
20°	350084	9466	7918
25°	397921	7801	12418
30°	431349	8531	11678
35°	454355	5529	7243
40°	464176	2456	3524
45°	419245	938	1309
50°	275975	368	368
55°	75576	323	0
60°	15095	370	0
65°	1060	499	0
70°	164	617	0
75°	0	915	0
80°	0	1364	149
85°	0	2717	296



TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.7	2.2
10°-20°	397.0	11.7
20°-30°	899.9	26.6
30°-40°	1080.2	31.9
40°-50°	761.3	22.5
50°-60°	157.1	4.6
60°-70°	5.6	0.2
70°-80°	3.3	0.1
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.7	40.6
0°-40°	2451.9	72.5
0°-60°	3370.3	99.6
0°-90°	3382.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3382.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	610	610	610	610	610	
5°	1559	1136	553	230	172	192
15°	5290	2327	280	100	108	1570
25°	8376	2815	164	230	261	3866
35°	8644	1971	105	138	138	5374
45°	6885	676	15	21	22	5064
55°	1007	14	4	3	0	1327
65°	10	3	5	3	0	31
75°	0	3	6	4	0	0
85°	0	4	6	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1
2.5°	1040.0	1008.7	1021.0	984.6	976.6	969.9	976.6	937.3	915.2	886.9	864.1
5°	1559.1	1521.5	1530.2	1466.9	1438.0	1418.3	1414.6	1333.4	1272.5	1205.5	1135.9
7.5°	2170.4	2134.8	2129.8	2031.4	1971.8	1938.0	1923.8	1807.6	1702.4	1583.1	1452.7
10°	3004.5	2923.2	2898.0	2755.3	2641.5	2569.6	2481.1	2295.3	2110.8	1930.6	1764.5
12.5°	3975.0	3930.7	3868.0	3616.4	3417.1	3315.0	3182.8	2892.5	2613.2	2315.6	2037.6
15°	5289.9	5132.5	5025.4	4661.9	4340.9	4183.5	3990.4	3546.3	3124.3	2747.3	2327.3
17.5°	6574.7	6492.3	6325.0	5853.3	5358.8	5110.3	4822.5	4219.1	3623.2	3086.9	2573.9
20°	7640.6	7563.0	7372.4	6927.7	6379.1	6012.6	5650.3	4822.5	4043.9	3357.4	2738.7
22.5°	8151.0	8101.8	7946.2	7565.5	7098.1	6749.3	6360.0	5336.0	4355.0	3534.6	2813.8
25°	8376.1	8353.4	8253.1	7953.0	7512.6	7216.8	6849.0	5699.5	4548.8	3617.0	2815.0
27.5°	8604.3	8608.6	8387.2	8149.8	7732.2	7448.1	7093.7	5860.6	4583.9	3570.9	2722.8
30°	8676.2	8630.7	8533.0	8192.3	7795.5	7493.6	7113.4	5786.2	4439.9	3381.5	2538.8
32.5°	8646.8	8628.9	8521.3	8160.9	7687.9	7355.1	6923.4	5491.0	4155.7	3110.8	2278.1
35°	8644.3	8611.0	8364.4	8055.1	7472.6	7061.7	6492.9	5013.7	3753.5	2754.1	1971.2
37.5°	8488.0	8405.6	8220.5	7803.5	7036.0	6515.0	5877.2	4430.7	3261.5	2353.8	1666.7
40°	8258.6	8147.9	7904.4	7273.4	6279.5	5679.2	5056.8	3768.3	2740.5	1958.9	1343.2
42.5°	7779.5	7612.3	7267.8	6400.0	5271.5	4730.2	4212.3	3097.3	2235.0	1596.0	1025.2
45°	6885.3	6656.5	6190.9	5238.2	4258.5	3816.9	3400.5	2492.1	1789.1	1183.9	675.9
47.5°	5534.0	5321.9	4898.1	4169.9	3339.7	2966.3	2634.2	1853.7	1212.8	685.8	322.9
50°	4120.1	3938.1	3607.1	2898.0	2241.8	1948.4	1664.3	1052.9	568.3	325.9	134.1
52.5°	2458.3	2367.9	2074.5	1607.0	1107.0	953.9	765.7	445.9	286.6	118.0	36.3
55°	1006.8	929.3	819.3	657.5	481.6	408.4	349.3	220.2	89.2	24.6	13.5
57.5°	455.1	437.9	388.0	305.1	221.4	185.8	125.5	41.8	19.7	12.3	8.0
60°	175.3	158.0	135.3	73.2	31.4	26.5	21.5	14.1	9.9	6.8	4.9
62.5°	25.2	24.0	21.5	17.2	13.5	12.3	10.4	7.3	5.5	4.3	3.7
65°	10.4	10.4	9.3	7.3	6.2	5.5	4.9	3.7	3.1	3.1	3.1
67.5°	4.3	4.3	3.7	3.1	2.4	2.4	2.4	1.8	2.4	2.4	3.1
70°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.4	2.4	3.1
72.5°	0.0	0.0	0.6	0.6	1.3	1.3	1.3	1.8	2.4	3.1	3.1
75°	0.0	0.0	0.6	0.6	1.3	1.3	1.3	1.8	2.4	3.1	3.1
77.5°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.1
80°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.7
82.5°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.7
85°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.7
87.5°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1
2.5°	844.5	805.1	794.1	759.6	730.7	716.5	698.7	658.7	628.6	588.6	564.6
5°	1087.3	1012.9	953.9	882.0	834.6	803.8	755.9	682.7	623.6	552.9	502.5
7.5°	1350.0	1214.1	1107.7	989.0	920.7	867.2	785.4	680.3	593.5	499.4	421.3
10°	1603.4	1400.4	1233.1	1062.8	973.0	898.6	786.0	653.8	538.7	420.1	337.6
12.5°	1826.6	1564.6	1329.1	1110.1	998.8	905.9	765.1	606.5	467.4	345.6	273.1
15°	2013.0	1691.9	1396.7	1128.0	1000.7	890.0	721.4	538.7	388.0	279.9	228.7
17.5°	2154.5	1759.0	1417.6	1106.5	964.9	844.5	654.4	453.2	314.9	237.4	192.5
20°	2227.6	1771.9	1387.5	1048.0	899.2	775.6	566.5	367.8	266.9	206.6	161.1
22.5°	2236.9	1735.6	1315.6	964.4	816.2	691.9	469.3	306.9	238.0	182.7	142.1
25°	2182.1	1656.9	1212.8	869.7	725.1	595.9	382.0	274.9	216.5	164.2	163.6
27.5°	2065.3	1521.5	1089.8	759.6	615.1	484.6	324.1	248.5	193.1	174.1	185.1
30°	1900.4	1348.1	938.6	620.6	480.3	372.7	273.1	204.8	169.7	171.6	180.8
32.5°	1677.2	1132.9	760.8	454.5	343.8	280.4	204.8	139.6	140.8	141.4	149.4
35°	1396.7	908.4	568.3	305.6	241.7	197.5	115.6	102.7	104.5	105.2	110.7
37.5°	1119.4	698.0	377.6	203.5	152.0	103.9	72.0	68.9	70.1	69.5	75.6
40°	857.3	486.5	226.3	100.9	58.4	48.6	44.2	42.4	43.1	43.7	47.3
42.5°	607.0	263.8	112.0	38.2	30.7	28.3	26.5	25.2	25.8	25.8	28.3
45°	308.2	124.8	38.2	20.9	19.0	17.2	16.0	15.4	15.4	15.4	16.6
47.5°	133.5	41.2	17.9	12.9	11.7	11.1	9.9	9.3	9.3	9.3	9.9
50°	41.8	16.6	11.1	8.6	7.3	6.8	6.2	6.2	6.2	5.5	6.2
52.5°	15.4	10.4	7.3	5.5	4.9	4.9	4.9	4.3	4.9	4.3	4.9
55°	9.3	6.8	4.9	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
57.5°	6.2	4.9	4.3	4.3	3.7	3.7	4.3	4.3	4.3	4.3	4.3
60°	4.3	4.3	3.7	3.7	3.7	3.7	4.3	4.3	4.3	4.3	4.3
62.5°	3.7	3.7	3.7	3.7	3.7	3.7	4.3	4.3	4.3	4.3	4.9
65°	3.1	3.7	3.7	3.7	3.7	3.7	4.3	4.3	4.9	4.9	4.9
67.5°	3.1	3.7	3.7	4.3	4.3	4.3	4.3	4.9	4.9	4.9	4.9
70°	3.7	3.7	4.3	4.3	4.3	4.3	4.9	4.9	4.9	4.9	5.5
72.5°	3.7	3.7	4.3	4.3	4.3	4.3	4.9	4.9	5.5	5.5	5.5
75°	3.7	4.3	4.3	4.3	4.3	4.9	4.9	4.9	5.5	5.5	5.5
77.5°	3.7	4.3	4.3	4.9	4.9	4.9	4.9	5.5	5.5	5.5	5.5
80°	3.7	4.3	4.3	4.9	4.9	4.9	5.5	5.5	5.5	5.5	6.2
82.5°	3.7	4.3	4.3	4.9	4.9	4.9	5.5	5.5	5.5	5.5	6.2
85°	4.3	4.3	4.9	4.9	4.9	4.9	5.5	5.5	5.5	5.5	6.2
87.5°	4.3	4.3	4.9	4.9	4.9	4.9	5.5	5.5	6.2	5.5	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1
2.5°	532.7	496.9	472.4	463.1	445.3	417.0	400.4	385.0	356.1	350.0	333.9
5°	444.6	387.5	346.9	331.5	311.2	287.2	263.8	248.5	230.0	222.7	211.6
7.5°	350.6	293.4	258.3	246.0	231.8	212.2	191.3	175.9	156.9	147.0	137.8
10°	275.5	233.1	203.5	191.3	176.5	155.6	134.1	113.8	97.2	86.7	84.9
12.5°	223.9	188.9	157.5	144.5	127.3	106.4	91.0	90.4	89.2	88.6	89.8
15°	183.3	149.4	116.2	102.1	97.2	96.6	98.4	100.3	99.6	101.5	102.7
17.5°	150.7	114.4	107.0	107.6	108.3	110.1	113.1	118.0	118.7	121.8	124.2
20°	123.0	121.1	124.2	126.7	128.6	132.2	139.0	145.2	147.0	151.3	156.2
22.5°	139.6	145.2	152.0	154.9	157.5	164.2	171.6	181.4	185.1	190.7	197.5
25°	168.5	177.7	188.2	191.8	195.6	206.6	215.2	226.9	230.0	236.8	243.5
27.5°	192.5	202.4	213.4	218.3	221.4	232.5	239.9	247.2	247.2	251.0	255.9
30°	188.9	196.8	206.0	209.7	211.0	219.0	226.3	228.7	227.6	229.4	233.1
32.5°	156.9	163.0	170.4	173.4	174.7	180.2	186.3	186.3	185.8	185.8	188.2
35°	116.2	120.6	124.2	127.3	129.2	132.8	138.4	137.8	137.8	136.5	138.4
37.5°	78.1	80.6	84.9	86.1	86.7	89.2	93.5	93.5	92.3	92.8	94.1
40°	47.3	50.4	52.9	53.5	54.8	56.6	59.7	59.7	59.7	59.7	60.3
42.5°	28.3	30.1	32.0	32.0	32.6	35.1	36.3	36.3	36.3	36.3	36.9
45°	16.6	17.2	18.5	19.0	19.0	20.3	20.9	20.9	20.9	20.9	21.5
47.5°	9.9	10.4	10.4	11.1	11.1	11.7	12.3	12.3	11.7	11.7	11.7
50°	6.2	6.2	6.2	6.2	6.8	6.8	6.8	6.8	6.8	6.8	6.2
52.5°	4.9	4.9	4.9	4.9	4.3	4.3	4.3	4.3	3.7	3.7	3.1
55°	4.3	4.3	4.3	4.3	4.3	3.7	3.7	3.7	3.1	2.4	1.8
57.5°	4.3	4.3	4.3	4.3	4.3	3.7	3.7	3.1	2.4	2.4	1.8
60°	4.3	4.3	4.3	4.3	4.3	3.7	3.7	3.1	2.4	2.4	1.8
62.5°	4.9	4.9	4.3	4.3	4.3	3.7	3.7	3.1	3.1	2.4	1.8
65°	4.9	4.9	4.3	4.3	4.3	4.3	3.7	3.7	3.1	2.4	1.8
67.5°	4.9	4.9	4.9	4.9	4.3	4.3	4.3	3.7	3.1	2.4	1.8
70°	5.5	5.5	4.9	4.9	4.9	4.3	4.3	3.7	3.1	3.1	2.4
72.5°	5.5	5.5	4.9	4.9	4.9	4.9	4.3	3.7	3.7	3.1	2.4
75°	5.5	5.5	5.5	5.5	4.9	4.9	4.3	4.3	3.7	3.1	2.4
77.5°	5.5	5.5	5.5	5.5	4.9	4.9	4.9	4.3	3.7	3.1	2.4
80°	5.5	5.5	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.1	2.4
82.5°	6.2	6.2	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.1	3.1
85°	6.2	6.2	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.7	3.1
87.5°	6.2	6.2	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.7	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212544

CATALOG NUMBER: LDSQA6A40927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1
2.5°	324.1	305.6	299.6	303.8	298.9	295.2	290.3	287.9
5°	203.0	189.4	185.1	186.3	182.1	178.3	173.4	172.2
7.5°	124.8	112.0	107.0	107.0	102.1	97.8	94.7	92.8
10°	83.7	81.1	81.8	82.4	81.8	82.4	80.6	81.8
12.5°	89.8	88.6	89.8	90.4	90.4	91.7	89.2	91.0
15°	104.5	103.4	105.2	106.4	106.4	108.3	105.8	107.6
17.5°	127.9	127.3	130.4	131.6	132.2	135.3	132.2	134.7
20°	161.7	161.1	165.5	167.3	166.6	172.8	168.5	172.8
22.5°	205.5	204.2	210.3	212.2	212.8	220.8	217.1	220.2
25°	249.1	250.3	253.4	256.5	257.1	263.8	258.3	261.4
27.5°	258.3	256.5	258.3	262.0	262.7	265.6	260.8	263.2
30°	233.7	230.7	231.3	235.5	236.8	238.0	233.7	234.9
32.5°	190.0	185.1	185.1	189.4	190.7	192.5	185.1	188.2
35°	140.3	135.9	135.9	139.0	139.6	140.8	135.3	137.8
37.5°	95.9	92.3	93.5	94.7	95.3	96.6	95.9	95.3
40°	61.5	59.0	60.9	60.9	61.5	62.1	62.1	62.7
42.5°	37.5	35.6	36.9	36.9	37.5	37.5	37.5	38.2
45°	21.5	20.9	20.9	21.5	21.5	21.5	20.9	21.5
47.5°	11.7	11.1	11.7	11.7	11.7	11.7	11.7	11.7
50°	6.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5
52.5°	3.1	2.4	2.4	2.4	1.8	2.4	1.8	1.8
55°	1.8	1.3	1.3	1.3	0.6	0.6	0.0	0.0
57.5°	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0
60°	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0
62.5°	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0
65°	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0
67.5°	1.8	1.3	0.6	0.6	0.6	0.0	0.0	0.0
70°	1.8	1.3	1.3	0.6	0.6	0.0	0.0	0.0
72.5°	1.8	1.3	1.3	1.3	0.6	0.6	0.0	0.0
75°	1.8	1.3	1.3	1.3	0.6	0.6	0.0	0.0
77.5°	1.8	1.8	1.3	1.3	0.6	0.6	0.6	0.0
80°	2.4	1.8	1.3	1.3	1.3	0.6	0.6	0.6
82.5°	2.4	1.8	1.3	1.3	1.3	0.6	0.6	0.6
85°	2.4	1.8	1.8	1.3	1.3	0.6	0.6	0.6
87.5°	2.4	1.8	1.8	1.3	1.3	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)