

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212546

Luminaire Tested: **LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3557.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	28701	28701	28701
5°	78782	26451	10792
10°	172641	21646	4114
15°	263712	16475	4823
20°	305534	12257	7491
25°	333297	10076	12095
30°	372192	9143	12355
35°	378683	6271	8468
40°	385337	2973	4283
45°	385963	1236	1869
50°	326293	536	576
55°	105069	368	98
60°	20865	422	0
65°	2129	499	0
70°	227	692	0
75°	0	915	0
80°	0	1537	149
85°	0	3063	296



TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	2.5
10°-20°	468.0	13.2
20°-30°	896.1	25.2
30°-40°	1055.8	29.7
40°-50°	829.3	23.3
50°-60°	202.1	5.7
60°-70°	8.7	0.2
70°-80°	3.3	0.1
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1454.7	40.9
0°-40°	2510.5	70.6
0°-60°	3541.8	99.6
0°-90°	3557.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3557.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	667	667	667	667	667	
5°	1823	1319	612	320	250	241
15°	5916	3039	370	106	108	1652
25°	7016	3695	212	222	255	3270
35°	7205	2336	119	154	161	4518
45°	6339	722	20	28	31	4763
55°	1400	26	5	3	1	1666
65°	21	3	5	3	0	55
75°	0	3	6	4	0	0
85°	0	4	6	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6
2.5°	1142.7	1140.2	1123.6	1139.0	1092.3	1090.4	1069.5	1060.3	1033.1	1007.3	970.4
5°	1822.8	1782.8	1750.3	1751.5	1661.7	1645.1	1598.3	1551.0	1478.5	1410.7	1319.2
7.5°	2778.5	2731.2	2662.3	2633.4	2461.9	2411.4	2314.8	2188.8	2030.7	1873.3	1703.5
10°	3948.8	3956.3	3867.1	3784.7	3525.1	3423.0	3266.8	3018.4	2718.9	2423.0	2122.3
12.5°	5126.6	5121.6	5015.3	4890.4	4570.6	4426.7	4218.8	3908.9	3512.2	3053.4	2583.0
15°	5916.2	5951.2	5906.4	5806.7	5533.7	5368.8	5134.6	4713.9	4230.5	3673.3	3038.6
17.5°	6411.9	6445.1	6429.1	6351.0	6110.0	5934.0	5738.5	5394.0	4835.0	4134.6	3397.8
20°	6668.3	6720.7	6713.2	6628.4	6446.3	6300.5	6084.7	5765.6	5281.5	4455.0	3630.3
22.5°	6839.3	6879.3	6890.4	6794.5	6606.2	6467.9	6309.8	5986.3	5531.2	4650.5	3722.6
25°	7015.8	7086.6	7017.0	6899.0	6726.2	6593.3	6424.8	6114.9	5650.5	4730.5	3694.9
27.5°	7232.2	7266.2	7108.7	7001.1	6809.1	6665.3	6486.3	6189.3	5671.5	4666.6	3536.8
30°	7486.3	7346.0	7236.0	7022.5	6804.9	6664.6	6482.6	6142.5	5561.4	4454.4	3230.5
32.5°	7444.5	7315.9	7191.1	6965.3	6750.1	6611.1	6408.2	5987.0	5301.2	4099.5	2808.1
35°	7204.6	7232.2	7097.6	6910.7	6667.1	6523.8	6302.4	5765.6	4859.7	3610.0	2335.7
37.5°	7002.2	7063.2	6975.2	6802.4	6555.2	6361.5	6062.6	5410.1	4283.4	2988.9	1888.0
40°	6855.9	6875.6	6828.3	6634.5	6337.4	6057.7	5712.1	4771.8	3583.6	2346.2	1490.2
42.5°	6629.0	6681.2	6597.6	6386.0	5935.9	5619.1	5118.5	4034.3	2783.4	1792.1	1121.7
45°	6338.7	6388.5	6285.2	5933.5	5307.4	4843.0	4232.3	3145.7	2059.0	1321.0	722.0
47.5°	5865.2	5895.9	5696.0	5209.5	4299.4	3862.2	3236.1	2193.0	1326.5	738.6	351.1
50°	4871.3	4856.6	4444.6	3846.1	2875.7	2416.9	1926.1	1188.8	595.9	349.9	219.6
52.5°	3139.5	3105.7	2697.9	2153.7	1456.3	1111.3	835.2	512.9	310.6	195.6	86.7
55°	1399.7	1386.8	1135.2	881.9	595.9	512.9	391.7	251.5	165.5	68.3	26.5
57.5°	519.0	507.3	447.1	375.1	287.8	239.3	190.0	120.6	42.4	22.8	14.1
60°	242.3	241.7	212.8	175.2	121.8	92.3	53.5	28.3	17.9	12.3	8.0
62.5°	77.5	75.6	52.9	38.7	27.6	24.0	19.0	14.1	9.2	6.8	4.9
65°	20.9	20.9	19.0	16.0	12.9	11.1	9.2	6.8	4.3	3.7	3.1
67.5°	8.0	8.0	7.3	6.8	4.9	4.3	3.7	3.1	2.4	3.1	3.1
70°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.4	2.4	3.1
72.5°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.1
75°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.1
77.5°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.1
80°	0.0	0.0	0.6	0.6	1.3	1.3	1.8	1.8	2.4	3.1	3.1
82.5°	0.0	0.0	0.6	1.3	1.3	1.3	1.8	2.4	2.4	3.1	3.7
85°	0.0	0.0	0.6	1.3	1.3	1.8	1.8	2.4	2.4	3.1	3.7
87.5°	0.0	0.0	0.6	1.3	1.3	1.8	1.8	2.4	2.4	3.1	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6
2.5°	943.4	902.8	846.8	814.2	806.2	789.0	758.9	714.0	677.1	641.4	620.6
5°	1241.7	1145.8	1038.1	962.4	931.7	890.5	817.3	741.7	672.1	612.0	564.5
7.5°	1557.8	1399.7	1225.7	1085.5	1035.1	969.9	850.6	738.0	642.7	559.0	495.7
10°	1872.0	1617.5	1381.3	1178.3	1095.9	1007.3	849.9	704.1	592.3	495.1	424.9
12.5°	2186.3	1820.3	1495.7	1234.3	1127.3	1015.4	824.7	652.5	528.3	429.3	362.2
15°	2476.5	1982.1	1573.1	1253.4	1124.2	992.0	773.7	589.7	461.3	369.6	307.5
17.5°	2693.0	2067.0	1591.0	1224.4	1075.6	929.3	695.5	515.9	397.3	316.8	253.4
20°	2799.5	2080.5	1548.5	1142.0	992.0	840.0	610.0	445.2	342.5	267.5	214.0
22.5°	2799.5	2016.5	1456.3	1038.7	887.5	737.3	527.6	386.8	299.5	233.1	188.2
25°	2693.0	1889.2	1332.7	919.4	772.4	635.9	456.3	343.1	266.3	212.1	174.7
27.5°	2486.4	1713.4	1174.0	786.6	659.3	545.5	399.7	303.2	241.1	191.3	191.8
30°	2202.3	1497.5	992.0	646.4	543.0	448.3	336.4	254.0	193.1	183.9	189.4
32.5°	1873.8	1239.2	785.9	501.3	420.7	353.0	255.8	179.6	153.8	154.9	161.1
35°	1536.9	975.4	591.6	371.4	313.0	255.8	167.9	118.0	116.9	119.3	123.6
37.5°	1213.4	730.0	428.0	271.8	210.3	157.5	90.4	81.1	81.1	83.7	86.1
40°	908.9	517.8	294.5	161.1	102.1	72.0	57.2	52.9	52.3	52.9	55.9
42.5°	624.2	327.8	175.2	64.5	49.2	41.8	36.3	33.2	32.6	33.2	35.1
45°	350.6	201.7	68.3	34.5	29.6	26.5	22.8	20.9	20.3	20.3	21.5
47.5°	219.6	80.0	30.7	21.5	18.5	17.2	14.8	13.5	12.9	12.9	13.5
50°	84.2	31.4	19.0	14.1	12.3	11.1	9.9	8.6	8.0	8.0	8.6
52.5°	28.9	18.5	12.3	9.2	8.0	7.3	6.2	5.5	5.5	5.5	5.5
55°	16.0	11.1	7.3	5.5	4.9	4.9	4.9	4.9	4.9	4.9	4.9
57.5°	9.9	6.8	4.9	4.3	4.3	4.3	4.3	4.3	4.3	4.9	4.9
60°	5.5	4.3	3.7	3.7	3.7	3.7	4.3	4.3	4.3	4.9	4.9
62.5°	3.7	3.7	3.7	3.7	3.7	3.7	4.3	4.3	4.9	4.9	4.9
65°	3.1	3.1	3.1	3.7	3.7	3.7	4.3	4.3	4.9	4.9	4.9
67.5°	3.1	3.1	3.7	3.7	3.7	4.3	4.3	4.9	4.9	4.9	4.9
70°	3.1	3.7	3.7	4.3	4.3	4.3	4.9	4.9	4.9	5.5	5.5
72.5°	3.1	3.7	3.7	4.3	4.3	4.3	4.9	4.9	5.5	5.5	5.5
75°	3.7	3.7	3.7	4.3	4.3	4.3	4.9	5.5	5.5	5.5	5.5
77.5°	3.7	3.7	4.3	4.3	4.3	4.9	4.9	5.5	5.5	5.5	5.5
80°	3.7	3.7	4.3	4.3	4.9	4.9	5.5	5.5	5.5	6.2	6.2
82.5°	3.7	3.7	4.3	4.9	4.9	4.9	5.5	5.5	6.2	6.2	6.2
85°	3.7	4.3	4.3	4.9	4.9	4.9	5.5	5.5	6.2	6.2	6.2
87.5°	3.7	4.3	4.3	4.9	4.9	4.9	5.5	5.5	6.2	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6
2.5°	592.8	567.0	541.2	522.1	512.9	503.7	483.4	456.9	445.9	429.9	420.7
5°	516.6	473.0	438.5	415.8	402.2	384.4	361.0	335.2	320.4	303.8	292.7
7.5°	437.9	386.8	353.7	332.7	319.2	297.0	267.5	236.8	218.9	200.4	187.6
10°	369.0	320.4	282.9	258.9	241.7	215.9	186.3	164.8	149.4	133.5	120.6
12.5°	308.2	255.8	215.9	195.6	183.9	159.3	134.7	110.7	101.4	98.4	98.4
15°	249.7	202.4	168.5	151.3	139.0	112.5	107.6	106.4	105.8	105.2	106.4
17.5°	203.5	163.5	127.9	119.3	118.0	117.5	118.0	118.0	118.7	120.6	123.6
20°	171.0	134.1	131.6	132.2	132.2	134.7	137.8	140.3	142.7	145.8	151.3
22.5°	151.9	151.3	155.6	156.2	159.3	163.0	168.5	172.2	178.3	181.4	189.4
25°	175.2	179.6	187.6	190.0	194.9	201.1	209.7	214.6	222.0	225.7	234.9
27.5°	198.6	205.4	215.2	218.3	222.7	232.4	238.6	242.9	246.6	249.0	254.6
30°	196.8	203.0	212.8	213.4	219.6	226.3	230.0	233.7	236.2	235.5	238.6
32.5°	166.6	172.2	181.4	181.4	188.2	193.7	195.6	198.6	198.6	198.6	199.9
35°	127.9	131.6	137.8	139.6	145.1	148.9	150.0	153.8	153.8	152.5	152.5
37.5°	88.6	93.5	97.8	99.0	102.7	105.2	108.2	108.9	107.6	108.2	108.2
40°	57.8	60.9	63.9	64.5	67.6	69.5	72.5	72.5	73.2	72.5	73.8
42.5°	35.6	38.2	40.0	41.2	42.4	43.7	45.5	46.1	46.8	46.1	47.3
45°	22.1	23.4	24.6	25.2	25.8	26.5	28.3	28.3	28.3	28.3	28.9
47.5°	13.5	14.1	14.8	14.8	15.4	16.0	16.6	16.6	16.6	16.6	17.2
50°	8.0	8.6	8.6	8.6	9.2	9.2	9.9	9.9	9.9	9.2	9.9
52.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.9	5.5
55°	4.9	4.9	4.3	4.3	4.3	4.3	4.3	3.7	3.1	3.1	2.4
57.5°	4.3	4.3	4.3	4.3	4.3	3.7	3.7	3.1	3.1	2.4	1.8
60°	4.3	4.3	4.3	4.3	4.3	3.7	3.7	3.1	2.4	2.4	1.8
62.5°	4.9	4.3	4.3	4.3	4.3	3.7	3.7	3.1	2.4	2.4	1.8
65°	4.9	4.9	4.3	4.3	4.3	3.7	3.7	3.1	3.1	2.4	1.8
67.5°	4.9	4.9	4.9	4.3	4.9	4.3	3.7	3.7	3.1	2.4	2.4
70°	5.5	4.9	4.9	4.9	4.9	4.3	4.3	3.7	3.1	2.4	2.4
72.5°	5.5	5.5	4.9	4.9	4.9	4.3	4.3	3.7	3.1	3.1	2.4
75°	5.5	5.5	4.9	4.9	4.9	4.3	4.3	3.7	3.7	3.1	2.4
77.5°	5.5	5.5	5.5	4.9	4.9	4.9	4.3	4.3	3.7	3.1	2.4
80°	5.5	5.5	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.1	2.4
82.5°	6.2	5.5	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.1	3.1
85°	6.2	6.2	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.7	3.1
87.5°	6.2	5.5	5.5	5.5	5.5	4.9	4.9	4.3	3.7	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212546

CATALOG NUMBER: LDSQA6A40927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	666.6	666.6	666.6	666.6	666.6	666.6	666.6	666.6
2.5°	411.4	406.5	406.5	397.9	396.6	389.9	395.5	391.7
5°	280.4	272.4	270.0	261.4	258.3	250.3	252.8	249.7
7.5°	176.5	168.5	166.1	159.9	156.2	150.0	150.7	148.9
10°	107.6	100.3	98.4	96.6	94.7	94.1	94.7	94.1
12.5°	97.8	97.2	95.9	96.6	95.3	95.9	96.6	95.9
15°	106.4	107.6	106.4	107.0	106.4	107.6	108.2	108.2
17.5°	124.8	127.3	126.1	127.9	127.3	130.4	130.4	130.4
20°	153.1	157.5	156.2	158.7	158.7	162.4	162.4	163.5
22.5°	192.5	198.0	197.5	203.0	201.7	206.0	206.0	207.2
25°	239.9	245.4	246.0	249.7	249.0	253.4	253.4	254.6
27.5°	259.6	262.6	262.0	263.8	264.5	266.9	268.7	267.5
30°	243.5	246.0	245.4	246.6	246.6	248.5	250.3	248.5
32.5°	204.8	206.6	206.6	209.1	207.2	207.9	211.0	209.1
35°	156.8	158.0	156.8	158.0	158.7	158.7	161.7	161.1
37.5°	112.0	112.5	112.5	114.4	112.5	112.5	115.6	116.2
40°	75.1	75.6	75.1	77.5	76.2	76.2	78.1	76.2
42.5°	48.0	48.6	48.0	49.8	48.6	49.8	50.4	51.0
45°	29.6	29.6	28.9	30.1	29.6	30.1	30.7	30.7
47.5°	17.2	17.2	16.6	17.9	17.2	17.2	17.2	17.9
50°	9.2	9.2	9.2	9.9	9.2	9.2	9.2	8.6
52.5°	4.9	4.9	4.3	4.9	4.3	4.3	4.3	4.3
55°	2.4	1.8	1.8	1.8	1.3	1.3	1.3	1.3
57.5°	1.8	1.3	1.3	0.6	0.6	0.6	0.0	0.0
60°	1.3	1.3	0.6	0.6	0.0	0.0	0.0	0.0
62.5°	1.3	1.3	0.6	0.6	0.0	0.0	0.0	0.0
65°	1.3	1.3	0.6	0.6	0.0	0.0	0.0	0.0
67.5°	1.8	1.3	1.3	0.6	0.6	0.0	0.0	0.0
70°	1.8	1.3	1.3	0.6	0.6	0.0	0.0	0.0
72.5°	1.8	1.3	1.3	1.3	0.6	0.6	0.0	0.0
75°	1.8	1.8	1.3	1.3	0.6	0.6	0.0	0.0
77.5°	2.4	1.8	1.3	1.3	0.6	0.6	0.0	0.0
80°	2.4	1.8	1.3	1.3	1.3	0.6	0.6	0.6
82.5°	2.4	1.8	1.8	1.3	1.3	0.6	0.6	0.6
85°	2.4	1.8	1.8	1.3	1.3	0.6	0.6	0.6
87.5°	2.4	1.8	1.8	1.3	1.3	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)