

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979422

Luminaire Tested: PRLX-240-935-12L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-935-12L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 881.2 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979422

CATALOG NUMBER: PRLX-240-935-12L-F-U-S-BLAK-X

Luminous Intensity Polar Plot



CATALOG NUMBER: PRLX-240-935-12L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	109	106	104	101	102	100	98	99	97	95	95	94	92	90		
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57		
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51		
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	57	51	47	46		
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	51	44	40	50	44	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4635
5°	4621
10°	4589
15°	4517
20°	4461
25°	4397
30°	4319
35°	4263
40°	4198
45°	4081
50°	3479
55°	1777
60°	288
65°	36
70°	35
75°	47
80°	46
85°	46

MAXIMUM LUMINANCE 45°-90°:

Luminance: 4081 cd/sqm

TEST NUMBER: P979422

CATALOG NUMBER: PRLX-240-935-12L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	4.9
10°-20°	122.3	13.9
20°-30°	182.2	20.7
30°-40°	216.8	24.6
40°-50°	216.5	24.6
50°-60°	94.9	10.8
60°-70°	3.3	0.4
70°-80°	1.2	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.9	39.5
0°-40°	564.7	64.1
0°-60°	876.1	99.4
0°-90°	881.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	457	43
15°	433	122
25°	396	182
35°	347	217
45°	287	216
55°	101	95
65°	2	3
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P979422

CATALOG NUMBER: PRLX-240-935-12L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.3
2.5°	460.0
5°	457.2
7.5°	453.4
10°	448.8
12.5°	442.2
15°	433.3
17.5°	424.4
20°	416.3
22.5°	406.7
25°	395.8
27.5°	383.5
30°	371.5
32.5°	359.2
35°	346.8
37.5°	333.3
40°	319.4
42.5°	304.7
45°	286.6
47.5°	261.1
50°	222.1
52.5°	166.8
55°	101.2
57.5°	45.6
60°	14.3
62.5°	3.1
65°	1.5
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

TEST NUMBER: P979422

CATALOG NUMBER: PRLX-240-935-12L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.64	8.98	8.00	9.30	9.61	7.64	8.98	8.00	9.30	9.61
	3H	7.51	8.69	7.89	9.02	9.39	7.51	8.69	7.89	9.02	9.39
	4H	7.45	8.54	7.85	8.89	9.28	7.45	8.54	7.85	8.89	9.28
	6H	7.38	8.38	7.79	8.75	9.14	7.38	8.38	7.79	8.75	9.14
	8H	7.34	8.29	7.77	8.68	9.08	7.34	8.29	7.77	8.68	9.08
	12H	7.30	8.21	7.73	8.59	9.02	7.30	8.21	7.73	8.59	9.02
4H	2H	7.44	8.53	7.84	8.88	9.27	7.44	8.53	7.84	8.88	9.27
	3H	7.32	8.19	7.73	8.60	9.00	7.32	8.19	7.73	8.60	9.00
	4H	7.24	8.02	7.68	8.44	8.88	7.24	8.02	7.68	8.44	8.88
	6H	7.17	7.84	7.64	8.29	8.76	7.17	7.84	7.64	8.29	8.76
	8H	7.12	7.75	7.59	8.19	8.67	7.12	7.75	7.59	8.19	8.67
	12H	7.08	7.63	7.57	8.12	8.59	7.08	7.63	7.57	8.12	8.59
8H	4H	7.11	7.73	7.58	8.18	8.65	7.11	7.73	7.58	8.18	8.65
	6H	7.01	7.53	7.52	8.03	8.51	7.01	7.53	7.52	8.03	8.51
	8H	6.96	7.43	7.48	7.94	8.43	6.96	7.43	7.48	7.94	8.43
	12H	6.91	7.34	7.43	7.83	8.40	6.91	7.34	7.43	7.83	8.40
12H	4H	7.06	7.61	7.54	8.09	8.57	7.06	7.61	7.54	8.09	8.57
	6H	6.95	7.42	7.47	7.93	8.42	6.95	7.42	7.47	7.93	8.42
	8H	6.91	7.33	7.42	7.83	8.40	6.91	7.33	7.42	7.83	8.40