

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212550

Luminaire Tested: **LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3620.1 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	28115	28115	28115
5°	72121	25578	7965
10°	140581	19656	3825
15°	252363	13350	5131
20°	374679	10135	8476
25°	425883	8347	13292
30°	461666	9128	12499
35°	486281	5913	7748
40°	496798	2630	3771
45°	448704	999	1400
50°	295367	395	395
55°	80890	345	0
60°	16154	396	0
65°	1141	540	0
70°	176	667	0
75°	0	981	0
80°	0	1463	174
85°	0	2915	346

TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	2.2
10°-20°	424.9	11.7
20°-30°	963.1	26.6
30°-40°	1156.1	31.9
40°-50°	814.8	22.5
50°-60°	168.1	4.6
60°-70°	6.0	0.2
70°-80°	3.6	0.1
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1468.1	40.6
0°-40°	2624.2	72.5
0°-60°	3607.1	99.6
0°-90°	3620.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3620.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	653	653	653	653	653	
5°	1669	1216	592	246	184	205
15°	5662	2491	300	107	115	1680
25°	8965	3013	176	246	280	4137
35°	9252	2110	112	147	147	5751
45°	7369	723	16	22	23	5420
55°	1078	14	5	3	0	1420
65°	11	3	5	3	0	33
75°	0	3	6	4	0	0
85°	0	4	6	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0
2.5°	1113.1	1079.5	1092.7	1053.8	1045.3	1038.1	1045.3	1003.2	979.4	949.2	924.8
5°	1668.7	1628.5	1637.8	1569.9	1539.0	1517.9	1514.0	1427.1	1362.0	1290.2	1215.8
7.5°	2322.9	2284.8	2279.5	2174.2	2110.3	2074.1	2059.0	1934.6	1822.1	1694.4	1554.8
10°	3215.5	3128.7	3101.6	2948.9	2827.2	2750.2	2655.3	2456.5	2259.1	2066.3	1888.5
12.5°	4254.3	4206.8	4139.7	3870.5	3657.3	3547.9	3406.4	3095.7	2796.9	2478.3	2180.7
15°	5661.6	5493.1	5378.6	4989.5	4645.9	4477.4	4270.7	3795.5	3343.9	2940.4	2490.8
17.5°	7036.6	6948.4	6769.4	6264.5	5735.3	5469.4	5161.3	4515.6	3877.7	3303.7	2754.7
20°	8177.4	8094.5	7890.4	7414.5	6827.4	6435.0	6047.4	5161.3	4328.0	3593.4	2931.2
22.5°	8723.8	8671.1	8504.6	8097.1	7596.8	7223.7	6806.9	5711.0	4661.0	3783.0	3011.5
25°	8964.7	8940.3	8833.0	8511.8	8040.5	7723.8	7330.3	6100.0	4868.4	3871.1	3012.8
27.5°	9208.9	9213.5	8976.6	8722.5	8275.5	7971.4	7592.3	6272.4	4905.9	3821.8	2914.0
30°	9286.0	9237.2	9132.6	8767.9	8343.3	8020.1	7613.3	6192.8	4751.9	3619.0	2717.3
32.5°	9254.3	9235.2	9120.0	8734.3	8228.1	7872.0	7409.9	5876.9	4447.8	3329.4	2438.2
35°	9251.7	9216.1	8952.2	8621.1	7997.7	7558.0	6949.1	5366.0	4017.3	2947.7	2109.6
37.5°	9084.5	8996.3	8798.1	8351.8	7530.4	6972.9	6290.2	4742.0	3490.7	2519.1	1783.8
40°	8839.0	8720.5	8459.8	7784.4	6720.8	6078.3	5412.1	4033.0	2933.2	2096.5	1437.6
42.5°	8326.1	8147.1	7778.5	6849.7	5641.8	5062.6	4508.3	3314.9	2392.1	1708.2	1097.3
45°	7369.1	7124.2	6625.9	5606.3	4557.7	4085.1	3639.5	2667.2	1914.8	1267.1	723.4
47.5°	5922.9	5695.8	5242.3	4462.9	3574.3	3174.8	2819.3	1984.0	1298.1	734.0	345.5
50°	4409.6	4214.8	3860.6	3101.6	2399.4	2085.3	1781.2	1126.9	608.2	348.9	143.5
52.5°	2631.0	2534.3	2220.3	1720.0	1184.9	1021.0	819.6	477.2	306.7	126.4	38.8
55°	1077.6	994.6	876.7	703.6	515.4	437.1	373.8	235.6	95.4	26.4	14.5
57.5°	487.1	468.7	415.4	326.5	237.0	198.8	134.3	44.7	21.1	13.1	8.6
60°	187.6	169.1	144.8	78.3	33.6	28.3	23.0	15.2	10.5	7.2	5.3
62.5°	27.0	25.7	23.0	18.5	14.5	13.1	11.2	7.9	5.9	4.6	4.0
65°	11.2	11.2	9.9	7.9	6.6	5.9	5.3	4.0	3.3	3.3	3.3
67.5°	4.6	4.6	4.0	3.3	2.6	2.6	2.6	1.9	2.6	2.6	3.3
70°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.6	2.6	3.3
72.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	1.9	2.6	3.3	3.3
75°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	1.9	2.6	3.3	3.3
77.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	3.3
80°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	4.0
82.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	4.0
85°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	4.0
87.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0
2.5°	903.8	861.7	849.8	813.0	782.0	766.9	747.8	705.0	672.7	629.9	604.2
5°	1163.7	1084.1	1021.0	944.0	893.3	860.3	809.0	730.7	667.5	591.8	537.8
7.5°	1444.8	1299.4	1185.5	1058.4	985.4	928.1	840.6	728.0	635.2	534.5	450.9
10°	1716.1	1498.8	1319.7	1137.5	1041.3	961.7	841.3	699.7	576.6	449.6	361.4
12.5°	1955.0	1674.6	1422.4	1188.2	1069.0	969.6	818.9	649.1	500.3	370.0	292.2
15°	2154.5	1810.9	1494.9	1207.2	1071.0	952.5	772.1	576.6	415.4	299.5	244.9
17.5°	2305.8	1882.6	1517.3	1184.2	1032.8	903.8	700.4	485.1	337.0	254.1	206.0
20°	2384.2	1896.5	1485.0	1121.6	962.3	830.1	606.3	393.6	285.6	221.2	172.4
22.5°	2394.0	1857.6	1408.0	1032.2	873.5	740.5	502.2	328.4	254.7	195.5	152.0
25°	2335.5	1773.3	1298.1	930.7	776.1	637.8	408.8	294.2	231.7	175.7	175.1
27.5°	2210.4	1628.5	1166.4	813.0	658.2	518.7	346.9	265.9	206.7	186.2	198.1
30°	2034.0	1442.9	1004.4	664.1	514.1	398.9	292.2	219.2	181.7	183.6	193.5
32.5°	1795.0	1212.5	814.2	486.5	367.9	300.1	219.2	149.4	150.7	151.4	160.0
35°	1494.9	972.3	608.2	327.2	258.7	211.3	123.7	109.9	111.9	112.5	118.5
37.5°	1198.0	747.1	404.2	217.8	162.6	111.3	77.0	73.7	75.1	74.4	81.0
40°	917.6	520.7	242.3	108.0	62.5	52.0	47.4	45.4	46.1	46.8	50.7
42.5°	649.7	282.4	119.8	40.8	32.9	30.2	28.3	27.0	27.6	27.6	30.2
45°	329.8	133.6	40.8	22.4	20.4	18.5	17.1	16.4	16.4	16.4	17.8
47.5°	142.9	44.1	19.1	13.8	12.5	11.9	10.5	9.9	9.9	9.9	10.5
50°	44.7	17.8	11.9	9.2	7.9	7.2	6.6	6.6	6.6	5.9	6.6
52.5°	16.4	11.2	7.9	5.9	5.3	5.3	5.3	4.6	5.3	4.6	5.3
55°	9.9	7.2	5.3	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
57.5°	6.6	5.3	4.6	4.6	4.0	4.0	4.6	4.6	4.6	4.6	4.6
60°	4.6	4.6	4.0	4.0	4.0	4.0	4.6	4.6	4.6	4.6	4.6
62.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.6	4.6	4.6	4.6	5.3
65°	3.3	4.0	4.0	4.0	4.0	4.0	4.6	4.6	5.3	5.3	5.3
67.5°	3.3	4.0	4.0	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.3
70°	4.0	4.0	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.3	5.9
72.5°	4.0	4.0	4.6	4.6	4.6	4.6	5.3	5.3	5.9	5.9	5.9
75°	4.0	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.9	5.9	5.9
77.5°	4.0	4.6	4.6	5.3	5.3	5.3	5.3	5.9	5.9	5.9	5.9
80°	4.0	4.6	4.6	5.3	5.3	5.3	5.9	5.9	5.9	5.9	6.6
82.5°	4.0	4.6	4.6	5.3	5.3	5.3	5.9	5.9	5.9	5.9	6.6
85°	4.6	4.6	5.3	5.3	5.3	5.3	5.9	5.9	5.9	5.9	6.6
87.5°	4.6	4.6	5.3	5.3	5.3	5.3	5.9	5.9	6.6	5.9	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0
2.5°	570.0	531.9	505.5	495.7	476.5	446.3	428.5	412.1	381.1	374.5	357.4
5°	475.9	414.7	371.2	354.8	333.1	307.4	282.4	265.9	246.2	238.3	226.4
7.5°	375.2	314.0	276.5	263.3	248.2	227.1	204.7	188.3	167.9	157.4	147.4
10°	294.9	249.5	217.8	204.7	188.9	166.5	143.5	121.8	104.0	92.8	90.8
12.5°	239.6	202.1	168.5	154.7	136.3	113.9	97.4	96.8	95.4	94.8	96.1
15°	196.2	160.0	124.4	109.3	104.0	103.4	105.3	107.3	106.6	108.6	109.9
17.5°	161.2	122.4	114.6	115.1	115.8	117.9	121.1	126.4	127.0	130.3	132.9
20°	131.7	129.6	132.9	135.6	137.6	141.5	148.8	155.3	157.4	161.9	167.2
22.5°	149.4	155.3	162.6	165.9	168.5	175.7	183.6	194.2	198.1	204.0	211.3
25°	180.4	190.2	201.4	205.4	209.3	221.2	230.4	242.9	246.2	253.4	260.6
27.5°	206.0	216.6	228.5	233.7	237.0	248.8	256.8	264.6	264.6	268.5	273.9
30°	202.1	210.7	220.5	224.5	225.8	234.4	242.3	244.9	243.5	245.6	249.5
32.5°	167.9	174.5	182.4	185.7	186.9	192.9	199.5	199.5	198.8	198.8	201.4
35°	124.4	129.1	132.9	136.3	138.2	142.2	148.1	147.4	147.4	146.2	148.1
37.5°	83.6	86.3	90.8	92.2	92.8	95.4	100.1	100.1	98.7	99.4	100.8
40°	50.7	54.0	56.6	57.3	58.5	60.6	63.9	63.9	63.9	63.9	64.5
42.5°	30.2	32.3	34.2	34.2	34.9	37.5	38.8	38.8	38.8	38.8	39.5
45°	17.8	18.5	19.7	20.4	20.4	21.7	22.4	22.4	22.4	22.4	23.0
47.5°	10.5	11.2	11.2	11.9	11.9	12.5	13.1	13.1	12.5	12.5	12.5
50°	6.6	6.6	6.6	6.6	7.2	7.2	7.2	7.2	7.2	7.2	6.6
52.5°	5.3	5.3	5.3	5.3	4.6	4.6	4.6	4.6	4.0	4.0	3.3
55°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	4.0	3.3	2.6	1.9
57.5°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	2.6	1.9
60°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	2.6	1.9
62.5°	5.3	5.3	4.6	4.6	4.6	4.0	4.0	3.3	3.3	2.6	1.9
65°	5.3	5.3	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	1.9
67.5°	5.3	5.3	5.3	5.3	4.6	4.6	4.6	4.0	3.3	2.6	1.9
70°	5.9	5.9	5.3	5.3	5.3	4.6	4.6	4.0	3.3	3.3	2.6
72.5°	5.9	5.9	5.3	5.3	5.3	5.3	4.6	4.0	4.0	3.3	2.6
75°	5.9	5.9	5.9	5.9	5.3	5.3	4.6	4.6	4.0	3.3	2.6
77.5°	5.9	5.9	5.9	5.9	5.3	5.3	5.3	4.6	4.0	3.3	2.6
80°	5.9	5.9	5.9	5.9	5.9	5.3	5.3	4.6	4.0	3.3	2.6
82.5°	6.6	6.6	5.9	5.9	5.9	5.3	5.3	4.6	4.0	3.3	3.3
85°	6.6	6.6	5.9	5.9	5.9	5.3	5.3	4.6	4.0	4.0	3.3
87.5°	6.6	6.6	5.9	5.9	5.9	5.3	5.3	4.6	4.0	4.0	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212550

CATALOG NUMBER: LDSQA6A40930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	653.0	653.0	653.0	653.0	653.0	653.0	653.0	653.0
2.5°	346.9	327.2	320.6	325.2	319.9	316.0	310.7	308.1
5°	217.3	202.8	198.1	199.5	194.8	190.9	185.7	184.3
7.5°	133.6	119.8	114.6	114.6	109.3	104.6	101.3	99.4
10°	89.5	86.8	87.5	88.2	87.5	88.2	86.3	87.5
12.5°	96.1	94.8	96.1	96.8	96.8	98.0	95.4	97.4
15°	111.9	110.6	112.5	113.9	113.9	115.8	113.2	115.1
17.5°	136.9	136.3	139.6	140.8	141.5	144.8	141.5	144.1
20°	173.1	172.4	177.1	179.0	178.4	185.0	180.4	185.0
22.5°	219.9	218.5	225.1	227.1	227.8	236.3	232.3	235.6
25°	266.6	267.9	271.2	274.5	275.1	282.4	276.5	279.8
27.5°	276.5	274.5	276.5	280.4	281.1	284.4	279.1	281.7
30°	250.1	246.8	247.5	252.1	253.4	254.7	250.1	251.4
32.5°	203.4	198.1	198.1	202.8	204.0	206.0	198.1	201.4
35°	150.1	145.5	145.5	148.8	149.4	150.7	144.8	147.4
37.5°	102.7	98.7	100.1	101.3	102.0	103.4	102.7	102.0
40°	65.8	63.2	65.2	65.2	65.8	66.5	66.5	67.1
42.5°	40.2	38.2	39.5	39.5	40.2	40.2	40.2	40.8
45°	23.0	22.4	22.4	23.0	23.0	23.0	22.4	23.0
47.5°	12.5	11.9	12.5	12.5	12.5	12.5	12.5	12.5
50°	6.6	5.9	5.9	5.9	5.9	5.9	5.9	5.9
52.5°	3.3	2.6	2.6	2.6	1.9	2.6	1.9	1.9
55°	1.9	1.4	1.4	1.4	0.7	0.7	0.0	0.0
57.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
60°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	1.9	1.4	0.7	0.7	0.7	0.0	0.0	0.0
70°	1.9	1.4	1.4	0.7	0.7	0.0	0.0	0.0
72.5°	1.9	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	1.9	1.4	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	1.9	1.9	1.4	1.4	0.7	0.7	0.7	0.0
80°	2.6	1.9	1.4	1.4	1.4	0.7	0.7	0.7
82.5°	2.6	1.9	1.4	1.4	1.4	0.7	0.7	0.7
85°	2.6	1.9	1.9	1.4	1.4	0.7	0.7	0.7
87.5°	2.6	1.9	1.9	1.4	1.4	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)