

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212556

Luminaire Tested: **LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3864.3 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30014	30014	30014
5°	76984	27302	8506
10°	150068	20981	4083
15°	269390	14250	5483
20°	399962	10818	9049
25°	454615	8912	14185
30°	492809	9744	13349
35°	519090	6318	8273
40°	530313	2799	4030
45°	478972	1072	1498
50°	315294	422	422
55°	86340	368	0
60°	17248	422	0
65°	1223	571	0
70°	176	705	0
75°	0	1048	0
80°	0	1562	174
85°	0	3112	346

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.4	2.2
10°-20°	453.6	11.7
20°-30°	1028.1	26.6
30°-40°	1234.1	31.9
40°-50°	869.8	22.5
50°-60°	179.5	4.6
60°-70°	6.4	0.2
70°-80°	3.8	0.1
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1567.1	40.6
0°-40°	2801.2	72.5
0°-60°	3850.5	99.6
0°-90°	3864.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3864.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	697	697	697	697	697	
5°	1781	1298	632	263	197	219
15°	6044	2659	320	114	123	1794
25°	9570	3216	188	263	299	4416
35°	9876	2252	120	157	157	6139
45°	7866	772	18	24	25	5785
55°	1150	16	5	4	0	1516
65°	12	4	6	4	0	35
75°	0	4	6	4	0	0
85°	0	4	6	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1
2.5°	1188.2	1152.3	1166.4	1125.0	1115.8	1108.1	1115.8	1070.8	1045.6	1013.2	987.3
5°	1781.2	1738.4	1748.2	1675.8	1642.8	1620.4	1616.1	1523.4	1453.8	1377.2	1297.8
7.5°	2479.7	2439.0	2433.4	2320.9	2252.7	2214.1	2197.9	2065.1	1944.9	1808.6	1659.7
10°	3432.5	3339.8	3311.0	3147.9	3017.9	2935.7	2834.5	2622.3	2411.5	2205.7	2015.9
12.5°	4541.3	4490.7	4419.1	4131.7	3904.0	3787.3	3636.2	3304.6	2985.6	2645.5	2327.9
15°	6043.6	5863.7	5741.4	5326.1	4959.3	4779.5	4558.8	4051.5	3569.5	3138.8	2658.8
17.5°	7511.4	7417.2	7226.2	6687.2	6122.2	5838.4	5509.6	4820.2	4139.4	3526.7	2940.6
20°	8729.2	8640.6	8422.7	7914.7	7288.0	6869.2	6455.3	5509.6	4620.0	3835.8	3129.0
22.5°	9312.3	9256.1	9078.4	8643.4	8109.4	7711.0	7266.2	6096.2	4975.5	4038.2	3214.7
25°	9569.5	9543.5	9428.9	9086.1	8583.0	8245.0	7824.8	6511.5	5196.9	4132.4	3216.1
27.5°	9830.2	9835.1	9582.1	9310.9	8833.8	8509.2	8104.5	6695.6	5236.9	4079.6	3110.7
30°	9912.4	9860.4	9748.7	9359.4	8906.2	8561.2	8127.0	6610.6	5072.5	3863.2	2900.6
32.5°	9878.7	9858.3	9735.3	9323.5	8783.3	8403.1	7909.8	6273.3	4747.9	3554.0	2602.7
35°	9875.9	9837.9	9556.2	9202.7	8537.3	8067.9	7418.0	5728.1	4288.4	3146.6	2252.0
37.5°	9697.4	9603.2	9391.7	8915.3	8038.4	7443.2	6714.6	5061.9	3726.2	2689.1	1904.2
40°	9435.3	9308.9	9030.6	8309.6	7174.2	6488.3	5777.3	4305.2	3131.1	2237.9	1534.6
42.5°	8888.0	8696.8	8303.3	7311.8	6022.5	5404.2	4812.5	3538.6	2553.4	1823.4	1171.4
45°	7866.2	7604.8	7073.0	5984.6	4865.2	4360.7	3885.0	2847.2	2044.1	1352.6	772.2
47.5°	6322.6	6080.1	5595.9	4764.0	3815.4	3388.9	3009.5	2117.9	1385.6	783.4	368.9
50°	4707.1	4499.1	4121.1	3311.0	2561.2	2226.1	1901.4	1203.0	649.2	372.4	153.2
52.5°	2808.5	2705.3	2370.1	1836.1	1264.8	1089.8	874.8	509.5	327.5	135.0	41.4
55°	1150.2	1061.7	936.0	751.2	550.1	466.6	399.2	251.5	101.9	28.1	15.5
57.5°	520.0	500.3	443.4	348.5	253.0	212.2	143.4	47.8	22.5	14.0	9.2
60°	200.3	180.5	154.6	83.7	35.8	30.2	24.6	16.1	11.2	7.7	5.6
62.5°	28.8	27.4	24.6	19.7	15.5	14.0	12.0	8.4	6.3	4.9	4.3
65°	12.0	12.0	10.5	8.4	7.1	6.3	5.6	4.3	3.5	3.5	3.5
67.5°	4.9	4.9	4.3	3.5	2.8	2.8	2.8	2.1	2.8	2.8	3.5
70°	1.4	1.4	1.4	1.4	1.4	1.4	2.1	2.1	2.8	2.8	3.5
72.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.8	3.5	3.5
75°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.8	3.5	3.5
77.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.8	3.5	3.5
80°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.8	3.5	4.3
82.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.8	3.5	4.3
85°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.8	3.5	4.3
87.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.8	3.5	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1
2.5°	964.7	919.8	907.2	867.8	834.7	818.6	798.2	752.5	718.1	672.4	645.0
5°	1242.3	1157.3	1089.8	1007.6	953.5	918.4	863.6	779.9	712.5	631.7	574.1
7.5°	1542.3	1387.1	1265.5	1129.8	1051.9	990.7	897.3	777.1	678.0	570.5	481.4
10°	1831.8	1600.0	1408.8	1214.2	1111.6	1026.6	898.0	746.9	615.5	479.9	385.7
12.5°	2086.8	1787.6	1518.5	1268.3	1141.1	1035.0	874.1	692.8	534.0	394.9	312.0
15°	2299.8	1933.1	1595.7	1288.6	1143.3	1016.7	824.2	615.5	443.4	319.7	261.4
17.5°	2461.4	2009.6	1619.6	1264.1	1102.5	964.7	747.6	517.9	359.7	271.3	220.0
20°	2545.0	2024.3	1585.2	1197.4	1027.2	886.0	647.1	420.2	305.0	236.1	184.1
22.5°	2555.6	1982.9	1503.0	1101.7	932.4	790.5	536.1	350.7	271.9	208.7	162.3
25°	2493.1	1893.0	1385.6	993.5	828.4	680.8	436.3	314.0	247.3	187.6	186.9
27.5°	2359.6	1738.4	1245.1	867.8	702.7	553.7	370.3	283.9	220.6	198.9	211.5
30°	2171.2	1540.2	1072.3	708.9	548.8	425.8	312.0	234.0	194.0	196.0	206.6
32.5°	1916.2	1294.3	869.2	519.2	392.8	320.4	234.0	159.5	160.9	161.6	170.8
35°	1595.7	1037.9	649.2	349.2	276.2	225.6	132.1	117.4	119.5	120.2	126.4
37.5°	1278.8	797.5	431.4	232.6	173.6	118.7	82.2	78.7	80.1	79.4	86.5
40°	979.5	555.8	258.6	115.2	66.8	55.5	50.6	48.5	49.2	49.8	54.1
42.5°	693.5	301.5	127.9	43.6	35.2	32.4	30.2	28.8	29.6	29.6	32.4
45°	352.0	142.7	43.6	23.9	21.7	19.7	18.3	17.6	17.6	17.6	18.9
47.5°	152.4	47.0	20.4	14.8	13.3	12.7	11.2	10.5	10.5	10.5	11.2
50°	47.8	18.9	12.7	9.9	8.4	7.7	7.1	7.1	7.1	6.3	7.1
52.5°	17.6	12.0	8.4	6.3	5.6	5.6	5.6	4.9	5.6	4.9	5.6
55°	10.5	7.7	5.6	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
57.5°	7.1	5.6	4.9	4.9	4.3	4.3	4.9	4.9	4.9	4.9	4.9
60°	4.9	4.9	4.3	4.3	4.3	4.3	4.9	4.9	4.9	4.9	4.9
62.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.9	4.9	4.9	4.9	5.6
65°	3.5	4.3	4.3	4.3	4.3	4.3	4.9	4.9	5.6	5.6	5.6
67.5°	3.5	4.3	4.3	4.9	4.9	4.9	4.9	5.6	5.6	5.6	5.6
70°	4.3	4.3	4.9	4.9	4.9	4.9	5.6	5.6	5.6	5.6	6.3
72.5°	4.3	4.3	4.9	4.9	4.9	4.9	5.6	5.6	6.3	6.3	6.3
75°	4.3	4.9	4.9	4.9	4.9	5.6	5.6	5.6	6.3	6.3	6.3
77.5°	4.3	4.9	4.9	5.6	5.6	5.6	5.6	6.3	6.3	6.3	6.3
80°	4.3	4.9	4.9	5.6	5.6	5.6	6.3	6.3	6.3	6.3	7.1
82.5°	4.3	4.9	4.9	5.6	5.6	5.6	6.3	6.3	6.3	6.3	7.1
85°	4.9	4.9	5.6	5.6	5.6	5.6	6.3	6.3	6.3	6.3	7.1
87.5°	4.9	4.9	5.6	5.6	5.6	5.6	6.3	6.3	7.1	6.3	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1
2.5°	608.5	567.7	539.6	529.1	508.7	476.4	457.4	439.8	406.9	399.8	381.6
5°	508.0	442.7	396.3	378.8	355.6	328.2	301.5	283.9	262.8	254.3	241.7
7.5°	400.5	335.2	295.1	281.1	264.9	242.4	218.5	200.9	179.2	167.9	157.4
10°	314.8	266.3	232.6	218.5	201.7	177.7	153.2	130.0	111.0	99.1	97.0
12.5°	255.8	215.7	179.9	165.1	145.5	121.5	104.0	103.3	101.9	101.1	102.6
15°	209.4	170.8	132.8	116.6	111.0	110.3	112.4	114.6	113.8	115.9	117.4
17.5°	172.1	130.7	122.3	123.0	123.6	125.8	129.3	135.0	135.6	139.1	141.9
20°	140.6	138.4	141.9	144.7	146.8	151.1	158.8	165.9	167.9	172.8	178.5
22.5°	159.5	165.9	173.6	177.1	179.9	187.6	196.0	207.3	211.5	217.8	225.6
25°	192.5	203.1	215.0	219.2	223.4	236.1	245.9	259.3	262.8	270.5	278.2
27.5°	220.0	231.2	243.8	249.4	253.0	265.6	274.1	282.5	282.5	286.7	292.3
30°	215.7	224.9	235.4	239.6	241.0	250.2	258.6	261.4	260.0	262.1	266.3
32.5°	179.2	186.2	194.6	198.1	199.6	205.9	212.9	212.9	212.2	212.2	215.0
35°	132.8	137.8	141.9	145.5	147.6	151.8	158.1	157.4	157.4	156.0	158.1
37.5°	89.3	92.1	97.0	98.3	99.1	101.9	106.8	106.8	105.4	106.1	107.5
40°	54.1	57.6	60.5	61.1	62.5	64.6	68.2	68.2	68.2	68.2	68.9
42.5°	32.4	34.4	36.5	36.5	37.3	40.1	41.4	41.4	41.4	41.4	42.1
45°	18.9	19.7	21.1	21.7	21.7	23.2	23.9	23.9	23.9	23.9	24.6
47.5°	11.2	12.0	12.0	12.7	12.7	13.3	14.0	14.0	13.3	13.3	13.3
50°	7.1	7.1	7.1	7.1	7.7	7.7	7.7	7.7	7.7	7.7	7.1
52.5°	5.6	5.6	5.6	5.6	4.9	4.9	4.9	4.9	4.3	4.3	3.5
55°	4.9	4.9	4.9	4.9	4.9	4.3	4.3	4.3	3.5	2.8	2.1
57.5°	4.9	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.8	2.1
60°	4.9	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.8	2.1
62.5°	5.6	5.6	4.9	4.9	4.9	4.3	4.3	3.5	3.5	2.8	2.1
65°	5.6	5.6	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.1
67.5°	5.6	5.6	5.6	5.6	4.9	4.9	4.9	4.3	3.5	2.8	2.1
70°	6.3	6.3	5.6	5.6	5.6	4.9	4.9	4.3	3.5	3.5	2.8
72.5°	6.3	6.3	5.6	5.6	5.6	5.6	4.9	4.3	4.3	3.5	2.8
75°	6.3	6.3	6.3	6.3	5.6	5.6	4.9	4.9	4.3	3.5	2.8
77.5°	6.3	6.3	6.3	6.3	5.6	5.6	5.6	4.9	4.3	3.5	2.8
80°	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.9	4.3	3.5	2.8
82.5°	7.1	7.1	6.3	6.3	6.3	5.6	5.6	4.9	4.3	3.5	3.5
85°	7.1	7.1	6.3	6.3	6.3	5.6	5.6	4.9	4.3	4.3	3.5
87.5°	7.1	7.1	6.3	6.3	6.3	5.6	5.6	4.9	4.3	4.3	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212556

CATALOG NUMBER: LDSQA6A40935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	697.1	697.1	697.1	697.1	697.1	697.1	697.1	697.1
2.5°	370.3	349.2	342.2	347.1	341.5	337.2	331.6	328.8
5°	231.8	216.4	211.5	212.9	208.0	203.7	198.1	196.8
7.5°	142.7	127.9	122.3	122.3	116.6	111.8	108.2	106.1
10°	95.5	92.7	93.4	94.2	93.4	94.2	92.1	93.4
12.5°	102.6	101.1	102.6	103.3	103.3	104.7	101.9	104.0
15°	119.5	118.0	120.2	121.5	121.5	123.6	120.8	123.0
17.5°	146.2	145.5	149.0	150.4	151.1	154.6	151.1	153.9
20°	184.8	184.1	189.0	191.2	190.4	197.5	192.5	197.5
22.5°	234.6	233.3	240.3	242.4	243.1	252.2	248.1	251.5
25°	284.6	285.9	289.5	293.0	293.7	301.5	295.1	298.6
27.5°	295.1	293.0	295.1	299.4	300.0	303.5	297.9	300.7
30°	267.0	263.5	264.2	269.1	270.5	271.9	267.0	268.5
32.5°	217.2	211.5	211.5	216.4	217.8	220.0	211.5	215.0
35°	160.2	155.3	155.3	158.8	159.5	160.9	154.6	157.4
37.5°	109.6	105.4	106.8	108.2	108.9	110.3	109.6	108.9
40°	70.2	67.4	69.6	69.6	70.2	71.0	71.0	71.7
42.5°	42.9	40.8	42.1	42.1	42.9	42.9	42.9	43.6
45°	24.6	23.9	23.9	24.6	24.6	24.6	23.9	24.6
47.5°	13.3	12.7	13.3	13.3	13.3	13.3	13.3	13.3
50°	7.1	6.3	6.3	6.3	6.3	6.3	6.3	6.3
52.5°	3.5	2.8	2.8	2.8	2.1	2.8	2.1	2.1
55°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
57.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
60°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	2.1	1.4	0.7	0.7	0.7	0.0	0.0	0.0
70°	2.1	1.4	1.4	0.7	0.7	0.0	0.0	0.0
72.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	2.1	2.1	1.4	1.4	0.7	0.7	0.7	0.0
80°	2.8	2.1	1.4	1.4	1.4	0.7	0.7	0.7
82.5°	2.8	2.1	1.4	1.4	1.4	0.7	0.7	0.7
85°	2.8	2.1	2.1	1.4	1.4	0.7	0.7	0.7
87.5°	2.8	2.1	2.1	1.4	1.4	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)