

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219619

Luminaire Tested: **LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3761.8 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45725	45725	45725
5°	88597	43575	14699
10°	150532	38128	6602
15°	231957	30413	10493
20°	335793	19794	18250
25°	492663	19102	23468
30°	572837	18097	17987
35°	579808	9582	9508
40°	480043	3614	3991
45°	362551	1230	1455
50°	248050	455	455
55°	34500	390	53
60°	896	388	0
65°	224	530	0
70°	88	655	0
75°	0	865	0
80°	0	1488	174
85°	0	2964	0

TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.4	3.0
10°-20°	471.0	12.5
20°-30°	1074.4	28.6
30°-40°	1243.3	33.1
40°-50°	749.8	19.9
50°-60°	101.9	2.7
60°-70°	3.3	0.1
70°-80°	3.5	0.1
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1656.7	44.0
0°-40°	2900.0	77.1
0°-60°	3751.7	99.7
0°-90°	3761.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3761.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1062	1062	1062	1062	1062	
5°	2050	1679	1008	552	340	239
15°	5204	2925	682	210	235	1541
25°	10370	3466	402	484	494	4693
35°	11031	2643	182	186	181	6648
45°	5954	720	20	25	24	4656
55°	460	5	5	4	1	901
65°	2	3	5	3	0	3
75°	0	4	5	4	0	0
85°	0	4	6	4	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0
2.5°	1535.8	1521.6	1527.6	1511.8	1472.3	1464.1	1463.4	1452.9	1419.3	1393.1	1361.7
5°	2049.9	2049.2	2053.0	2019.4	1949.9	1928.2	1917.8	1892.4	1810.8	1748.0	1678.6
7.5°	2692.0	2687.5	2683.0	2621.7	2512.6	2470.8	2443.9	2352.0	2239.8	2128.5	2004.5
10°	3443.1	3440.8	3423.6	3316.0	3141.1	3064.2	3011.8	2866.1	2686.0	2527.6	2316.8
12.5°	4315.3	4295.0	4264.4	4106.8	3866.8	3783.2	3668.1	3437.1	3160.6	2917.7	2623.2
15°	5203.8	5174.7	5120.1	4917.6	4620.1	4477.4	4334.7	4030.5	3655.4	3302.5	2925.2
17.5°	6073.1	6040.9	5913.1	5569.3	5278.6	5104.4	4946.0	4528.3	4087.3	3633.7	3155.4
20°	7328.7	7212.0	6989.3	6447.5	5907.1	5593.2	5407.9	4966.2	4420.6	3892.3	3319.1
22.5°	9005.7	8747.1	8272.5	7392.1	6620.1	6167.2	5863.8	5276.3	4660.6	4061.2	3419.9
25°	10370.4	10253.0	9713.5	8460.9	7256.1	6722.5	6300.2	5523.0	4835.5	4173.9	3466.2
27.5°	11250.0	11220.9	10604.3	9345.8	7775.6	7075.3	6603.7	5685.9	4919.8	4197.9	3443.9
30°	11522.1	11567.6	10975.7	9646.1	7925.7	7146.3	6630.5	5688.2	4854.8	4089.6	3300.3
32.5°	11501.8	11504.2	10778.4	9386.8	7681.3	6939.9	6406.4	5499.1	4614.9	3818.3	3027.5
35°	11031.1	10915.2	10094.7	8590.2	7112.7	6458.6	5962.4	5132.9	4219.6	3410.2	2642.7
37.5°	9997.4	9845.7	8889.1	7570.0	6439.3	5834.6	5434.0	4652.3	3748.7	2974.5	2245.0
40°	8540.9	8325.5	7536.4	6621.6	5702.3	5247.9	4911.7	4115.0	3245.0	2547.0	1872.1
42.5°	7082.7	6977.4	6455.7	5712.1	5082.8	4655.4	4304.0	3552.2	2760.8	2125.6	1400.6
45°	5954.2	5863.8	5513.2	5023.0	4405.6	4015.5	3677.0	2965.5	2144.9	1425.9	719.7
47.5°	5132.1	5058.9	4723.3	4208.4	3531.3	3104.5	2755.5	1944.6	1215.2	615.9	180.1
50°	3703.2	3628.5	3299.6	2703.2	2091.9	1734.6	1483.6	868.4	344.4	124.8	18.7
52.5°	1815.4	1754.1	1530.6	1145.7	769.1	553.1	404.4	163.0	39.6	13.4	8.9
55°	459.6	422.2	352.0	221.2	108.4	65.0	41.9	15.0	9.8	7.4	5.2
57.5°	26.1	25.4	23.2	17.2	12.7	11.2	9.8	7.4	5.2	4.5	3.7
60°	10.4	9.8	8.9	7.4	6.0	5.2	5.2	3.7	3.0	3.0	3.0
62.5°	4.5	4.5	4.5	3.7	3.0	3.0	3.0	2.2	3.0	3.0	3.0
65°	2.2	2.2	2.2	1.5	1.5	1.5	2.2	2.2	2.2	3.0	3.0
67.5°	1.5	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.2	3.0	3.0
70°	0.7	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.2	3.0	3.7
72.5°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.2	3.0	3.7
75°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.0	3.7
77.5°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.0	3.7
80°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.0	3.7
82.5°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.0	3.7
85°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.0	3.7
87.5°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	2.2	3.0	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0
2.5°	1321.3	1294.4	1254.8	1228.7	1203.3	1179.4	1139.7	1117.3	1077.0	1039.6	1007.4
5°	1594.8	1527.6	1446.2	1376.6	1331.7	1287.7	1207.8	1148.7	1074.6	1008.2	946.9
7.5°	1871.4	1752.6	1618.8	1504.5	1434.9	1366.9	1247.4	1151.7	1047.1	952.1	861.6
10°	2122.5	1943.9	1754.8	1591.2	1496.9	1408.8	1251.1	1124.0	989.5	872.1	758.6
12.5°	2355.7	2111.2	1864.6	1650.9	1534.3	1428.2	1235.4	1079.9	920.0	781.0	648.6
15°	2563.4	2249.6	1944.6	1685.3	1548.6	1422.9	1198.7	1018.0	837.7	682.3	515.0
17.5°	2721.2	2335.5	1979.7	1680.0	1523.2	1383.4	1136.0	940.2	750.4	562.0	372.9
20°	2816.8	2372.1	1972.4	1639.7	1468.6	1320.6	1061.2	855.7	645.0	432.0	328.8
22.5°	2857.2	2369.1	1937.1	1579.2	1401.3	1251.7	989.5	773.4	534.4	390.9	343.1
25°	2864.0	2338.5	1887.8	1512.7	1334.7	1186.1	917.1	680.2	464.2	402.1	384.2
27.5°	2812.3	2266.8	1795.1	1416.9	1241.3	1087.4	808.6	540.3	435.8	400.5	412.5
30°	2659.9	2103.1	1631.4	1248.8	1079.2	925.3	577.6	423.8	361.8	364.0	367.0
32.5°	2391.6	1831.0	1368.4	1003.0	817.5	609.9	359.4	283.2	275.1	275.1	273.5
35°	2033.6	1498.4	1074.0	634.5	406.5	293.0	186.1	186.9	183.1	182.3	181.7
37.5°	1663.6	1182.4	680.2	262.3	176.4	122.6	109.9	111.3	109.9	112.1	110.7
40°	1311.6	730.2	248.1	83.7	62.0	59.8	61.3	62.8	62.8	64.3	64.3
42.5°	762.3	242.1	65.0	33.7	33.7	32.1	32.9	34.3	35.2	35.9	35.2
45°	226.4	50.0	20.9	18.7	18.7	18.0	18.0	18.7	19.3	20.2	20.2
47.5°	35.9	14.1	12.0	10.4	10.4	10.4	10.4	10.4	11.2	11.2	12.0
50°	11.2	8.9	7.4	6.8	6.8	6.0	6.0	6.8	6.8	6.8	7.4
52.5°	6.8	5.2	5.2	4.5	5.2	5.2	4.5	5.2	5.2	5.2	6.0
55°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.2	5.2	5.2
57.5°	3.7	3.7	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
60°	3.7	3.7	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.2
62.5°	3.7	3.7	4.5	4.5	4.5	4.5	4.5	4.5	5.2	5.2	5.2
65°	3.7	3.7	4.5	4.5	4.5	4.5	4.5	5.2	5.2	5.2	5.2
67.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	5.2	5.2	5.2
70°	3.7	4.5	4.5	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
72.5°	3.7	4.5	4.5	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
75°	4.5	4.5	4.5	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.0
77.5°	4.5	4.5	5.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0
80°	4.5	4.5	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0
82.5°	4.5	4.5	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0
85°	4.5	4.5	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0
87.5°	4.5	4.5	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0
2.5°	979.8	945.4	929.0	905.7	889.3	852.7	837.7	812.3	791.4	757.1	759.3
5°	894.6	829.5	785.4	751.1	727.2	668.9	630.0	589.0	551.5	505.2	488.1
7.5°	776.5	696.5	629.3	588.2	557.5	479.9	393.8	326.6	275.8	239.2	225.0
10°	658.4	554.5	447.6	384.2	340.1	265.3	227.1	209.2	192.8	172.6	159.2
12.5°	520.9	372.9	275.8	250.3	232.4	207.8	183.1	163.7	167.3	168.2	173.4
15°	355.8	268.3	237.7	220.5	201.0	186.9	195.1	200.3	210.0	210.8	217.5
17.5°	289.2	251.9	227.1	226.4	228.0	236.2	248.9	255.6	268.3	271.2	281.0
20°	289.2	267.5	288.4	288.4	292.2	303.4	319.9	329.6	343.8	349.0	361.0
22.5°	329.6	344.4	370.8	373.8	375.1	387.1	408.1	417.8	434.2	437.2	449.9
25°	402.1	415.5	439.4	441.7	442.4	451.4	467.1	472.3	483.5	477.6	485.1
27.5°	425.3	431.2	446.2	447.6	444.0	447.6	453.6	453.6	457.4	445.4	447.6
30°	373.8	375.1	382.6	383.3	375.1	376.7	377.4	376.7	376.0	363.2	363.2
32.5°	277.3	277.3	287.0	284.8	275.8	278.0	278.0	278.0	277.3	266.9	265.3
35°	183.9	184.6	192.8	191.3	184.6	186.1	186.1	188.3	186.1	180.1	178.7
37.5°	112.1	112.8	116.6	117.3	115.1	115.9	116.6	115.9	117.3	114.3	112.8
40°	65.0	66.5	69.5	70.2	69.5	69.5	70.2	71.0	73.9	70.2	68.7
42.5°	38.1	38.9	40.4	40.4	40.4	40.4	41.1	41.9	42.6	41.9	41.1
45°	21.7	22.4	23.2	23.2	23.9	23.2	23.9	23.9	24.6	23.9	23.9
47.5°	12.7	12.7	13.4	13.4	14.1	13.4	14.1	14.1	14.1	13.4	13.4
50°	7.4	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.4	7.4
52.5°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	5.2	5.2	4.5	4.5
55°	5.2	5.2	5.2	5.2	5.2	5.2	4.5	3.7	3.7	3.0	3.0
57.5°	4.5	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	2.2	2.2
60°	5.2	5.2	5.2	5.2	4.5	4.5	4.5	3.7	3.0	2.2	2.2
62.5°	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	2.2	2.2
65°	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	2.2	2.2
67.5°	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	3.0	2.2
70°	5.2	6.0	6.0	5.2	5.2	5.2	4.5	3.7	3.7	3.0	2.2
72.5°	5.2	6.0	6.0	5.2	5.2	5.2	4.5	3.7	3.7	3.0	2.2
75°	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	3.7	3.0	2.2
77.5°	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	3.7	3.0	2.2
80°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.0	3.0
82.5°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.0	3.0
85°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.0	2.2
87.5°	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	3.7	3.0	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219619

CATALOG NUMBER: LDSQA6A40950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0	1062.0
2.5°	731.6	714.5	707.0	719.0	713.0	695.0	698.8	687.5
5°	436.4	410.3	393.8	401.3	377.4	355.8	355.8	340.1
7.5°	210.8	202.5	198.0	199.5	194.3	187.6	183.9	183.9
10°	148.0	145.0	145.8	145.8	150.2	149.4	151.7	151.0
12.5°	175.7	177.1	177.8	180.9	184.6	184.6	186.9	185.3
15°	225.0	223.4	228.0	228.7	234.7	235.4	238.4	235.4
17.5°	286.2	289.2	293.8	293.0	304.9	305.8	305.8	304.9
20°	368.4	370.8	375.1	376.7	390.9	392.4	397.6	398.3
22.5°	458.1	458.1	460.3	463.3	476.8	477.6	479.9	479.9
25°	488.8	484.3	485.1	488.8	496.3	493.3	495.5	494.0
27.5°	449.2	442.4	441.0	446.2	451.4	443.1	446.2	446.2
30°	364.7	358.8	357.2	362.4	366.2	357.2	360.3	361.8
32.5°	266.9	263.1	262.3	266.0	269.0	261.6	264.5	266.9
35°	180.1	178.7	177.1	177.8	182.3	176.4	179.3	180.9
37.5°	114.3	111.3	112.1	113.7	116.6	112.8	115.9	115.9
40°	70.2	68.7	68.7	70.2	71.8	68.7	70.2	71.0
42.5°	41.1	41.1	41.1	41.9	42.6	41.1	41.1	41.9
45°	23.9	23.2	23.2	23.9	24.6	23.2	23.9	23.9
47.5°	13.4	12.7	12.7	13.4	13.4	12.7	13.4	13.4
50°	7.4	6.8	6.8	7.4	7.4	6.8	6.8	6.8
52.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.0	3.0
55°	2.2	2.2	1.5	1.5	1.5	1.5	1.5	0.7
57.5°	1.5	1.5	0.7	0.7	0.7	0.7	0.0	0.0
60°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
62.5°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
65°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
67.5°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
70°	2.2	1.5	1.5	0.7	0.7	0.7	0.0	0.0
72.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
75°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
77.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.0
80°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.7
82.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.7
85°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.0
87.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)