

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219621

Luminaire Tested: **LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4110.1 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31917	31917	31917
5°	81885	29040	9042
10°	159608	22315	4341
15°	286525	15160	5830
20°	425396	11505	9622
25°	483528	9478	15088
30°	524155	10361	14194
35°	552103	6717	8793
40°	564047	2979	4283
45°	509441	1139	1589
50°	335356	455	455
55°	91842	390	0
60°	18342	448	0
65°	1294	611	0
70°	189	755	0
75°	0	1131	0
80°	0	1686	174
85°	0	3359	346

TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	2.2
10°-20°	482.5	11.7
20°-30°	1093.5	26.6
30°-40°	1312.6	31.9
40°-50°	925.1	22.5
50°-60°	190.9	4.6
60°-70°	6.7	0.2
70°-80°	4.0	0.1
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1666.8	40.6
0°-40°	2979.4	72.5
0°-60°	4095.4	99.6
0°-90°	4110.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4110.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	741	741	741	741	741	
5°	1895	1380	672	279	209	233
15°	6428	2828	340	121	131	1908
25°	10178	3421	200	279	318	4697
35°	10504	2395	128	167	167	6530
45°	8367	821	19	25	26	6153
55°	1224	16	5	4	0	1612
65°	13	4	6	4	0	38
75°	0	4	7	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3
2.5°	1263.7	1225.6	1240.6	1196.5	1186.7	1178.5	1186.7	1139.0	1112.1	1077.6	1050.1
5°	1894.6	1848.9	1859.4	1782.5	1747.3	1723.4	1718.9	1620.3	1546.3	1464.7	1380.4
7.5°	2637.3	2594.1	2588.0	2468.5	2396.0	2354.9	2337.7	2196.5	2068.7	1923.7	1765.3
10°	3650.7	3552.1	3521.4	3348.2	3209.9	3122.4	3014.9	2789.1	2565.0	2345.9	2144.1
12.5°	4830.1	4776.3	4700.1	4394.4	4152.3	4028.2	3867.6	3514.8	3175.4	2813.8	2475.9
15°	6428.0	6236.6	6106.6	5664.9	5274.8	5083.5	4848.8	4309.2	3796.5	3338.4	2828.0
17.5°	7989.2	7889.0	7685.7	7112.6	6511.6	6209.6	5860.0	5126.8	4402.6	3751.0	3127.7
20°	9284.3	9190.2	8958.5	8418.2	7751.5	7306.0	6865.9	5860.0	4913.8	4079.7	3328.0
22.5°	9904.6	9844.8	9655.8	9193.2	8625.1	8201.3	7728.3	6484.1	5291.9	4295.0	3419.1
25°	10178.1	10150.5	10028.7	9663.9	9128.9	8769.4	8322.4	6925.7	5527.4	4395.2	3420.6
27.5°	10455.4	10460.6	10191.6	9903.1	9395.7	9050.4	8619.9	7121.5	5570.0	4339.2	3308.4
30°	10542.9	10487.6	10368.7	9954.7	9472.6	9105.6	8643.9	7031.0	5395.1	4108.8	3085.1
32.5°	10506.9	10485.3	10354.6	9916.6	9341.8	8937.6	8413.0	6672.3	5049.8	3780.1	2768.2
35°	10504.0	10463.6	10163.9	9788.0	9080.3	8581.0	7889.8	6092.3	4561.0	3346.6	2395.2
37.5°	10314.1	10213.9	9989.0	9482.4	8549.7	7916.7	7141.7	5383.9	3963.2	2860.1	2025.4
40°	10035.5	9900.8	9604.9	8838.1	7630.5	6901.0	6144.6	4579.0	3330.2	2380.2	1632.3
42.5°	9453.3	9250.0	8831.4	7776.9	6405.5	5747.9	5118.7	3763.7	2715.9	1939.4	1245.8
45°	8366.6	8088.6	7522.8	6365.2	5174.6	4638.0	4132.1	3028.3	2174.0	1438.6	821.3
47.5°	6724.6	6466.7	5951.9	5067.0	4058.2	3604.4	3200.9	2252.5	1473.8	833.2	392.3
50°	5006.6	4785.4	4383.3	3521.4	2724.1	2367.7	2022.4	1279.5	690.6	396.1	163.0
52.5°	2987.2	2877.3	2520.9	1952.8	1345.2	1159.2	930.5	541.8	348.3	143.4	44.1
55°	1223.5	1129.2	995.5	798.9	585.2	496.2	424.4	267.5	108.4	30.0	16.4
57.5°	553.1	532.2	471.5	370.8	269.0	225.8	152.5	50.9	23.9	15.0	9.8
60°	213.0	192.1	164.4	88.9	38.1	32.1	26.1	17.2	12.0	8.2	6.0
62.5°	30.7	29.1	26.1	20.9	16.4	15.0	12.7	8.9	6.8	5.2	4.5
65°	12.7	12.7	11.2	8.9	7.4	6.8	6.0	4.5	3.7	3.7	3.7
67.5°	5.2	5.2	4.5	3.7	3.0	3.0	3.0	2.2	3.0	3.0	3.7
70°	1.5	1.5	1.5	1.5	1.5	1.5	2.2	2.2	3.0	3.0	3.7
72.5°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.7	3.7
75°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	3.0	3.7	3.7
77.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	3.7
80°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	4.5
82.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	4.5
85°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	4.5
87.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3
2.5°	1026.2	978.3	964.8	923.0	887.8	870.6	849.1	800.4	763.8	715.2	686.1
5°	1321.3	1230.8	1159.2	1071.6	1014.2	976.8	918.4	829.5	757.8	671.9	610.6
7.5°	1640.5	1475.3	1346.0	1201.7	1118.7	1053.7	954.4	826.6	721.2	606.8	512.0
10°	1948.3	1701.8	1498.4	1291.5	1182.3	1091.8	955.1	794.5	654.7	510.4	410.3
12.5°	2219.7	1901.3	1615.0	1348.9	1213.7	1100.8	929.7	736.9	568.0	420.1	331.9
15°	2446.1	2056.0	1697.3	1370.6	1215.9	1081.4	876.6	654.7	471.5	340.1	278.0
17.5°	2618.0	2137.4	1722.7	1344.5	1172.6	1026.2	795.2	550.9	382.6	288.4	233.9
20°	2706.9	2153.1	1685.9	1273.5	1092.6	942.4	688.3	447.0	324.4	251.1	195.8
22.5°	2718.1	2109.0	1598.6	1171.8	991.7	840.7	570.2	372.9	289.2	221.9	172.6
25°	2651.6	2013.4	1473.8	1056.7	881.2	724.2	464.2	334.0	263.1	199.5	198.8
27.5°	2509.6	1848.9	1324.3	923.0	747.3	589.0	393.8	301.9	234.7	211.4	225.0
30°	2309.2	1638.2	1140.5	754.1	583.6	452.9	331.9	248.9	206.2	208.4	219.8
32.5°	2038.0	1376.6	924.5	552.2	417.8	340.8	248.9	169.7	171.2	171.9	181.7
35°	1697.3	1103.8	690.6	371.4	293.8	239.9	140.5	124.8	127.1	127.8	134.5
37.5°	1360.2	848.2	459.0	247.3	184.6	126.3	87.4	83.7	85.2	84.4	91.9
40°	1041.8	591.1	275.1	122.6	71.0	59.1	53.9	51.6	52.3	53.0	57.6
42.5°	737.6	320.6	136.0	46.3	37.3	34.3	32.1	30.7	31.3	31.3	34.3
45°	374.4	151.7	46.3	25.4	23.2	20.9	19.3	18.7	18.7	18.7	20.2
47.5°	162.1	50.0	21.7	15.7	14.1	13.4	12.0	11.2	11.2	11.2	12.0
50°	50.9	20.2	13.4	10.4	8.9	8.2	7.4	7.4	7.4	6.8	7.4
52.5°	18.7	12.7	8.9	6.8	6.0	6.0	6.0	5.2	6.0	5.2	6.0
55°	11.2	8.2	6.0	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
57.5°	7.4	6.0	5.2	5.2	4.5	4.5	5.2	5.2	5.2	5.2	5.2
60°	5.2	5.2	4.5	4.5	4.5	4.5	5.2	5.2	5.2	5.2	5.2
62.5°	4.5	4.5	4.5	4.5	4.5	4.5	5.2	5.2	5.2	5.2	6.0
65°	3.7	4.5	4.5	4.5	4.5	4.5	5.2	5.2	6.0	6.0	6.0
67.5°	3.7	4.5	4.5	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0
70°	4.5	4.5	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0	6.8
72.5°	4.5	4.5	5.2	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8
75°	4.5	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.8	6.8	6.8
77.5°	4.5	5.2	5.2	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8
80°	4.5	5.2	5.2	6.0	6.0	6.0	6.8	6.8	6.8	6.8	7.4
82.5°	4.5	5.2	5.2	6.0	6.0	6.0	6.8	6.8	6.8	6.8	7.4
85°	5.2	5.2	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8	7.4
87.5°	5.2	5.2	6.0	6.0	6.0	6.0	6.8	6.8	7.4	6.8	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3
2.5°	647.2	603.9	574.0	562.8	541.1	506.8	486.5	467.9	432.7	425.3	405.8
5°	540.3	470.9	421.5	402.9	378.1	349.0	320.6	301.9	279.4	270.5	257.1
7.5°	426.0	356.4	313.9	299.0	281.7	257.8	232.4	213.8	190.6	178.7	167.3
10°	334.9	283.2	247.3	232.4	214.4	189.1	163.0	138.2	118.0	105.4	103.2
12.5°	272.1	229.4	191.3	175.7	154.8	129.3	110.7	109.9	108.4	107.6	109.1
15°	222.8	181.7	141.2	124.1	118.0	117.3	119.6	121.9	121.1	123.2	124.8
17.5°	183.1	139.0	130.0	130.8	131.5	133.8	137.5	143.4	144.2	148.0	151.0
20°	149.4	147.2	151.0	153.9	156.2	160.7	168.9	176.4	178.7	183.9	189.8
22.5°	169.7	176.4	184.6	188.3	191.3	199.5	208.4	220.4	225.0	231.7	239.9
25°	204.8	216.0	228.7	233.2	237.7	251.1	261.6	275.8	279.4	287.8	296.0
27.5°	233.9	245.9	259.3	265.3	269.0	282.5	291.4	300.4	300.4	304.9	311.0
30°	229.4	239.1	250.3	254.9	256.4	266.0	275.1	278.0	276.4	278.8	283.2
32.5°	190.6	198.0	207.1	210.8	212.3	219.0	226.4	226.4	225.8	225.8	228.7
35°	141.2	146.4	151.0	154.8	156.9	161.4	168.2	167.3	167.3	165.9	168.2
37.5°	95.0	98.0	103.2	104.6	105.4	108.4	113.7	113.7	112.1	112.8	114.3
40°	57.6	61.3	64.3	65.0	66.5	68.7	72.5	72.5	72.5	72.5	73.2
42.5°	34.3	36.7	38.9	38.9	39.6	42.6	44.1	44.1	44.1	44.1	44.8
45°	20.2	20.9	22.4	23.2	23.2	24.6	25.4	25.4	25.4	25.4	26.1
47.5°	12.0	12.7	12.7	13.4	13.4	14.1	15.0	15.0	14.1	14.1	14.1
50°	7.4	7.4	7.4	7.4	8.2	8.2	8.2	8.2	8.2	8.2	7.4
52.5°	6.0	6.0	6.0	6.0	5.2	5.2	5.2	5.2	4.5	4.5	3.7
55°	5.2	5.2	5.2	5.2	5.2	5.2	4.5	4.5	4.5	3.7	3.0
57.5°	5.2	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	2.2
60°	5.2	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	2.2
62.5°	6.0	6.0	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.7	3.0
65°	6.0	6.0	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	2.2
67.5°	6.0	6.0	6.0	6.0	5.2	5.2	5.2	4.5	3.7	3.0	2.2
70°	6.8	6.8	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.7	3.0
72.5°	6.8	6.8	6.0	6.0	6.0	6.0	5.2	4.5	4.5	3.7	3.0
75°	6.8	6.8	6.8	6.8	6.0	6.0	5.2	5.2	4.5	3.7	3.0
77.5°	6.8	6.8	6.8	6.8	6.0	6.0	6.0	5.2	4.5	3.7	3.0
80°	6.8	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.5	3.7	3.0
82.5°	7.4	7.4	6.8	6.8	6.8	6.0	6.0	5.2	4.5	3.7	3.7
85°	7.4	7.4	6.8	6.8	6.8	6.0	6.0	5.2	4.5	4.5	3.7
87.5°	7.4	7.4	6.8	6.8	6.8	6.0	6.0	5.2	4.5	4.5	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219621

CATALOG NUMBER: LDSQA6A40950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3
2.5°	393.8	371.4	364.0	369.2	363.2	358.8	352.8	349.8
5°	246.7	230.2	225.0	226.4	221.2	216.7	210.8	209.2
7.5°	151.7	136.0	130.0	130.0	124.1	118.9	115.1	112.8
10°	101.7	98.7	99.3	100.2	99.3	100.2	98.0	99.3
12.5°	109.1	107.6	109.1	109.9	109.9	111.3	108.4	110.7
15°	127.1	125.6	127.8	129.3	129.3	131.5	128.5	130.8
17.5°	155.4	154.8	158.4	160.0	160.7	164.4	160.7	163.7
20°	196.5	195.8	201.0	203.2	202.5	210.0	204.8	210.0
22.5°	249.7	248.1	255.6	257.8	258.5	268.3	263.8	267.5
25°	302.7	304.2	307.9	311.7	312.3	320.6	313.9	317.6
27.5°	313.9	311.7	313.9	318.3	319.1	322.9	316.9	319.9
30°	284.0	280.3	281.0	286.2	287.8	289.2	284.0	285.5
32.5°	231.0	225.0	225.0	230.2	231.7	233.9	225.0	228.7
35°	170.4	165.2	165.2	168.9	169.7	171.2	164.4	167.3
37.5°	116.6	112.1	113.7	115.1	115.9	117.3	116.6	115.9
40°	74.8	71.8	73.9	73.9	74.8	75.4	75.4	76.2
42.5°	45.7	43.3	44.8	44.8	45.7	45.7	45.7	46.3
45°	26.1	25.4	25.4	26.1	26.1	26.1	25.4	26.1
47.5°	14.1	13.4	14.1	14.1	14.1	14.1	14.1	14.1
50°	7.4	6.8	6.8	6.8	6.8	6.8	6.8	6.8
52.5°	3.7	3.0	3.0	3.0	2.2	3.0	2.2	2.2
55°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
57.5°	1.5	0.7	0.7	0.7	0.0	0.0	0.0	0.0
60°	1.5	0.7	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.5	0.7	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.5	0.7	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	2.2	1.5	0.7	0.7	0.7	0.0	0.0	0.0
70°	2.2	1.5	1.5	0.7	0.7	0.0	0.0	0.0
72.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
75°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
77.5°	2.2	2.2	1.5	1.5	0.7	0.7	0.7	0.0
80°	3.0	2.2	1.5	1.5	1.5	0.7	0.7	0.7
82.5°	3.0	2.2	1.5	1.5	1.5	0.7	0.7	0.7
85°	3.0	2.2	2.2	1.5	1.5	0.7	0.7	0.7
87.5°	3.0	2.2	2.2	1.5	1.5	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)