

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212594

Luminaire Tested: **LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4345.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35060	35060	35060
5°	96238	32307	13182
10°	210887	26442	5023
15°	322131	20125	5893
20°	373218	14969	9155
25°	407132	12309	14775
30°	454646	11171	15089
35°	462576	7658	10344
40°	470701	3636	5233
45°	471464	1510	2283
50°	398581	656	703
55°	128347	450	113
60°	25480	517	0
65°	2598	611	0
70°	277	843	0
75°	0	1115	0
80°	0	1884	174
85°	0	3754	346



TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.5	2.5
10°-20°	571.7	13.2
20°-30°	1094.7	25.2
30°-40°	1289.7	29.7
40°-50°	1013.0	23.3
50°-60°	246.9	5.7
60°-70°	10.6	0.2
70°-80°	4.0	0.1
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1776.9	40.9
0°-40°	3066.6	70.6
0°-60°	4326.5	99.6
0°-90°	4345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4345.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	814	814	814	814	814	
5°	2227	1611	748	391	305	294
15°	7227	3712	452	129	132	2017
25°	8570	4513	259	271	311	3994
35°	8801	2853	146	188	197	5518
45°	7743	882	25	35	38	5818
55°	1710	32	6	4	2	2035
65°	26	4	6	4	0	68
75°	0	4	7	4	0	0
85°	0	4	8	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3
2.5°	1395.8	1392.8	1372.5	1391.3	1334.2	1332.0	1306.4	1295.2	1262.0	1230.5	1185.4
5°	2226.7	2177.8	2138.0	2139.5	2029.8	2009.5	1952.4	1894.6	1806.0	1723.3	1611.4
7.5°	3394.0	3336.2	3252.1	3216.8	3007.2	2945.6	2827.6	2673.6	2480.6	2288.3	2080.9
10°	4823.6	4832.7	4723.8	4623.1	4306.1	4181.3	3990.5	3687.0	3321.2	2959.8	2592.5
12.5°	6262.3	6256.2	6126.3	5973.8	5583.2	5407.3	5153.4	4774.9	4290.2	3729.9	3155.2
15°	7226.8	7269.6	7214.9	7093.1	6759.6	6558.2	6272.1	5758.2	5167.7	4487.1	3711.8
17.5°	7832.4	7872.8	7853.4	7757.9	7463.5	7248.6	7009.8	6589.0	5906.1	5050.5	4150.5
20°	8145.5	8209.5	8200.4	8096.8	7874.4	7696.3	7432.7	7042.8	6451.5	5441.9	4434.6
22.5°	8354.4	8403.3	8416.8	8299.6	8069.7	7900.7	7707.6	7312.5	6756.6	5680.8	4547.2
25°	8570.0	8656.5	8571.5	8427.3	8216.2	8054.0	7848.1	7469.5	6902.3	5778.5	4513.4
27.5°	8834.4	8875.8	8683.5	8552.0	8317.6	8141.9	7923.2	7560.4	6927.9	5700.3	4320.3
30°	9144.8	8973.4	8839.0	8578.2	8312.4	8141.1	7918.7	7503.3	6793.4	5441.2	3946.2
32.5°	9093.7	8936.6	8784.2	8508.4	8245.5	8075.7	7827.8	7313.3	6475.6	5007.7	3430.1
35°	8800.7	8834.4	8669.9	8441.6	8144.1	7969.0	7698.6	7042.8	5936.2	4409.8	2853.1
37.5°	8553.5	8627.9	8520.4	8309.3	8007.4	7770.8	7405.7	6608.6	5232.4	3651.0	2306.3
40°	8374.7	8398.8	8340.9	8104.2	7741.4	7399.7	6977.5	5828.8	4377.4	2866.0	1820.3
42.5°	8097.5	8161.4	8059.2	7800.7	7250.9	6863.9	6252.5	4928.0	3400.1	2189.1	1370.2
45°	7742.9	7803.8	7677.6	7247.9	6483.2	5915.9	5169.9	3842.6	2515.2	1613.6	881.9
47.5°	7164.5	7202.0	6957.9	6363.6	5251.8	4717.8	3953.0	2678.8	1620.4	902.2	428.9
50°	5950.5	5932.4	5429.2	4698.2	3512.7	2952.4	2352.8	1452.1	727.9	427.4	268.2
52.5°	3835.0	3793.7	3295.6	2630.8	1779.0	1357.5	1020.2	626.6	379.4	239.0	106.0
55°	1709.8	1694.0	1386.7	1077.2	727.9	626.6	478.5	307.3	202.1	83.4	32.3
57.5°	634.0	619.7	546.1	458.2	351.5	292.3	232.1	147.3	51.8	27.8	17.2
60°	295.9	295.2	260.0	214.1	148.8	112.7	65.4	34.6	21.8	15.0	9.8
62.5°	94.6	92.4	64.7	47.3	33.7	29.3	23.2	17.2	11.2	8.3	6.0
65°	25.5	25.5	23.2	19.6	15.8	13.6	11.2	8.3	5.3	4.5	3.8
67.5°	9.8	9.8	9.0	8.3	6.0	5.3	4.5	3.8	2.9	3.8	3.8
70°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.9	2.9	3.8
72.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	2.9	3.8	3.8
75°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	2.9	3.8	3.8
77.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	2.9	3.8	3.8
80°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	2.9	3.8	3.8
82.5°	0.0	0.0	0.7	1.5	1.5	1.5	2.2	2.9	2.9	3.8	4.5
85°	0.0	0.0	0.7	1.5	1.5	2.2	2.2	2.9	2.9	3.8	4.5
87.5°	0.0	0.0	0.7	1.5	1.5	2.2	2.2	2.9	2.9	3.8	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3
2.5°	1152.4	1102.8	1034.4	994.6	984.8	963.8	927.0	872.1	827.1	783.5	758.0
5°	1516.8	1399.6	1268.0	1175.6	1138.1	1087.7	998.4	906.0	821.0	747.5	689.6
7.5°	1902.9	1709.8	1497.2	1326.0	1264.4	1184.7	1039.0	901.5	785.1	682.9	605.5
10°	2286.7	1975.8	1687.3	1439.4	1338.7	1230.5	1038.2	860.1	723.5	604.8	519.1
12.5°	2670.6	2223.6	1827.0	1507.7	1377.1	1240.3	1007.4	797.1	645.3	524.4	442.5
15°	3025.2	2421.2	1921.6	1531.0	1373.3	1211.7	945.1	720.4	563.4	451.5	375.6
17.5°	3289.6	2524.8	1943.5	1495.6	1313.9	1135.2	849.6	630.2	485.3	386.9	309.5
20°	3419.6	2541.4	1891.5	1395.0	1211.7	1026.1	745.2	543.9	418.4	326.7	261.4
22.5°	3419.6	2463.2	1779.0	1268.9	1084.1	900.7	644.5	472.5	365.8	284.7	229.9
25°	3289.6	2307.7	1627.9	1123.1	943.5	776.8	557.4	419.1	325.3	259.1	213.3
27.5°	3037.2	2093.0	1434.1	960.9	805.3	666.3	488.3	370.4	294.5	233.6	234.3
30°	2690.2	1829.2	1211.7	789.5	663.3	547.6	410.9	310.2	235.9	224.7	231.4
32.5°	2289.0	1513.7	960.0	612.3	513.9	431.2	312.5	219.4	187.9	189.3	196.8
35°	1877.4	1191.4	722.6	453.7	382.3	312.5	205.1	144.2	142.8	145.7	151.0
37.5°	1482.2	891.7	522.9	332.1	256.9	192.3	110.4	99.1	99.1	102.2	105.1
40°	1110.3	632.5	359.8	196.8	124.7	87.9	69.9	64.7	63.8	64.7	68.3
42.5°	762.5	400.4	214.1	78.8	60.1	51.1	44.4	40.6	39.8	40.6	42.8
45°	428.2	246.4	83.4	42.1	36.1	32.3	27.8	25.5	24.8	24.8	26.3
47.5°	268.2	97.7	37.5	26.3	22.5	21.0	18.1	16.5	15.8	15.8	16.5
50°	102.9	38.4	23.2	17.2	15.0	13.6	12.0	10.5	9.8	9.8	10.5
52.5°	35.3	22.5	15.0	11.2	9.8	9.0	7.6	6.7	6.7	6.7	6.7
55°	19.6	13.6	9.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0
57.5°	12.0	8.3	6.0	5.3	5.3	5.3	5.3	5.3	5.3	6.0	6.0
60°	6.7	5.3	4.5	4.5	4.5	4.5	5.3	5.3	5.3	6.0	6.0
62.5°	4.5	4.5	4.5	4.5	4.5	4.5	5.3	5.3	6.0	6.0	6.0
65°	3.8	3.8	3.8	4.5	4.5	4.5	5.3	5.3	6.0	6.0	6.0
67.5°	3.8	3.8	4.5	4.5	4.5	5.3	5.3	6.0	6.0	6.0	6.0
70°	3.8	4.5	4.5	5.3	5.3	5.3	6.0	6.0	6.0	6.7	6.7
72.5°	3.8	4.5	4.5	5.3	5.3	5.3	6.0	6.0	6.7	6.7	6.7
75°	4.5	4.5	4.5	5.3	5.3	5.3	6.0	6.7	6.7	6.7	6.7
77.5°	4.5	4.5	5.3	5.3	5.3	6.0	6.0	6.7	6.7	6.7	6.7
80°	4.5	4.5	5.3	5.3	6.0	6.0	6.7	6.7	6.7	7.6	7.6
82.5°	4.5	4.5	5.3	6.0	6.0	6.0	6.7	6.7	7.6	7.6	7.6
85°	4.5	5.3	5.3	6.0	6.0	6.0	6.7	6.7	7.6	7.6	7.6
87.5°	4.5	5.3	5.3	6.0	6.0	6.0	6.7	6.7	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3
2.5°	724.2	692.7	661.0	637.8	626.6	615.3	590.5	558.1	544.7	525.1	513.9
5°	631.1	577.7	535.6	507.9	491.4	469.5	441.0	409.5	391.4	371.1	357.5
7.5°	534.9	472.5	432.0	406.4	389.9	362.8	326.7	289.2	267.4	244.8	229.2
10°	450.8	391.4	345.6	316.2	295.2	263.7	227.6	201.3	182.5	163.1	147.3
12.5°	376.4	312.5	263.7	239.0	224.7	194.6	164.5	135.2	123.9	120.2	120.2
15°	305.0	247.2	205.8	184.8	169.8	137.5	131.5	129.9	129.2	128.5	129.9
17.5°	248.6	199.8	156.2	145.7	144.2	143.5	144.2	144.2	145.0	147.3	151.0
20°	208.9	163.8	160.7	161.5	161.5	164.5	168.3	171.3	174.3	178.1	184.8
22.5°	185.5	184.8	190.1	190.8	194.6	199.1	205.8	210.4	217.8	221.6	231.4
25°	214.1	219.4	229.2	232.1	238.1	245.7	256.2	262.2	271.2	275.6	287.0
27.5°	242.6	250.9	262.9	266.7	272.0	283.9	291.5	296.8	301.3	304.2	311.0
30°	240.4	247.9	260.0	260.7	268.2	276.5	281.0	285.4	288.5	287.7	291.5
32.5°	203.5	210.4	221.6	221.6	229.9	236.6	239.0	242.6	242.6	242.6	244.1
35°	156.2	160.7	168.3	170.5	177.2	181.8	183.3	187.9	187.9	186.3	186.3
37.5°	108.2	114.2	119.4	121.0	125.4	128.5	132.2	133.0	131.5	132.2	132.2
40°	70.6	74.3	78.1	78.8	82.6	84.8	88.6	88.6	89.4	88.6	90.2
42.5°	43.5	46.6	48.9	50.4	51.8	53.3	55.6	56.3	57.1	56.3	57.8
45°	27.0	28.6	30.1	30.8	31.5	32.3	34.6	34.6	34.6	34.6	35.3
47.5°	16.5	17.2	18.1	18.1	18.8	19.6	20.3	20.3	20.3	20.3	21.0
50°	9.8	10.5	10.5	10.5	11.2	11.2	12.0	12.0	12.0	11.2	12.0
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.0	6.7
55°	6.0	6.0	5.3	5.3	5.3	5.3	5.3	4.5	3.8	3.8	2.9
57.5°	5.3	5.3	5.3	5.3	5.3	4.5	4.5	3.8	3.8	2.9	2.2
60°	5.3	5.3	5.3	5.3	5.3	4.5	4.5	3.8	2.9	2.9	2.2
62.5°	6.0	5.3	5.3	5.3	5.3	4.5	4.5	3.8	2.9	2.9	2.2
65°	6.0	6.0	5.3	5.3	5.3	4.5	4.5	3.8	3.8	2.9	2.2
67.5°	6.0	6.0	6.0	5.3	6.0	5.3	4.5	4.5	3.8	2.9	2.9
70°	6.7	6.0	6.0	6.0	6.0	5.3	5.3	4.5	3.8	2.9	2.9
72.5°	6.7	6.7	6.0	6.0	6.0	5.3	5.3	4.5	3.8	3.8	2.9
75°	6.7	6.7	6.0	6.0	6.0	5.3	5.3	4.5	4.5	3.8	2.9
77.5°	6.7	6.7	6.7	6.0	6.0	6.0	5.3	5.3	4.5	3.8	2.9
80°	6.7	6.7	6.7	6.7	6.7	6.0	6.0	5.3	4.5	3.8	2.9
82.5°	7.6	6.7	6.7	6.7	6.7	6.0	6.0	5.3	4.5	3.8	3.8
85°	7.6	7.6	6.7	6.7	6.7	6.0	6.0	5.3	4.5	4.5	3.8
87.5°	7.6	6.7	6.7	6.7	6.7	6.0	6.0	5.3	4.5	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212594

CATALOG NUMBER: LDSQA6A50927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	814.3	814.3	814.3	814.3	814.3	814.3	814.3	814.3
2.5°	502.6	496.5	496.5	486.0	484.5	476.2	483.1	478.5
5°	342.6	332.8	329.8	319.3	315.5	305.7	308.8	305.0
7.5°	215.6	205.8	202.8	195.3	190.8	183.3	184.1	181.8
10°	131.5	122.5	120.2	118.0	115.6	114.9	115.6	114.9
12.5°	119.4	118.7	117.2	118.0	116.5	117.2	118.0	117.2
15°	129.9	131.5	129.9	130.7	129.9	131.5	132.2	132.2
17.5°	152.5	155.5	154.0	156.2	155.5	159.3	159.3	159.3
20°	187.0	192.3	190.8	193.9	193.9	198.4	198.4	199.8
22.5°	235.2	241.9	241.2	247.9	246.4	251.7	251.7	253.1
25°	293.0	299.7	300.5	305.0	304.2	309.5	309.5	311.0
27.5°	317.1	320.7	320.0	322.3	323.1	326.0	328.3	326.7
30°	297.5	300.5	299.7	301.3	301.3	303.5	305.7	303.5
32.5°	250.2	252.4	252.4	255.5	253.1	253.9	257.7	255.5
35°	191.5	193.0	191.5	193.0	193.9	193.9	197.5	196.8
37.5°	136.8	137.5	137.5	139.7	137.5	137.5	141.2	142.0
40°	91.7	92.4	91.7	94.6	93.1	93.1	95.5	93.1
42.5°	58.6	59.4	58.6	60.9	59.4	60.9	61.6	62.3
45°	36.1	36.1	35.3	36.8	36.1	36.8	37.5	37.5
47.5°	21.0	21.0	20.3	21.8	21.0	21.0	21.0	21.8
50°	11.2	11.2	11.2	12.0	11.2	11.2	11.2	10.5
52.5°	6.0	6.0	5.3	6.0	5.3	5.3	5.3	5.3
55°	2.9	2.2	2.2	2.2	1.5	1.5	1.5	1.5
57.5°	2.2	1.5	1.5	0.7	0.7	0.7	0.0	0.0
60°	1.5	1.5	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.5	1.5	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.5	1.5	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	2.2	1.5	1.5	0.7	0.7	0.0	0.0	0.0
70°	2.2	1.5	1.5	0.7	0.7	0.0	0.0	0.0
72.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
75°	2.2	2.2	1.5	1.5	0.7	0.7	0.0	0.0
77.5°	2.9	2.2	1.5	1.5	0.7	0.7	0.0	0.0
80°	2.9	2.2	1.5	1.5	1.5	0.7	0.7	0.7
82.5°	2.9	2.2	2.2	1.5	1.5	0.7	0.7	0.7
85°	2.9	2.2	2.2	1.5	1.5	0.7	0.7	0.7
87.5°	2.9	2.2	2.2	1.5	1.5	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)