

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212598

Luminaire Tested: **LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4422.1 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34346	34346	34346
5°	88096	31244	9729
10°	171727	24011	4674
15°	308273	16305	6272
20°	457680	12380	10355
25°	520226	10195	16233
30°	563938	11151	15273
35°	594005	7227	9466
40°	606853	3209	4609
45°	548107	1224	1711
50°	360802	482	482
55°	98808	428	0
60°	19737	491	0
65°	1396	662	0
70°	214	818	0
75°	0	1198	0
80°	0	1785	198
85°	0	3557	395

TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.7	2.2
10°-20°	519.1	11.7
20°-30°	1176.5	26.6
30°-40°	1412.2	31.9
40°-50°	995.3	22.5
50°-60°	205.4	4.6
60°-70°	7.3	0.2
70°-80°	4.3	0.1
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1793.3	40.6
0°-40°	3205.5	72.5
0°-60°	4406.2	99.6
0°-90°	4422.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4422.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	798	798	798	798	798	
5°	2038	1485	723	301	225	251
15°	6916	3043	366	130	141	2052
25°	10951	3680	215	301	342	5054
35°	11301	2577	138	180	180	7026
45°	9002	884	20	27	28	6620
55°	1316	18	6	4	0	1734
65°	14	4	6	4	0	41
75°	0	4	7	5	0	0
85°	0	5	7	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7
2.5°	1359.7	1318.6	1334.8	1287.3	1276.9	1268.0	1276.9	1225.4	1196.4	1159.5	1129.7
5°	2038.3	1989.2	2000.6	1917.7	1880.0	1854.1	1849.4	1743.2	1663.7	1576.0	1485.1
7.5°	2837.5	2790.9	2784.4	2655.8	2577.8	2533.6	2515.2	2363.2	2225.7	2069.7	1899.2
10°	3927.9	3821.8	3788.7	3602.2	3453.5	3359.5	3243.6	3000.7	2759.5	2524.0	2306.9
12.5°	5196.7	5138.8	5056.8	4727.9	4467.5	4333.9	4161.0	3781.5	3416.5	3027.3	2663.8
15°	6915.9	6710.0	6570.1	6094.8	5675.1	5469.3	5216.8	4636.3	4084.7	3591.8	3042.6
17.5°	8595.5	8487.7	8269.1	7652.3	7005.9	6681.0	6304.7	5515.9	4736.8	4035.6	3365.0
20°	9988.9	9887.7	9638.4	9057.1	8339.9	7860.6	7387.0	6304.7	5286.8	4389.5	3580.6
22.5°	10656.3	10592.0	10388.6	9890.9	9279.8	8823.9	8314.9	6976.2	5693.6	4621.0	3678.6
25°	10950.6	10920.9	10789.8	10397.5	9821.7	9434.9	8954.2	7451.3	5947.0	4728.7	3680.2
27.5°	11248.9	11254.6	10965.2	10654.8	10108.8	9737.4	9274.2	7662.0	5992.7	4668.4	3559.6
30°	11343.1	11283.5	11155.7	10710.3	10191.7	9796.8	9299.9	7564.7	5804.7	4420.8	3319.2
32.5°	11304.4	11281.2	11140.4	10669.2	10050.9	9615.9	9051.4	7178.8	5433.1	4067.0	2978.3
35°	11301.2	11257.8	10935.4	10530.9	9769.5	9232.3	8488.6	6554.8	4907.3	3600.7	2577.0
37.5°	11097.0	10989.2	10747.2	10202.0	9198.6	8517.6	7683.7	5792.5	4264.0	3077.2	2179.0
40°	10797.1	10652.3	10334.0	9508.9	8209.6	7424.8	6611.1	4926.5	3583.0	2561.0	1756.1
42.5°	10170.7	9952.0	9501.7	8367.1	6891.7	6184.1	5507.1	4049.3	2922.0	2086.6	1340.4
45°	9001.6	8702.5	8093.7	6848.2	5567.4	4990.1	4445.8	3258.1	2339.0	1547.8	883.7
47.5°	7235.1	6957.6	6403.6	5451.6	4366.1	3878.1	3443.8	2423.5	1585.7	896.6	422.1
50°	5386.5	5148.5	4715.9	3788.7	2930.9	2547.3	2175.8	1376.6	742.9	426.2	175.2
52.5°	3213.8	3095.7	2712.1	2101.0	1447.4	1247.1	1001.1	582.9	374.6	154.3	47.4
55°	1316.3	1214.9	1071.0	859.5	629.5	533.9	456.7	287.8	116.6	32.2	17.7
57.5°	595.0	572.5	507.4	398.8	289.5	242.8	164.0	54.6	25.7	16.0	10.5
60°	229.2	206.6	176.9	95.7	41.1	34.6	28.1	18.5	12.9	8.8	6.5
62.5°	32.9	31.4	28.1	22.5	17.7	16.0	13.7	9.7	7.2	5.7	4.8
65°	13.7	13.7	12.0	9.7	8.0	7.2	6.5	4.8	4.0	4.0	4.0
67.5°	5.7	5.7	4.8	4.0	3.2	3.2	3.2	2.4	3.2	3.2	4.0
70°	1.7	1.7	1.7	1.7	1.7	1.7	2.4	2.4	3.2	3.2	4.0
72.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.4	3.2	4.0	4.0
75°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.4	3.2	4.0	4.0
77.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.0
80°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.8
82.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.8
85°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.8
87.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7
2.5°	1104.0	1052.6	1038.0	993.1	955.2	936.8	913.4	861.2	821.8	769.5	738.1
5°	1421.5	1324.3	1247.1	1153.1	1091.1	1050.9	988.2	892.6	815.4	722.9	656.9
7.5°	1764.9	1587.2	1448.1	1292.9	1203.7	1133.7	1026.8	889.2	776.0	652.9	550.8
10°	2096.3	1830.9	1612.1	1389.4	1272.0	1174.8	1027.7	854.7	704.3	549.2	441.4
12.5°	2388.1	2045.5	1737.6	1451.4	1305.8	1184.4	1000.3	792.8	611.1	451.9	357.0
15°	2631.8	2212.0	1826.0	1474.6	1308.3	1163.5	943.2	704.3	507.4	365.8	299.1
17.5°	2816.7	2299.7	1853.4	1446.6	1261.5	1104.0	855.5	592.6	411.7	310.3	251.7
20°	2912.4	2316.6	1814.0	1370.1	1175.5	1014.0	740.6	480.8	348.9	270.2	210.6
22.5°	2924.4	2269.1	1720.0	1260.8	1067.0	904.6	613.5	401.2	311.2	238.8	185.7
25°	2852.9	2166.1	1585.7	1136.9	948.0	779.2	499.4	359.4	283.1	214.6	213.9
27.5°	2700.1	1989.2	1424.8	993.1	804.1	633.7	423.7	324.9	252.5	227.5	242.0
30°	2484.6	1762.6	1227.0	811.2	628.0	487.2	357.0	267.7	222.0	224.3	236.4
32.5°	2192.7	1481.1	994.6	594.2	449.5	366.6	267.7	182.5	184.1	184.9	195.4
35°	1826.0	1187.7	742.9	399.7	316.0	258.1	151.2	134.3	136.6	137.5	144.8
37.5°	1463.4	912.6	493.7	266.1	198.6	135.9	94.0	90.0	91.7	90.9	98.9
40°	1120.9	636.0	295.9	131.9	76.3	63.5	57.9	55.5	56.3	57.1	62.0
42.5°	793.7	344.9	146.3	49.8	40.2	36.9	34.6	32.9	33.7	33.7	36.9
45°	402.9	163.2	49.8	27.4	24.9	22.5	20.9	20.1	20.1	20.1	21.7
47.5°	174.5	53.9	23.4	16.9	15.2	14.5	12.9	12.0	12.0	12.0	12.9
50°	54.6	21.7	14.5	11.2	9.7	8.8	8.0	8.0	8.0	7.2	8.0
52.5°	20.1	13.7	9.7	7.2	6.5	6.5	6.5	5.7	6.5	5.7	6.5
55°	12.0	8.8	6.5	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
57.5°	8.0	6.5	5.7	5.7	4.8	4.8	5.7	5.7	5.7	5.7	5.7
60°	5.7	5.7	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7
62.5°	4.8	4.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	6.5
65°	4.0	4.8	4.8	4.8	4.8	4.8	5.7	5.7	6.5	6.5	6.5
67.5°	4.0	4.8	4.8	5.7	5.7	5.7	5.7	6.5	6.5	6.5	6.5
70°	4.8	4.8	5.7	5.7	5.7	5.7	6.5	6.5	6.5	6.5	7.2
72.5°	4.8	4.8	5.7	5.7	5.7	5.7	6.5	6.5	7.2	7.2	7.2
75°	4.8	5.7	5.7	5.7	5.7	6.5	6.5	6.5	7.2	7.2	7.2
77.5°	4.8	5.7	5.7	6.5	6.5	6.5	6.5	7.2	7.2	7.2	7.2
80°	4.8	5.7	5.7	6.5	6.5	6.5	7.2	7.2	7.2	7.2	8.0
82.5°	4.8	5.7	5.7	6.5	6.5	6.5	7.2	7.2	7.2	7.2	8.0
85°	5.7	5.7	6.5	6.5	6.5	6.5	7.2	7.2	7.2	7.2	8.0
87.5°	5.7	5.7	6.5	6.5	6.5	6.5	7.2	7.2	8.0	7.2	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7
2.5°	696.3	649.7	617.5	605.5	582.1	545.2	523.4	503.4	465.5	457.5	436.6
5°	581.4	506.6	453.5	433.4	406.9	375.5	344.9	324.9	300.8	291.1	276.6
7.5°	458.3	383.5	337.7	321.7	303.1	277.4	250.0	230.0	205.1	192.2	180.1
10°	360.3	304.8	266.1	250.0	230.8	203.4	175.2	148.8	127.1	113.4	110.9
12.5°	292.6	246.9	205.8	188.9	166.5	139.1	118.9	118.2	116.6	115.8	117.4
15°	239.7	195.4	152.0	133.5	127.1	126.3	128.6	131.1	130.3	132.6	134.3
17.5°	196.9	149.5	139.9	140.7	141.5	144.0	148.0	154.3	155.2	159.2	162.4
20°	160.8	158.4	162.4	165.7	168.0	172.9	181.7	189.7	192.2	197.8	204.3
22.5°	182.5	189.7	198.6	202.6	205.8	214.6	224.3	237.2	242.0	249.2	258.1
25°	220.3	232.3	246.0	250.9	255.7	270.2	281.4	296.7	300.8	309.5	318.4
27.5°	251.7	264.6	279.1	285.4	289.5	304.0	313.6	323.2	323.2	328.0	334.5
30°	246.9	257.4	269.4	274.2	275.8	286.3	295.9	299.1	297.5	300.0	304.8
32.5°	205.1	213.1	222.8	226.8	228.3	235.6	243.7	243.7	242.8	242.8	246.0
35°	152.0	157.6	162.4	166.5	168.9	173.7	180.9	180.1	180.1	178.5	180.9
37.5°	102.1	105.4	110.9	112.6	113.4	116.6	122.2	122.2	120.6	121.4	123.1
40°	62.0	66.0	69.1	70.0	71.5	74.0	78.0	78.0	78.0	78.0	78.8
42.5°	36.9	39.4	41.8	41.8	42.6	45.8	47.4	47.4	47.4	47.4	48.3
45°	21.7	22.5	24.1	24.9	24.9	26.6	27.4	27.4	27.4	27.4	28.1
47.5°	12.9	13.7	13.7	14.5	14.5	15.2	16.0	16.0	15.2	15.2	15.2
50°	8.0	8.0	8.0	8.0	8.8	8.8	8.8	8.8	8.8	8.8	8.0
52.5°	6.5	6.5	6.5	6.5	5.7	5.7	5.7	5.7	4.8	4.8	4.0
55°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.8	4.0	3.2	2.4
57.5°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	3.2	2.4
60°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	3.2	2.4
62.5°	6.5	6.5	5.7	5.7	5.7	4.8	4.8	4.0	4.0	3.2	2.4
65°	6.5	6.5	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	2.4
67.5°	6.5	6.5	6.5	6.5	5.7	5.7	5.7	4.8	4.0	3.2	2.4
70°	7.2	7.2	6.5	6.5	6.5	5.7	5.7	4.8	4.0	4.0	3.2
72.5°	7.2	7.2	6.5	6.5	6.5	6.5	5.7	4.8	4.8	4.0	3.2
75°	7.2	7.2	7.2	7.2	6.5	6.5	5.7	5.7	4.8	4.0	3.2
77.5°	7.2	7.2	7.2	7.2	6.5	6.5	6.5	5.7	4.8	4.0	3.2
80°	7.2	7.2	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.0	3.2
82.5°	8.0	8.0	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.0	4.0
85°	8.0	8.0	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.8	4.0
87.5°	8.0	8.0	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.8	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212598

CATALOG NUMBER: LDSQA6A50930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	797.7	797.7	797.7	797.7	797.7	797.7	797.7	797.7
2.5°	423.7	399.7	391.6	397.2	390.8	386.0	379.5	376.3
5°	265.4	247.7	242.0	243.7	238.0	233.2	226.8	225.1
7.5°	163.2	146.3	139.9	139.9	133.5	127.8	123.8	121.4
10°	109.4	106.1	106.9	107.7	106.9	107.7	105.4	106.9
12.5°	117.4	115.8	117.4	118.2	118.2	119.8	116.6	118.9
15°	136.6	135.1	137.5	139.1	139.1	141.5	138.3	140.7
17.5°	167.2	166.5	170.5	172.0	172.9	176.9	172.9	176.1
20°	211.5	210.6	216.3	218.7	217.9	226.0	220.3	226.0
22.5°	268.6	266.9	274.9	277.4	278.2	288.6	283.8	287.8
25°	325.7	327.2	331.2	335.4	336.1	344.9	337.7	341.7
27.5°	337.7	335.4	337.7	342.6	343.4	347.4	340.9	344.1
30°	305.5	301.5	302.3	308.0	309.5	311.2	305.5	307.2
32.5°	248.5	242.0	242.0	247.7	249.2	251.7	242.0	246.0
35°	183.4	177.7	177.7	181.7	182.5	184.1	176.9	180.1
37.5°	125.4	120.6	122.2	123.8	124.6	126.3	125.4	124.6
40°	80.4	77.2	79.6	79.6	80.4	81.2	81.2	82.0
42.5°	49.1	46.6	48.3	48.3	49.1	49.1	49.1	49.8
45°	28.1	27.4	27.4	28.1	28.1	28.1	27.4	28.1
47.5°	15.2	14.5	15.2	15.2	15.2	15.2	15.2	15.2
50°	8.0	7.2	7.2	7.2	7.2	7.2	7.2	7.2
52.5°	4.0	3.2	3.2	3.2	2.4	3.2	2.4	2.4
55°	2.4	1.7	1.7	1.7	0.8	0.8	0.0	0.0
57.5°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
60°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.4	1.7	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.4	1.7	1.7	0.8	0.8	0.0	0.0	0.0
72.5°	2.4	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.4	1.7	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	2.4	2.4	1.7	1.7	0.8	0.8	0.8	0.0
80°	3.2	2.4	1.7	1.7	1.7	0.8	0.8	0.8
82.5°	3.2	2.4	1.7	1.7	1.7	0.8	0.8	0.8
85°	3.2	2.4	2.4	1.7	1.7	0.8	0.8	0.8
87.5°	3.2	2.4	2.4	1.7	1.7	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)