

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212600

Luminaire Tested: **LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4650.4 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	37523	37523	37523
5°	102998	34576	14107
10°	225708	28295	5378
15°	344770	21538	6307
20°	399449	16027	9796
25°	435745	13178	15815
30°	486589	11952	16153
35°	495080	8200	11069
40°	503778	3884	5604
45°	504595	1620	2448
50°	426586	703	750
55°	137362	488	128
60°	27280	560	0
65°	2791	662	0
70°	302	906	0
75°	0	1198	0
80°	0	1984	198
85°	0	3952	395



TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.3	2.5
10°-20°	611.9	13.2
20°-30°	1171.6	25.2
30°-40°	1380.3	29.7
40°-50°	1084.2	23.3
50°-60°	264.2	5.7
60°-70°	11.4	0.2
70°-80°	4.3	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1901.8	40.9
0°-40°	3282.1	70.6
0°-60°	4630.5	99.6
0°-90°	4650.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4650.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	872	872	872	872	872	
5°	2383	1725	800	419	326	315
15°	7735	3973	483	138	142	2159
25°	9172	4831	277	290	333	4275
35°	9419	3054	156	201	211	5906
45°	8287	944	27	37	40	6226
55°	1830	35	6	4	2	2178
65°	27	4	6	4	0	72
75°	0	4	7	5	0	0
85°	0	5	8	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5
2.5°	1493.9	1490.7	1469.0	1489.0	1427.9	1425.6	1398.2	1386.1	1350.7	1317.0	1268.7
5°	2383.1	2330.9	2288.3	2289.8	2172.5	2150.8	2089.7	2027.7	1932.8	1844.5	1724.6
7.5°	3632.5	3570.7	3480.6	3442.8	3218.4	3152.6	3026.3	2861.5	2654.9	2449.1	2227.1
10°	5162.6	5172.3	5055.7	4948.0	4608.6	4475.2	4270.9	3946.2	3554.5	3167.8	2774.7
12.5°	6702.3	6695.9	6556.8	6393.6	5975.5	5787.3	5515.6	5110.3	4591.7	3991.9	3376.9
15°	7734.7	7780.4	7721.8	7591.5	7234.6	7019.1	6712.8	6162.8	5530.9	4802.4	3972.7
17.5°	8382.7	8426.1	8405.3	8303.1	7987.9	7758.0	7502.3	7052.0	6321.1	5405.5	4442.2
20°	8718.0	8786.3	8776.7	8665.7	8427.7	8237.2	7955.0	7537.7	6904.9	5824.4	4746.1
22.5°	8941.4	8993.7	9008.2	8882.8	8636.8	8455.9	8249.3	7826.4	7231.4	6080.0	4866.7
25°	9172.3	9264.7	9173.9	9019.4	8793.6	8619.9	8399.6	7994.4	7387.3	6184.5	4830.6
27.5°	9455.2	9499.5	9293.7	9152.9	8902.0	8713.9	8480.0	8091.6	7414.6	6100.8	4623.9
30°	9787.3	9604.0	9460.1	9181.1	8896.5	8713.1	8475.1	8030.5	7270.7	5823.5	4223.5
32.5°	9732.6	9564.6	9401.4	9106.3	8824.9	8643.1	8377.9	7827.2	6930.6	5359.6	3671.1
35°	9419.1	9455.2	9279.2	9034.8	8716.4	8529.0	8239.6	7537.7	6353.4	4719.6	3053.7
37.5°	9154.6	9234.2	9119.2	8893.3	8570.0	8316.8	7926.1	7072.9	5600.0	3907.6	2468.3
40°	8963.2	8988.9	8927.1	8673.7	8285.4	7919.6	7467.7	6238.4	4685.1	3067.3	1948.2
42.5°	8666.5	8734.8	8625.6	8349.0	7760.4	7346.3	6691.9	5274.4	3639.0	2342.9	1466.5
45°	8287.0	8352.2	8217.0	7757.2	6938.6	6331.6	5533.3	4112.5	2691.8	1727.0	943.9
47.5°	7667.9	7708.1	7446.9	6810.8	5620.9	5049.2	4230.8	2867.2	1734.2	965.6	459.1
50°	6368.6	6349.3	5810.7	5028.3	3759.6	3159.8	2518.2	1554.2	779.0	457.5	287.0
52.5°	4104.5	4060.3	3527.3	2815.7	1903.9	1452.8	1091.9	670.6	406.0	255.7	113.4
55°	1829.9	1813.1	1484.2	1153.0	779.0	670.6	512.1	328.9	216.3	89.2	34.6
57.5°	678.6	663.3	584.6	490.4	376.3	312.8	248.4	157.5	55.5	29.7	18.5
60°	316.8	316.0	278.2	229.2	159.2	120.6	70.0	36.9	23.4	16.0	10.5
62.5°	101.4	98.9	69.1	50.6	36.2	31.4	24.9	18.5	12.0	8.8	6.5
65°	27.4	27.4	24.9	20.9	16.9	14.5	12.0	8.8	5.7	4.8	4.0
67.5°	10.5	10.5	9.7	8.8	6.5	5.7	4.8	4.0	3.2	4.0	4.0
70°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	4.0
72.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.0
75°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.0
77.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.0
80°	0.0	0.0	0.8	0.8	1.7	1.7	2.4	2.4	3.2	4.0	4.0
82.5°	0.0	0.0	0.8	1.7	1.7	1.7	2.4	3.2	3.2	4.0	4.8
85°	0.0	0.0	0.8	1.7	1.7	2.4	2.4	3.2	3.2	4.0	4.8
87.5°	0.0	0.0	0.8	1.7	1.7	2.4	2.4	3.2	3.2	4.0	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5
2.5°	1233.3	1180.4	1107.1	1064.5	1054.1	1031.6	992.1	933.5	885.2	838.6	811.2
5°	1623.3	1497.9	1357.2	1258.2	1218.1	1164.2	1068.5	969.6	878.7	800.0	738.1
7.5°	2036.6	1829.9	1602.4	1419.1	1353.1	1267.9	1111.9	964.8	840.2	730.9	648.1
10°	2447.4	2114.6	1805.9	1540.5	1432.8	1317.0	1111.2	920.6	774.3	647.2	555.5
12.5°	2858.3	2379.9	1955.4	1613.6	1473.8	1327.4	1078.2	853.0	690.7	561.2	473.5
15°	3237.8	2591.4	2056.6	1638.5	1469.7	1296.9	1011.5	771.0	603.0	483.2	402.0
17.5°	3520.8	2702.3	2080.0	1600.8	1406.2	1214.9	909.3	674.6	519.4	414.1	331.2
20°	3659.9	2720.0	2024.5	1493.1	1296.9	1098.3	797.6	582.1	447.8	349.8	279.8
22.5°	3659.9	2636.4	1903.9	1357.9	1160.2	964.1	689.8	505.7	391.5	304.7	246.0
25°	3520.8	2470.0	1742.3	1202.1	1009.8	831.3	596.6	448.6	348.1	277.4	228.3
27.5°	3250.7	2240.0	1534.8	1028.4	861.9	713.2	522.6	396.4	315.2	250.0	250.9
30°	2879.2	1957.7	1296.9	845.0	710.0	586.1	439.8	332.1	252.5	240.4	247.7
32.5°	2449.8	1620.1	1027.5	655.3	550.0	461.5	334.5	234.8	201.0	202.6	210.6
35°	2009.2	1275.2	773.5	485.6	409.2	334.5	219.5	154.3	152.8	156.0	161.7
37.5°	1586.3	954.4	559.6	355.4	274.9	205.8	118.2	106.1	106.1	109.4	112.6
40°	1188.4	677.0	385.2	210.6	133.5	94.0	74.8	69.1	68.3	69.1	73.2
42.5°	816.1	428.6	229.2	84.4	64.3	54.6	47.4	43.4	42.6	43.4	45.8
45°	458.3	263.7	89.2	45.1	38.6	34.6	29.7	27.4	26.6	26.6	28.1
47.5°	287.0	104.5	40.2	28.1	24.1	22.5	19.4	17.7	16.9	16.9	17.7
50°	110.1	40.9	24.9	18.5	16.0	14.5	12.9	11.2	10.5	10.5	11.2
52.5°	37.8	24.1	16.0	12.0	10.5	9.7	8.0	7.2	7.2	7.2	7.2
55°	20.9	14.5	9.7	7.2	6.5	6.5	6.5	6.5	6.5	6.5	6.5
57.5°	12.9	8.8	6.5	5.7	5.7	5.7	5.7	5.7	5.7	6.5	6.5
60°	7.2	5.7	4.8	4.8	4.8	4.8	5.7	5.7	5.7	6.5	6.5
62.5°	4.8	4.8	4.8	4.8	4.8	4.8	5.7	5.7	6.5	6.5	6.5
65°	4.0	4.0	4.0	4.8	4.8	4.8	5.7	5.7	6.5	6.5	6.5
67.5°	4.0	4.0	4.8	4.8	4.8	5.7	5.7	6.5	6.5	6.5	6.5
70°	4.0	4.8	4.8	5.7	5.7	5.7	6.5	6.5	6.5	7.2	7.2
72.5°	4.0	4.8	4.8	5.7	5.7	5.7	6.5	6.5	7.2	7.2	7.2
75°	4.8	4.8	4.8	5.7	5.7	5.7	6.5	7.2	7.2	7.2	7.2
77.5°	4.8	4.8	5.7	5.7	5.7	6.5	6.5	7.2	7.2	7.2	7.2
80°	4.8	4.8	5.7	5.7	6.5	6.5	7.2	7.2	7.2	8.0	8.0
82.5°	4.8	4.8	5.7	6.5	6.5	6.5	7.2	7.2	8.0	8.0	8.0
85°	4.8	5.7	5.7	6.5	6.5	6.5	7.2	7.2	8.0	8.0	8.0
87.5°	4.8	5.7	5.7	6.5	6.5	6.5	7.2	7.2	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5
2.5°	775.0	741.3	707.5	682.6	670.6	658.4	632.0	597.4	582.9	562.0	550.0
5°	675.4	618.3	573.2	543.5	525.8	502.6	472.0	438.1	418.9	397.2	382.7
7.5°	572.4	505.7	462.3	434.9	417.2	388.3	349.8	309.5	286.3	262.1	245.2
10°	482.4	418.9	369.8	338.5	316.0	282.3	243.7	215.5	195.4	174.5	157.5
12.5°	402.9	334.5	282.3	255.7	240.4	208.3	176.1	144.7	132.6	128.6	128.6
15°	326.4	264.6	220.3	197.8	181.7	147.1	140.7	139.1	138.3	137.5	139.1
17.5°	266.1	213.8	167.2	156.0	154.3	153.5	154.3	154.3	155.2	157.5	161.7
20°	223.5	175.2	172.0	172.9	172.9	176.1	180.1	183.4	186.6	190.6	197.8
22.5°	198.6	197.8	203.4	204.3	208.3	213.1	220.3	225.1	233.2	237.2	247.7
25°	229.2	234.8	245.2	248.4	254.9	262.9	274.1	280.6	290.3	295.1	307.2
27.5°	259.7	268.6	281.4	285.4	291.1	304.0	312.0	317.5	322.4	325.7	332.9
30°	257.2	265.4	278.2	279.0	287.0	295.8	300.7	305.5	308.7	308.0	312.0
32.5°	217.9	225.1	237.2	237.2	246.0	253.2	255.7	259.7	259.7	259.7	261.3
35°	167.2	172.0	180.1	182.5	189.7	194.6	196.2	201.0	201.0	199.4	199.4
37.5°	115.8	122.2	127.8	129.4	134.3	137.5	141.5	142.3	140.7	141.5	141.5
40°	75.5	79.6	83.7	84.4	88.5	90.9	94.9	94.9	95.7	94.9	96.5
42.5°	46.6	49.8	52.3	53.9	55.5	57.1	59.5	60.3	61.1	60.3	62.0
45°	28.9	30.6	32.2	32.9	33.7	34.6	36.9	36.9	36.9	36.9	37.8
47.5°	17.7	18.5	19.4	19.4	20.1	20.9	21.7	21.7	21.7	21.7	22.5
50°	10.5	11.2	11.2	11.2	12.0	12.0	12.9	12.9	12.9	12.0	12.9
52.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.5	7.2
55°	6.5	6.5	5.7	5.7	5.7	5.7	5.7	4.8	4.0	4.0	3.2
57.5°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	4.0	3.2	2.4
60°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	3.2	2.4
62.5°	6.5	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	3.2	2.4
65°	6.5	6.5	5.7	5.7	5.7	4.8	4.8	4.0	4.0	3.2	2.4
67.5°	6.5	6.5	6.5	5.7	6.5	5.7	4.8	4.8	4.0	3.2	3.2
70°	7.2	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.0	3.2	3.2
72.5°	7.2	7.2	6.5	6.5	6.5	5.7	5.7	4.8	4.0	4.0	3.2
75°	7.2	7.2	6.5	6.5	6.5	5.7	5.7	4.8	4.8	4.0	3.2
77.5°	7.2	7.2	7.2	6.5	6.5	6.5	5.7	5.7	4.8	4.0	3.2
80°	7.2	7.2	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.0	3.2
82.5°	8.0	7.2	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.0	4.0
85°	8.0	8.0	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.8	4.0
87.5°	8.0	7.2	7.2	7.2	7.2	6.5	6.5	5.7	4.8	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212600

CATALOG NUMBER: LDSQA6A50930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	871.5	871.5	871.5	871.5	871.5	871.5	871.5	871.5
2.5°	537.8	531.5	531.5	520.1	518.6	509.8	517.0	512.1
5°	366.6	356.1	352.9	341.7	337.7	327.2	330.4	326.4
7.5°	230.8	220.3	217.1	209.1	204.3	196.2	196.9	194.6
10°	140.7	131.1	128.6	126.3	123.8	123.0	123.8	123.0
12.5°	127.8	127.1	125.4	126.3	124.6	125.4	126.3	125.4
15°	139.1	140.7	139.1	139.9	139.1	140.7	141.5	141.5
17.5°	163.2	166.4	164.8	167.2	166.4	170.5	170.5	170.5
20°	200.2	205.8	204.3	207.4	207.4	212.3	212.3	213.8
22.5°	251.7	258.9	258.1	265.4	263.7	269.4	269.4	270.9
25°	313.5	320.8	321.6	326.4	325.7	331.2	331.2	332.9
27.5°	339.2	343.3	342.6	344.9	345.7	348.9	351.4	349.8
30°	318.4	321.6	320.8	322.4	322.4	324.9	327.2	324.9
32.5°	267.7	270.1	270.1	273.4	270.9	271.8	275.8	273.4
35°	205.0	206.6	205.0	206.6	207.4	207.4	211.5	210.6
37.5°	146.3	147.1	147.1	149.5	147.1	147.1	151.2	152.0
40°	98.1	98.9	98.1	101.4	99.7	99.7	102.1	99.7
42.5°	62.7	63.5	62.7	65.1	63.5	65.1	66.0	66.8
45°	38.6	38.6	37.8	39.4	38.6	39.4	40.2	40.2
47.5°	22.5	22.5	21.7	23.4	22.5	22.5	22.5	23.4
50°	12.0	12.0	12.0	12.9	12.0	12.0	12.0	11.2
52.5°	6.5	6.5	5.7	6.5	5.7	5.7	5.7	5.7
55°	3.2	2.4	2.4	2.4	1.7	1.7	1.7	1.7
57.5°	2.4	1.7	1.7	0.8	0.8	0.8	0.0	0.0
60°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.4	1.7	1.7	0.8	0.8	0.0	0.0	0.0
70°	2.4	1.7	1.7	0.8	0.8	0.0	0.0	0.0
72.5°	2.4	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.4	2.4	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	3.2	2.4	1.7	1.7	0.8	0.8	0.0	0.0
80°	3.2	2.4	1.7	1.7	1.7	0.8	0.8	0.8
82.5°	3.2	2.4	2.4	1.7	1.7	0.8	0.8	0.8
85°	3.2	2.4	2.4	1.7	1.7	0.8	0.8	0.8
87.5°	3.2	2.4	2.4	1.7	1.7	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)