

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212606

Luminaire Tested: **LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4964.1 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40055	40055	40055
5°	109943	36910	15062
10°	240940	30206	5740
15°	368029	22992	6731
20°	426400	17109	10460
25°	465138	14067	16879
30°	519417	12757	17237
35°	528477	8751	11821
40°	537765	4154	5980
45°	538638	1723	2618
50°	455369	750	804
55°	146632	510	135
60°	29123	586	0
65°	2965	693	0
70°	327	969	0
75°	0	1281	0
80°	0	2132	198
85°	0	4248	395

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.5
10°-20°	653.2	13.2
20°-30°	1250.6	25.2
30°-40°	1473.4	29.7
40°-50°	1157.3	23.3
50°-60°	282.0	5.7
60°-70°	12.1	0.2
70°-80°	4.5	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2030.1	40.9
0°-40°	3503.5	70.6
0°-60°	4942.9	99.6
0°-90°	4964.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4964.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	930	930	930	930	930	
5°	2544	1841	854	447	348	336
15°	8256	4241	516	148	151	2305
25°	9791	5156	296	310	355	4564
35°	10054	3260	166	214	225	6305
45°	8846	1008	28	40	43	6647
55°	1953	37	7	4	2	2325
65°	29	4	7	4	0	77
75°	0	4	8	5	0	0
85°	0	5	9	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	1594.7	1591.2	1568.1	1589.5	1524.3	1521.7	1492.5	1479.6	1441.8	1405.9	1354.3
5°	2543.8	2488.1	2442.6	2444.4	2319.1	2295.8	2230.7	2164.6	2063.2	1968.8	1840.9
7.5°	3877.6	3811.5	3715.5	3675.1	3435.6	3365.2	3230.5	3054.5	2834.0	2614.3	2377.3
10°	5511.0	5521.2	5396.7	5281.8	4919.5	4777.1	4559.0	4212.4	3794.4	3381.5	2961.9
12.5°	7154.5	7147.6	6999.2	6824.9	6378.6	6177.8	5887.7	5455.1	4901.5	4261.3	3604.7
15°	8256.5	8305.4	8242.8	8103.8	7722.6	7492.6	7165.7	6578.6	5904.0	5126.4	4240.7
17.5°	8948.3	8994.6	8972.2	8863.3	8526.8	8281.4	8008.4	7527.8	6747.7	5770.1	4741.9
20°	9306.2	9379.1	9368.8	9250.4	8996.3	8792.9	8491.6	8046.2	7370.8	6217.3	5066.3
22.5°	9544.8	9600.5	9615.9	9482.1	9219.5	9026.4	8805.8	8354.3	7719.2	6490.2	5195.1
25°	9791.0	9889.8	9792.8	9628.0	9386.8	9201.4	8966.2	8533.8	7885.7	6601.7	5156.5
27.5°	10093.1	10140.3	9920.6	9770.5	9502.7	9301.8	9052.1	8637.6	7914.8	6512.5	4935.8
30°	10447.6	10252.0	10098.3	9800.5	9496.6	9301.0	9046.9	8572.3	7761.3	6216.4	4508.4
32.5°	10389.3	10209.9	10035.7	9720.7	9420.3	9226.3	8943.1	8355.2	7398.2	5721.2	3918.8
35°	10054.5	10093.1	9905.3	9644.3	9304.4	9104.4	8795.5	8046.2	6782.0	5038.0	3259.6
37.5°	9772.2	9857.1	9734.4	9493.2	9148.2	8877.8	8460.7	7550.1	5977.8	4171.2	2634.8
40°	9567.9	9595.4	9529.3	9259.0	8844.5	8453.9	7971.5	6659.2	5001.1	3274.3	2079.5
42.5°	9251.2	9324.1	9207.4	8912.2	8284.0	7841.9	7143.4	5630.3	3884.4	2501.0	1565.5
45°	8846.1	8915.6	8771.4	8280.5	7406.9	6758.8	5906.6	4390.1	2873.4	1843.5	1007.6
47.5°	8185.3	8228.1	7949.2	7270.3	6000.1	5389.9	4516.2	3060.6	1851.3	1030.7	490.1
50°	6798.3	6777.7	6202.7	5367.6	4013.2	3373.0	2688.0	1659.1	831.7	488.4	306.4
52.5°	4381.5	4334.3	3765.1	3005.7	2032.3	1550.9	1165.5	715.8	433.4	272.9	121.1
55°	1953.4	1935.4	1584.4	1230.7	831.7	715.8	546.7	351.0	230.9	95.2	36.9
57.5°	724.4	708.1	624.0	523.6	401.7	333.8	265.1	168.3	59.2	31.7	19.7
60°	338.2	337.2	297.0	244.6	169.9	128.7	74.7	39.5	24.9	17.1	11.2
62.5°	108.1	105.6	73.9	54.0	38.6	33.5	26.6	19.7	12.9	9.4	6.8
65°	29.1	29.1	26.6	22.3	18.1	15.5	12.9	9.4	6.0	5.2	4.2
67.5°	11.2	11.2	10.3	9.4	6.8	6.0	5.2	4.2	3.4	4.2	4.2
70°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	3.4	3.4	4.2
72.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	4.2
75°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	4.2
77.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	4.2
80°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	4.2
82.5°	0.0	0.0	0.8	1.8	1.8	1.8	2.6	3.4	3.4	4.2	5.2
85°	0.0	0.0	0.8	1.8	1.8	2.6	2.6	3.4	3.4	4.2	5.2
87.5°	0.0	0.0	0.8	1.8	1.8	2.6	2.6	3.4	3.4	4.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	1316.5	1259.9	1181.8	1136.3	1125.1	1101.2	1059.0	996.4	944.9	895.1	866.0
5°	1732.8	1598.9	1448.8	1343.2	1300.2	1242.8	1140.6	1035.1	938.1	854.0	787.9
7.5°	2174.0	1953.4	1710.5	1514.9	1444.4	1353.5	1187.0	1029.9	896.9	780.2	691.7
10°	2612.5	2257.2	1927.6	1644.4	1529.4	1405.9	1186.1	982.7	826.5	690.9	593.1
12.5°	3051.1	2540.4	2087.3	1722.6	1573.2	1416.9	1151.0	910.6	737.3	599.1	505.5
15°	3456.2	2766.2	2195.4	1749.1	1568.9	1384.4	1079.7	823.0	643.7	515.8	429.2
17.5°	3758.3	2884.6	2220.3	1708.8	1501.1	1296.8	970.7	720.0	554.5	442.0	353.6
20°	3906.9	2903.5	2161.1	1593.8	1384.4	1172.3	851.4	621.4	478.0	373.4	298.7
22.5°	3906.9	2814.3	2032.3	1449.6	1238.5	1029.1	736.4	539.8	418.0	325.3	262.7
25°	3758.3	2636.6	1859.8	1283.1	1077.9	887.5	636.8	479.0	371.6	296.1	243.8
27.5°	3469.9	2391.2	1638.4	1097.8	920.0	761.3	557.9	423.1	336.4	266.9	267.7
30°	3073.4	2089.9	1384.4	902.0	757.8	625.6	469.5	354.5	269.5	256.6	264.3
32.5°	2615.1	1729.4	1096.8	699.5	587.0	492.6	357.1	250.6	214.5	216.3	224.9
35°	2144.8	1361.2	825.6	518.4	436.8	357.1	234.3	164.7	163.1	166.5	172.5
37.5°	1693.3	1018.8	597.3	379.4	293.6	219.7	126.1	113.3	113.3	116.7	120.1
40°	1268.5	722.6	411.1	224.9	142.4	100.4	79.8	73.9	72.9	73.9	78.1
42.5°	871.2	457.5	244.6	90.2	68.7	58.4	50.6	46.4	45.4	46.4	49.0
45°	489.2	281.5	95.2	48.0	41.2	36.9	31.7	29.1	28.3	28.3	30.1
47.5°	306.4	111.6	43.0	30.1	25.7	24.1	20.6	18.9	18.1	18.1	18.9
50°	117.5	43.8	26.6	19.7	17.1	15.5	13.7	12.0	11.2	11.2	12.0
52.5°	40.4	25.7	17.1	12.9	11.2	10.3	8.6	7.7	7.7	7.7	7.7
55°	22.3	15.5	10.3	7.7	6.8	6.8	6.8	6.8	6.8	6.8	6.8
57.5°	13.7	9.4	6.8	6.0	6.0	6.0	6.0	6.0	6.0	6.8	6.8
60°	7.7	6.0	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.8	6.8
62.5°	5.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8
65°	4.2	4.2	4.2	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8
67.5°	4.2	4.2	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8	6.8
70°	4.2	5.2	5.2	6.0	6.0	6.0	6.8	6.8	6.8	7.7	7.7
72.5°	4.2	5.2	5.2	6.0	6.0	6.0	6.8	6.8	7.7	7.7	7.7
75°	5.2	5.2	5.2	6.0	6.0	6.0	6.8	7.7	7.7	7.7	7.7
77.5°	5.2	5.2	6.0	6.0	6.0	6.8	6.8	7.7	7.7	7.7	7.7
80°	5.2	5.2	6.0	6.0	6.8	6.8	7.7	7.7	7.7	8.6	8.6
82.5°	5.2	5.2	6.0	6.8	6.8	6.8	7.7	7.7	8.6	8.6	8.6
85°	5.2	6.0	6.0	6.8	6.8	6.8	7.7	7.7	8.6	8.6	8.6
87.5°	5.2	6.0	6.0	6.8	6.8	6.8	7.7	7.7	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	827.4	791.3	755.3	728.6	715.8	702.9	674.6	637.7	622.2	599.9	587.0
5°	721.0	660.0	611.9	580.2	561.3	536.4	503.7	467.8	447.1	424.0	408.5
7.5°	611.1	539.8	493.5	464.3	445.4	414.5	373.4	330.4	305.5	279.8	261.7
10°	515.0	447.1	394.8	361.3	337.2	301.3	260.1	230.0	208.5	186.2	168.3
12.5°	430.0	357.1	301.3	272.9	256.6	222.3	188.0	154.5	141.6	137.4	137.4
15°	348.5	282.4	235.2	211.1	194.0	157.1	150.2	148.4	147.6	146.8	148.4
17.5°	284.1	228.3	178.5	166.5	164.7	163.9	164.7	164.7	165.7	168.3	172.5
20°	238.6	187.1	183.7	184.6	184.6	188.0	192.2	195.6	199.1	203.4	211.1
22.5°	212.0	211.1	217.1	217.9	222.3	227.4	235.2	240.4	248.9	253.2	264.3
25°	244.6	250.6	261.7	265.1	272.1	280.6	292.6	299.5	309.9	314.9	327.8
27.5°	277.2	286.6	300.4	304.7	310.7	324.4	333.0	339.0	344.2	347.6	355.3
30°	274.6	283.2	297.0	297.8	306.4	315.9	321.0	326.2	329.6	328.7	333.0
32.5°	232.6	240.4	253.2	253.2	262.7	270.3	272.9	277.2	277.2	277.2	279.0
35°	178.5	183.7	192.2	194.8	202.6	207.7	209.4	214.5	214.5	212.9	212.9
37.5°	123.5	130.5	136.4	138.2	143.4	146.8	151.0	151.9	150.2	151.0	151.0
40°	80.7	85.0	89.2	90.2	94.4	97.0	101.2	101.2	102.2	101.2	103.0
42.5°	49.8	53.2	55.8	57.5	59.2	60.9	63.5	64.4	65.3	64.4	66.1
45°	30.9	32.6	34.3	35.2	36.0	36.9	39.5	39.5	39.5	39.5	40.4
47.5°	18.9	19.7	20.6	20.6	21.5	22.3	23.1	23.1	23.1	23.1	24.1
50°	11.2	12.0	12.0	12.0	12.9	12.9	13.7	13.7	13.7	12.9	13.7
52.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	6.8	7.7
55°	6.8	6.8	6.0	6.0	6.0	6.0	6.0	5.2	4.2	4.2	3.4
57.5°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	4.2	3.4	2.6
60°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	3.4	2.6
62.5°	6.8	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	3.4	2.6
65°	6.8	6.8	6.0	6.0	6.0	5.2	5.2	4.2	4.2	3.4	2.6
67.5°	6.8	6.8	6.8	6.0	6.8	6.0	5.2	5.2	4.2	3.4	3.4
70°	7.7	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.2	3.4	3.4
72.5°	7.7	7.7	6.8	6.8	6.8	6.0	6.0	5.2	4.2	4.2	3.4
75°	7.7	7.7	6.8	6.8	6.8	6.0	6.0	5.2	5.2	4.2	3.4
77.5°	7.7	7.7	7.7	6.8	6.8	6.8	6.0	6.0	5.2	4.2	3.4
80°	7.7	7.7	7.7	7.7	7.7	6.8	6.8	6.0	5.2	4.2	3.4
82.5°	8.6	7.7	7.7	7.7	7.7	6.8	6.8	6.0	5.2	4.2	4.2
85°	8.6	8.6	7.7	7.7	7.7	6.8	6.8	6.0	5.2	5.2	4.2
87.5°	8.6	7.7	7.7	7.7	7.7	6.8	6.8	6.0	5.2	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212606

CATALOG NUMBER: LDSQA6A50935D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	574.2	567.3	567.3	555.3	553.5	544.1	551.9	546.7
5°	391.4	380.2	376.8	364.7	360.5	349.3	352.7	348.5
7.5°	246.3	235.2	231.8	223.1	217.9	209.4	210.3	207.7
10°	150.2	139.9	137.4	134.8	132.2	131.3	132.2	131.3
12.5°	136.4	135.6	133.9	134.8	133.0	133.9	134.8	133.9
15°	148.4	150.2	148.4	149.4	148.4	150.2	151.0	151.0
17.5°	174.3	177.7	175.9	178.5	177.7	182.0	182.0	182.0
20°	213.7	219.7	217.9	221.5	221.5	226.6	226.6	228.3
22.5°	268.7	276.4	275.5	283.2	281.5	287.6	287.6	289.2
25°	334.8	342.4	343.3	348.5	347.6	353.6	353.6	355.3
27.5°	362.1	366.5	365.6	368.2	369.1	372.5	375.0	373.4
30°	339.8	343.3	342.4	344.2	344.2	346.7	349.3	346.7
32.5°	285.8	288.4	288.4	291.8	289.2	290.0	294.4	291.8
35°	218.9	220.5	218.9	220.5	221.5	221.5	225.7	224.9
37.5°	156.2	157.1	157.1	159.7	157.1	157.1	161.3	162.2
40°	104.7	105.6	104.7	108.1	106.4	106.4	109.0	106.4
42.5°	66.9	67.8	66.9	69.5	67.8	69.5	70.3	71.3
45°	41.2	41.2	40.4	42.0	41.2	42.0	43.0	43.0
47.5°	24.1	24.1	23.1	24.9	24.1	24.1	24.1	24.9
50°	12.9	12.9	12.9	13.7	12.9	12.9	12.9	12.0
52.5°	6.8	6.8	6.0	6.8	6.0	6.0	6.0	6.0
55°	3.4	2.6	2.6	2.6	1.8	1.8	1.8	1.8
57.5°	2.6	1.8	1.8	0.8	0.8	0.8	0.0	0.0
60°	1.8	1.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.8	1.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.8	1.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.6	1.8	1.8	0.8	0.8	0.0	0.0	0.0
70°	2.6	1.8	1.8	0.8	0.8	0.0	0.0	0.0
72.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
75°	2.6	2.6	1.8	1.8	0.8	0.8	0.0	0.0
77.5°	3.4	2.6	1.8	1.8	0.8	0.8	0.0	0.0
80°	3.4	2.6	1.8	1.8	1.8	0.8	0.8	0.8
82.5°	3.4	2.6	2.6	1.8	1.8	0.8	0.8	0.8
85°	3.4	2.6	2.6	1.8	1.8	0.8	0.8	0.8
87.5°	3.4	2.6	2.6	1.8	1.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)