

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979492

Luminaire Tested: PRLX-240-935-LL8-F-U-S-BLAK-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P979492  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-240-935-LL8-F-U-S-BLAK-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5387.2 lumens  
Efficiency: N/A  
Efficacy: 87.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33  
Luminous Opening: Circular (Dia: 1.17' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 61.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P979492  
CATALOG NUMBER: PRLX-240-935-LL8-F-U-S-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P979492

CATALOG NUMBER: PRLX-240-935-LL8-F-U-S-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	112	109	106	103	110	106	104	101	102	100	98	99	97	95	95	94	92	90													90															
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81													81															
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72													72															
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64													64															
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57													57															
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51													51															
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	57	51	47	46													46															
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41													41															
9	64	52	45	40	63	51	44	40	50	44	39	49	43	39	48	43	39	37													37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34													34															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	28340
5°	28258
10°	28054
15°	27618
20°	27276
25°	26889
30°	26411
35°	26064
40°	25668
45°	24949
50°	21268
55°	10861
60°	1760
65°	224
70°	209
75°	276
80°	273
85°	277

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24949 cd/sqm

TEST NUMBER: P979492

CATALOG NUMBER: PRLX-240-935-LL8-F-U-S-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	265.2	4.9
10°-20°	747.7	13.9
20°-30°	1114.1	20.7
30°-40°	1325.8	24.6
40°-50°	1323.5	24.6
50°-60°	580.5	10.8
60°-70°	20.1	0.4
70°-80°	7.2	0.1
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2127.0	39.5
0°-40°	3452.7	64.1
0°-60°	5356.6	99.4
0°-90°	5387.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5387.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2815	
5°	2796	265
15°	2649	748
25°	2420	1114
35°	2120	1326
45°	1752	1323
55°	619	580
65°	9	20
75°	7	7
85°	2	3
90°	0	

TEST NUMBER: P979492

CATALOG NUMBER: PRLX-240-935-LL8-F-U-S-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2814.6
2.5°	2812.3
5°	2795.8
7.5°	2772.1
10°	2743.8
12.5°	2703.7
15°	2649.4
17.5°	2595.0
20°	2545.5
22.5°	2486.4
25°	2420.3
27.5°	2344.8
30°	2271.6
32.5°	2196.0
35°	2120.4
37.5°	2037.8
40°	1952.8
42.5°	1863.1
45°	1752.1
47.5°	1596.2
50°	1357.7
52.5°	1020.1
55°	618.7
57.5°	278.6
60°	87.4
62.5°	18.9
65°	9.4
67.5°	7.1
70°	7.1
72.5°	7.1
75°	7.1
77.5°	7.1
80°	4.7
82.5°	4.7
85°	2.4
87.5°	2.4
90°	0.0

TEST NUMBER: P979492  
 CATALOG NUMBER: PRLX-240-935-LL8-F-U-S-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.92	15.27	14.29	15.58	15.90	13.92	15.27	14.29	15.58	15.90
	3H	13.80	14.98	14.18	15.31	15.67	13.80	14.98	14.18	15.31	15.67
	4H	13.73	14.83	14.14	15.18	15.56	13.73	14.83	14.14	15.18	15.56
	6H	13.66	14.66	14.08	15.03	15.43	13.66	14.66	14.08	15.03	15.43
	8H	13.63	14.57	14.06	14.96	15.37	13.63	14.57	14.06	14.96	15.37
	12H	13.59	14.49	14.02	14.87	15.30	13.59	14.49	14.02	14.87	15.30
4H	2H	13.73	14.82	14.13	15.17	15.55	13.73	14.82	14.13	15.17	15.55
	3H	13.61	14.48	14.02	14.88	15.29	13.61	14.48	14.02	14.88	15.29
	4H	13.53	14.30	13.96	14.72	15.17	13.53	14.30	13.96	14.72	15.17
	6H	13.46	14.13	13.92	14.57	15.04	13.46	14.13	13.92	14.57	15.04
	8H	13.41	14.03	13.88	14.48	14.95	13.41	14.03	13.88	14.48	14.95
	12H	13.36	13.91	13.85	14.40	14.87	13.36	13.91	13.85	14.40	14.87
8H	4H	13.39	14.01	13.86	14.46	14.93	13.39	14.01	13.86	14.46	14.93
	6H	13.30	13.81	13.80	14.31	14.79	13.30	13.81	13.80	14.31	14.79
	8H	13.24	13.71	13.76	14.22	14.72	13.24	13.71	13.76	14.22	14.72
	12H	13.20	13.62	13.71	14.11	14.68	13.20	13.62	13.71	14.11	14.68
12H	4H	13.34	13.89	13.83	14.38	14.85	13.34	13.89	13.83	14.38	14.85
	6H	13.23	13.70	13.75	14.21	14.71	13.23	13.70	13.75	14.21	14.71
	8H	13.19	13.61	13.70	14.11	14.68	13.19	13.61	13.70	14.11	14.68