

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219633

Luminaire Tested: **LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5020.5 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	89	83	78		86	81	77			83	79	76			81
4	91	82	75	70	89	81	74	69		78	73	68			76	71	67			74
5	85	74	67	62	83	73	67	61		71	65	61			70	64	60			68
6	79	68	60	55	77	67	60	55		65	59	54			64	58	54			62
7	74	62	55	49	72	61	54	49		60	53	49			59	53	49			57
8	69	57	49	44	67	56	49	44		55	49	44			54	48	44			53
9	64	52	45	40	63	52	45	40		51	44	40			50	44	40			49
10	60	48	41	36	59	48	41	36		47	40	36			46	40	36			45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38987	38987	38987
5°	100020	35475	11047
10°	194969	27264	5308
15°	349999	18516	7119
20°	519636	14053	11753
25°	590646	11577	18433
30°	640273	12658	17341
35°	674413	8205	10749
40°	688997	3642	5238
45°	622295	1388	1942
50°	409640	549	549
55°	112185	473	0
60°	22406	543	0
65°	1579	754	0
70°	239	932	0
75°	0	1364	0
80°	0	2033	198
85°	0	4051	395

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	2.2
10°-20°	589.3	11.7
20°-30°	1335.8	26.6
30°-40°	1603.4	31.9
40°-50°	1130.0	22.5
50°-60°	233.1	4.6
60°-70°	8.2	0.2
70°-80°	4.9	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2036.0	40.6
0°-40°	3639.4	72.5
0°-60°	5002.6	99.6
0°-90°	5020.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5020.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	906	906	906	906	906	
5°	2314	1686	821	341	256	285
15°	7852	3454	415	148	160	2330
25°	12433	4178	244	341	388	5738
35°	12831	2926	156	204	204	7977
45°	10220	1003	23	31	32	7517
55°	1494	20	6	5	0	1969
65°	16	5	7	5	0	46
75°	0	5	8	6	0	0
85°	0	6	8	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5
2.5°	1543.7	1497.2	1515.5	1461.6	1449.7	1439.7	1449.7	1391.3	1358.3	1316.4	1282.6
5°	2314.2	2258.6	2271.3	2177.3	2134.4	2105.2	2099.8	1979.2	1888.7	1789.2	1686.2
7.5°	3221.6	3168.8	3161.4	3015.4	2926.8	2876.5	2855.5	2683.0	2526.9	2349.9	2156.3
10°	4459.5	4339.0	4301.5	4089.9	3920.9	3814.1	3682.7	3406.9	3133.2	2865.6	2619.1
12.5°	5900.1	5834.4	5741.3	5367.9	5072.2	4920.6	4724.3	4293.3	3878.9	3437.1	3024.4
15°	7852.0	7618.2	7459.4	6919.8	6443.3	6209.6	5923.0	5263.9	4637.6	4077.9	3454.5
17.5°	9759.0	9636.7	9388.3	8688.2	7954.2	7585.3	7158.1	6262.6	5377.9	4581.8	3820.5
20°	11341.1	11226.1	10943.1	10283.1	9468.7	8924.6	8387.0	7158.1	6002.4	4983.6	4065.3
22.5°	12098.8	12025.8	11794.8	11229.7	10535.9	10018.2	9440.4	7920.4	6464.2	5246.5	4176.5
25°	12432.9	12399.1	12250.4	11804.8	11151.2	10712.1	10166.1	8460.0	6751.9	5368.9	4178.4
27.5°	12771.6	12778.0	12449.3	12097.0	11477.1	11055.3	10529.5	8699.1	6804.0	5300.4	4041.4
30°	12878.5	12810.8	12665.6	12160.0	11571.1	11122.8	10558.7	8588.6	6590.3	5019.1	3768.4
32.5°	12834.5	12808.1	12648.4	12113.4	11411.4	10917.5	10276.7	8150.5	6168.6	4617.5	3381.5
35°	12831.0	12781.7	12415.6	11956.4	11091.9	10482.1	9637.6	7442.0	5571.5	4088.0	2925.9
37.5°	12599.1	12476.7	12201.9	11583.0	10443.7	9670.4	8723.8	6576.5	4841.2	3493.7	2474.1
40°	12258.6	12094.2	11732.8	10796.0	9320.8	8429.7	7505.9	5593.4	4068.0	2907.6	1993.8
42.5°	11547.4	11299.1	10787.8	9499.8	7824.5	7021.1	6252.6	4597.4	3317.5	2369.0	1521.8
45°	10220.0	9880.4	9189.4	7775.2	6320.9	5665.5	5047.4	3699.2	2655.6	1757.4	1003.2
47.5°	8214.3	7899.3	7270.4	6189.5	4957.2	4402.9	3910.0	2751.5	1800.3	1017.8	479.2
50°	6115.6	5845.4	5354.2	4301.5	3327.6	2892.1	2470.3	1562.9	843.5	483.9	199.1
52.5°	3648.9	3514.7	3079.3	2385.4	1643.2	1416.0	1136.6	661.9	425.5	175.2	53.9
55°	1494.5	1379.4	1216.1	975.8	714.8	606.1	518.5	326.8	132.4	36.6	20.2
57.5°	675.6	650.0	576.1	452.8	328.6	275.7	186.3	62.1	29.2	18.3	11.9
60°	260.2	234.6	200.9	108.6	46.5	39.3	31.9	21.0	14.6	10.1	7.4
62.5°	37.4	35.6	31.9	25.5	20.2	18.3	15.5	10.9	8.2	6.3	5.5
65°	15.5	15.5	13.7	10.9	9.0	8.2	7.4	5.5	4.6	4.6	4.6
67.5°	6.3	6.3	5.5	4.6	3.6	3.6	3.6	2.7	3.6	3.6	4.6
70°	1.9	1.9	1.9	1.9	1.9	1.9	2.7	2.7	3.6	3.6	4.6
72.5°	0.0	0.0	0.8	0.8	1.9	1.9	1.9	2.7	3.6	4.6	4.6
75°	0.0	0.0	0.8	0.8	1.9	1.9	1.9	2.7	3.6	4.6	4.6
77.5°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	4.6
80°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	5.5
82.5°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	5.5
85°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	5.5
87.5°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5
2.5°	1253.5	1195.1	1178.6	1127.5	1084.5	1063.5	1037.1	977.7	933.1	873.6	838.0
5°	1614.0	1503.5	1416.0	1309.0	1238.8	1193.2	1122.0	1013.3	925.7	820.8	745.9
7.5°	2003.9	1802.1	1644.2	1468.0	1366.6	1287.2	1165.8	1009.7	881.0	741.2	625.4
10°	2379.9	2078.8	1830.4	1577.6	1444.1	1333.7	1166.7	970.4	799.8	623.6	501.2
12.5°	2711.4	2322.5	1972.9	1647.8	1482.6	1344.7	1135.7	900.1	693.9	513.1	405.4
15°	2988.0	2511.5	2073.2	1674.3	1485.3	1321.0	1070.9	799.8	576.1	415.4	339.6
17.5°	3198.0	2610.8	2104.2	1642.4	1432.4	1253.5	971.4	672.9	467.5	352.4	285.7
20°	3306.6	2630.2	2059.5	1555.6	1334.7	1151.3	840.7	546.0	396.2	306.7	239.2
22.5°	3320.3	2576.3	1952.7	1431.5	1211.5	1027.0	696.6	455.5	353.3	271.1	210.8
25°	3239.0	2459.4	1800.3	1290.8	1076.4	884.5	567.0	408.0	321.4	243.7	242.8
27.5°	3065.5	2258.6	1617.7	1127.5	912.9	719.4	481.1	368.8	286.6	258.3	274.8
30°	2820.8	2001.1	1393.1	921.1	713.0	553.2	405.4	304.0	252.0	254.6	268.4
32.5°	2489.4	1681.7	1129.2	674.5	510.2	416.3	304.0	207.3	209.1	210.0	221.8
35°	2073.2	1348.4	843.5	453.6	358.8	293.1	171.7	152.5	155.3	156.1	164.3
37.5°	1661.5	1036.2	560.6	302.1	225.5	154.2	106.8	102.2	104.1	103.2	112.3
40°	1272.6	722.1	336.0	149.8	86.7	72.2	65.7	62.9	64.0	64.8	70.3
42.5°	901.1	391.6	166.2	56.6	45.7	42.0	39.3	37.4	38.3	38.3	42.0
45°	457.4	185.3	56.6	31.1	28.4	25.5	23.7	22.8	22.8	22.8	24.6
47.5°	198.1	61.2	26.5	19.1	17.3	16.4	14.6	13.7	13.7	13.7	14.6
50°	62.1	24.6	16.4	12.8	10.9	10.1	9.0	9.0	9.0	8.2	9.0
52.5°	22.8	15.5	10.9	8.2	7.4	7.4	7.4	6.3	7.4	6.3	7.4
55°	13.7	10.1	7.4	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
57.5°	9.0	7.4	6.3	6.3	5.5	5.5	6.3	6.3	6.3	6.3	6.3
60°	6.3	6.3	5.5	5.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	6.3	6.3	7.4
65°	4.6	5.5	5.5	5.5	5.5	5.5	6.3	6.3	7.4	7.4	7.4
67.5°	4.6	5.5	5.5	6.3	6.3	6.3	6.3	7.4	7.4	7.4	7.4
70°	5.5	5.5	6.3	6.3	6.3	6.3	7.4	7.4	7.4	7.4	8.2
72.5°	5.5	5.5	6.3	6.3	6.3	6.3	7.4	7.4	8.2	8.2	8.2
75°	5.5	6.3	6.3	6.3	6.3	7.4	7.4	7.4	8.2	8.2	8.2
77.5°	5.5	6.3	6.3	7.4	7.4	7.4	7.4	8.2	8.2	8.2	8.2
80°	5.5	6.3	6.3	7.4	7.4	7.4	8.2	8.2	8.2	8.2	9.0
82.5°	5.5	6.3	6.3	7.4	7.4	7.4	8.2	8.2	8.2	8.2	9.0
85°	6.3	6.3	7.4	7.4	7.4	7.4	8.2	8.2	8.2	8.2	9.0
87.5°	6.3	6.3	7.4	7.4	7.4	7.4	8.2	8.2	9.0	8.2	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5
2.5°	790.6	737.7	701.1	687.4	660.9	619.0	594.4	571.5	528.5	519.5	495.7
5°	660.0	575.2	514.9	492.1	462.0	426.3	391.6	368.8	341.4	330.5	314.1
7.5°	520.3	435.4	383.3	365.2	344.1	314.9	284.0	261.1	232.8	218.2	204.5
10°	409.0	345.9	302.1	284.0	262.0	231.0	199.1	168.9	144.1	128.8	126.0
12.5°	332.3	280.3	233.7	214.6	189.0	158.0	135.1	134.3	132.4	131.5	133.2
15°	272.1	221.8	172.5	151.5	144.1	143.3	146.0	148.8	147.9	150.6	152.5
17.5°	223.7	169.8	158.8	159.7	160.7	163.5	168.0	175.2	176.2	180.8	184.5
20°	182.6	179.8	184.5	188.0	190.8	196.2	206.3	215.5	218.2	224.5	231.8
22.5°	207.3	215.5	225.5	230.0	233.7	243.7	254.6	269.3	274.8	283.0	293.1
25°	250.1	263.8	279.3	284.9	290.4	306.7	319.6	336.9	341.4	351.5	361.5
27.5°	285.7	300.2	316.8	324.1	328.6	345.1	356.0	366.9	366.9	372.4	379.8
30°	280.3	292.0	305.9	311.4	313.1	325.0	336.0	339.6	337.7	340.5	345.9
32.5°	232.8	241.9	252.9	257.5	259.3	267.5	276.6	276.6	275.7	275.7	279.3
35°	172.5	178.9	184.5	189.0	191.7	197.2	205.4	204.5	204.5	202.6	205.4
37.5°	116.0	119.6	126.0	127.7	128.8	132.4	138.8	138.8	137.0	137.8	139.7
40°	70.3	74.9	78.5	79.4	81.2	83.9	88.6	88.6	88.6	88.6	89.4
42.5°	42.0	44.8	47.5	47.5	48.4	52.0	53.9	53.9	53.9	53.9	54.7
45°	24.6	25.5	27.4	28.4	28.4	30.1	31.1	31.1	31.1	31.1	31.9
47.5°	14.6	15.5	15.5	16.4	16.4	17.3	18.3	18.3	17.3	17.3	17.3
50°	9.0	9.0	9.0	9.0	10.1	10.1	10.1	10.1	10.1	10.1	9.0
52.5°	7.4	7.4	7.4	7.4	6.3	6.3	6.3	6.3	5.5	5.5	4.6
55°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	5.5	4.6	3.6	2.7
57.5°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.6	3.6	3.6	2.7
60°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.6	3.6	3.6	2.7
62.5°	7.4	7.4	6.3	6.3	6.3	5.5	5.5	4.6	4.6	3.6	2.7
65°	7.4	7.4	6.3	6.3	6.3	6.3	5.5	5.5	4.6	3.6	2.7
67.5°	7.4	7.4	7.4	7.4	6.3	6.3	6.3	5.5	4.6	3.6	2.7
70°	8.2	8.2	7.4	7.4	7.4	6.3	6.3	5.5	4.6	4.6	3.6
72.5°	8.2	8.2	7.4	7.4	7.4	7.4	6.3	5.5	5.5	4.6	3.6
75°	8.2	8.2	8.2	8.2	7.4	7.4	6.3	6.3	5.5	4.6	3.6
77.5°	8.2	8.2	8.2	8.2	7.4	7.4	7.4	6.3	5.5	4.6	3.6
80°	8.2	8.2	8.2	8.2	8.2	7.4	7.4	6.3	5.5	4.6	3.6
82.5°	9.0	9.0	8.2	8.2	8.2	7.4	7.4	6.3	5.5	4.6	4.6
85°	9.0	9.0	8.2	8.2	8.2	7.4	7.4	6.3	5.5	5.5	4.6
87.5°	9.0	9.0	8.2	8.2	8.2	7.4	7.4	6.3	5.5	5.5	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219633

CATALOG NUMBER: LDSQA6A50950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	905.5	905.5	905.5	905.5	905.5	905.5	905.5	905.5
2.5°	481.1	453.6	444.6	450.9	443.7	438.3	430.9	427.2
5°	301.3	281.1	274.8	276.6	270.2	264.7	257.5	255.6
7.5°	185.3	166.2	158.8	158.8	151.5	145.2	140.6	137.8
10°	124.2	120.5	121.4	122.3	121.4	122.3	119.6	121.4
12.5°	133.2	131.5	133.2	134.3	134.3	135.9	132.4	135.1
15°	155.3	153.4	156.1	158.0	158.0	160.7	157.0	159.7
17.5°	189.8	189.0	193.5	195.4	196.2	200.9	196.2	199.9
20°	240.0	239.2	245.5	248.2	247.4	256.5	250.1	256.5
22.5°	304.9	303.2	312.2	314.9	315.8	327.8	322.3	326.8
25°	369.7	371.6	376.2	380.6	381.6	391.6	383.3	388.0
27.5°	383.3	380.6	383.3	388.9	389.8	394.5	387.1	390.7
30°	346.9	342.4	343.2	349.6	351.5	353.3	346.9	348.8
32.5°	282.2	274.8	274.8	281.1	283.0	285.7	274.8	279.3
35°	208.1	201.8	201.8	206.3	207.3	209.1	200.9	204.5
37.5°	142.4	137.0	138.8	140.6	141.5	143.3	142.4	141.5
40°	91.3	87.7	90.3	90.3	91.3	92.1	92.1	93.2
42.5°	55.7	52.9	54.7	54.7	55.7	55.7	55.7	56.6
45°	31.9	31.1	31.1	31.9	31.9	31.9	31.1	31.9
47.5°	17.3	16.4	17.3	17.3	17.3	17.3	17.3	17.3
50°	9.0	8.2	8.2	8.2	8.2	8.2	8.2	8.2
52.5°	4.6	3.6	3.6	3.6	2.7	3.6	2.7	2.7
55°	2.7	1.9	1.9	1.9	0.8	0.8	0.0	0.0
57.5°	1.9	0.8	0.8	0.8	0.0	0.0	0.0	0.0
60°	1.9	0.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.9	0.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.9	0.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.7	1.9	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.7	1.9	1.9	0.8	0.8	0.0	0.0	0.0
72.5°	2.7	1.9	1.9	1.9	0.8	0.8	0.0	0.0
75°	2.7	1.9	1.9	1.9	0.8	0.8	0.0	0.0
77.5°	2.7	2.7	1.9	1.9	0.8	0.8	0.8	0.0
80°	3.6	2.7	1.9	1.9	1.9	0.8	0.8	0.8
82.5°	3.6	2.7	1.9	1.9	1.9	0.8	0.8	0.8
85°	3.6	2.7	2.7	1.9	1.9	0.8	0.8	0.8
87.5°	3.6	2.7	2.7	1.9	1.9	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)