

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219637

Luminaire Tested: **LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5144.2 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	50		59
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	61	50	43	38	60	49	43	38	48	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62525	62525	62525
5°	121159	59588	20097
10°	205846	52145	9028
15°	317197	41592	14349
20°	459178	27065	24962
25°	673692	26114	32091
30°	783327	24744	24595
35°	792866	13109	12998
40°	656431	4940	5458
45°	495784	1681	1997
50°	339200	616	616
55°	47186	540	75
60°	1240	525	0
65°	306	734	0
70°	126	906	0
75°	0	1198	0
80°	0	2033	248
85°	0	4051	0



TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.4	3.0
10°-20°	644.0	12.5
20°-30°	1469.1	28.6
30°-40°	1700.1	33.0
40°-50°	1025.3	19.9
50°-60°	139.3	2.7
60°-70°	4.5	0.1
70°-80°	4.9	0.1
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2265.5	44.0
0°-40°	3965.7	77.1
0°-60°	5130.3	99.7
0°-90°	5144.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5144.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1452	1452	1452	1452	1452	
5°	2803	2295	1379	754	465	326
15°	7116	4000	933	287	322	2107
25°	14181	4740	550	661	676	6418
35°	15085	3614	249	254	247	9091
45°	8142	984	28	34	33	6367
55°	629	7	7	5	1	1232
65°	3	4	7	4	0	5
75°	0	5	7	5	0	0
85°	0	5	8	5	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2
2.5°	2100.2	2080.7	2088.9	2067.4	2013.3	2002.1	2001.1	1986.7	1940.7	1905.0	1862.0
5°	2803.3	2802.3	2807.4	2761.4	2666.5	2636.7	2622.4	2587.6	2476.2	2390.4	2295.3
7.5°	3681.2	3675.0	3669.0	3585.2	3436.0	3378.6	3341.9	3216.2	3062.9	2910.6	2740.9
10°	4708.3	4705.3	4681.8	4534.5	4295.4	4190.1	4118.6	3919.2	3673.0	3456.3	3168.2
12.5°	5901.1	5873.3	5831.4	5615.9	5287.8	5173.3	5015.8	4700.1	4321.9	3989.9	3587.2
15°	7116.1	7076.3	7001.6	6724.6	6317.9	6122.8	5927.6	5511.6	4998.4	4516.1	4000.0
17.5°	8304.7	8260.7	8086.0	7615.8	7218.3	6980.2	6763.5	6192.2	5589.3	4968.9	4314.8
20°	10021.6	9862.2	9557.7	8816.7	8077.8	7648.6	7395.1	6791.1	6045.1	5322.5	4538.7
22.5°	12315.0	11961.4	11312.4	10108.5	9052.8	8433.5	8018.5	7215.3	6373.1	5553.5	4676.6
25°	14181.0	14020.6	13282.8	11569.9	9922.4	9192.8	8615.4	7552.6	6612.2	5707.8	4740.0
27.5°	15383.9	15344.2	14500.9	12779.9	10632.8	9675.2	9030.3	7775.2	6727.8	5740.5	4709.3
30°	15755.9	15818.3	15009.0	13190.8	10838.3	9772.3	9067.0	7778.3	6638.8	5592.3	4513.1
32.5°	15728.3	15731.6	14739.1	12836.2	10504.0	9490.2	8760.4	7519.8	6310.7	5221.3	4140.0
35°	15084.6	14926.2	13804.0	11746.7	9726.3	8832.0	8153.4	7019.0	5770.1	4663.4	3613.8
37.5°	13671.1	13463.6	12155.5	10351.7	8805.4	7978.7	7430.8	6361.9	5126.4	4067.5	3070.0
40°	11679.2	11385.0	10305.7	9054.9	7797.8	7176.4	6716.4	5627.0	4437.5	3482.9	2560.1
42.5°	9685.4	9541.3	8827.9	7811.0	6950.5	6365.9	5885.7	4857.5	3775.2	2906.5	1915.2
45°	8142.3	8018.5	7539.2	6868.7	6024.6	5491.2	5028.2	4055.2	2933.1	1949.9	984.2
47.5°	7017.9	6917.8	6459.0	5754.8	4828.8	4245.4	3768.0	2659.3	1661.7	842.1	246.3
50°	5064.0	4961.7	4512.1	3696.6	2860.6	2372.0	2028.6	1187.6	471.1	170.7	25.6
52.5°	2482.5	2398.7	2093.0	1566.7	1051.6	756.3	553.0	222.8	54.1	18.4	12.2
55°	628.6	577.5	481.3	302.5	148.2	88.9	57.3	20.4	13.3	10.2	7.2
57.5°	35.8	34.7	31.7	23.5	17.4	15.4	13.3	10.2	7.2	6.1	5.2
60°	14.4	13.3	12.2	10.2	8.2	7.2	7.2	5.2	4.1	4.1	4.1
62.5°	6.1	6.1	6.1	5.2	4.1	4.1	4.1	3.0	4.1	4.1	4.1
65°	3.0	3.0	3.0	2.0	2.0	2.0	3.0	3.0	3.0	4.1	4.1
67.5°	2.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	4.1
70°	1.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.2
72.5°	0.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.2
75°	0.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.2
77.5°	0.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.2
80°	0.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.2
82.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.2
85°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.2
87.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2
2.5°	1806.8	1770.1	1716.0	1680.1	1645.4	1612.6	1558.5	1527.9	1472.7	1421.6	1377.7
5°	2181.0	2088.9	1977.6	1882.4	1821.1	1760.9	1651.5	1570.7	1469.5	1378.7	1294.9
7.5°	2559.1	2396.6	2213.6	2057.2	1962.3	1869.2	1705.6	1574.9	1431.8	1302.1	1178.3
10°	2902.5	2658.2	2399.6	2175.8	2047.0	1926.5	1710.8	1537.0	1353.1	1192.7	1037.3
12.5°	3221.3	2887.1	2549.9	2257.5	2098.1	1953.0	1689.4	1476.7	1258.0	1068.0	887.0
15°	3505.4	3076.1	2659.3	2304.6	2117.5	1945.8	1639.4	1391.9	1145.7	933.1	704.2
17.5°	3721.1	3193.7	2707.2	2297.5	2082.8	1891.8	1553.3	1285.8	1026.1	768.5	510.0
20°	3851.8	3243.8	2697.0	2242.2	2008.1	1805.9	1451.2	1170.2	882.0	590.7	449.6
22.5°	3907.1	3239.7	2648.9	2159.5	1916.2	1711.8	1353.1	1057.8	730.7	534.5	469.1
25°	3916.2	3197.9	2581.5	2068.6	1825.3	1622.0	1254.0	930.0	634.6	549.7	525.3
27.5°	3845.8	3099.7	2454.7	1937.7	1697.6	1487.1	1105.7	738.9	595.8	547.8	564.1
30°	3637.3	2875.8	2231.0	1707.8	1475.8	1265.2	790.0	579.5	494.7	497.7	501.8
32.5°	3270.3	2503.8	1871.3	1371.6	1118.1	834.0	491.5	387.3	376.2	376.2	374.0
35°	2780.9	2049.0	1468.6	867.7	556.0	400.7	254.5	255.4	250.4	249.4	248.2
37.5°	2274.9	1616.8	930.0	358.8	241.3	167.6	150.3	152.3	150.3	153.3	151.2
40°	1793.6	998.5	339.2	114.5	84.9	81.7	83.8	85.8	85.8	87.9	87.9
42.5°	1042.5	331.1	88.9	46.0	46.0	43.9	44.9	47.1	48.0	49.1	48.0
45°	309.7	68.4	28.6	25.6	25.6	24.5	24.5	25.6	26.5	27.6	27.6
47.5°	49.1	19.3	16.3	14.4	14.4	14.4	14.4	14.4	15.4	15.4	16.3
50°	15.4	12.2	10.2	9.2	9.2	8.2	8.2	9.2	9.2	9.2	10.2
52.5°	9.2	7.2	7.2	6.1	7.2	7.2	6.1	7.2	7.2	7.2	8.2
55°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	7.2	7.2	7.2
57.5°	5.2	5.2	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
60°	5.2	5.2	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	7.2
62.5°	5.2	5.2	6.1	6.1	6.1	6.1	6.1	6.1	7.2	7.2	7.2
65°	5.2	5.2	6.1	6.1	6.1	6.1	6.1	7.2	7.2	7.2	7.2
67.5°	5.2	6.1	6.1	6.1	6.1	7.2	7.2	7.2	7.2	7.2	7.2
70°	5.2	6.1	6.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
72.5°	5.2	6.1	6.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
75°	6.1	6.1	6.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2	8.2
77.5°	6.1	6.1	7.2	7.2	7.2	7.2	7.2	7.2	8.2	8.2	8.2
80°	6.1	6.1	7.2	7.2	7.2	7.2	7.2	8.2	8.2	8.2	8.2
82.5°	6.1	6.1	7.2	7.2	7.2	7.2	7.2	8.2	8.2	8.2	8.2
85°	6.1	6.1	7.2	7.2	7.2	7.2	7.2	8.2	8.2	8.2	8.2
87.5°	6.1	6.1	7.2	7.2	7.2	7.2	7.2	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2
2.5°	1339.8	1292.7	1270.4	1238.6	1216.1	1166.0	1145.7	1110.9	1082.2	1035.3	1038.3
5°	1223.2	1134.4	1074.2	1027.1	994.3	914.7	861.5	805.4	754.3	690.9	667.4
7.5°	1061.8	952.4	860.5	804.2	762.4	656.1	538.6	446.6	377.1	327.1	307.6
10°	900.4	758.3	612.2	525.3	465.0	362.8	310.6	286.2	263.6	236.1	217.7
12.5°	712.4	510.0	377.1	342.4	317.8	284.1	250.4	223.9	228.9	229.9	237.1
15°	486.5	366.9	325.0	301.5	275.0	255.4	266.8	273.9	287.1	288.2	297.3
17.5°	395.5	344.4	310.6	309.7	311.7	322.9	340.3	349.4	366.9	371.0	384.3
20°	395.5	365.8	394.5	394.5	399.6	414.9	437.4	450.7	470.2	477.4	493.7
22.5°	450.7	471.1	506.9	511.1	513.0	529.4	558.0	571.3	593.7	597.9	615.3
25°	549.7	568.2	600.9	604.0	605.1	617.2	638.8	645.9	661.1	653.1	663.3
27.5°	581.5	589.7	610.1	612.2	607.0	612.2	620.4	620.4	625.5	609.0	612.2
30°	511.1	513.0	523.2	524.3	513.0	515.1	516.0	515.1	514.1	496.7	496.7
32.5°	379.2	379.2	392.5	389.4	377.1	380.1	380.1	380.1	379.2	364.8	362.8
35°	251.5	252.4	263.6	261.7	252.4	254.5	254.5	257.6	254.5	246.3	244.3
37.5°	153.3	154.2	159.4	160.5	157.5	158.4	159.4	158.4	160.5	156.4	154.2
40°	88.9	91.0	95.1	96.0	95.1	95.1	96.0	97.1	101.2	96.0	94.0
42.5°	52.1	53.1	55.2	55.2	55.2	55.2	56.3	57.3	58.2	57.3	56.3
45°	29.7	30.7	31.7	31.7	32.8	31.7	32.8	32.8	33.7	32.8	32.8
47.5°	17.4	17.4	18.4	18.4	19.3	18.4	19.3	19.3	19.3	18.4	18.4
50°	10.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2	10.2	10.2
52.5°	8.2	8.2	8.2	8.2	8.2	7.2	7.2	7.2	7.2	6.1	6.1
55°	7.2	7.2	7.2	7.2	7.2	7.2	6.1	5.2	5.2	4.1	4.1
57.5°	6.1	7.2	7.2	7.2	7.2	6.1	6.1	5.2	4.1	3.0	3.0
60°	7.2	7.2	7.2	7.2	6.1	6.1	6.1	5.2	4.1	3.0	3.0
62.5°	7.2	7.2	7.2	7.2	7.2	6.1	6.1	5.2	4.1	3.0	3.0
65°	7.2	7.2	7.2	7.2	7.2	6.1	6.1	5.2	4.1	3.0	3.0
67.5°	7.2	7.2	7.2	7.2	7.2	6.1	6.1	5.2	4.1	4.1	3.0
70°	7.2	8.2	8.2	7.2	7.2	7.2	6.1	5.2	5.2	4.1	3.0
72.5°	7.2	8.2	8.2	7.2	7.2	7.2	6.1	5.2	5.2	4.1	3.0
75°	8.2	8.2	8.2	8.2	7.2	7.2	6.1	6.1	5.2	4.1	3.0
77.5°	8.2	8.2	8.2	8.2	7.2	7.2	6.1	6.1	5.2	4.1	3.0
80°	8.2	8.2	8.2	8.2	8.2	7.2	7.2	6.1	5.2	4.1	4.1
82.5°	8.2	8.2	8.2	8.2	8.2	7.2	7.2	6.1	5.2	4.1	4.1
85°	8.2	8.2	8.2	8.2	8.2	7.2	7.2	6.1	5.2	4.1	3.0
87.5°	8.2	8.2	8.2	8.2	7.2	7.2	6.1	6.1	5.2	4.1	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219637

CATALOG NUMBER: LDSQA6A55950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2	1452.2
2.5°	1000.6	977.0	966.8	983.2	975.0	950.5	955.6	940.3
5°	596.9	561.1	538.6	548.8	516.0	486.5	486.5	465.0
7.5°	288.2	277.0	270.8	272.8	265.8	256.5	251.5	251.5
10°	202.4	198.3	199.4	199.4	205.4	204.4	207.5	206.5
12.5°	240.2	242.2	243.3	247.3	252.4	252.4	255.4	253.4
15°	307.6	305.6	311.7	312.7	320.9	321.9	326.0	321.9
17.5°	391.4	395.5	401.6	400.7	416.9	418.1	418.1	416.9
20°	503.9	506.9	513.0	515.1	534.5	536.5	543.7	544.8
22.5°	626.4	626.4	629.6	633.6	652.0	653.1	656.1	656.1
25°	668.3	662.3	663.3	668.3	678.7	674.5	677.6	675.5
27.5°	614.2	605.1	603.0	610.1	617.2	606.0	610.1	610.1
30°	498.7	490.6	488.5	495.7	500.8	488.5	492.5	494.7
32.5°	364.8	359.7	358.8	363.8	368.0	357.7	361.8	364.8
35°	246.3	244.3	242.2	243.3	249.4	241.3	245.2	247.3
37.5°	156.4	152.3	153.3	155.3	159.4	154.2	158.4	158.4
40°	96.0	94.0	94.0	96.0	98.2	94.0	96.0	97.1
42.5°	56.3	56.3	56.3	57.3	58.2	56.3	56.3	57.3
45°	32.8	31.7	31.7	32.8	33.7	31.7	32.8	32.8
47.5°	18.4	17.4	17.4	18.4	18.4	17.4	18.4	18.4
50°	10.2	9.2	9.2	10.2	10.2	9.2	9.2	9.2
52.5°	5.2	5.2	5.2	5.2	5.2	5.2	4.1	4.1
55°	3.0	3.0	2.0	2.0	2.0	2.0	2.0	1.0
57.5°	2.0	2.0	1.0	1.0	1.0	1.0	0.0	0.0
60°	2.0	2.0	1.0	1.0	1.0	0.0	0.0	0.0
62.5°	2.0	2.0	1.0	1.0	1.0	0.0	0.0	0.0
65°	2.0	2.0	1.0	1.0	1.0	0.0	0.0	0.0
67.5°	2.0	2.0	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.0	2.0	2.0	1.0	1.0	1.0	0.0	0.0
72.5°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
75°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
77.5°	3.0	2.0	2.0	2.0	1.0	1.0	1.0	0.0
80°	3.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0
82.5°	3.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0
85°	3.0	2.0	2.0	2.0	1.0	1.0	1.0	0.0
87.5°	3.0	2.0	2.0	2.0	1.0	1.0	1.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)