

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219641

Luminaire Tested: **LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5910.6 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47697	47697	47697
5°	130914	43946	17932
10°	286877	35964	6833
15°	438199	27378	8014
20°	507696	20366	12458
25°	553833	16751	20100
30°	618452	15193	20528
35°	629242	10418	14076
40°	640301	4940	7121
45°	641341	2052	3111
50°	542192	891	965
55°	174594	616	150
60°	34677	706	0
65°	3535	835	0
70°	378	1158	0
75°	0	1530	0
80°	0	2529	248
85°	0	5039	494



TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.4	2.5
10°-20°	777.7	13.2
20°-30°	1489.1	25.2
30°-40°	1754.4	29.7
40°-50°	1378.0	23.3
50°-60°	335.8	5.7
60°-70°	14.4	0.2
70°-80°	5.4	0.1
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2417.2	40.9
0°-40°	4171.6	70.6
0°-60°	5885.4	99.6
0°-90°	5910.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5910.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1108	1108	1108	1108	1108	
5°	3029	2192	1017	532	415	400
15°	9831	5049	614	176	180	2744
25°	11658	6140	353	369	423	5434
35°	11972	3881	198	255	268	7507
45°	10533	1200	34	47	51	7914
55°	2326	44	8	5	2	2768
65°	35	5	8	5	0	92
75°	0	5	9	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8
2.5°	1898.6	1894.7	1867.0	1892.5	1814.9	1811.9	1777.2	1761.8	1716.8	1673.9	1612.5
5°	3029.0	2962.5	2908.3	2910.4	2761.2	2733.6	2656.0	2577.2	2456.7	2344.3	2192.0
7.5°	4617.0	4538.2	4423.7	4375.8	4090.6	4006.9	3846.4	3636.9	3374.3	3112.8	2830.7
10°	6561.7	6573.8	6425.7	6288.9	5857.6	5688.0	5428.4	5015.5	4517.8	4026.3	3526.5
12.5°	8518.6	8510.4	8333.6	8126.2	7594.8	7355.7	7010.3	6495.2	5836.1	5073.7	4292.0
15°	9830.7	9889.0	9814.4	9648.8	9195.2	8921.2	8531.8	7832.9	7029.7	6103.9	5049.2
17.5°	10654.4	10709.6	10683.1	10553.2	10152.7	9860.3	9535.4	8963.0	8034.2	6870.2	5646.1
20°	11080.5	11167.4	11155.0	11014.1	10711.6	10469.4	10110.8	9580.4	8776.0	7402.6	6032.3
22.5°	11364.6	11431.1	11449.5	11290.0	10977.3	10747.4	10484.8	9947.3	9191.0	7727.7	6185.5
25°	11658.0	11775.5	11660.0	11463.8	11176.6	10955.9	10675.9	10160.8	9389.3	7860.4	6139.6
27.5°	12017.6	12073.9	11812.2	11633.4	11314.6	11075.5	10778.0	10284.4	9424.1	7754.2	5876.9
30°	12439.6	12206.6	12023.8	11669.1	11307.4	11074.4	10771.9	10206.8	9241.0	7401.7	5368.1
32.5°	12370.2	12156.7	11949.2	11574.2	11216.4	10985.4	10648.2	9948.3	8808.8	6812.0	4666.1
35°	11971.6	12017.6	11793.8	11483.2	11078.5	10840.3	10472.5	9580.4	8075.2	5998.5	3881.2
37.5°	11635.4	11736.6	11590.5	11303.3	10892.4	10570.6	10074.0	8989.8	7117.6	4966.4	3137.2
40°	11392.2	11424.9	11346.2	11024.3	10530.8	10065.8	9491.5	7929.0	5954.6	3898.5	2476.0
42.5°	11015.2	11102.0	10963.1	10611.4	9863.5	9337.2	8505.2	6703.7	4625.1	2977.8	1864.0
45°	10532.8	10615.6	10443.9	9859.3	8819.0	8047.5	7032.7	5227.0	3421.3	2195.0	1199.7
47.5°	9745.9	9797.0	9464.9	8656.5	7144.2	6417.6	5377.3	3644.1	2204.2	1227.3	583.5
50°	8094.5	8070.0	7385.2	6391.0	4778.4	4016.1	3200.6	1975.3	990.2	581.5	364.8
52.5°	5216.8	5160.6	4483.0	3578.7	2419.9	1846.6	1387.8	852.3	516.0	324.9	144.0
55°	2325.9	2304.4	1886.5	1465.4	990.2	852.3	650.9	417.9	274.9	113.4	43.9
57.5°	862.5	843.1	743.0	623.4	478.2	397.5	315.7	200.3	70.5	37.8	23.5
60°	402.7	401.5	353.6	291.2	202.4	153.3	88.8	47.1	29.5	20.4	13.3
62.5°	128.8	125.7	87.9	64.5	46.0	39.9	31.7	23.5	15.4	11.2	8.2
65°	34.7	34.7	31.7	26.5	21.5	18.4	15.4	11.2	7.2	6.1	5.2
67.5°	13.3	13.3	12.2	11.2	8.2	7.2	6.1	5.2	4.1	5.2	5.2
70°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	4.1	4.1	5.2
72.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.2	5.2
75°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.2	5.2
77.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.2	5.2
80°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.2	5.2
82.5°	0.0	0.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.2	6.1
85°	0.0	0.0	1.0	2.0	2.0	3.0	3.0	4.1	4.1	5.2	6.1
87.5°	0.0	0.0	1.0	2.0	2.0	3.0	3.0	4.1	4.1	5.2	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8
2.5°	1567.6	1500.1	1407.1	1353.0	1339.7	1311.1	1261.0	1186.4	1125.2	1065.9	1031.2
5°	2063.3	1903.8	1725.0	1599.3	1548.2	1479.7	1358.0	1232.5	1117.0	1016.8	938.2
7.5°	2588.6	2325.9	2036.6	1803.7	1719.8	1611.5	1413.4	1226.3	1067.9	928.9	823.6
10°	3110.6	2687.6	2295.2	1957.9	1821.0	1673.9	1412.3	1170.1	984.0	822.6	706.1
12.5°	3632.8	3024.8	2485.2	2051.0	1873.1	1687.1	1370.4	1084.2	877.9	713.2	601.8
15°	4115.2	3293.6	2614.0	2082.7	1868.0	1648.4	1285.5	980.0	766.5	614.2	511.0
17.5°	4474.9	3434.7	2643.7	2034.6	1787.3	1544.1	1155.8	857.4	660.2	526.2	421.1
20°	4651.7	3457.1	2573.2	1897.7	1648.4	1396.0	1013.8	739.9	569.2	444.5	355.6
22.5°	4651.7	3350.9	2419.9	1726.0	1474.6	1225.3	876.8	642.8	497.7	387.3	312.7
25°	4474.9	3139.3	2214.4	1527.7	1283.6	1056.6	758.3	570.2	442.4	352.6	290.2
27.5°	4131.6	2847.0	1950.7	1307.0	1095.4	906.5	664.1	503.8	400.5	317.8	318.9
30°	3659.4	2488.4	1648.4	1074.0	902.4	745.0	559.0	422.0	320.9	305.6	314.7
32.5°	3113.8	2059.1	1305.9	832.8	699.1	586.6	425.0	298.4	255.4	257.5	267.8
35°	2553.8	1620.7	983.1	617.2	520.1	425.0	279.0	196.1	194.2	198.2	205.4
37.5°	2016.2	1213.0	711.3	451.7	349.4	261.7	150.3	134.9	134.9	138.9	143.1
40°	1510.3	860.5	489.5	267.8	169.6	119.6	95.1	87.9	86.8	87.9	93.0
42.5°	1037.2	544.6	291.2	107.3	81.7	69.5	60.3	55.2	54.1	55.2	58.2
45°	582.5	335.2	113.4	57.3	49.1	43.9	37.8	34.7	33.7	33.7	35.8
47.5°	364.8	132.9	51.1	35.8	30.7	28.6	24.5	22.6	21.5	21.5	22.6
50°	140.1	52.1	31.7	23.5	20.4	18.4	16.3	14.4	13.3	13.3	14.4
52.5°	48.0	30.7	20.4	15.4	13.3	12.2	10.2	9.2	9.2	9.2	9.2
55°	26.5	18.4	12.2	9.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
57.5°	16.3	11.2	8.2	7.2	7.2	7.2	7.2	7.2	7.2	8.2	8.2
60°	9.2	7.2	6.1	6.1	6.1	6.1	7.2	7.2	7.2	8.2	8.2
62.5°	6.1	6.1	6.1	6.1	6.1	6.1	7.2	7.2	8.2	8.2	8.2
65°	5.2	5.2	5.2	6.1	6.1	6.1	7.2	7.2	8.2	8.2	8.2
67.5°	5.2	5.2	6.1	6.1	6.1	7.2	7.2	8.2	8.2	8.2	8.2
70°	5.2	6.1	6.1	7.2	7.2	7.2	8.2	8.2	8.2	9.2	9.2
72.5°	5.2	6.1	6.1	7.2	7.2	7.2	8.2	8.2	9.2	9.2	9.2
75°	6.1	6.1	6.1	7.2	7.2	7.2	8.2	9.2	9.2	9.2	9.2
77.5°	6.1	6.1	7.2	7.2	7.2	8.2	8.2	9.2	9.2	9.2	9.2
80°	6.1	6.1	7.2	7.2	8.2	8.2	9.2	9.2	9.2	10.2	10.2
82.5°	6.1	6.1	7.2	8.2	8.2	8.2	9.2	9.2	10.2	10.2	10.2
85°	6.1	7.2	7.2	8.2	8.2	8.2	9.2	9.2	10.2	10.2	10.2
87.5°	6.1	7.2	7.2	8.2	8.2	8.2	9.2	9.2	10.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8
2.5°	985.1	942.1	899.3	867.6	852.3	837.0	803.2	759.3	740.8	714.3	699.1
5°	858.3	785.8	728.6	690.9	668.3	638.7	599.9	556.9	532.5	504.9	486.4
7.5°	727.6	642.8	587.5	552.9	530.4	493.6	444.5	393.3	363.8	333.1	311.7
10°	613.1	532.5	470.2	430.2	401.5	358.6	309.7	273.8	248.2	221.7	200.3
12.5°	511.9	425.0	358.6	324.9	305.6	264.7	223.7	184.0	168.6	163.5	163.5
15°	414.9	336.2	280.0	251.5	230.9	187.0	178.8	176.8	175.8	174.8	176.8
17.5°	338.2	271.9	212.6	198.2	196.1	195.2	196.1	196.1	197.2	200.3	205.4
20°	284.1	222.8	218.7	219.8	219.8	223.7	228.9	233.1	237.1	242.2	251.5
22.5°	252.4	251.5	258.6	259.6	264.7	270.8	280.0	286.2	296.4	301.5	314.7
25°	291.2	298.4	311.7	315.7	324.0	334.2	348.4	356.6	369.0	375.0	390.3
27.5°	330.1	341.3	357.7	362.8	369.9	386.4	396.6	403.7	409.8	413.9	423.1
30°	327.1	337.3	353.6	354.6	364.8	376.0	382.2	388.3	392.4	391.4	396.6
32.5°	277.0	286.2	301.5	301.5	312.7	321.9	324.9	330.1	330.1	330.1	332.1
35°	212.6	218.7	228.9	231.9	241.1	247.3	249.3	255.4	255.4	253.4	253.4
37.5°	147.1	155.3	162.4	164.4	170.7	174.8	179.8	180.9	178.8	179.8	179.8
40°	96.0	101.2	106.3	107.3	112.4	115.5	120.5	120.5	121.6	120.5	122.6
42.5°	59.3	63.3	66.5	68.4	70.5	72.6	75.6	76.6	77.7	76.6	78.6
45°	36.7	38.9	40.9	41.9	43.0	43.9	47.1	47.1	47.1	47.1	48.0
47.5°	22.6	23.5	24.5	24.5	25.6	26.5	27.6	27.6	27.6	27.6	28.6
50°	13.3	14.4	14.4	14.4	15.4	15.4	16.3	16.3	16.3	15.4	16.3
52.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.2	9.2
55°	8.2	8.2	7.2	7.2	7.2	7.2	7.2	6.1	5.2	5.2	4.1
57.5°	7.2	7.2	7.2	7.2	7.2	6.1	6.1	5.2	5.2	4.1	3.0
60°	7.2	7.2	7.2	7.2	7.2	6.1	6.1	5.2	4.1	4.1	3.0
62.5°	8.2	7.2	7.2	7.2	7.2	6.1	6.1	5.2	4.1	4.1	3.0
65°	8.2	8.2	7.2	7.2	7.2	6.1	6.1	5.2	5.2	4.1	3.0
67.5°	8.2	8.2	8.2	7.2	8.2	7.2	6.1	6.1	5.2	4.1	4.1
70°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.1	5.2	4.1	4.1
72.5°	9.2	9.2	8.2	8.2	8.2	7.2	7.2	6.1	5.2	5.2	4.1
75°	9.2	9.2	8.2	8.2	8.2	7.2	7.2	6.1	6.1	5.2	4.1
77.5°	9.2	9.2	9.2	8.2	8.2	8.2	7.2	7.2	6.1	5.2	4.1
80°	9.2	9.2	9.2	9.2	9.2	8.2	8.2	7.2	6.1	5.2	4.1
82.5°	10.2	9.2	9.2	9.2	9.2	8.2	8.2	7.2	6.1	5.2	5.2
85°	10.2	10.2	9.2	9.2	9.2	8.2	8.2	7.2	6.1	6.1	5.2
87.5°	10.2	9.2	9.2	9.2	9.2	8.2	8.2	7.2	6.1	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219641

CATALOG NUMBER: LDSQA6A55950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8	1107.8
2.5°	683.7	675.5	675.5	661.1	659.2	647.9	657.2	650.9
5°	466.0	452.6	448.7	434.3	429.2	415.9	420.1	414.9
7.5°	293.4	280.0	276.0	265.6	259.6	249.3	250.4	247.3
10°	178.8	166.6	163.5	160.5	157.5	156.3	157.5	156.3
12.5°	162.4	161.4	159.4	160.5	158.4	159.4	160.5	159.4
15°	176.8	178.8	176.8	177.8	176.8	178.8	179.8	179.8
17.5°	207.4	211.5	209.6	212.6	211.5	216.7	216.7	216.7
20°	254.5	261.7	259.6	263.6	263.6	269.8	269.8	271.9
22.5°	319.9	329.1	328.0	337.3	335.2	342.3	342.3	344.4
25°	398.5	407.7	408.7	414.9	413.9	421.1	421.1	423.1
27.5°	431.3	436.4	435.2	438.5	439.4	443.5	446.6	444.5
30°	404.7	408.7	407.7	409.8	409.8	412.9	415.9	412.9
32.5°	340.3	343.4	343.4	347.5	344.4	345.4	350.5	347.5
35°	260.6	262.6	260.6	262.6	263.6	263.6	268.8	267.8
37.5°	186.0	187.0	187.0	190.0	187.0	187.0	192.2	193.1
40°	124.7	125.7	124.7	128.8	126.7	126.7	129.8	126.7
42.5°	79.7	80.8	79.7	82.8	80.8	82.8	83.8	84.9
45°	49.1	49.1	48.0	50.1	49.1	50.1	51.1	51.1
47.5°	28.6	28.6	27.6	29.5	28.6	28.6	28.6	29.5
50°	15.4	15.4	15.4	16.3	15.4	15.4	15.4	14.4
52.5°	8.2	8.2	7.2	8.2	7.2	7.2	7.2	7.2
55°	4.1	3.0	3.0	3.0	2.0	2.0	2.0	2.0
57.5°	3.0	2.0	2.0	1.0	1.0	1.0	0.0	0.0
60°	2.0	2.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.0	2.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.0	2.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.0	2.0	2.0	1.0	1.0	0.0	0.0	0.0
70°	3.0	2.0	2.0	1.0	1.0	0.0	0.0	0.0
72.5°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
75°	3.0	3.0	2.0	2.0	1.0	1.0	0.0	0.0
77.5°	4.1	3.0	2.0	2.0	1.0	1.0	0.0	0.0
80°	4.1	3.0	2.0	2.0	2.0	1.0	1.0	1.0
82.5°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
85°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
87.5°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)