

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212658

Luminaire Tested: **LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5895.5 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45785	45785	45785
5°	117451	41651	12975
10°	228948	32012	6234
15°	410990	21739	8362
20°	610193	16504	13801
25°	693578	13596	21649
30°	751846	14870	20359
35°	791940	9634	12620
40°	809068	4283	6143
45°	730740	1632	2283
50°	481023	643	643
55°	131725	563	0
60°	26316	646	0
65°	1854	876	0
70°	264	1083	0
75°	0	1597	0
80°	0	2380	273
85°	0	4742	543

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.2
10°-20°	692.1	11.7
20°-30°	1568.5	26.6
30°-40°	1882.8	31.9
40°-50°	1326.9	22.5
50°-60°	273.8	4.6
60°-70°	9.7	0.2
70°-80°	5.8	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2390.9	40.6
0°-40°	4273.7	72.5
0°-60°	5874.4	99.6
0°-90°	5895.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5895.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1063	1063	1063	1063	1063	
5°	2718	1980	964	401	300	334
15°	9220	4056	488	174	188	2736
25°	14600	4907	286	401	456	6738
35°	15067	3436	183	240	240	9367
45°	12001	1178	27	36	38	8827
55°	1755	24	8	5	0	2312
65°	18	5	9	5	0	54
75°	0	5	10	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4
2.5°	1812.8	1758.1	1779.5	1716.3	1702.3	1690.5	1702.3	1633.8	1595.1	1545.9	1506.1
5°	2717.5	2652.1	2667.2	2556.7	2506.3	2472.1	2465.6	2324.1	2218.0	2101.2	1980.0
7.5°	3783.1	3720.9	3712.4	3540.8	3436.9	3377.9	3353.2	3150.6	2967.4	2759.3	2532.0
10°	5236.7	5095.2	5051.2	4802.6	4604.3	4478.8	4324.5	4000.7	3679.1	3364.9	3075.6
12.5°	6928.3	6851.2	6741.8	6303.4	5956.0	5778.0	5547.6	5041.6	4554.9	4036.0	3551.6
15°	9220.3	8945.9	8759.3	8125.8	7566.2	7291.7	6955.1	6181.2	5445.8	4788.6	4056.5
17.5°	11459.7	11316.1	11024.5	10202.3	9340.3	8907.2	8405.5	7354.0	6315.1	5380.3	4486.3
20°	13317.5	13182.4	12850.1	12075.0	11118.8	10479.9	9848.5	8405.5	7048.4	5852.1	4773.6
22.5°	14207.2	14121.5	13850.2	13186.7	12372.0	11764.1	11085.5	9300.7	7590.8	6160.8	4904.5
25°	14599.6	14559.9	14385.2	13862.0	13094.5	12578.8	11937.8	9934.2	7928.4	6304.5	4906.6
27.5°	14997.3	15004.8	14618.9	14205.0	13477.2	12981.9	12364.4	10215.1	7989.6	6224.1	4745.8
30°	15122.7	15043.4	14873.0	14279.1	13587.6	13061.3	12398.8	10085.3	7738.8	5893.8	4425.2
32.5°	15071.2	15040.2	14852.5	14224.3	13400.0	12820.1	12067.4	9570.8	7243.5	5422.2	3970.7
35°	15067.0	15009.1	14579.1	14040.0	13024.8	12308.7	11317.2	8738.9	6542.4	4800.4	3435.7
37.5°	14794.7	14651.1	14328.3	13601.5	12263.7	11355.7	10244.0	7722.7	5684.8	4102.6	2905.1
40°	14394.9	14201.9	13777.4	12677.4	10945.2	9898.8	8814.0	6568.2	4776.8	3414.3	2341.3
42.5°	13559.7	13268.1	12667.8	11155.2	9188.1	8244.7	7342.1	5398.5	3895.6	2781.9	1787.0
45°	12001.0	11602.3	10790.7	9130.2	7422.5	6652.8	5927.1	4343.7	3118.5	2063.6	1178.1
47.5°	9645.9	9276.0	8537.4	7268.2	5820.9	5170.3	4591.4	3231.0	2114.0	1195.3	562.8
50°	7181.3	6864.0	6287.3	5051.2	3907.5	3396.1	2900.8	1835.3	990.5	568.1	233.6
52.5°	4284.7	4127.2	3615.9	2801.2	1929.6	1662.7	1334.7	777.2	499.5	205.8	63.2
55°	1754.8	1619.8	1427.8	1146.0	839.4	711.7	608.9	383.7	155.5	42.9	23.6
57.5°	793.3	763.2	676.4	531.7	386.0	323.8	218.7	72.9	34.3	21.4	14.0
60°	305.6	275.5	235.9	127.5	54.6	46.1	37.5	24.7	17.2	11.7	8.6
62.5°	44.0	41.8	37.5	30.0	23.6	21.4	18.2	12.8	9.6	7.5	6.5
65°	18.2	18.2	16.1	12.8	10.7	9.6	8.6	6.5	5.4	5.4	5.4
67.5°	7.5	7.5	6.5	5.4	4.2	4.2	4.2	3.2	4.2	4.2	5.4
70°	2.1	2.1	2.1	2.1	2.1	2.1	3.2	3.2	4.2	4.2	5.4
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.2	5.4	5.4
75°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.2	5.4	5.4
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	5.4
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	6.5
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	6.5
85°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	6.5
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.2	5.4	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4
2.5°	1471.8	1403.3	1383.9	1324.0	1273.5	1248.9	1217.8	1148.1	1095.6	1025.9	984.1
5°	1895.3	1765.6	1662.7	1537.3	1454.6	1401.0	1317.5	1190.0	1087.0	963.7	875.8
7.5°	2353.0	2116.1	1930.6	1723.8	1604.7	1511.5	1369.0	1185.6	1034.5	870.4	734.3
10°	2794.7	2440.9	2149.4	1852.4	1695.9	1566.2	1370.0	1139.6	939.0	732.2	588.6
12.5°	3183.8	2727.1	2316.6	1935.0	1740.9	1579.1	1333.6	1057.1	814.7	602.4	476.0
15°	3508.7	2949.0	2434.5	1966.0	1744.1	1551.1	1257.4	939.0	676.4	487.7	398.8
17.5°	3755.3	3066.0	2470.9	1928.5	1681.9	1471.8	1140.6	790.0	548.9	413.8	335.5
20°	3882.8	3088.4	2418.4	1826.7	1567.2	1351.8	987.4	641.0	465.3	360.2	280.9
22.5°	3898.9	3025.2	2293.0	1680.9	1422.6	1206.0	817.9	534.9	414.9	318.4	247.6
25°	3803.4	2888.0	2114.0	1515.8	1263.9	1038.7	665.7	479.2	377.4	286.2	285.1
27.5°	3599.8	2652.1	1899.6	1324.0	1072.0	844.8	565.0	433.1	336.6	303.3	322.6
30°	3312.5	2349.9	1635.9	1081.6	837.3	649.6	476.0	356.9	295.8	299.1	315.2
32.5°	2923.4	1974.6	1326.1	792.3	599.3	488.8	356.9	243.4	245.5	246.6	260.4
35°	2434.5	1583.3	990.5	532.8	421.3	344.1	201.6	179.0	182.3	183.3	193.0
37.5°	1951.1	1216.8	658.2	354.8	264.8	181.1	125.4	120.1	122.2	121.2	131.9
40°	1494.4	848.0	394.5	175.8	101.9	84.7	77.2	73.9	75.0	76.2	82.5
42.5°	1058.1	459.9	195.1	66.5	53.6	49.4	46.1	44.0	45.0	45.0	49.4
45°	537.1	217.7	66.5	36.4	33.3	30.0	27.9	26.8	26.8	26.8	28.9
47.5°	232.6	71.8	31.2	22.6	20.3	19.3	17.2	16.1	16.1	16.1	17.2
50°	72.9	28.9	19.3	15.0	12.8	11.7	10.7	10.7	10.7	9.6	10.7
52.5°	26.8	18.2	12.8	9.6	8.6	8.6	8.6	7.5	8.6	7.5	8.6
55°	16.1	11.7	8.6	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
57.5°	10.7	8.6	7.5	7.5	6.5	6.5	7.5	7.5	7.5	7.5	7.5
60°	7.5	7.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	7.5	7.5
62.5°	6.5	6.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	7.5	8.6
65°	5.4	6.5	6.5	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6
67.5°	5.4	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
70°	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6	9.6
72.5°	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6
75°	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6
77.5°	6.5	7.5	7.5	8.6	8.6	8.6	8.6	9.6	9.6	9.6	9.6
80°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6	9.6	10.7
82.5°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6	9.6	10.7
85°	7.5	7.5	8.6	8.6	8.6	8.6	9.6	9.6	9.6	9.6	10.7
87.5°	7.5	7.5	8.6	8.6	8.6	8.6	9.6	9.6	10.7	9.6	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4
2.5°	928.4	866.2	823.3	807.2	776.2	726.8	697.9	671.1	620.7	610.0	582.1
5°	775.1	675.3	604.6	577.8	542.4	500.7	459.9	433.1	400.9	388.1	368.8
7.5°	611.0	511.4	450.3	428.7	404.2	369.9	333.4	306.6	273.4	256.2	240.1
10°	480.2	406.3	354.8	333.4	307.7	271.3	233.6	198.3	169.4	151.1	148.0
12.5°	390.2	329.1	274.4	251.9	221.9	185.5	158.7	157.6	155.5	154.3	156.6
15°	319.4	260.4	202.6	177.9	169.4	168.3	171.5	174.8	173.7	176.9	179.0
17.5°	262.7	199.5	186.5	187.6	188.6	191.9	197.2	205.8	206.8	212.3	216.5
20°	214.4	211.2	216.5	220.8	224.0	230.5	242.2	253.0	256.2	263.7	272.3
22.5°	243.4	253.0	264.8	270.2	274.4	286.2	299.1	316.3	322.6	332.4	344.1
25°	293.7	309.8	328.0	334.5	341.0	360.2	375.1	395.6	400.9	412.8	424.5
27.5°	335.5	352.7	372.0	380.6	386.0	405.2	418.0	431.0	431.0	437.3	445.9
30°	329.1	343.1	359.2	365.5	367.8	381.6	394.5	398.8	396.7	399.8	406.3
32.5°	273.4	284.1	297.0	302.3	304.4	314.2	324.9	324.9	323.8	323.8	328.0
35°	202.6	210.1	216.5	221.9	225.1	231.5	241.2	240.1	240.1	238.0	241.2
37.5°	136.1	140.4	148.0	150.1	151.1	155.5	162.9	162.9	160.8	161.8	164.1
40°	82.5	87.9	92.1	93.3	95.4	98.6	104.0	104.0	104.0	104.0	105.1
42.5°	49.4	52.5	55.7	55.7	56.8	61.1	63.2	63.2	63.2	63.2	64.3
45°	28.9	30.0	32.2	33.3	33.3	35.4	36.4	36.4	36.4	36.4	37.5
47.5°	17.2	18.2	18.2	19.3	19.3	20.3	21.4	21.4	20.3	20.3	20.3
50°	10.7	10.7	10.7	10.7	11.7	11.7	11.7	11.7	11.7	11.7	10.7
52.5°	8.6	8.6	8.6	8.6	7.5	7.5	7.5	7.5	6.5	6.5	5.4
55°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	6.5	5.4	4.2	3.2
57.5°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.4	4.2	4.2	3.2
60°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.4	4.2	4.2	3.2
62.5°	8.6	8.6	7.5	7.5	7.5	6.5	6.5	5.4	5.4	4.2	3.2
65°	8.6	8.6	7.5	7.5	7.5	7.5	6.5	6.5	5.4	4.2	3.2
67.5°	8.6	8.6	8.6	8.6	7.5	7.5	7.5	6.5	5.4	4.2	3.2
70°	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	5.4	5.4	4.2
72.5°	9.6	9.6	8.6	8.6	8.6	8.6	7.5	6.5	6.5	5.4	4.2
75°	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5	6.5	5.4	4.2
77.5°	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5	6.5	5.4	4.2
80°	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.4	4.2
82.5°	10.7	10.7	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.4	5.4
85°	10.7	10.7	9.6	9.6	9.6	8.6	8.6	7.5	6.5	6.5	5.4
87.5°	10.7	10.7	9.6	9.6	9.6	8.6	8.6	7.5	6.5	6.5	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212658

CATALOG NUMBER: LDSQA6A60940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4	1063.4
2.5°	565.0	532.8	522.1	529.6	521.0	514.5	506.0	501.7
5°	353.8	330.1	322.6	324.9	317.3	310.9	302.3	300.2
7.5°	217.7	195.1	186.5	186.5	177.9	170.4	165.1	161.8
10°	145.7	141.5	142.6	143.6	142.6	143.6	140.4	142.6
12.5°	156.6	154.3	156.6	157.6	157.6	159.7	155.5	158.7
15°	182.3	180.0	183.3	185.5	185.5	188.6	184.4	187.6
17.5°	222.9	221.9	227.3	229.4	230.5	235.9	230.5	234.8
20°	282.0	280.9	288.4	291.6	290.5	301.2	293.7	301.2
22.5°	358.0	355.9	366.6	369.9	370.9	384.9	378.4	383.7
25°	434.1	436.3	441.7	447.1	448.1	459.9	450.3	455.7
27.5°	450.3	447.1	450.3	456.7	457.8	463.1	454.5	458.8
30°	407.4	401.9	403.1	410.5	412.8	414.9	407.4	409.5
32.5°	331.2	322.6	322.6	330.1	332.4	335.5	322.6	328.0
35°	244.5	236.9	236.9	242.2	243.4	245.5	235.9	240.1
37.5°	167.2	160.8	162.9	165.1	166.2	168.3	167.2	166.2
40°	107.2	103.0	106.1	106.1	107.2	108.2	108.2	109.3
42.5°	65.3	62.2	64.3	64.3	65.3	65.3	65.3	66.5
45°	37.5	36.4	36.4	37.5	37.5	37.5	36.4	37.5
47.5°	20.3	19.3	20.3	20.3	20.3	20.3	20.3	20.3
50°	10.7	9.6	9.6	9.6	9.6	9.6	9.6	9.6
52.5°	5.4	4.2	4.2	4.2	3.2	4.2	3.2	3.2
55°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
57.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.2	3.2	2.1	2.1	1.1	1.1	1.1	0.0
80°	4.2	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.2	3.2	2.1	2.1	2.1	1.1	1.1	1.1
85°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.2	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)